

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583309

Luminaire Tested: **HC607D010-HM60525830-61WDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583309
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC607D010-HM60525830-61WDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 922.7 lumens
Efficiency: N/A
Efficacy: 115.3 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583309

CATALOG NUMBER: HC607D010-HM60525830-61WDW

Luminous Intensity Polar Plot





TEST NUMBER: P583309

CATALOG NUMBER: HC607D010-HM60525830-61WDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89		
2	103	97	91	87	101	95	90	86	91	87	84	88	85	82	85	83	80	78		
3	96	87	81	76	94	86	80	75	83	78	74	81	76	72	78	74	71	69		
4	89	80	72	67	87	78	72	66	76	70	66	74	69	65	72	67	64	62		
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	61	58	56		
6	78	67	59	54	76	66	59	54	64	58	53	63	57	53	61	56	52	51		
7	73	62	54	49	72	61	54	49	60	53	48	58	52	48	57	52	48	46		
8	69	57	50	45	68	57	50	45	55	49	44	54	48	44	53	48	44	42		
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	44	41	39		
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	47	41	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	31483
5°	31466
10°	31162
15°	30840
20°	29968
25°	28701
30°	26637
35°	22914
40°	16724
45°	11466
50°	9219
55°	8038
60°	7412
65°	7057
70°	6572
75°	6164
80°	5588
85°	4780



TEST NUMBER: P583309

CATALOG NUMBER: HC607D010-HM60525830-61WDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.2	5.9
10°-20°	152.6	16.5
20°-30°	217.0	23.5
30°-40°	208.9	22.6
40°-50°	120.2	13.0
50°-60°	76.2	8.3
60°-70°	53.9	5.8
70°-80°	30.7	3.3
80°-90°	8.8	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	423.8	45.9
0°-40°	632.8	68.6
0°-60°	829.2	89.9
0°-90°	922.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	922.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	574	
5°	572	54
15°	543	153
25°	474	217
35°	342	209
45°	148	120
55°	84	76
65°	54	54
75°	29	31
85°	8	9
90°	0	



TEST NUMBER: P583309

CATALOG NUMBER: HC607D010-HM60525830-61WDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	574.3
2.5°	571.8
5°	571.8
7.5°	568.0
10°	559.8
12.5°	551.5
15°	543.4
17.5°	530.7
20°	513.7
22.5°	494.7
25°	474.5
27.5°	449.8
30°	420.8
32.5°	385.4
35°	342.4
37.5°	290.0
40°	233.7
42.5°	184.5
45°	147.9
47.5°	124.5
50°	108.1
52.5°	94.7
55°	84.1
57.5°	74.6
60°	67.6
62.5°	61.3
65°	54.4
67.5°	48.0
70°	41.0
72.5°	34.8
75°	29.1
77.5°	23.3
80°	17.7
82.5°	12.7
85°	7.6
87.5°	3.2
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)