

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582235

Luminaire Tested: **HC630D010-HM63040935-61MDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582235
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC630D010-HM63040935-61MDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3210.4 lumens
Efficiency: N/A
Efficacy: 114.7 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 28
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582235

CATALOG NUMBER: HC630D010-HM63040935-61MDC

Luminous Intensity Polar Plot





TEST NUMBER: P582235

CATALOG NUMBER: HC630D010-HM63040935-61MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	80	86	82	79		84	81	78		83
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	73	68	63	72	67	63		71	66	63		70
8	79	70	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	66	60	56	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	152460
5°	154831
10°	163646
15°	182209
20°	188964
25°	155035
30°	108637
35°	74124
40°	38615
45°	13575
50°	6072
55°	1940
60°	1118
65°	791
70°	641
75°	424
80°	0
85°	0



TEST NUMBER: P582235

CATALOG NUMBER: HC630D010-HM63040935-61MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	272.5	8.5
10°-20°	902.9	28.1
20°-30°	1149.7	35.8
30°-40°	685.2	21.3
40°-50°	166.2	5.2
50°-60°	25.5	0.8
60°-70°	6.2	0.2
70°-80°	2.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2325.2	72.4
0°-40°	3010.4	93.8
0°-60°	3202.1	99.7
0°-90°	3210.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3210.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2781	
5°	2814	273
15°	3210	903
25°	2563	1150
35°	1108	685
45°	175	166
55°	20	25
65°	6	6
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P582235

CATALOG NUMBER: HC630D010-HM63040935-61MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	2781.1
2.5°	2781.1
5°	2813.6
7.5°	2864.5
10°	2939.8
12.5°	3057.9
15°	3210.5
17.5°	3306.3
20°	3239.1
22.5°	2980.6
25°	2563.1
27.5°	2103.1
30°	1716.2
32.5°	1402.8
35°	1107.6
37.5°	816.4
40°	539.6
42.5°	291.2
45°	175.1
47.5°	110.0
50°	71.2
52.5°	42.8
55°	20.3
57.5°	12.2
60°	10.2
62.5°	8.1
65°	6.1
67.5°	4.0
70°	4.0
72.5°	2.0
75°	2.0
77.5°	2.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)