

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582392

Luminaire Tested: **HC635D010-HM63040935-61WDWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582392
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC635D010-HM63040935-61WDWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3804.7 lumens
Efficiency: N/A
Efficacy: 112.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.05
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582392

CATALOG NUMBER: HC635D010-HM63040935-61WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P582392

CATALOG NUMBER: HC635D010-HM63040935-61WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	85	78	73	91	83	78	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	73	66	61	81	72	66	61	70	65	60		69	64	60		67
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	51	48		56
10	66	56	49	45	65	55	49	45	54	48	45		53	48	44		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	141902
5°	143115
10°	148272
15°	161051
20°	167525
25°	160231
30°	138281
35°	99568
40°	56098
45°	29073
50°	17330
55°	12482
60°	10602
65°	12232
70°	15499
75°	16394
80°	16037
85°	15222



TEST NUMBER: P582392

CATALOG NUMBER: HC635D010-HM63040935-61WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	250.2	6.6
10°-20°	800.4	21.0
20°-30°	1196.3	31.4
30°-40°	914.5	24.0
40°-50°	319.4	8.4
50°-60°	121.7	3.2
60°-70°	95.4	2.5
70°-80°	80.8	2.1
80°-90°	26.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2246.9	59.1
0°-40°	3161.4	83.1
0°-60°	3602.5	94.7
0°-90°	3804.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3804.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2588	
5°	2601	250
15°	2838	800
25°	2649	1196
35°	1488	914
45°	375	319
55°	131	122
65°	94	95
75°	77	81
85°	24	26
90°	0	



TEST NUMBER: P582392

CATALOG NUMBER: HC635D010-HM63040935-61WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2588.5
2.5°	2581.3
5°	2600.7
7.5°	2627.3
10°	2663.6
12.5°	2745.8
15°	2837.7
17.5°	2893.3
20°	2871.6
22.5°	2784.5
25°	2649.0
27.5°	2455.5
30°	2184.5
32.5°	1860.3
35°	1487.8
37.5°	1103.2
40°	783.9
42.5°	549.2
45°	375.0
47.5°	263.7
50°	203.2
52.5°	159.6
55°	130.6
57.5°	106.4
60°	96.7
62.5°	94.3
65°	94.3
67.5°	99.2
70°	96.7
72.5°	89.5
75°	77.4
77.5°	65.4
80°	50.8
82.5°	36.3
85°	24.2
87.5°	9.7
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)