

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583393

Luminaire Tested: **HC607D010-HM60525935-61PSMDW**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583393
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-12)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC607D010-HM60525935-61PSMDW
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" PLASTIC TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 807.5 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.09 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583393

CATALOG NUMBER: HC607D010-HM60525935-61PSMDW

Luminous Intensity Polar Plot





TEST NUMBER: P583393

CATALOG NUMBER: HC607D010-HM60525935-61PSMDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	103	96	91	86	101	95	90	85	91	87	83	88	85	82	85	82	80	78		
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69		
4	89	80	72	67	87	78	72	66	76	70	65	74	69	65	72	67	64	62		
5	84	73	65	60	82	72	65	59	70	64	59	68	63	58	66	62	58	56		
6	78	67	59	54	77	66	59	54	64	58	53	63	57	53	61	56	53	51		
7	73	62	54	49	72	61	54	49	60	53	49	58	53	48	57	52	48	46		
8	69	57	50	45	68	57	50	45	56	49	45	54	49	44	53	48	44	43		
9	65	53	46	41	64	53	46	41	52	46	41	51	45	41	50	45	41	39		
10	62	50	43	38	60	49	43	38	49	42	38	48	42	38	47	42	38	36		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	28863
5°	28786
10°	28356
15°	27906
20°	26987
25°	25707
30°	23466
35°	18892
40°	12738
45°	9288
50°	8034
55°	7254
60°	6885
65°	6512
70°	6123
75°	5804
80°	5398
85°	4969



TEST NUMBER: P583393

CATALOG NUMBER: HC607D010-HM60525935-61PSMDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.5	6.1
10°-20°	138.1	17.1
20°-30°	194.0	24.0
30°-40°	172.7	21.4
40°-50°	96.5	12.0
50°-60°	68.8	8.5
60°-70°	50.0	6.2
70°-80°	28.9	3.6
80°-90°	9.0	1.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	381.6	47.3
0°-40°	554.3	68.6
0°-60°	719.6	89.1
0°-90°	807.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	807.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	526	
5°	523	50
15°	492	138
25°	425	194
35°	282	173
45°	120	97
55°	76	69
65°	50	50
75°	27	29
85°	8	9
90°	0	



TEST NUMBER: P583393

CATALOG NUMBER: HC607D010-HM60525935-61PSMDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	526.5
2.5°	524.2
5°	523.1
7.5°	518.5
10°	509.4
12.5°	500.8
15°	491.7
17.5°	479.1
20°	462.6
22.5°	444.4
25°	425.0
27.5°	401.0
30°	370.7
32.5°	332.0
35°	282.3
37.5°	226.5
40°	178.0
42.5°	142.1
45°	119.8
47.5°	104.9
50°	94.2
52.5°	84.4
55°	75.9
57.5°	69.0
60°	62.8
62.5°	57.0
65°	50.2
67.5°	44.5
70°	38.2
72.5°	32.5
75°	27.4
77.5°	22.2
80°	17.1
82.5°	12.6
85°	7.9
87.5°	4.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)