

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582407

Luminaire Tested: **HC635D010-HM63040940-61WDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582407
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC635D010-HM63040940-61WDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4002.1 lumens
Efficiency: N/A
Efficacy: 118.8 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582407

CATALOG NUMBER: HC635D010-HM63040940-61WDC

Luminous Intensity Polar Plot





TEST NUMBER: P582407

CATALOG NUMBER: HC635D010-HM63040940-61WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	105		111	108	106	103		104	102	100		100	99	97		97	96	94
2	107	102	97	94		105	100	96	93		97	94	91		94	91	89		91	89	87
3	101	94	89	85		99	93	88	84		90	86	82		88	84	81		85	82	80
4	95	87	81	77		93	86	80	76		84	79	75		82	78	74		80	76	74
5	90	81	75	70		88	80	74	70		78	73	69		76	72	68		75	71	68
6	85	75	69	64		83	74	68	64		73	67	63		71	67	63		70	66	62
7	80	70	63	59		79	69	63	59		68	62	58		67	62	58		66	61	58
8	76	65	59	54		74	65	59	54		64	58	54		62	57	54		61	57	53
9	71	61	55	50		70	60	54	50		60	54	50		59	53	50		58	53	50
10	68	57	51	47		67	57	51	47		56	50	46		55	50	46		54	50	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	141886
5°	143787
10°	149179
15°	162237
20°	181386
25°	190922
30°	168076
35°	116580
40°	69609
45°	33089
50°	12494
55°	5218
60°	1634
65°	1284
70°	801
75°	530
80°	789
85°	0



TEST NUMBER: P582407

CATALOG NUMBER: HC635D010-HM63040940-61WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	251.5	6.3
10°-20°	820.8	20.5
20°-30°	1406.5	35.1
30°-40°	1092.3	27.3
40°-50°	361.1	9.0
50°-60°	55.4	1.4
60°-70°	9.8	0.2
70°-80°	3.6	0.1
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2478.8	61.9
0°-40°	3571.2	89.2
0°-60°	3987.7	99.6
0°-90°	4002.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4002.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2588	
5°	2613	251
15°	2859	821
25°	3156	1407
35°	1742	1092
45°	427	361
55°	55	55
65°	10	10
75°	2	4
85°	0	1
90°	0	



TEST NUMBER: P582407

CATALOG NUMBER: HC635D010-HM63040940-61WDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	2588.2
2.5°	2585.6
5°	2612.9
7.5°	2642.7
10°	2679.9
12.5°	2754.4
15°	2858.6
17.5°	2985.2
20°	3109.2
22.5°	3181.1
25°	3156.4
27.5°	2985.2
30°	2655.2
32.5°	2211.0
35°	1742.0
37.5°	1322.6
40°	972.7
42.5°	687.4
45°	426.8
47.5°	238.2
50°	146.5
52.5°	89.3
55°	54.6
57.5°	27.3
60°	14.9
62.5°	12.4
65°	9.9
67.5°	7.5
70°	5.0
72.5°	5.0
75°	2.5
77.5°	2.5
80°	2.5
82.5°	2.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)