

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583963

Luminaire Tested: **HC815D010-HM80520940-81WDWB**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583963
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-10)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC815D010-HM80520940-81WDWB
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1721.6 lumens
Efficiency: N/A
Efficacy: 123.0 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583963

CATALOG NUMBER: HC815D010-HM80520940-81WDWB

Luminous Intensity Polar Plot





TEST NUMBER: P583963

CATALOG NUMBER: HC815D010-HM80520940-81WDWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90		
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81		
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73		
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65		
5	86	75	68	63	84	74	68	63	73	67	62	71	66	62	69	65	61	59		
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54		
7	75	64	57	52	74	63	57	52	62	56	51	61	55	51	59	55	51	49		
8	71	59	52	47	69	59	52	47	58	51	47	56	51	47	55	50	47	45		
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	47	43	41		
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	30235
5°	30025
10°	29947
15°	30733
20°	33271
25°	35674
30°	34873
35°	29039
40°	17841
45°	12354
50°	9427
55°	6183
60°	3867
65°	2904
70°	2921
75°	3360
80°	3694
85°	3326



TEST NUMBER: P583963

CATALOG NUMBER: HC815D010-HM80520940-81WDWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.2	5.4
10°-20°	276.4	16.1
20°-30°	475.8	27.6
30°-40°	460.9	26.8
40°-50°	227.0	13.2
50°-60°	107.1	6.2
60°-70°	42.3	2.5
70°-80°	29.1	1.7
80°-90°	10.8	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	844.3	49.0
0°-40°	1305.2	75.8
0°-60°	1639.4	95.2
0°-90°	1721.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1721.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	980	
5°	970	92
15°	963	276
25°	1048	476
35°	771	461
45°	283	227
55°	115	107
65°	40	42
75°	28	29
85°	9	11
90°	0	



TEST NUMBER: P583963

CATALOG NUMBER: HC815D010-HM80520940-81WDWB

CANDELA DISTRIBUTION (FULL):

	0°
0°	980.5
2.5°	977.4
5°	970.0
7.5°	962.7
10°	956.4
12.5°	955.4
15°	962.7
17.5°	984.6
20°	1013.9
22.5°	1040.0
25°	1048.5
27.5°	1029.6
30°	979.4
32.5°	896.9
35°	771.4
37.5°	599.0
40°	443.2
42.5°	343.9
45°	283.3
47.5°	238.3
50°	196.5
52.5°	154.7
55°	115.0
57.5°	83.6
60°	62.7
62.5°	49.2
65°	39.8
67.5°	34.5
70°	32.4
72.5°	30.4
75°	28.2
77.5°	25.1
80°	20.8
82.5°	15.7
85°	9.4
87.5°	4.2
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)