

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593759

Luminaire Tested: **HC845D010-HM82555850-81MDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P593759
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC845D010-HM82555850-81MDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5966.2 lumens
Efficiency: N/A
Efficacy: 135.6 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.67
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593759

CATALOG NUMBER: HC845D010-HM82555850-81MDC

Luminous Intensity Polar Plot





TEST NUMBER: P593759

CATALOG NUMBER: HC845D010-HM82555850-81MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	109	107		112	109	107	105		105	104	102		102	100	99		98	97	96
2	109	105	101	98		107	103	100	97		100	97	95		97	95	93		94	92	91
3	104	98	94	90		102	97	93	90		94	91	88		92	89	87		90	87	85
4	100	93	88	84		98	92	87	83		90	86	82		88	84	82		86	83	81
5	95	88	82	78		94	87	82	78		85	81	77		83	80	77		82	79	76
6	91	83	78	74		90	82	77	74		81	76	73		79	76	73		78	75	72
7	87	79	73	70		86	78	73	69		77	72	69		76	72	69		75	71	68
8	84	75	70	66		82	74	69	66		73	69	65		72	68	65		71	68	65
9	80	71	66	62		79	71	66	62		70	65	62		69	65	62		68	65	62
10	77	68	63	59		76	68	63	59		67	62	59		66	62	59		66	62	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	356480
5°	340127
10°	293653
15°	224545
20°	171808
25°	135926
30°	102676
35°	54622
40°	20807
45°	9986
50°	4250
55°	1785
60°	678
65°	540
70°	325
75°	0
80°	0
85°	0



TEST NUMBER: P593759

CATALOG NUMBER: HC845D010-HM82555850-81MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	997.4	16.7
10°-20°	1963.6	32.9
20°-30°	1828.7	30.7
30°-40°	943.6	15.8
40°-50°	192.2	3.2
50°-60°	32.9	0.6
60°-70°	6.3	0.1
70°-80°	1.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4789.8	80.3
0°-40°	5733.4	96.1
0°-60°	5958.5	99.9
0°-90°	5966.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5966.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11560	
5°	10988	997
15°	7034	1964
25°	3995	1829
35°	1451	944
45°	229	192
55°	33	33
65°	7	6
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P593759

CATALOG NUMBER: HC845D010-HM82555850-81MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	11560.4
2.5°	11405.3
5°	10988.1
7.5°	10301.3
10°	9378.3
12.5°	8167.2
15°	7033.7
17.5°	6051.5
20°	5235.6
22.5°	4570.9
25°	3995.0
27.5°	3448.5
30°	2883.6
32.5°	2211.7
35°	1451.0
37.5°	841.9
40°	516.9
42.5°	339.7
45°	229.0
47.5°	144.0
50°	88.6
52.5°	51.7
55°	33.2
57.5°	14.8
60°	11.0
62.5°	7.4
65°	7.4
67.5°	3.6
70°	3.6
72.5°	3.6
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)