

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583543

Luminaire Tested: **HC805D010-HM80520940-81MDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583543
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-5)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC805D010-HM80520940-81MDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 685.1 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.81
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583543

CATALOG NUMBER: HC805D010-HM80520940-81MDH

Luminous Intensity Polar Plot





TEST NUMBER: P583543

CATALOG NUMBER: HC805D010-HM80520940-81MDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88
4	97	90	85	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	79	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	87	78	73	69	77	72	68		76	71	68		74
7	84	75	69	64	82	74	68	64	73	68	64		71	67	64		70
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	56		64	60	56		63
10	73	63	57	54	72	63	57	53	62	57	53		61	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	31330
5°	28549
10°	24392
15°	21274
20°	18961
25°	16822
30°	13773
35°	7909
40°	3506
45°	2041
50°	1175
55°	677
60°	370
65°	233
70°	162
75°	119
80°	89
85°	177



TEST NUMBER: P583543

CATALOG NUMBER: HC805D010-HM80520940-81MDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.5	12.2
10°-20°	187.3	27.3
20°-30°	224.2	32.7
30°-40°	135.6	19.8
40°-50°	38.0	5.5
50°-60°	11.8	1.7
60°-70°	3.3	0.5
70°-80°	1.0	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	495.0	72.3
0°-40°	630.6	92.0
0°-60°	680.5	99.3
0°-90°	685.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	685.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1016	
5°	922	83
15°	666	187
25°	494	224
35°	210	136
45°	47	38
55°	13	12
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P583543

CATALOG NUMBER: HC805D010-HM80520940-81MDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1016.0
2.5°	987.3
5°	922.3
7.5°	849.0
10°	779.0
12.5°	717.8
15°	666.4
17.5°	620.9
20°	577.8
22.5°	537.9
25°	494.4
27.5°	445.2
30°	386.8
32.5°	311.1
35°	210.1
37.5°	130.7
40°	87.1
42.5°	62.6
45°	46.8
47.5°	34.4
50°	24.5
52.5°	17.1
55°	12.6
57.5°	8.4
60°	6.0
62.5°	4.2
65°	3.2
67.5°	2.3
70°	1.8
72.5°	1.0
75°	1.0
77.5°	0.5
80°	0.5
82.5°	0.5
85°	0.5
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)