

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P593273

Luminaire Tested: **HC6R40D010-HM63040850-62RMDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P593273
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC6R40D010-HM63040850-62RMDC
Description: HALO COMMERCIAL 6" ROUND, RETROFIT FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 5000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5207.0 lumens
Efficiency: N/A
Efficacy: 127.0 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 41
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P593273

CATALOG NUMBER: HC6R40D010-HM63040850-62RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P593273

CATALOG NUMBER: HC6R40D010-HM63040850-62RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	92		95	93	91		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	79		84	81	78		83
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70
8	79	69	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	60	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	241521
5°	246808
10°	261624
15°	292436
20°	306183
25°	255287
30°	178667
35°	120321
40°	61966
45°	21522
50°	9586
55°	3164
60°	1447
65°	1284
70°	1058
75°	699
80°	1042
85°	0



TEST NUMBER: P593273

CATALOG NUMBER: HC6R40D010-HM63040850-62RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	434.7	8.3
10°-20°	1451.8	27.9
20°-30°	1886.8	36.2
30°-40°	1114.5	21.4
40°-50°	265.9	5.1
50°-60°	39.2	0.8
60°-70°	9.8	0.2
70°-80°	3.9	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3773.3	72.5
0°-40°	4887.8	93.9
0°-60°	5192.8	99.7
0°-90°	5207.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5207.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4406	
5°	4485	435
15°	5153	1452
25°	4220	1887
35°	1798	1114
45°	278	266
55°	33	39
65°	10	10
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P593273

CATALOG NUMBER: HC6R40D010-HM63040850-62RMDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	4405.7
2.5°	4415.6
5°	4485.0
7.5°	4574.3
10°	4699.9
12.5°	4898.1
15°	5152.7
17.5°	5324.5
20°	5248.4
22.5°	4865.1
25°	4220.5
27.5°	3483.6
30°	2822.5
32.5°	2283.8
35°	1797.9
37.5°	1322.0
40°	865.9
42.5°	472.6
45°	277.6
47.5°	171.9
50°	112.4
52.5°	66.1
55°	33.1
57.5°	16.5
60°	13.2
62.5°	13.2
65°	9.9
67.5°	6.6
70°	6.6
72.5°	3.3
75°	3.3
77.5°	3.3
80°	3.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)