

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584403

Luminaire Tested: **HCC8S35D010BZ-HM82555830-81WWW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584403
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S35D010BZ-HM82555830-81WWW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3546.1 lumens
Efficiency: N/A
Efficacy: 105.2 lumens/watt
Spacing Criteria (0/90/45): 1.09 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584403

CATALOG NUMBER: HCC8S35D010BZ-HM82555830-81WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P584403

CATALOG NUMBER: HCC8S35D010BZ-HM82555830-81WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	93	91	89	87		
2	102	95	89	84	99	93	88	83	90	85	81	86	83	79	83	80	78	76		
3	94	85	78	72	92	83	77	71	81	75	70	78	73	69	75	71	68	66		
4	87	76	69	63	85	75	68	62	73	67	62	71	65	61	68	64	60	58		
5	81	69	61	55	79	68	61	55	66	60	54	64	59	54	63	57	53	51		
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46		
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	41		
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38		
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34		
10	58	46	39	34	57	45	38	34	44	38	33	44	38	33	43	37	33	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	59252	59252	59252
5°	61332	58909	56569
10°	62693	57877	53387
15°	63586	55931	49853
20°	63396	53213	46283
25°	61825	49760	42489
30°	58577	45765	38989
35°	53293	41416	35427
40°	46807	36832	32006
45°	40818	32402	28533
50°	35519	28390	25138
55°	31676	24951	21865
60°	28776	21869	18650
65°	25873	19022	16935
70°	23036	16220	15282
75°	20195	13678	13046
80°	17119	11099	11578
85°	12914	8314	9234

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P584403

CATALOG NUMBER: HCC8S35D010BZ-HM82555830-81WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.0	5.1
10°-20°	495.9	14.0
20°-30°	688.3	19.4
30°-40°	711.6	20.1
40°-50°	595.9	16.8
50°-60°	432.6	12.2
60°-70°	273.0	7.7
70°-80°	135.2	3.8
80°-90°	33.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1364.2	38.5
0°-40°	2075.8	58.5
0°-60°	3104.2	87.5
0°-90°	3546.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3546.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1922	1922	1922	1922	1922	
5°	1981	1958	1903	1851	1828	190
15°	1992	1916	1752	1611	1562	561
25°	1817	1700	1462	1304	1249	833
35°	1416	1311	1100	975	941	882
45°	936	868	743	670	654	724
55°	589	537	464	425	407	532
65°	355	310	261	229	232	354
75°	170	141	115	110	110	182
85°	36	29	24	26	26	44
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P584403

CATALOG NUMBER: HCC8S35D010BZ-HM82555830-81WWW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1921.5	1921.5	1921.5	1921.5	1921.5	1921.5	1921.5	1921.5	1921.5	1921.5	1921.5
2.5°	1952.7	1952.7	1955.3	1952.7	1952.7	1952.7	1950.1	1950.1	1947.5	1947.5	1942.3
5°	1981.4	1976.2	1981.4	1976.2	1976.2	1976.2	1973.6	1968.3	1965.7	1960.5	1957.9
7.5°	1994.4	1991.8	1991.8	1989.2	1989.2	1986.6	1984.0	1981.4	1970.9	1968.3	1960.5
10°	2002.2	1999.6	1999.6	1997.1	1991.8	1991.8	1986.6	1984.0	1970.9	1965.7	1955.3
12.5°	1999.6	1999.6	1999.6	1997.1	1989.2	1986.6	1981.4	1973.6	1963.2	1952.7	1942.3
15°	1991.8	1991.8	1986.6	1984.0	1976.2	1970.9	1968.3	1955.3	1944.8	1931.9	1916.2
17.5°	1965.7	1965.7	1963.2	1957.9	1950.1	1944.8	1939.7	1926.6	1916.2	1895.4	1879.7
20°	1931.9	1929.3	1926.6	1918.8	1910.9	1908.4	1900.5	1882.3	1869.2	1853.7	1832.8
22.5°	1882.3	1879.7	1877.1	1871.9	1858.8	1853.7	1848.4	1835.3	1812.0	1796.3	1770.2
25°	1817.1	1817.1	1812.0	1804.1	1791.0	1785.9	1778.1	1765.0	1744.2	1720.7	1699.8
27.5°	1741.5	1738.9	1731.1	1725.8	1715.4	1707.6	1694.6	1679.0	1658.2	1639.8	1613.8
30°	1645.1	1645.1	1639.8	1632.0	1619.0	1613.8	1603.4	1585.1	1564.2	1540.7	1522.5
32.5°	1535.6	1535.6	1527.7	1522.5	1514.8	1501.7	1499.1	1478.2	1460.0	1441.7	1420.8
35°	1415.7	1418.2	1413.0	1402.6	1389.6	1389.6	1384.4	1366.1	1345.2	1327.0	1311.3
37.5°	1295.8	1287.8	1285.3	1280.1	1272.3	1261.9	1256.6	1248.8	1230.6	1217.5	1194.0
40°	1162.8	1165.4	1160.1	1155.0	1152.4	1144.4	1141.9	1128.9	1115.8	1100.2	1089.7
42.5°	1042.9	1042.9	1042.9	1037.6	1032.4	1024.5	1022.0	1014.1	998.5	988.1	972.4
45°	936.0	928.1	928.1	925.5	922.9	917.7	909.9	904.6	894.2	886.4	868.2
47.5°	831.7	834.3	831.7	829.0	821.2	818.6	816.0	805.5	795.1	787.3	774.3
50°	740.4	745.6	740.4	740.4	735.2	732.6	727.4	719.5	711.7	698.7	685.6
52.5°	664.8	664.8	662.3	659.6	651.7	646.6	643.9	641.3	628.4	617.9	607.5
55°	589.2	591.8	591.8	584.0	581.4	576.1	573.6	565.7	560.5	544.9	537.1
57.5°	524.0	521.4	524.0	518.9	513.6	508.4	505.8	500.5	492.7	482.3	471.9
60°	466.6	461.5	461.5	458.8	453.7	451.0	445.8	438.0	430.2	419.8	411.9
62.5°	409.4	406.7	404.1	401.4	396.3	393.7	391.0	383.2	375.5	367.5	359.8
65°	354.6	354.6	352.0	346.7	344.2	341.5	338.9	333.8	323.2	318.1	310.3
67.5°	305.0	302.4	302.4	297.2	292.0	289.4	289.4	284.2	276.4	268.5	263.3
70°	255.5	258.0	255.5	252.9	247.6	247.6	242.5	239.8	229.4	226.8	219.0
72.5°	211.2	211.2	208.6	208.6	203.3	200.8	200.8	195.5	190.4	185.1	179.9
75°	169.5	169.5	169.5	166.9	164.2	159.0	159.0	156.5	151.2	146.0	140.8
77.5°	133.0	130.3	130.3	127.7	125.2	122.6	122.6	119.9	114.8	112.1	106.9
80°	96.4	93.8	93.8	93.8	88.7	91.3	88.7	86.0	83.4	80.9	78.2
82.5°	62.5	65.2	65.2	62.5	60.0	60.0	60.0	57.4	57.4	54.7	52.1
85°	36.5	36.5	36.5	36.5	33.9	33.9	33.9	31.3	31.3	31.3	28.6
87.5°	15.7	15.7	15.7	15.7	15.7	15.7	13.1	13.1	13.1	13.1	13.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P584403

CATALOG NUMBER: HCC8S35D010BZ-HM82555830-81WWW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1921.5	1921.5	1921.5	1921.5	1921.5	1921.5	1921.5	1921.5	1921.5	1921.5	1921.5
2.5°	1942.3	1937.0	1934.4	1931.9	1931.9	1929.3	1926.6	1921.5	1921.5	1916.2	1913.6
5°	1952.7	1944.8	1939.7	1934.4	1931.9	1926.6	1921.5	1913.6	1910.9	1903.1	1895.4
7.5°	1955.3	1942.3	1937.0	1926.6	1921.5	1916.2	1905.8	1898.0	1887.6	1879.7	1869.2
10°	1944.8	1934.4	1921.5	1908.4	1905.8	1898.0	1882.3	1871.9	1858.8	1848.4	1832.8
12.5°	1929.3	1913.6	1900.5	1884.9	1877.1	1869.2	1853.7	1838.0	1819.8	1801.4	1785.9
15°	1903.1	1884.9	1866.7	1848.4	1838.0	1830.2	1812.0	1793.6	1775.4	1752.0	1736.3
17.5°	1864.1	1843.2	1824.9	1801.4	1791.0	1783.2	1759.7	1738.9	1715.4	1691.9	1676.4
20°	1814.5	1788.5	1767.6	1741.5	1733.7	1720.7	1697.2	1673.7	1647.7	1621.6	1603.4
22.5°	1749.3	1723.3	1699.8	1673.7	1660.7	1647.7	1624.2	1595.5	1569.5	1548.7	1530.3
25°	1673.7	1650.2	1621.6	1598.1	1582.4	1566.9	1540.7	1517.3	1493.9	1462.5	1444.3
27.5°	1590.3	1561.6	1540.7	1509.5	1493.9	1483.5	1454.7	1423.5	1402.6	1374.0	1353.0
30°	1496.4	1470.4	1446.9	1415.7	1400.0	1389.6	1363.4	1334.8	1314.0	1285.3	1264.5
32.5°	1397.3	1368.7	1340.1	1319.2	1300.9	1290.5	1261.9	1243.5	1217.5	1194.0	1170.6
35°	1290.5	1261.9	1241.0	1212.3	1201.8	1191.4	1167.9	1144.4	1121.1	1100.2	1081.9
37.5°	1175.8	1155.0	1131.5	1110.7	1102.8	1092.3	1063.7	1042.9	1024.5	1003.7	988.1
40°	1063.7	1045.5	1029.8	1009.0	995.9	988.1	967.3	948.9	928.1	915.0	899.5
42.5°	962.0	941.1	925.5	909.9	896.8	889.0	870.7	857.8	842.1	829.0	810.8
45°	855.1	844.7	826.5	813.4	805.5	795.1	782.2	766.5	753.4	743.0	729.9
47.5°	761.2	750.8	737.8	722.2	717.0	709.1	696.0	685.6	675.2	664.8	651.7
50°	675.2	662.3	651.7	641.3	636.1	628.4	615.3	610.0	602.2	591.8	584.0
52.5°	597.0	586.5	576.1	563.2	560.5	555.3	547.5	537.1	529.3	524.0	518.9
55°	526.6	516.2	508.4	498.0	495.4	490.1	479.7	474.5	469.3	464.1	458.8
57.5°	464.1	453.7	443.3	438.0	432.7	427.6	424.9	417.1	411.9	409.4	404.1
60°	406.7	396.3	388.5	380.6	378.0	375.5	370.2	365.0	359.8	354.6	352.0
62.5°	352.0	341.5	336.3	331.1	325.9	325.9	320.7	315.4	310.3	307.6	302.4
65°	302.4	297.2	289.4	281.5	279.0	279.0	271.1	268.5	266.0	260.7	255.5
67.5°	255.5	250.3	242.5	239.8	237.2	234.7	232.1	226.8	221.6	219.0	213.7
70°	213.7	208.6	203.3	200.8	198.1	195.5	190.4	187.7	182.5	179.9	177.3
72.5°	172.0	169.5	164.2	161.6	159.0	156.5	153.8	151.2	146.0	143.4	140.8
75°	138.1	135.6	130.3	127.7	125.2	125.2	122.6	117.3	114.8	114.8	112.1
77.5°	104.2	101.7	99.1	96.4	93.8	93.8	91.3	88.7	86.0	86.0	83.4
80°	75.6	73.0	70.4	70.4	70.4	67.8	65.2	65.2	62.5	62.5	60.0
82.5°	49.5	49.5	47.0	47.0	47.0	44.3	44.3	41.7	41.7	41.7	41.7
85°	28.6	28.6	28.6	26.1	26.1	26.1	26.1	26.1	26.1	23.5	26.1
87.5°	13.1	13.1	13.1	13.1	13.1	13.1	13.1	13.1	10.4	10.4	10.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P584403

CATALOG NUMBER: HCC8S35D010BZ-HM82555830-81WWW

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1921.5	1921.5	1921.5	1921.5	1921.5	1921.5	1921.5	1921.5	1921.5	1921.5	1921.5
2.5°	1910.9	1908.4	1903.1	1903.1	1898.0	1898.0	1895.4	1892.7	1890.1	1887.6	1884.9
5°	1892.7	1882.3	1877.1	1874.5	1869.2	1866.7	1858.8	1853.7	1851.0	1845.8	1840.6
7.5°	1858.8	1848.4	1838.0	1835.3	1832.8	1822.4	1814.5	1806.7	1801.4	1796.3	1791.0
10°	1819.8	1809.3	1796.3	1791.0	1785.9	1772.8	1762.4	1754.6	1744.2	1733.7	1731.1
12.5°	1772.8	1757.2	1741.5	1736.3	1728.5	1715.4	1705.0	1691.9	1684.1	1671.1	1668.6
15°	1718.1	1699.8	1686.8	1673.7	1668.6	1655.5	1637.2	1626.8	1611.2	1605.9	1593.0
17.5°	1652.9	1634.7	1616.3	1611.2	1603.4	1585.1	1566.9	1553.8	1538.2	1530.3	1522.5
20°	1585.1	1561.6	1543.4	1538.2	1527.7	1512.1	1493.9	1480.8	1467.8	1452.1	1444.3
22.5°	1506.8	1480.8	1465.2	1452.1	1449.6	1431.3	1410.4	1400.0	1389.6	1376.5	1366.1
25°	1420.8	1397.3	1379.1	1368.7	1363.4	1347.9	1332.2	1319.2	1303.5	1295.8	1282.7
27.5°	1332.2	1316.6	1293.1	1282.7	1274.9	1261.9	1243.5	1235.7	1220.2	1209.7	1201.8
30°	1246.2	1222.7	1209.7	1196.7	1188.8	1175.8	1160.1	1152.4	1139.3	1128.9	1121.1
32.5°	1152.4	1136.7	1118.5	1113.2	1102.8	1089.7	1079.3	1066.3	1055.9	1045.5	1042.9
35°	1066.3	1045.5	1027.2	1022.0	1014.1	1001.2	995.9	988.1	975.1	972.4	962.0
37.5°	972.4	962.0	941.1	933.4	930.7	920.3	909.9	904.6	896.8	889.0	886.4
40°	883.8	870.7	860.3	852.5	847.3	839.4	829.0	826.5	821.2	810.8	808.2
42.5°	800.4	787.3	776.9	774.3	766.5	758.7	753.4	745.6	743.0	740.4	735.2
45°	719.5	711.7	701.3	698.7	696.0	685.6	680.5	675.2	670.0	667.4	662.3
47.5°	646.6	638.8	630.9	628.4	623.1	620.4	612.7	610.0	602.2	599.6	597.0
50°	576.1	571.0	565.7	563.2	557.9	555.3	550.1	544.9	539.7	537.1	534.4
52.5°	513.6	508.4	503.2	500.5	498.0	492.7	487.5	482.3	479.7	477.0	474.5
55°	453.7	448.4	445.8	443.3	440.6	438.0	430.2	427.6	424.9	422.3	417.1
57.5°	398.9	393.7	388.5	388.5	385.9	383.2	378.0	372.8	372.8	367.5	362.4
60°	349.3	344.2	338.9	336.3	333.8	328.5	325.9	323.2	320.7	318.1	312.8
62.5°	297.2	294.6	289.4	289.4	284.2	281.5	279.0	276.4	273.7	268.5	266.0
65°	252.9	250.3	245.1	242.5	242.5	239.8	234.7	232.1	229.4	229.4	226.8
67.5°	211.2	208.6	203.3	200.8	200.8	198.1	195.5	195.5	192.9	190.4	192.9
70°	174.7	169.5	169.5	166.9	166.9	164.2	161.6	161.6	161.6	164.2	164.2
72.5°	138.1	135.6	133.0	133.0	133.0	133.0	130.3	130.3	133.0	135.6	135.6
75°	109.5	106.9	106.9	106.9	104.2	104.2	106.9	106.9	109.5	109.5	109.5
77.5°	80.9	80.9	80.9	80.9	80.9	80.9	83.4	83.4	86.0	86.0	86.0
80°	60.0	60.0	60.0	60.0	60.0	62.5	62.5	62.5	62.5	62.5	65.2
82.5°	41.7	41.7	41.7	41.7	41.7	41.7	41.7	44.3	44.3	44.3	44.3
85°	23.5	26.1	26.1	26.1	26.1	26.1	26.1	26.1	26.1	26.1	26.1
87.5°	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P584403

CATALOG NUMBER: HCC8S35D010BZ-HM82555830-81WWW

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	1921.5	1921.5	1921.5	1921.5	1921.5	1921.5	1921.5	1921.5
2.5°	1882.3	1882.3	1882.3	1884.9	1879.7	1879.7	1879.7	1879.7
5°	1838.0	1835.3	1832.8	1835.3	1830.2	1830.2	1827.5	1827.5
7.5°	1783.2	1780.6	1778.1	1778.1	1772.8	1772.8	1770.2	1767.6
10°	1723.3	1718.1	1720.7	1715.4	1712.9	1710.3	1707.6	1705.0
12.5°	1658.2	1652.9	1650.2	1645.1	1639.8	1637.2	1639.8	1634.7
15°	1587.7	1579.9	1577.3	1572.0	1566.9	1564.2	1564.2	1561.6
17.5°	1509.5	1504.3	1501.7	1496.4	1493.9	1488.6	1486.0	1483.5
20°	1436.5	1423.5	1426.1	1420.8	1418.2	1407.8	1407.8	1410.4
22.5°	1355.7	1347.9	1342.6	1337.4	1334.8	1329.7	1329.7	1327.0
25°	1274.9	1267.0	1264.5	1259.2	1256.6	1251.4	1248.8	1248.8
27.5°	1196.7	1186.3	1186.3	1181.0	1175.8	1173.2	1170.6	1167.9
30°	1113.2	1105.4	1102.8	1102.8	1100.2	1100.2	1092.3	1095.0
32.5°	1035.0	1029.8	1027.2	1022.0	1022.0	1019.4	1019.4	1011.6
35°	956.8	948.9	951.6	946.4	943.8	941.1	943.8	941.1
37.5°	881.2	876.0	876.0	870.7	870.7	868.2	865.6	870.7
40°	805.5	803.0	800.4	797.7	800.4	797.7	792.6	795.1
42.5°	729.9	729.9	727.4	727.4	724.8	724.8	724.8	724.8
45°	662.3	659.6	659.6	657.0	657.0	657.0	657.0	654.3
47.5°	594.4	591.8	591.8	591.8	589.2	589.2	586.5	589.2
50°	529.3	529.3	526.6	526.6	529.3	526.6	524.0	524.0
52.5°	469.3	469.3	466.6	466.6	464.1	461.5	464.1	464.1
55°	414.5	411.9	409.4	409.4	406.7	404.1	404.1	406.7
57.5°	362.4	359.8	357.1	357.1	352.0	349.3	349.3	349.3
60°	312.8	307.6	307.6	305.0	305.0	302.4	302.4	302.4
62.5°	266.0	263.3	263.3	263.3	263.3	260.7	260.7	260.7
65°	226.8	226.8	226.8	229.4	229.4	232.1	232.1	232.1
67.5°	195.5	198.1	198.1	198.1	200.8	200.8	200.8	198.1
70°	166.9	166.9	166.9	169.5	169.5	169.5	169.5	169.5
72.5°	138.1	138.1	138.1	138.1	138.1	138.1	138.1	138.1
75°	109.5	112.1	112.1	112.1	109.5	112.1	112.1	109.5
77.5°	86.0	86.0	86.0	86.0	86.0	86.0	86.0	86.0
80°	65.2	65.2	65.2	65.2	65.2	65.2	65.2	65.2
82.5°	44.3	44.3	44.3	44.3	44.3	44.3	44.3	44.3
85°	26.1	26.1	26.1	26.1	26.1	26.1	26.1	26.1
87.5°	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)