

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584680

Luminaire Tested: **HCC8S45D010SL-HM82555835-81NDC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584680
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S45D010SL-HM82555835-81NDC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5062.2 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.27
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584680

CATALOG NUMBER: HCC8S45D010SL-HM82555835-81NDC

Luminous Intensity Polar Plot





TEST NUMBER: P584680

CATALOG NUMBER: HCC8S45D010SL-HM82555835-81NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			0
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			100
1	115	112	110	108		112	110	108	107		106	105	103			102	101	100			96
2	110	106	103	100		108	104	101	99		101	99	97			98	96	95			91
3	106	101	97	93		104	99	96	93		97	94	91			95	92	90			87
4	102	96	91	88		100	95	91	88		93	89	87			91	88	86			83
5	98	92	87	83		97	91	86	83		89	85	82			87	84	82			80
6	95	88	83	79		93	87	82	79		86	82	79			84	81	78			76
7	91	84	79	76		90	83	79	76		82	78	75			81	78	75			73
8	88	81	76	73		87	80	76	73		79	75	72			78	75	72			71
9	85	78	73	70		84	77	73	70		76	72	70			76	72	69			68
10	83	75	70	67		82	75	70	67		74	70	67			73	69	67			66

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	952808
5°	611152
10°	276081
15°	166580
20°	126940
25°	102511
30°	75116
35°	27202
40°	10152
45°	4609
50°	1468
55°	366
60°	210
65°	248
70°	0
75°	0
80°	604
85°	1203



TEST NUMBER: P584680

CATALOG NUMBER: HCC8S45D010SL-HM82555835-81NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1505.8	29.7
10°-20°	1529.5	30.2
20°-30°	1369.2	27.0
30°-40°	551.5	10.9
40°-50°	90.4	1.8
50°-60°	8.2	0.2
60°-70°	2.9	0.1
70°-80°	2.3	0.0
80°-90°	3.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4404.5	87.0
0°-40°	4956.0	97.9
0°-60°	5054.6	99.9
0°-90°	5063.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5062.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	30899	
5°	19744	###
15°	5218	1529
25°	3013	1369
35°	723	552
45°	106	90
55°	7	8
65°	3	3
75°	0	2
85°	3	3
90°	0	



TEST NUMBER: P584680

CATALOG NUMBER: HCC8S45D010SL-HM82555835-81NDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	30898.9
0.5°	30803.4
1°	30404.7
1.5°	29763.9
2°	28792.6
2.5°	27644.1
3°	26205.8
3.5°	24627.7
4°	23066.8
4.5°	21318.3
5°	19743.8
5.5°	18029.5
6°	16638.9
6.5°	15190.5
7°	14052.1
7.5°	12848.9
8°	11881.1
8.5°	10909.7
9°	10180.3
9.5°	9376.0
10°	8817.1
12.5°	6502.9
15°	5218.0
17.5°	4458.0
20°	3868.3
22.5°	3397.9
25°	3012.9
27.5°	2627.8
30°	2109.6
32.5°	1356.5
35°	722.6
37.5°	398.7
40°	252.2
42.5°	167.0
45°	105.7
47.5°	64.7
50°	30.6
52.5°	10.2
55°	6.8
57.5°	3.4
60°	3.4
62.5°	3.4
65°	3.4



TEST NUMBER: P584680
CATALOG NUMBER: HCC8S45D010SL-HM82555835-81NDC

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	3.4
80°	3.4
82.5°	3.4
85°	3.4
87.5°	3.4
90°	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°	3.4
70°	0.0

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)