

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584682

Luminaire Tested: **HCC8S45D010MB-HM82555835-81NDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584682
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-3)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S45D010MB-HM82555835-81NDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" NARROW DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4564.5 lumens
Efficiency: N/A
Efficacy: 103.7 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.92
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct

Input Watts (W): 44
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584682
CATALOG NUMBER: HCC8S45D010MB-HM82555835-81NDW

Luminous Intensity Polar Plot





TEST NUMBER: P584682
 CATALOG NUMBER: HCC8S45D010MB-HM82555835-81NDW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									50									30									10									0									
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																									
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	112	108	105	102	109	106	103	101	102	100	98	98	96	95	95	93	92	90																												
2	105	99	94	90	102	97	92	88	94	90	87	91	87	85	88	85	83	81																												
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73																												
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	72	68	67																												
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	63	61																												
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56																												
7	77	66	59	54	76	66	59	54	64	58	54	63	58	54	62	57	53	52																												
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48																												
9	69	58	51	47	68	57	51	47	56	51	46	55	50	46	55	50	46	45																												
10	65	55	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	42																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	113774
5°	113468
10°	111580
15°	109947
20°	107313
25°	101868
30°	84021
35°	43261
40°	28963
45°	24835
50°	21429
55°	18698
60°	16615
65°	14929
70°	13524
75°	12188
80°	10886
85°	10862



TEST NUMBER: P584682
 CATALOG NUMBER: HCC8S45D010MB-HM82555835-81NDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	346.6	7.6
10°-20°	969.0	21.2
20°-30°	1342.6	29.4
30°-40°	806.4	17.7
40°-50°	441.4	9.7
50°-60°	313.6	6.9
60°-70°	203.6	4.5
70°-80°	108.8	2.4
80°-90°	32.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2658.2	58.2
0°-40°	3464.6	75.9
0°-60°	4219.6	92.4
0°-90°	4564.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4564.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3690	
5°	3666	347
15°	3444	969
25°	2994	1343
35°	1149	806
45°	570	441
55°	348	314
65°	205	204
75°	102	109
85°	31	32
90°	0	



TEST NUMBER: P584682
CATALOG NUMBER: HCC8S45D010MB-HM82555835-81NDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	3689.6
2.5°	3682.8
5°	3665.7
7.5°	3624.8
10°	3563.5
12.5°	3505.4
15°	3444.0
17.5°	3365.7
20°	3270.2
22.5°	3154.2
25°	2994.0
27.5°	2741.7
30°	2359.7
32.5°	1728.9
35°	1149.2
37.5°	849.1
40°	719.5
42.5°	637.6
45°	569.5
47.5°	504.6
50°	446.7
52.5°	392.1
55°	347.8
57.5°	306.9
60°	269.4
62.5°	235.3
65°	204.6
67.5°	174.0
70°	150.0
72.5°	122.8
75°	102.3
77.5°	81.9
80°	61.3
82.5°	44.3
85°	30.7
87.5°	13.6
90°	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)