

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582702

Luminaire Tested: **HC6R45D010-HM64560940-62RMDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582702
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC6R45D010-HM64560940-62RMDC
Description: HALO COMMERCIAL 6" ROUND, RETROFIT FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4985.6 lumens
Efficiency: N/A
Efficacy: 113.3 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582702

CATALOG NUMBER: HC6R45D010-HM64560940-62RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P582702

CATALOG NUMBER: HC6R45D010-HM64560940-62RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	111	108	106	111	109	106	104		105	103	101			101	99	98			97
2	108	103	99	96	106	101	98	95		98	95	92			95	93	91			92
3	102	96	91	87	100	95	90	86		92	88	85			90	86	84			87
4	97	90	84	80	95	89	83	79		86	82	79			84	81	78			83
5	92	84	78	74	91	83	77	73		81	76	73			79	75	72			78
6	88	79	73	68	86	78	72	68		76	71	68			75	71	67			74
7	83	74	68	64	82	73	67	63		72	67	63			71	66	63			70
8	79	69	63	59	78	69	63	59		68	63	59			67	62	59			66
9	75	65	59	55	74	65	59	55		64	59	55			63	58	55			62
10	72	62	56	52	71	61	56	52		60	55	52			60	55	52			59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	231242
5°	236308
10°	250491
15°	279990
20°	293162
25°	244435
30°	171071
35°	115208
40°	59333
45°	20607
50°	9177
55°	3030
60°	1392
65°	1232
70°	1010
75°	678
80°	1010
85°	0



TEST NUMBER: P582702

CATALOG NUMBER: HC6R45D010-HM64560940-62RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	416.2	8.3
10°-20°	1390.0	27.9
20°-30°	1806.5	36.2
30°-40°	1067.1	21.4
40°-50°	254.6	5.1
50°-60°	37.5	0.8
60°-70°	9.4	0.2
70°-80°	3.8	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3612.8	72.5
0°-40°	4679.9	93.9
0°-60°	4972.0	99.7
0°-90°	4985.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4985.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4218	
5°	4294	416
15°	4933	1390
25°	4041	1807
35°	1722	1067
45°	266	255
55°	32	38
65°	10	9
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P582702

CATALOG NUMBER: HC6R45D010-HM64560940-62RMDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	4218.2
2.5°	4227.7
5°	4294.2
7.5°	4379.6
10°	4499.9
12.5°	4689.8
15°	4933.4
17.5°	5098.0
20°	5025.2
22.5°	4658.1
25°	4041.1
27.5°	3335.3
30°	2702.5
32.5°	2186.7
35°	1721.5
37.5°	1265.8
40°	829.1
42.5°	452.5
45°	265.8
47.5°	164.6
50°	107.6
52.5°	63.3
55°	31.7
57.5°	15.8
60°	12.7
62.5°	12.7
65°	9.5
67.5°	6.3
70°	6.3
72.5°	3.2
75°	3.2
77.5°	3.2
80°	3.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)