

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582766

Luminaire Tested: **HC650D010-HM64560840-61WDBB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582766
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-11)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC650D010-HM64560840-61WDBB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5008.5 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 48
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582766

CATALOG NUMBER: HC650D010-HM64560840-61WDBB

Luminous Intensity Polar Plot





TEST NUMBER: P582766

CATALOG NUMBER: HC650D010-HM64560840-61WDBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97
2	107	101	97	93	104	100	95	92	96	93	90		93	91	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	75	93	85	79	75	83	78	74		81	77	73		79
5	89	80	73	68	87	79	73	68	77	72	67		75	70	67		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	68	62	57	77	68	61	57	66	61	57		65	60	56		64
8	74	64	57	52	73	63	57	52	62	56	52		61	56	52		60
9	70	59	53	48	69	59	53	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	48	45		53	48	44		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	177875
5°	179182
10°	182311
15°	189536
20°	197481
25°	204526
30°	201791
35°	168131
40°	107816
45°	53835
50°	21364
55°	7254
60°	2083
65°	1466
70°	1218
75°	1610
80°	1200
85°	0



TEST NUMBER: P582766

CATALOG NUMBER: HC650D010-HM64560840-61WDBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	311.4	6.2
10°-20°	947.2	18.9
20°-30°	1546.6	30.9
30°-40°	1516.1	30.3
40°-50°	581.3	11.6
50°-60°	85.3	1.7
60°-70°	12.6	0.3
70°-80°	6.5	0.1
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2805.2	56.0
0°-40°	4321.3	86.3
0°-60°	4987.8	99.6
0°-90°	5008.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5008.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3245	
5°	3256	311
15°	3340	947
25°	3381	1547
35°	2512	1516
45°	694	581
55°	76	85
65°	11	13
75°	8	7
85°	0	2
90°	0	



TEST NUMBER: P582766

CATALOG NUMBER: HC650D010-HM64560840-61WDBB

CANDELA DISTRIBUTION (FULL):

	0°
0°	3244.7
2.5°	3237.1
5°	3256.1
7.5°	3267.5
10°	3275.1
12.5°	3301.6
15°	3339.6
17.5°	3370.0
20°	3385.1
22.5°	3389.0
25°	3381.3
27.5°	3328.2
30°	3187.8
32.5°	2922.1
35°	2512.3
37.5°	2007.6
40°	1506.6
42.5°	1074.0
45°	694.4
47.5°	425.0
50°	250.5
52.5°	144.2
55°	75.9
57.5°	34.1
60°	19.0
62.5°	15.2
65°	11.3
67.5°	11.3
70°	7.6
72.5°	7.6
75°	7.6
77.5°	3.8
80°	3.8
82.5°	3.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)