

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582833

Luminaire Tested: **HC650D010-HM64560940-61NDH**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582833
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-2)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC650D010-HM64560940-61NDH
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4861.0 lumens
Efficiency: N/A
Efficacy: 101.3 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 0.89 / 0.89
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 48
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582833

CATALOG NUMBER: HC650D010-HM64560940-61NDH

Luminous Intensity Polar Plot





TEST NUMBER: P582833

CATALOG NUMBER: HC650D010-HM64560940-61NDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70
8	79	70	64	59	78	69	63	59	68	63	59		67	62	59		66
9	75	66	60	56	74	65	59	56	64	59	55		63	59	55		62
10	72	62	56	52	71	62	56	52	61	56	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	297569
5°	296307
10°	289301
15°	274621
20°	244782
25°	206189
30°	164272
35°	117202
40°	63025
45°	27003
50°	12281
55°	4483
60°	2204
65°	1725
70°	1603
75°	699
80°	1042
85°	0



TEST NUMBER: P582833

CATALOG NUMBER: HC650D010-HM64560940-61NDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	508.3	10.5
10°-20°	1341.3	27.6
20°-30°	1553.5	32.0
30°-40°	1074.1	22.1
40°-50°	310.2	6.4
50°-60°	53.4	1.1
60°-70°	13.6	0.3
70°-80°	5.2	0.1
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3403.0	70.0
0°-40°	4477.2	92.1
0°-60°	4840.8	99.6
0°-90°	4861.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4861.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5428	
5°	5384	508
15°	4839	1341
25°	3409	1553
35°	1751	1074
45°	348	310
55°	47	53
65°	13	14
75°	3	5
85°	0	1
90°	0	



TEST NUMBER: P582833

CATALOG NUMBER: HC650D010-HM64560940-61NDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	5428.1
2.5°	5404.6
5°	5384.5
7.5°	5324.3
10°	5197.1
12.5°	5043.0
15°	4838.8
17.5°	4550.7
20°	4195.9
22.5°	3804.0
25°	3408.8
27.5°	3003.8
30°	2595.1
32.5°	2186.6
35°	1751.3
37.5°	1299.2
40°	880.7
42.5°	555.9
45°	348.3
47.5°	224.4
50°	144.0
52.5°	87.0
55°	46.9
57.5°	26.8
60°	20.1
62.5°	16.8
65°	13.3
67.5°	10.0
70°	10.0
72.5°	6.7
75°	3.3
77.5°	3.3
80°	3.3
82.5°	3.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)