

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582966

Luminaire Tested: **HC605D010-HM60525935-61WDH**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P582966  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC605D010-HM60525935-61WDH  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 637.2 lumens  
Efficiency: N/A  
Efficacy: 106.2 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.08  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P582966

CATALOG NUMBER: HC605D010-HM60525935-61WDH

### Luminous Intensity Polar Plot





TEST NUMBER: P582966

CATALOG NUMBER: HC605D010-HM60525935-61WDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 113 | 110 | 107 | 105 | 110 | 108 | 105 | 103 | 103 | 101 | 100 | 100 | 98  | 97  | 96  | 95  | 94  | 92  |    |    |
| 2   | 106 | 101 | 96  | 93  | 104 | 99  | 95  | 92  | 96  | 92  | 90  | 93  | 90  | 88  | 90  | 88  | 86  | 84  |    |    |
| 3   | 100 | 93  | 87  | 83  | 98  | 91  | 86  | 82  | 89  | 84  | 81  | 86  | 83  | 80  | 84  | 81  | 78  | 77  |    |    |
| 4   | 94  | 86  | 79  | 75  | 92  | 85  | 79  | 74  | 82  | 77  | 73  | 80  | 76  | 72  | 78  | 75  | 72  | 70  |    |    |
| 5   | 89  | 79  | 73  | 68  | 87  | 78  | 72  | 68  | 76  | 71  | 67  | 75  | 70  | 66  | 73  | 69  | 66  | 64  |    |    |
| 6   | 83  | 73  | 67  | 62  | 82  | 73  | 66  | 62  | 71  | 65  | 61  | 70  | 65  | 61  | 68  | 64  | 60  | 59  |    |    |
| 7   | 79  | 68  | 62  | 57  | 77  | 68  | 61  | 57  | 66  | 60  | 56  | 65  | 60  | 56  | 64  | 59  | 56  | 54  |    |    |
| 8   | 74  | 64  | 57  | 52  | 73  | 63  | 57  | 52  | 62  | 56  | 52  | 61  | 56  | 52  | 60  | 55  | 51  | 50  |    |    |
| 9   | 70  | 59  | 53  | 48  | 69  | 59  | 53  | 48  | 58  | 52  | 48  | 57  | 52  | 48  | 56  | 51  | 48  | 46  |    |    |
| 10  | 66  | 56  | 49  | 45  | 65  | 55  | 49  | 45  | 54  | 49  | 45  | 53  | 48  | 45  | 53  | 48  | 44  | 43  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 24954 |
| 5°  | 25121 |
| 10° | 25411 |
| 15° | 25937 |
| 20° | 26077 |
| 25° | 25260 |
| 30° | 22921 |
| 35° | 18631 |
| 40° | 12373 |
| 45° | 6884  |
| 50° | 3863  |
| 55° | 2141  |
| 60° | 1173  |
| 65° | 895   |
| 70° | 609   |
| 75° | 445   |
| 80° | 284   |
| 85° | 314   |



TEST NUMBER: P582966

CATALOG NUMBER: HC605D010-HM60525935-61WDH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 43.6   | 6.8       |
| 10°-20°   | 128.8  | 20.2      |
| 20°-30°   | 189.9  | 29.8      |
| 30°-40°   | 169.8  | 26.7      |
| 40°-50°   | 73.7   | 11.6      |
| 50°-60°   | 21.6   | 3.4       |
| 60°-70°   | 6.9    | 1.1       |
| 70°-80°   | 2.4    | 0.4       |
| 80°-90°   | 0.4    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 362.3  | 56.9      |
| 0°-40°    | 532.1  | 83.5      |
| 0°-60°    | 627.5  | 98.5      |
| 0°-90°    | 637.2  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 637.2  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 455 |      |
| 5°  | 456 | 44   |
| 15° | 457 | 129  |
| 25° | 418 | 190  |
| 35° | 278 | 170  |
| 45° | 89  | 74   |
| 55° | 22  | 22   |
| 65° | 7   | 7    |
| 75° | 2   | 2    |
| 85° | 0   | 0    |
| 90° | 0   |      |



TEST NUMBER: P582966

CATALOG NUMBER: HC605D010-HM60525935-61WDH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 455.2 |
| 2.5°  | 453.9 |
| 5°    | 456.5 |
| 7.5°  | 457.3 |
| 10°   | 456.5 |
| 12.5° | 456.5 |
| 15°   | 457.0 |
| 17.5° | 454.4 |
| 20°   | 447.0 |
| 22.5° | 434.5 |
| 25°   | 417.6 |
| 27.5° | 394.0 |
| 30°   | 362.1 |
| 32.5° | 324.2 |
| 35°   | 278.4 |
| 37.5° | 226.3 |
| 40°   | 172.9 |
| 42.5° | 126.3 |
| 45°   | 88.8  |
| 47.5° | 63.4  |
| 50°   | 45.3  |
| 52.5° | 32.3  |
| 55°   | 22.4  |
| 57.5° | 15.1  |
| 60°   | 10.7  |
| 62.5° | 8.6   |
| 65°   | 6.9   |
| 67.5° | 5.2   |
| 70°   | 3.8   |
| 72.5° | 3.1   |
| 75°   | 2.1   |
| 77.5° | 1.7   |
| 80°   | 0.9   |
| 82.5° | 0.5   |
| 85°   | 0.5   |
| 87.5° | 0.0   |
| 90°   | 0.0   |



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)