

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583036

Luminaire Tested: **HC655D010-HM64560835-61WDBB**

Issue Date: 9/16/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P583036  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-11)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/16/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HC655D010-HM64560835-61WDBB  
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5037.7 lumens  
Efficiency: N/A  
Efficacy: 96.9 lumens/watt  
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.14  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 52  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P583036

CATALOG NUMBER: HC655D010-HM64560835-61WDBB

### Luminous Intensity Polar Plot





TEST NUMBER: P583036

CATALOG NUMBER: HC655D010-HM64560835-61WDBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 110 | 107 | 105 | 110 | 108 | 105 | 103 | 104 | 102 | 100 |  | 100 | 98  | 97  |  | 97  |
| 2   | 107 | 101 | 97  | 93  | 104 | 100 | 95  | 92  | 96  | 93  | 90  |  | 93  | 91  | 88  |  | 90  |
| 3   | 100 | 93  | 88  | 83  | 98  | 92  | 87  | 83  | 89  | 85  | 81  |  | 87  | 83  | 80  |  | 84  |
| 4   | 95  | 86  | 80  | 75  | 93  | 85  | 79  | 75  | 83  | 78  | 74  |  | 81  | 77  | 73  |  | 79  |
| 5   | 89  | 80  | 73  | 68  | 87  | 79  | 73  | 68  | 77  | 72  | 67  |  | 75  | 70  | 67  |  | 73  |
| 6   | 84  | 74  | 67  | 62  | 82  | 73  | 67  | 62  | 71  | 66  | 62  |  | 70  | 65  | 61  |  | 69  |
| 7   | 79  | 68  | 62  | 57  | 77  | 68  | 61  | 57  | 66  | 61  | 57  |  | 65  | 60  | 56  |  | 64  |
| 8   | 74  | 64  | 57  | 52  | 73  | 63  | 57  | 52  | 62  | 56  | 52  |  | 61  | 56  | 52  |  | 60  |
| 9   | 70  | 59  | 53  | 48  | 69  | 59  | 53  | 48  | 58  | 52  | 48  |  | 57  | 52  | 48  |  | 56  |
| 10  | 66  | 56  | 49  | 45  | 65  | 55  | 49  | 45  | 54  | 48  | 45  |  | 53  | 48  | 44  |  | 53  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 178906 |
| 5°  | 180222 |
| 10° | 183369 |
| 15° | 190637 |
| 20° | 198631 |
| 25° | 205718 |
| 30° | 202962 |
| 35° | 169108 |
| 40° | 108446 |
| 45° | 54161  |
| 50° | 21492  |
| 55° | 7292   |
| 60° | 2083   |
| 65° | 1492   |
| 70° | 1234   |
| 75° | 1631   |
| 80° | 1200   |
| 85° | 0      |



TEST NUMBER: P583036

CATALOG NUMBER: HC655D010-HM64560835-61WDBB

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 313.2  | 6.2       |
| 10°-20°   | 952.7  | 18.9      |
| 20°-30°   | 1555.6 | 30.9      |
| 30°-40°   | 1525.0 | 30.3      |
| 40°-50°   | 584.7  | 11.6      |
| 50°-60°   | 85.8   | 1.7       |
| 60°-70°   | 12.8   | 0.3       |
| 70°-80°   | 6.6    | 0.1       |
| 80°-90°   | 1.5    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 2821.4 | 56.0      |
| 0°-40°    | 4346.4 | 86.3      |
| 0°-60°    | 5016.8 | 99.6      |
| 0°-90°    | 5037.7 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 5037.7 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3264 |      |
| 5°  | 3275 | 313  |
| 15° | 3359 | 953  |
| 25° | 3401 | 1556 |
| 35° | 2527 | 1525 |
| 45° | 699  | 585  |
| 55° | 76   | 86   |
| 65° | 12   | 13   |
| 75° | 8    | 7    |
| 85° | 0    | 2    |
| 90° | 0    |      |



TEST NUMBER: P583036

CATALOG NUMBER: HC655D010-HM64560835-61WDBB

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 3263.5 |
| 2.5°  | 3256.0 |
| 5°    | 3275.0 |
| 7.5°  | 3286.5 |
| 10°   | 3294.1 |
| 12.5° | 3320.8 |
| 15°   | 3359.0 |
| 17.5° | 3389.5 |
| 20°   | 3404.8 |
| 22.5° | 3408.6 |
| 25°   | 3401.0 |
| 27.5° | 3347.5 |
| 30°   | 3206.3 |
| 32.5° | 2939.2 |
| 35°   | 2526.9 |
| 37.5° | 2019.3 |
| 40°   | 1515.4 |
| 42.5° | 1080.2 |
| 45°   | 698.6  |
| 47.5° | 427.5  |
| 50°   | 252.0  |
| 52.5° | 145.0  |
| 55°   | 76.3   |
| 57.5° | 34.3   |
| 60°   | 19.0   |
| 62.5° | 15.3   |
| 65°   | 11.5   |
| 67.5° | 11.5   |
| 70°   | 7.7    |
| 72.5° | 7.7    |
| 75°   | 7.7    |
| 77.5° | 3.8    |
| 80°   | 3.8    |
| 82.5° | 3.8    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By 670245859 / DESKTOP-HRDQ47P







— 0°-180°







(END OF REPORT)