

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583044

Luminaire Tested: **HC6R55D010-HM64560835-62RMDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583044
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-13)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC6R55D010-HM64560835-62RMDC
Description: HALO COMMERCIAL 6" ROUND, RETROFIT FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6014.7 lumens
Efficiency: N/A
Efficacy: 115.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 52
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583044

CATALOG NUMBER: HC6R55D010-HM64560835-62RMDC

Luminous Intensity Polar Plot





TEST NUMBER: P583044

CATALOG NUMBER: HC6R55D010-HM64560835-62RMDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	114	111	108	106	111	109	106	104		105	103	101			101	99	98			97
2	108	103	99	96	106	101	98	95		98	95	92			95	93	91			92
3	102	96	91	87	100	95	90	86		92	88	85			90	86	84			87
4	97	90	84	80	95	89	83	79		86	82	79			84	81	78			83
5	92	84	78	74	91	83	77	73		81	76	73			79	75	72			78
6	88	79	73	68	86	78	72	68		76	71	68			75	71	67			74
7	83	74	68	64	82	73	67	63		72	67	63			71	66	63			70
8	79	69	63	59	78	69	63	59		68	63	59			67	62	59			66
9	75	65	59	55	74	65	59	55		64	59	55			63	58	55			62
10	72	62	56	52	71	61	56	52		60	55	52			60	55	52			59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	278980
5°	285092
10°	302199
15°	337789
20°	353677
25°	294894
30°	206380
35°	138993
40°	71577
45°	24863
50°	11070
55°	3651
60°	1677
65°	1492
70°	1234
75°	805
80°	1200
85°	0



TEST NUMBER: P583044

CATALOG NUMBER: HC6R55D010-HM64560835-62RMDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	502.2	8.3
10°-20°	1677.0	27.9
20°-30°	2179.4	36.2
30°-40°	1287.4	21.4
40°-50°	307.1	5.1
50°-60°	45.2	0.8
60°-70°	11.3	0.2
70°-80°	4.5	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4358.6	72.5
0°-40°	5645.9	93.9
0°-60°	5998.3	99.7
0°-90°	6014.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6014.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5089	
5°	5181	502
15°	5952	1677
25°	4875	2179
35°	2077	1287
45°	321	307
55°	38	45
65°	12	11
75°	4	5
85°	0	1
90°	0	



TEST NUMBER: P583044

CATALOG NUMBER: HC6R55D010-HM64560835-62RMDC

CANDELA DISTRIBUTION (FULL):

0°	
0°	5089.0
2.5°	5100.5
5°	5180.7
7.5°	5283.8
10°	5428.8
12.5°	5657.8
15°	5951.8
17.5°	6150.4
20°	6062.5
22.5°	5619.7
25°	4875.3
27.5°	4023.9
30°	3260.3
32.5°	2638.1
35°	2076.9
37.5°	1527.1
40°	1000.2
42.5°	546.0
45°	320.7
47.5°	198.5
50°	129.8
52.5°	76.3
55°	38.2
57.5°	19.0
60°	15.3
62.5°	15.3
65°	11.5
67.5°	7.7
70°	7.7
72.5°	3.8
75°	3.8
77.5°	3.8
80°	3.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)