

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583030

Luminaire Tested: **HC655D010-HM64560835-61NDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583030
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-1)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC655D010-HM64560835-61NDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" NARROW DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5812.5 lumens
Efficiency: N/A
Efficacy: 111.8 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.88
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 52
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583030

CATALOG NUMBER: HC655D010-HM64560835-61NDC

Luminous Intensity Polar Plot





TEST NUMBER: P583030

CATALOG NUMBER: HC655D010-HM64560835-61NDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98
2	108	103	99	96	106	102	98	95	98	96	93		96	93	91		93
3	103	97	92	88	101	95	91	87	93	89	86		90	87	84		88
4	98	90	85	81	96	89	84	80	87	83	79		85	81	79		83
5	93	85	79	75	91	84	79	75	82	77	74		80	76	73		79
6	88	80	74	70	87	79	73	69	77	73	69		76	72	68		75
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	70	65	61	69	64	60		68	64	60		67
9	76	67	61	57	75	66	61	57	65	60	57		65	60	57		64
10	73	63	58	54	72	63	57	54	62	57	54		61	57	53		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	347121
5°	347814
10°	353539
15°	356120
20°	325534
25°	255801
30°	187244
35°	132822
40°	62825
45°	23964
50°	10746
55°	2915
60°	1261
65°	999
70°	609
75°	805
80°	0
85°	0



TEST NUMBER: P583030

CATALOG NUMBER: HC655D010-HM64560835-61NDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	604.6	10.4
10°-20°	1734.3	29.8
20°-30°	1929.1	33.2
30°-40°	1205.1	20.7
40°-50°	286.3	4.9
50°-60°	41.0	0.7
60°-70°	8.5	0.1
70°-80°	3.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4268.0	73.4
0°-40°	5473.1	94.2
0°-60°	5800.4	99.8
0°-90°	5812.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5812.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6332	
5°	6320	605
15°	6275	1734
25°	4229	1929
35°	1985	1205
45°	309	286
55°	30	41
65°	8	9
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P583030

CATALOG NUMBER: HC655D010-HM64560835-61NDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	6332.0
2.5°	6305.3
5°	6320.5
7.5°	6343.5
10°	6351.1
12.5°	6347.3
15°	6274.8
17.5°	6030.5
20°	5580.1
22.5°	4946.5
25°	4229.0
27.5°	3541.9
30°	2958.0
32.5°	2473.3
35°	1984.7
37.5°	1458.0
40°	877.9
42.5°	507.6
45°	309.1
47.5°	198.5
50°	126.0
52.5°	72.5
55°	30.5
57.5°	15.3
60°	11.5
62.5°	11.5
65°	7.7
67.5°	7.7
70°	3.8
72.5°	3.8
75°	3.8
77.5°	3.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)