

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583181

Luminaire Tested: **HC660D010-HM64560835-61WDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583181
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-7)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC660D010-HM64560835-61WDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WIDE DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6418.2 lumens
Efficiency: N/A
Efficacy: 116.7 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.28 / 1.09
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 55
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583181

CATALOG NUMBER: HC660D010-HM64560835-61WDC

Luminous Intensity Polar Plot





TEST NUMBER: P583181

CATALOG NUMBER: HC660D010-HM64560835-61WDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	82		88	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		76	72	68		75
6	85	75	69	64	83	74	68	64	73	67	63		71	67	63		70
7	80	70	63	59	79	69	63	59	68	62	58		67	62	58		66
8	76	65	59	54	74	65	59	54	64	58	54		62	57	54		61
9	71	61	55	50	70	60	54	50	60	54	50		59	53	50		58
10	68	57	51	47	67	57	51	47	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	227542
5°	230596
10°	239241
15°	260183
20°	290893
25°	306181
30°	269535
35°	186956
40°	111631
45°	53068
50°	20025
55°	8363
60°	2609
65°	2075
70°	1282
75°	847
80°	1263
85°	0



TEST NUMBER: P583181

CATALOG NUMBER: HC660D010-HM64560835-61WDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	403.3	6.3
10°-20°	1316.4	20.5
20°-30°	2255.6	35.1
30°-40°	1751.8	27.3
40°-50°	579.1	9.0
50°-60°	88.8	1.4
60°-70°	15.7	0.2
70°-80°	5.8	0.1
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3975.3	61.9
0°-40°	5727.1	89.2
0°-60°	6395.0	99.6
0°-90°	6418.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6418.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4151	
5°	4190	403
15°	4584	1316
25°	5062	2256
35°	2794	1752
45°	684	579
55°	88	89
65°	16	16
75°	4	6
85°	0	2
90°	0	



TEST NUMBER: P583181

CATALOG NUMBER: HC660D010-HM64560835-61WDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	4150.7
2.5°	4146.7
5°	4190.4
7.5°	4238.2
10°	4297.8
12.5°	4417.3
15°	4584.4
17.5°	4787.3
20°	4986.3
22.5°	5101.7
25°	5061.9
27.5°	4787.3
30°	4258.0
32.5°	3545.7
35°	2793.6
37.5°	2121.1
40°	1559.9
42.5°	1102.3
45°	684.5
47.5°	382.1
50°	234.8
52.5°	143.3
55°	87.5
57.5°	43.8
60°	23.8
62.5°	19.9
65°	16.0
67.5°	12.0
70°	8.0
72.5°	8.0
75°	4.0
77.5°	4.0
80°	4.0
82.5°	4.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)