

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583297

Luminaire Tested: **HC607D010-HM60525830-61MDC**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P583297
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC607D010-HM60525830-61MDC
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" MEDIUM DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 996.6 lumens
Efficiency: N/A
Efficacy: 124.6 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 0.96
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583297

CATALOG NUMBER: HC607D010-HM60525830-61MDC

Luminous Intensity Polar Plot





TEST NUMBER: P583297

CATALOG NUMBER: HC607D010-HM60525830-61MDC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	79		84	81	78		83
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	73	67	63	72	67	63		71	66	63		70
8	79	70	63	59	78	69	63	59	68	63	59		67	62	59		66
9	75	66	60	56	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47321
5°	48057
10°	50795
15°	56561
20°	58653
25°	48124
30°	33720
35°	23008
40°	11987
45°	4217
50°	1885
55°	602
60°	351
65°	246
70°	192
75°	148
80°	0
85°	0



TEST NUMBER: P583297

CATALOG NUMBER: HC607D010-HM60525830-61MDC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.6	8.5
10°-20°	280.3	28.1
20°-30°	356.9	35.8
30°-40°	212.7	21.3
40°-50°	51.6	5.2
50°-60°	7.9	0.8
60°-70°	1.9	0.2
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	721.7	72.4
0°-40°	934.4	93.8
0°-60°	993.9	99.7
0°-90°	996.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	996.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	863	
5°	873	85
15°	997	280
25°	796	357
35°	344	213
45°	54	52
55°	6	8
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P583297

CATALOG NUMBER: HC607D010-HM60525830-61MDC

CANDELA DISTRIBUTION (FULL):

	0°
0°	863.2
2.5°	863.2
5°	873.3
7.5°	889.2
10°	912.5
12.5°	949.1
15°	996.6
17.5°	1026.3
20°	1005.4
22.5°	925.2
25°	795.6
27.5°	652.8
30°	532.7
32.5°	435.4
35°	343.8
37.5°	253.5
40°	167.5
42.5°	90.4
45°	54.4
47.5°	34.1
50°	22.1
52.5°	13.3
55°	6.3
57.5°	3.7
60°	3.2
62.5°	2.5
65°	1.9
67.5°	1.2
70°	1.2
72.5°	0.7
75°	0.7
77.5°	0.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)