

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P583553

Luminaire Tested: **HC805D010-HM80520940-81WDH**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P583553
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-8)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HC805D010-HM80520940-81WDH
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WIDE DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 738.0 lumens
Efficiency: N/A
Efficacy: 123.0 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P583553

CATALOG NUMBER: HC805D010-HM80520940-81WDH

Luminous Intensity Polar Plot





TEST NUMBER: P583553

CATALOG NUMBER: HC805D010-HM80520940-81WDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	113	109	107	104	110	107	105	102		103	101	99			99	98	96			96
2	106	100	95	91	103	98	94	90		95	91	88			92	89	86			89
3	99	92	86	81	97	90	85	81		88	83	79			85	81	78			83
4	93	84	78	73	91	83	77	72		81	76	72			79	74	71			77
5	87	78	71	66	86	77	70	66		75	69	65			73	68	64			71
6	82	72	65	60	80	71	64	60		69	64	59			68	63	59			66
7	77	67	60	55	76	66	59	55		64	59	54			63	58	54			62
8	73	62	55	50	71	61	55	50		60	54	50			59	54	50			58
9	69	58	51	46	67	57	51	46		56	50	46			55	50	46			54
10	65	54	47	43	64	53	47	43		53	47	43			52	46	43			51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	16895
5°	16514
10°	16007
15°	15681
20°	15545
25°	15311
30°	14503
35°	12050
40°	7097
45°	4692
50°	3694
55°	2715
60°	1887
65°	1153
70°	505
75°	226
80°	178
85°	0



TEST NUMBER: P583553

CATALOG NUMBER: HC805D010-HM80520940-81WDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.2	6.8
10°-20°	138.9	18.8
20°-30°	205.8	27.9
30°-40°	190.1	25.8
40°-50°	87.7	11.9
50°-60°	46.1	6.2
60°-70°	16.3	2.2
70°-80°	2.6	0.3
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	394.9	53.5
0°-40°	585.0	79.3
0°-60°	718.8	97.4
0°-90°	738.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	738.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	548	
5°	534	50
15°	491	139
25°	450	206
35°	320	190
45°	108	88
55°	50	46
65°	16	16
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P583553

CATALOG NUMBER: HC805D010-HM80520940-81WDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	547.9
2.5°	543.2
5°	533.5
7.5°	522.8
10°	511.2
12.5°	500.1
15°	491.2
17.5°	483.3
20°	473.7
22.5°	463.0
25°	450.0
27.5°	432.4
30°	407.3
32.5°	371.5
35°	320.1
37.5°	245.9
40°	176.3
42.5°	132.3
45°	107.6
47.5°	91.3
50°	77.0
52.5°	63.1
55°	50.5
57.5°	39.9
60°	30.6
62.5°	23.2
65°	15.8
67.5°	9.3
70°	5.6
72.5°	3.2
75°	1.9
77.5°	1.4
80°	1.0
82.5°	0.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670245859 / DESKTOP-HRDQ47P





— 0°-180°







(END OF REPORT)