

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P582377

Luminaire Tested: **HCC6S35D010BZ-HM63040930-61WWWB**

Issue Date: 9/16/2021

Test Information

Test Method: LM-41-14
Report Number: P582377
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2105-241-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/16/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC6S35D010BZ-HM63040930-61WWWB
Description: HALO COMMERCIAL 6" ROUND, NEW CONSTRUCTION FRAME, WITH 6" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3515.3 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.09 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 33.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P582377
CATALOG NUMBER: HCC6S35D010BZ-HM63040930-61WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P582377

CATALOG NUMBER: HCC6S35D010BZ-HM63040930-61WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76					76			
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66					66			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58					58			
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52					52			
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46					46			
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	48	43	42					42			
8	66	53	46	40	64	53	45	40	51	45	40	50	44	40	49	44	39	38					38			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34					34			
10	58	46	38	34	57	45	38	33	44	38	33	43	37	33	43	37	33	31					31			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	98408	98408	98408
5°	100534	98371	96621
10°	103605	97465	94187
15°	106885	96170	91856
20°	108579	92554	88126
25°	106796	87072	83061
30°	101680	80721	77620
35°	92722	72866	71721
40°	81073	65458	65108
45°	69775	57603	58936
50°	60655	50190	51239
55°	52968	44061	44529
60°	47047	38177	34953
65°	41989	32118	26721
70°	36945	26335	22408
75°	31687	20778	21308
80°	25540	17805	20899
85°	16983	15410	18492



TEST NUMBER: P582377
 CATALOG NUMBER: HCC6S35D010BZ-HM63040930-61WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.0	4.8
10°-20°	483.8	13.8
20°-30°	690.7	19.6
30°-40°	723.5	20.6
40°-50°	609.1	17.3
50°-60°	433.5	12.3
60°-70°	253.7	7.2
70°-80°	120.1	3.4
80°-90°	30.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1344.5	38.2
0°-40°	2067.9	58.8
0°-60°	3110.6	88.5
0°-90°	3515.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3515.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1795	1795	1795	1795	1795	
5°	1827	1812	1788	1763	1756	176
15°	1883	1815	1694	1626	1618	532
25°	1766	1641	1440	1371	1373	808
35°	1386	1270	1089	1052	1072	861
45°	900	834	743	746	760	699
55°	554	508	461	461	466	499
65°	324	287	248	208	206	323
75°	150	125	98	96	101	161
85°	27	22	24	29	29	35
90°	0	0	0	0	0	



TEST NUMBER: P582377

CATALOG NUMBER: HCC6S35D010BZ-HM63040930-61WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1795.1	1795.1	1795.1	1795.1	1795.1	1795.1	1795.1	1795.1	1795.1
2.5°	1797.5	1797.5	1795.1	1792.6	1787.6	1780.3	1775.4	1770.5	1770.5
5°	1826.9	1822.0	1812.2	1800.0	1787.6	1772.9	1763.1	1755.8	1755.8
7.5°	1851.4	1841.6	1822.0	1800.0	1777.8	1758.2	1741.0	1731.2	1728.8
10°	1861.2	1849.0	1819.6	1785.2	1750.9	1723.9	1704.3	1692.0	1692.0
12.5°	1871.1	1856.3	1817.1	1768.0	1723.9	1687.1	1667.5	1657.7	1655.3
15°	1883.3	1863.7	1814.7	1753.3	1694.5	1652.8	1625.9	1618.5	1618.5
17.5°	1883.3	1858.8	1797.5	1721.4	1647.9	1601.4	1576.7	1569.4	1571.8
20°	1861.2	1834.3	1760.7	1667.5	1586.5	1537.5	1513.0	1508.1	1510.6
22.5°	1819.6	1787.6	1704.3	1603.8	1515.5	1464.0	1441.9	1441.9	1439.5
25°	1765.6	1731.2	1640.6	1535.1	1439.5	1387.9	1370.8	1373.2	1373.2
27.5°	1694.5	1660.2	1569.4	1456.6	1361.0	1309.5	1297.2	1302.1	1304.6
30°	1606.3	1569.4	1473.8	1363.4	1275.2	1223.6	1216.2	1223.6	1226.2
32.5°	1498.3	1471.4	1378.1	1265.4	1181.9	1137.8	1135.4	1142.7	1152.5
35°	1385.5	1356.1	1270.3	1167.2	1088.8	1052.1	1052.1	1064.3	1071.7
37.5°	1262.9	1233.5	1155.0	1069.2	1002.9	968.6	973.5	985.8	988.2
40°	1132.9	1110.9	1044.7	971.1	914.7	887.7	895.1	907.3	909.8
42.5°	1010.3	990.7	936.8	870.6	828.8	809.2	819.0	833.7	838.6
45°	900.0	877.9	833.7	777.3	743.0	733.2	745.5	755.3	760.2
47.5°	799.4	779.8	743.0	691.6	667.1	662.2	674.4	679.3	684.2
50°	711.2	691.6	654.7	608.1	588.5	588.5	598.3	603.2	600.8
52.5°	625.3	608.1	573.8	534.6	522.3	522.3	529.7	532.2	537.1
55°	554.2	537.1	507.6	470.9	461.0	456.1	461.0	461.0	465.9
57.5°	488.0	473.3	446.3	412.0	399.7	394.8	392.3	389.9	394.8
60°	429.1	416.9	387.4	358.0	348.2	336.0	326.2	316.4	318.8
62.5°	375.2	362.9	336.0	306.6	296.8	279.5	267.2	255.0	259.9
65°	323.7	311.5	287.0	262.3	247.6	228.0	208.4	201.1	206.0
67.5°	277.0	267.2	242.7	218.2	206.0	183.9	164.3	164.3	166.8
70°	230.5	220.7	201.1	179.0	164.3	144.7	137.4	139.8	139.8
72.5°	188.8	181.5	161.9	142.3	127.6	115.3	115.3	117.8	120.2
75°	149.6	144.7	125.1	107.9	98.1	90.7	95.7	98.1	100.6
77.5°	115.3	107.9	93.1	80.9	73.5	76.0	80.9	83.3	85.8
80°	80.9	78.4	66.2	58.8	56.4	58.8	63.7	66.2	66.2
82.5°	51.5	49.0	41.7	39.2	39.2	41.7	46.6	46.6	46.6
85°	27.0	24.5	22.1	22.1	24.5	27.0	29.4	29.4	29.4
87.5°	9.8	7.4	9.8	9.8	12.3	12.3	12.3	12.3	12.3
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)