

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584684

Luminaire Tested: **HCC8S45D010BZ-HM82555835-81RWWC**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584684
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S45D010BZ-HM82555835-81RWWC
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4854.2 lumens
Efficiency: N/A
Efficacy: 110.3 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.08 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584684

CATALOG NUMBER: HCC8S45D010BZ-HM82555835-81RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P584684

CATALOG NUMBER: HCC8S45D010BZ-HM82555835-81RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88		
2	103	96	90	85	100	94	89	84	91	86	82	87	84	81	85	82	79	77		
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67		
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	69	65	61	59		
5	81	70	62	56	80	69	62	56	67	61	56	65	59	55	63	58	54	52		
6	76	64	56	50	74	63	55	50	61	55	50	60	54	49	58	53	49	47		
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42		
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38		
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35		
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	78759	78759	78759
5°	79800	78428	77689
10°	80616	77626	76451
15°	81429	75989	74463
20°	81014	73181	71505
25°	79126	68800	67875
30°	75159	63864	63622
35°	68422	58277	58793
40°	59986	52161	54085
45°	51751	46396	49671
50°	45315	40734	44989
55°	40149	35020	39595
60°	36171	29443	32810
65°	32593	23641	25129
70°	28599	17220	13830
75°	24377	8948	3658
80°	18770	2415	604
85°	12065	0	0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P584684

CATALOG NUMBER: HCC8S45D010BZ-HM82555835-81RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.0	5.0
10°-20°	677.4	14.0
20°-30°	961.5	19.8
30°-40°	1012.1	20.9
40°-50°	861.0	17.7
50°-60°	622.2	12.8
60°-70°	353.9	7.3
70°-80°	111.5	2.3
80°-90°	13.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1879.9	38.7
0°-40°	2892.1	59.6
0°-60°	4375.3	90.1
0°-90°	4854.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4854.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	2554	2554	2554	2554	2554	
5°	2578	2564	2534	2517	2510	246
15°	2551	2486	2380	2336	2332	718
25°	2326	2210	2022	1988	1995	1065
35°	1818	1712	1548	1538	1562	1131
45°	1187	1142	1064	1091	1139	922
55°	747	692	651	689	736	673
65°	447	385	324	321	344	443
75°	205	157	75	34	31	220
85°	34	20	0	0	0	44
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P584684

CATALOG NUMBER: HCC8S45D010BZ-HM82555835-81RWWC

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2554.1	2554.1	2554.1	2554.1	2554.1	2554.1	2554.1	2554.1	2554.1	2554.1	2554.1
2.5°	2567.8	2571.2	2564.3	2564.3	2571.2	2564.3	2567.8	2567.8	2564.3	2564.3	2560.9
5°	2578.0	2574.6	2574.6	2574.6	2578.0	2571.2	2567.8	2571.2	2564.3	2564.3	2564.3
7.5°	2581.4	2581.4	2578.0	2574.6	2574.6	2574.6	2571.2	2567.8	2564.3	2557.5	2554.1
10°	2574.6	2574.6	2578.0	2571.2	2571.2	2564.3	2564.3	2557.5	2557.5	2550.7	2540.5
12.5°	2567.8	2564.3	2564.3	2557.5	2557.5	2550.7	2550.7	2540.5	2537.1	2526.9	2516.6
15°	2550.7	2547.3	2540.5	2537.1	2533.7	2530.3	2523.5	2520.1	2509.8	2496.1	2485.9
17.5°	2516.6	2513.2	2509.8	2502.9	2496.1	2492.7	2489.3	2479.1	2465.4	2455.2	2438.2
20°	2468.8	2465.4	2465.4	2455.2	2451.8	2441.6	2438.2	2424.6	2414.3	2393.9	2380.3
22.5°	2404.1	2407.5	2400.7	2393.9	2387.1	2376.8	2369.9	2356.3	2339.3	2318.8	2301.8
25°	2325.6	2329.1	2322.2	2315.4	2305.2	2298.4	2291.6	2271.0	2254.0	2230.1	2209.7
27.5°	2226.7	2226.7	2226.7	2219.9	2202.9	2199.5	2192.7	2172.2	2148.3	2127.8	2107.4
30°	2110.8	2107.4	2107.4	2097.2	2090.4	2076.7	2066.5	2049.5	2032.3	2008.5	1984.6
32.5°	1971.0	1974.4	1964.2	1957.4	1947.2	1947.2	1933.5	1919.8	1899.4	1875.5	1851.7
35°	1817.6	1821.0	1814.2	1810.8	1793.6	1790.2	1786.8	1769.8	1756.2	1739.1	1711.9
37.5°	1660.7	1657.3	1653.8	1653.8	1643.6	1636.8	1630.0	1619.8	1599.3	1585.7	1572.1
40°	1490.2	1490.2	1490.2	1486.8	1483.4	1476.6	1473.2	1466.4	1452.6	1439.0	1428.8
42.5°	1336.8	1336.8	1333.3	1329.9	1323.1	1326.5	1319.6	1312.8	1299.2	1289.0	1282.2
45°	1186.7	1186.7	1186.7	1190.1	1183.3	1173.0	1173.0	1166.2	1159.4	1152.6	1142.4
47.5°	1053.7	1063.9	1057.1	1053.7	1057.1	1043.5	1043.5	1036.7	1029.8	1023.0	1009.4
50°	944.6	944.6	944.6	937.8	934.3	934.3	924.1	917.3	913.9	907.1	893.5
52.5°	845.7	838.8	838.8	835.4	832.0	825.2	825.2	818.4	804.8	798.0	787.7
55°	746.8	746.8	743.3	739.9	736.5	733.1	729.7	719.5	712.7	702.5	692.2
57.5°	658.2	665.0	661.6	654.8	648.0	648.0	641.0	634.2	624.0	613.8	603.6
60°	586.5	583.1	583.1	579.7	572.9	569.5	566.1	555.9	545.6	535.4	525.2
62.5°	511.5	511.5	511.5	504.7	497.8	494.4	491.0	484.2	470.6	460.4	453.5
65°	446.7	443.3	439.9	436.5	433.1	426.3	422.9	416.1	405.7	395.5	385.3
67.5°	381.9	378.5	378.5	375.1	364.9	361.5	361.5	351.2	341.0	330.8	320.6
70°	317.2	317.2	317.2	310.3	306.9	303.5	300.1	293.2	283.0	272.8	262.5
72.5°	262.5	259.1	259.1	255.7	245.5	242.1	238.7	231.9	221.7	214.8	208.0
75°	204.6	204.6	201.2	197.8	194.4	191.0	187.6	180.8	170.6	160.2	156.8
77.5°	156.8	153.4	153.4	150.0	143.2	139.8	139.8	133.0	122.8	115.9	109.1
80°	105.7	109.1	105.7	102.3	98.9	95.5	92.1	88.7	81.9	75.1	68.2
82.5°	64.7	68.2	64.7	64.7	61.3	57.9	57.9	51.1	47.7	44.3	40.9
85°	34.1	34.1	34.1	34.1	30.7	30.7	30.7	27.3	23.8	20.4	20.4
87.5°	10.2	13.6	10.2	10.2	10.2	10.2	10.2	10.2	6.8	6.8	6.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P584684

CATALOG NUMBER: HCC8S45D010BZ-HM82555835-81RWWC

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2554.1	2554.1	2554.1	2554.1	2554.1	2554.1	2554.1	2554.1	2554.1	2554.1	2554.1
2.5°	2564.3	2560.9	2557.5	2557.5	2557.5	2557.5	2557.5	2554.1	2550.7	2550.7	2550.7
5°	2557.5	2557.5	2557.5	2554.1	2550.7	2550.7	2543.9	2540.5	2537.1	2533.7	2530.3
7.5°	2550.7	2543.9	2540.5	2537.1	2533.7	2533.7	2526.9	2520.1	2520.1	2513.2	2506.3
10°	2530.3	2526.9	2520.1	2513.2	2509.8	2506.3	2499.5	2489.3	2485.9	2479.1	2472.3
12.5°	2506.3	2499.5	2492.7	2479.1	2475.7	2472.3	2458.6	2448.4	2441.6	2438.2	2421.1
15°	2475.7	2462.0	2451.8	2434.8	2431.4	2424.6	2414.3	2404.1	2390.5	2380.3	2373.3
17.5°	2421.1	2407.5	2390.5	2373.3	2366.5	2366.5	2349.5	2335.9	2318.8	2312.0	2298.4
20°	2356.3	2339.3	2325.6	2305.2	2295.0	2284.8	2274.4	2254.0	2240.4	2230.1	2213.1
22.5°	2281.4	2257.4	2240.4	2219.9	2202.9	2192.7	2175.6	2158.6	2141.5	2131.2	2117.6
25°	2185.9	2165.4	2138.1	2117.6	2107.4	2093.8	2073.3	2056.3	2039.1	2022.1	2015.3
27.5°	2080.1	2052.9	2028.9	2005.1	1994.9	1984.6	1960.8	1940.3	1926.7	1909.6	1902.8
30°	1964.2	1936.9	1909.6	1889.1	1878.9	1861.9	1848.3	1824.4	1807.4	1793.6	1776.6
32.5°	1831.2	1810.8	1786.8	1756.2	1749.3	1735.7	1715.3	1705.1	1684.5	1674.3	1660.7
35°	1687.9	1674.3	1650.4	1626.6	1616.4	1609.6	1592.5	1572.1	1558.3	1548.1	1541.3
37.5°	1551.5	1534.5	1510.6	1493.6	1486.8	1476.6	1456.0	1445.8	1432.2	1425.4	1411.7
40°	1404.9	1387.9	1370.9	1360.6	1350.4	1343.6	1329.9	1319.6	1306.0	1295.8	1292.4
42.5°	1261.7	1251.5	1237.9	1224.3	1220.7	1210.5	1203.7	1193.5	1183.3	1179.9	1169.6
45°	1132.2	1121.9	1108.3	1094.6	1091.2	1084.4	1081.0	1070.7	1063.9	1063.9	1063.9
47.5°	1002.6	992.4	978.6	971.8	975.2	961.6	961.6	958.2	951.4	951.4	954.8
50°	886.6	872.9	869.5	862.7	855.9	849.1	852.5	842.3	842.3	849.1	845.7
52.5°	777.5	763.9	760.5	753.7	750.3	750.3	746.8	746.8	743.3	746.8	746.8
55°	678.6	668.4	661.6	654.8	651.4	651.4	651.4	648.0	644.4	651.4	654.8
57.5°	589.9	586.5	579.7	569.5	566.1	562.7	559.3	559.3	559.3	559.3	562.7
60°	511.5	504.7	497.8	487.6	487.6	484.2	480.8	477.4	477.4	477.4	477.4
62.5°	443.3	433.1	422.9	416.1	412.7	409.3	405.7	398.9	398.9	398.9	398.9
65°	375.1	364.9	358.0	351.2	344.4	344.4	337.6	334.2	327.4	324.0	317.2
67.5°	310.3	303.5	296.7	286.4	283.0	279.6	272.8	269.4	259.1	255.7	252.3
70°	252.3	242.1	235.3	228.5	225.1	218.3	211.4	204.6	197.8	191.0	184.2
72.5°	197.8	187.6	180.8	174.0	167.0	167.0	156.8	150.0	139.8	133.0	122.8
75°	146.6	136.4	129.6	119.3	115.9	112.5	102.3	95.5	85.3	75.1	68.2
77.5°	98.9	92.1	85.3	75.1	68.2	68.2	57.9	51.1	44.3	34.1	30.7
80°	61.3	54.5	47.7	40.9	40.9	34.1	30.7	23.8	17.0	13.6	10.2
82.5°	34.1	30.7	27.3	20.4	20.4	17.0	13.6	10.2	6.8	3.4	3.4
85°	17.0	13.6	10.2	10.2	6.8	6.8	6.8	3.4	3.4	0.0	0.0
87.5°	6.8	3.4	3.4	3.4	3.4	3.4	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P584684

CATALOG NUMBER: HCC8S45D010BZ-HM82555835-81RWWC

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2554.1	2554.1	2554.1	2554.1	2554.1	2554.1	2554.1	2554.1	2554.1	2554.1	2554.1
2.5°	2547.3	2547.3	2543.9	2543.9	2543.9	2540.5	2543.9	2540.5	2540.5	2540.5	2543.9
5°	2533.7	2526.9	2526.9	2523.5	2523.5	2520.1	2523.5	2520.1	2516.6	2513.2	2516.6
7.5°	2506.3	2499.5	2496.1	2492.7	2492.7	2492.7	2489.3	2485.9	2489.3	2479.1	2485.9
10°	2468.8	2465.4	2458.6	2455.2	2451.8	2455.2	2451.8	2445.0	2445.0	2445.0	2441.6
12.5°	2421.1	2414.3	2410.9	2407.5	2400.7	2400.7	2404.1	2397.3	2397.3	2390.5	2390.5
15°	2363.1	2356.3	2349.5	2349.5	2342.7	2342.7	2339.3	2339.3	2335.9	2332.5	2332.5
17.5°	2291.6	2281.4	2274.4	2277.8	2274.4	2271.0	2271.0	2264.2	2260.8	2264.2	2264.2
20°	2206.3	2199.5	2192.7	2196.1	2189.3	2185.9	2189.3	2179.0	2182.4	2182.4	2182.4
22.5°	2110.8	2107.4	2097.2	2097.2	2090.4	2086.9	2090.4	2090.4	2093.8	2090.4	2090.4
25°	2005.1	1998.3	1991.4	1991.4	1988.0	1984.6	1988.0	1991.4	1988.0	1991.4	1991.4
27.5°	1892.5	1882.3	1882.3	1875.5	1875.5	1878.9	1875.5	1878.9	1882.3	1882.3	1889.1
30°	1769.8	1766.4	1763.0	1759.6	1759.6	1763.0	1763.0	1763.0	1766.4	1773.2	1773.2
32.5°	1653.8	1647.0	1640.2	1640.2	1647.0	1643.6	1647.0	1647.0	1653.8	1653.8	1660.7
35°	1527.7	1527.7	1520.9	1524.3	1524.3	1524.3	1524.3	1531.1	1537.9	1541.3	1548.1
37.5°	1411.7	1401.5	1404.9	1404.9	1408.3	1404.9	1415.1	1415.1	1422.0	1422.0	1428.8
40°	1285.6	1285.6	1289.0	1285.6	1289.0	1289.0	1295.8	1302.6	1306.0	1312.8	1316.2
42.5°	1166.2	1173.0	1166.2	1169.6	1173.0	1176.5	1179.9	1183.3	1196.9	1203.7	1213.9
45°	1057.1	1060.5	1063.9	1067.3	1063.9	1070.7	1074.1	1081.0	1091.2	1094.6	1098.0
47.5°	951.4	954.8	958.2	961.6	961.6	968.4	971.8	978.6	985.6	989.0	992.4
50°	849.1	855.9	859.3	859.3	862.7	869.5	876.3	876.3	883.2	893.5	896.9
52.5°	757.1	757.1	763.9	767.3	770.7	770.7	780.9	784.3	787.7	794.6	801.4
55°	654.8	665.0	668.4	668.4	675.2	682.0	685.4	688.8	688.8	702.5	702.5
57.5°	566.1	569.5	576.3	576.3	576.3	586.5	586.5	593.3	596.7	600.2	607.0
60°	477.4	484.2	484.2	487.6	484.2	491.0	494.4	501.2	504.7	508.1	511.5
62.5°	395.5	395.5	398.9	398.9	398.9	398.9	405.7	405.7	412.7	416.1	419.5
65°	317.2	317.2	317.2	317.2	317.2	317.2	317.2	317.2	320.6	320.6	327.4
67.5°	245.5	242.1	235.3	238.7	235.3	235.3	231.9	231.9	235.3	235.3	242.1
70°	177.4	174.0	167.0	167.0	163.6	160.2	156.8	153.4	150.0	150.0	150.0
72.5°	115.9	109.1	98.9	95.5	95.5	88.7	81.9	78.5	78.5	78.5	78.5
75°	57.9	51.1	44.3	40.9	40.9	34.1	37.5	34.1	34.1	34.1	34.1
77.5°	23.8	17.0	13.6	13.6	13.6	10.2	10.2	10.2	10.2	10.2	10.2
80°	6.8	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
82.5°	3.4	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P584684

CATALOG NUMBER: HCC8S45D010BZ-HM82555835-81RWWC

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	2554.1	2554.1	2554.1	2554.1	2554.1	2554.1	2554.1	2554.1
2.5°	2540.5	2540.5	2533.7	2537.1	2537.1	2537.1	2537.1	2537.1
5°	2509.8	2513.2	2509.8	2513.2	2513.2	2509.8	2509.8	2509.8
7.5°	2479.1	2482.5	2479.1	2482.5	2482.5	2482.5	2479.1	2479.1
10°	2441.6	2441.6	2441.6	2441.6	2441.6	2438.2	2441.6	2441.6
12.5°	2390.5	2390.5	2390.5	2393.9	2393.9	2390.5	2390.5	2387.1
15°	2335.9	2329.1	2332.5	2335.9	2332.5	2332.5	2332.5	2332.5
17.5°	2260.8	2264.2	2260.8	2260.8	2260.8	2260.8	2264.2	2260.8
20°	2182.4	2182.4	2185.9	2182.4	2182.4	2182.4	2182.4	2179.0
22.5°	2093.8	2090.4	2090.4	2093.8	2093.8	2090.4	2093.8	2093.8
25°	1994.9	1998.3	1994.9	1994.9	1998.3	1998.3	1998.3	1994.9
27.5°	1889.1	1892.5	1896.0	1892.5	1892.5	1892.5	1896.0	1899.4
30°	1780.0	1786.8	1780.0	1780.0	1786.8	1783.4	1786.8	1786.8
32.5°	1664.1	1674.3	1667.5	1674.3	1674.3	1677.7	1674.3	1677.7
35°	1548.1	1558.3	1558.3	1558.3	1561.8	1565.3	1565.3	1561.8
37.5°	1439.0	1442.4	1442.4	1449.2	1452.6	1456.0	1456.0	1452.6
40°	1326.5	1333.3	1336.8	1336.8	1336.8	1343.6	1350.4	1343.6
42.5°	1217.3	1220.7	1224.3	1224.3	1231.1	1234.5	1237.9	1237.9
45°	1111.7	1118.5	1121.9	1125.3	1128.8	1135.6	1132.2	1139.0
47.5°	1002.6	1012.8	1016.2	1019.6	1026.4	1029.8	1033.3	1036.7
50°	903.7	910.5	910.5	917.3	927.5	927.5	934.3	937.8
52.5°	804.8	808.2	811.6	815.0	821.8	828.6	828.6	835.4
55°	709.3	712.7	712.7	716.1	719.5	733.1	736.5	736.5
57.5°	610.4	610.4	617.2	620.6	624.0	630.8	630.8	630.8
60°	514.9	518.3	518.3	521.8	525.2	532.0	535.4	532.0
62.5°	419.5	422.9	422.9	426.3	433.1	436.5	433.1	433.1
65°	330.8	334.2	334.2	337.6	344.4	344.4	341.0	344.4
67.5°	242.1	242.1	242.1	242.1	242.1	242.1	242.1	242.1
70°	153.4	150.0	146.6	150.0	150.0	150.0	146.6	153.4
72.5°	75.1	78.5	78.5	78.5	78.5	78.5	78.5	75.1
75°	34.1	34.1	30.7	30.7	30.7	34.1	34.1	30.7
77.5°	10.2	10.2	10.2	10.2	10.2	10.2	10.2	10.2
80°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



— 0°-180° - - 45°-225° - - - 90°-270°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)