

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P584679

Luminaire Tested: **HCC8S45D010BZ-HM82555835-81MDW**

Issue Date: 10/21/2021

Test Information

Test Method: LM-41-14
Report Number: P584679
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2109-368-6)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 10/21/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC8S45D010BZ-HM82555835-81MDW
Description: HALO COMMERCIAL 8" ROUND, NEW CONSTRUCTION FRAME, WITH 8" MEDIUM DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5048.6 lumens
Efficiency: N/A
Efficacy: 114.7 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.95
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 44
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P584679

CATALOG NUMBER: HCC8S45D010BZ-HM82555835-81MDW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



COOPER
Lighting Solutions

CATALOG NUMBER: HCC8S45D010BZ-HM82555835-81MDW

RF	20					20					20					20					20											
RC	80					70					50					30					10					0						
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		50	30	10		0					
RCR																																
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100					100				
1	112	108	105	102		109	106	103	100		102	99	97		98	96	94		94	93	92		90					90				
2	104	98	93	89		102	96	92	88		93	89	86		90	87	84		87	84	82		80					80				
3	98	89	83	78		95	88	82	78		85	80	76		83	78	75		80	77	74		72					72				
4	91	82	75	70		89	81	74	69		78	73	69		76	72	68		74	70	67		65					65				
5	86	76	68	63		84	75	68	63		73	67	62		71	66	62		69	65	61		59					59				
6	81	70	63	58		79	69	62	57		67	61	57		66	61	56		64	60	56		54					54				
7	76	65	58	53		74	64	57	53		63	57	52		62	56	52		60	55	52		50					50				
8	72	61	54	49		70	60	53	49		59	53	48		58	52	48		57	52	48		46					46				
9	68	57	50	45		67	56	50	45		55	49	45		54	49	45		53	48	45		43					43				
10	64	53	46	42		63	53	46	42		52	46	42		51	46	42		50	45	42		40					40				

	0°
0°	129090
5°	125575
10°	118168
15°	111881
20°	107621
25°	103464
30°	91890
35°	58522
40°	32662
45°	27356
50°	24696
55°	23279
60°	21234
65°	19153
70°	16896
75°	15024
80°	13318
85°	12065



TEST NUMBER: P584679

CATALOG NUMBER: HCC8S45D010BZ-HM82555835-81MDW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	378.2	7.5
10°-20°	988.4	19.6
20°-30°	1378.8	27.3
30°-40°	992.2	19.7
40°-50°	491.7	9.7
50°-60°	384.7	7.6
60°-70°	260.4	5.2
70°-80°	135.2	2.7
80°-90°	38.9	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2745.4	54.4
0°-40°	3737.6	74.0
0°-60°	4614.0	91.4
0°-90°	5048.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5048.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4186	
5°	4057	378
15°	3505	988
25°	3041	1379
35°	1555	992
45°	627	492
55°	433	385
65°	262	260
75°	126	135
85°	34	39
90°	0	



TEST NUMBER: P584679

CATALOG NUMBER: HCC8S45D010BZ-HM82555835-81MDW

CANDELA DISTRIBUTION (FULL):

	0°
0°	4186.3
2.5°	4148.9
5°	4056.8
7.5°	3927.3
10°	3773.9
12.5°	3630.7
15°	3504.6
17.5°	3385.3
20°	3279.6
22.5°	3173.9
25°	3040.9
27.5°	2850.0
30°	2580.7
32.5°	2158.0
35°	1554.6
37.5°	1060.3
40°	811.4
42.5°	698.9
45°	627.3
47.5°	565.9
50°	514.8
52.5°	470.5
55°	433.0
57.5°	388.6
60°	344.3
62.5°	300.1
65°	262.5
67.5°	225.0
70°	187.4
72.5°	156.8
75°	126.1
77.5°	98.9
80°	75.0
82.5°	54.5
85°	34.1
87.5°	17.0
90°	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)