

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P990609

Luminaire Tested: **ML2ALSFL9FS1E-TIR1D40FL-TL2RDSL-550LM-3500K**

Issue Date: 5/13/2025

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
Report Number: P990609
Test Lab: Cooper Lighting Solutions
Issue Date: 5/13/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: ML2ALSFL9FS1E-TIR1D40FL-TL2RDSL-550LM-3500K
Description: 2IN ROUND ML FLEX ADJUSTABLE, SELECTABLE CCT, WITH 40D TIR, METALLIC SILVER TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 549.7 lumens
Efficiency: N/A
Efficacy: 72.3 lumens/watt
Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.69
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P990609
CATALOG NUMBER: ML2ALSFL9FS1E-TIR1D40FL-TL2RDSL-550LM-3500K

Luminous Intensity Polar Plot



TEST NUMBER: P990609

CATALOG NUMBER: ML2ALSFL9FS1E-TIR1D40FL-TL2RDSL-550LM-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	100	98		97
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93
3	103	96	92	88	101	95	91	87	92	89	86		90	87	84		88
4	98	90	85	81	96	89	84	80	87	83	79		85	82	79		83
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79
6	89	80	74	70	87	79	74	70	78	73	70		77	72	69		75
7	85	76	70	66	83	75	70	66	74	69	65		73	68	65		72
8	81	72	66	62	80	71	66	62	70	65	62		69	65	61		68
9	77	68	63	59	76	68	62	59	67	62	58		66	61	58		65
10	74	65	59	56	73	65	59	56	64	59	55		63	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	444584
5°	431375
10°	390622
15°	326953
20°	252598
25°	181225
30°	121746
35°	77637
40°	47725
45°	29235
50°	18959
55°	12903
60°	9572
65°	7472
70°	6203
75°	4003
80°	3125
85°	0

TEST NUMBER: P990609
 CATALOG NUMBER: ML2ALSFL9FS1E-TIR1D40FL-TL2RDSL-550LM-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.2	14.6
10°-20°	176.0	32.0
20°-30°	153.1	27.9
30°-40°	82.8	15.1
40°-50°	34.2	6.2
50°-60°	14.1	2.6
60°-70°	6.8	1.2
70°-80°	2.4	0.4
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	409.4	74.5
0°-40°	492.2	89.5
0°-60°	540.4	98.3
0°-90°	549.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	549.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	901	
5°	871	80
15°	640	176
25°	333	153
35°	129	83
45°	42	34
55°	15	14
65°	6	7
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P990609

CATALOG NUMBER: ML2ALSFL9FS1E-TIR1D40FL-TL2RDSL-550LM-3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	901.1
2.5°	894.6
5°	871.0
7.5°	832.3
10°	779.7
12.5°	714.2
15°	640.1
17.5°	560.6
20°	481.1
22.5°	403.8
25°	332.9
27.5°	270.6
30°	213.7
32.5°	167.5
35°	128.9
37.5°	97.7
40°	74.1
42.5°	55.8
45°	41.9
47.5°	32.2
50°	24.7
52.5°	19.3
55°	15.0
57.5°	11.8
60°	9.7
62.5°	8.6
65°	6.4
67.5°	5.4
70°	4.3
72.5°	3.2
75°	2.1
77.5°	1.1
80°	1.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)