

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P990694

Luminaire Tested: **ML2ALSFLD2W1E-TIR1D55WFL-TL2RDSL-400LM-2700K**

Issue Date: 5/13/2025

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
Report Number: P990694
Test Lab: Cooper Lighting Solutions
Issue Date: 5/13/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: ML2ALSFLD2W1E-TIR1D55WFL-TL2RDSL-400LM-2700K
Description: 2IN ROUND ML FLEX ADJUSTABLE, SELECTABLE CCT, WITH 55D TIR, METALLIC SILVER TRIM
Light Source: (1) D2W LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 402.9 lumens
Efficiency: N/A
Efficacy: 66.1 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 6.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P990694
CATALOG NUMBER: ML2ALSFLD2W1E-TIR1D55WFL-TL2RDSL-400LM-2700K

Luminous Intensity Polar Plot



TEST NUMBER: P990694

CATALOG NUMBER: ML2ALSFLD2W1E-TIR1D55WFL-TL2RDSL-400LM-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	85	91	87	84		89	85	83		86
4	96	89	83	79	95	88	82	78	85	81	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	72		78	74	71		77
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73
7	83	73	67	63	81	72	67	62	71	66	62		70	65	62		69
8	78	69	63	59	77	68	62	58	67	62	58		66	61	58		65
9	75	65	59	55	74	64	59	55	64	58	55		63	58	54		62
10	71	62	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	240227
5°	237182
10°	226648
15°	208553
20°	181140
25°	145405
30°	105111
35°	70048
40°	43925
45°	26305
50°	16042
55°	11010
60°	7894
65°	6538
70°	4616
75°	3050
80°	0
85°	0

TEST NUMBER: P990694

CATALOG NUMBER: ML2ALSFLD2W1E-TIR1D55WFL-TL2RDSL-400LM-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.9	11.1
10°-20°	113.2	28.1
20°-30°	120.9	30.0
30°-40°	74.1	18.4
40°-50°	30.8	7.6
50°-60°	11.9	3.0
60°-70°	5.5	1.4
70°-80°	1.7	0.4
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	278.9	69.2
0°-40°	353.0	87.6
0°-60°	395.7	98.2
0°-90°	402.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	402.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	487	
5°	479	45
15°	408	113
25°	267	121
35°	116	74
45°	38	31
55°	13	12
65°	6	6
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P990694
 CATALOG NUMBER: ML2ALSFLD2W1E-TIR1D55WFL-TL2RDSL-400LM-2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	486.9
2.5°	485.3
5°	478.9
7.5°	467.7
10°	452.4
12.5°	433.2
15°	408.3
17.5°	378.6
20°	345.0
22.5°	307.2
25°	267.1
27.5°	224.6
30°	184.5
32.5°	148.4
35°	116.3
37.5°	89.8
40°	68.2
42.5°	51.3
45°	37.7
47.5°	28.1
50°	20.9
52.5°	16.0
55°	12.8
57.5°	10.4
60°	8.0
62.5°	6.4
65°	5.6
67.5°	4.8
70°	3.2
72.5°	2.4
75°	1.6
77.5°	0.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)