

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P601170

Luminaire Tested: **ML406AWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 5000K**

Issue Date: 7/29/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P601170
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 7/29/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: ML406AWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 5000K
 Description: RETROFIT, 25D WW OPTIC, OPEN TRIM
 Light Source: (1) SELECTABLE LUMEN LED 90CRI / 5000K CCT
 Ballast/Driver: -

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 548.7 lumens
 Efficiency: N/A
 Efficacy: 66.1 lumens/watt
 Spacing Criteria (0/90/45): 1.31 / 0.61 / 0.81
 Luminous Opening: Circular (Dia: 0.21' x H: 0')
 CIE Type: Direct


Input Watts (W): 8.3
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



Meas		Calibration Due Date	
Instrument	Identificatio		
Photometer	GONIO 1 11111111	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P601170
CATALOG NUMBER: ML406AWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 5000K

Luminous Intensity Polar Plot



TEST NUMBER: P601170
 CATALOG NUMBER: ML406AWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	93	93	
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85	85	85	85	
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	78	78	78	78	
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72	
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66	
6	85	75	69	64	83	75	68	64	73	68	64	72	67	63	70	66	63	61	61	61	61	
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57	57	57	57	
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53	53	53	53	
9	72	62	56	51	71	61	55	51	60	55	51	60	54	51	59	54	51	49	49	49	49	
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46	46	46	46	

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	173229	173229	173229
5°	223782	167900	128849
10°	288060	143036	85353
15°	346911	113763	62929
20°	391643	87637	45633
25°	412655	64874	34144
30°	380366	46233	27528
35°	298823	31185	23938
40°	222053	18920	21146
45°	143390	12861	18889
50°	83954	9285	16801
55°	44537	6441	14864
60°	18756	3410	13073
65°	6724	2690	10087
70°	831	1662	5816
75°	1098	1098	0
80°	0	0	0
85°	0	0	0

TEST NUMBER: P601170
 CATALOG NUMBER: ML406AWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.6	9.2
10°-20°	130.9	23.9
20°-30°	160.0	29.2
30°-40°	119.8	21.8
40°-50°	59.4	10.8
50°-60°	21.9	4.0
60°-70°	5.4	1.0
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	341.5	62.2
0°-40°	461.3	84.1
0°-60°	542.5	98.9
0°-90°	548.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	548.7	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	549	549	549	549	549	
5°	706	635	530	434	406	74
15°	1061	667	348	211	192	302
25°	1184	476	186	94	98	531
35°	775	228	81	43	62	489
45°	321	75	29	24	42	256
55°	81	21	12	10	27	77
65°	9	3	4	4	14	11
75°	1	1	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P601170
 CATALOG NUMBER: ML406AWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	45°	67.5°	90°	112.5°	135°
0°	548.6	548.6	548.6	548.6	548.6	548.6	548.6	548.6	548.6	548.6	548.6
2.5°	617.8	617.8	625.0	613.3	613.3	609.7	583.7	568.4	551.3	526.1	496.4
5°	706.0	724.0	709.6	689.8	701.5	696.1	634.9	579.2	529.7	481.1	434.4
7.5°	819.3	823.8	811.2	786.0	780.6	777.0	671.8	580.1	493.7	420.9	366.9
10°	898.4	904.7	899.3	890.3	859.8	852.6	683.5	545.9	446.1	368.7	304.0
12.5°	1000.0	998.3	990.2	964.1	929.0	919.1	676.3	515.3	395.7	310.3	249.1
15°	1061.2	1072.0	1060.3	991.1	974.9	949.7	667.3	473.9	348.0	268.9	211.3
17.5°	1114.3	1109.8	1087.3	1043.2	1001.8	979.4	632.2	413.7	305.8	223.9	174.5
20°	1165.5	1166.4	1131.4	1077.4	1010.8	970.4	580.1	372.3	260.8	184.4	144.8
22.5°	1188.9	1187.1	1142.1	1062.1	984.8	943.4	530.6	325.6	218.5	149.3	116.0
25°	1184.4	1152.0	1122.4	1027.9	940.7	890.3	475.7	285.1	186.2	125.9	93.5
27.5°	1126.9	1110.7	1060.3	965.9	865.2	813.9	407.4	243.7	155.6	98.9	76.4
30°	1043.2	1024.3	964.1	885.8	753.6	713.2	347.1	199.7	126.8	84.5	63.0
32.5°	919.1	904.7	842.7	740.1	636.7	590.9	287.8	159.2	102.5	62.1	51.3
35°	775.2	774.3	719.5	635.8	527.9	481.1	228.4	127.7	80.9	49.5	43.2
37.5°	665.5	642.1	588.2	510.8	420.0	381.3	179.0	99.8	60.3	38.7	36.0
40°	538.7	528.8	472.1	406.5	326.5	297.7	132.2	74.6	45.9	31.5	32.4
42.5°	433.5	420.0	373.2	309.4	252.7	229.3	100.7	57.6	36.0	27.0	28.8
45°	321.1	314.8	287.8	230.2	187.1	170.9	74.6	45.0	28.8	22.5	24.3
47.5°	233.8	226.6	207.7	170.9	135.8	125.9	57.6	35.1	23.4	18.0	18.9
50°	170.9	166.4	153.8	124.1	99.8	91.7	43.2	27.0	18.9	14.4	16.2
52.5°	117.8	119.6	108.8	88.1	71.0	65.7	32.4	19.8	15.3	11.7	13.5
55°	80.9	79.1	74.6	57.6	45.9	42.3	20.7	13.5	11.7	9.0	9.9
57.5°	49.5	49.5	45.9	36.0	28.8	27.0	12.6	9.0	8.1	6.3	8.1
60°	29.7	29.7	25.2	20.7	17.1	15.3	7.2	5.4	5.4	4.5	6.3
62.5°	16.2	16.2	14.4	11.7	9.0	8.1	4.5	4.5	3.6	3.6	5.4
65°	9.0	8.1	7.2	5.4	4.5	4.5	2.7	3.6	3.6	3.6	3.6
67.5°	3.6	3.6	3.6	2.7	2.7	2.7	1.8	2.7	2.7	2.7	2.7
70°	0.9	1.8	1.8	1.8	0.9	0.9	1.8	1.8	1.8	1.8	1.8
72.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
75°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.9	0.9	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P601170
 CATALOG NUMBER: ML406AWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 5000K

CANDELA DISTRIBUTION (continued):

	157.5°	180°
0°	548.6	548.6
2.5°	497.3	489.2
5°	416.4	406.5
7.5°	331.0	324.7
10°	270.7	266.2
12.5°	228.4	225.7
15°	193.4	192.5
17.5°	162.8	160.1
20°	133.1	135.8
22.5°	109.7	107.9
25°	92.6	98.0
27.5°	79.1	86.3
30°	69.2	75.5
32.5°	59.4	69.2
35°	52.2	62.1
37.5°	46.8	55.8
40°	43.2	51.3
42.5°	37.8	47.7
45°	33.3	42.3
47.5°	28.8	37.8
50°	26.1	34.2
52.5°	22.5	30.6
55°	18.9	27.0
57.5°	17.1	24.3
60°	14.4	20.7
62.5°	10.8	17.1
65°	8.1	13.5
67.5°	5.4	9.9
70°	2.7	6.3
72.5°	0.9	1.8
75°	0.0	0.0
77.5°	0.0	0.0
80°	0.0	0.0
82.5°	0.0	0.0
85°	0.0	0.0
87.5°	0.0	0.0
90°	0.0	0.0

(END OF REPORT)