

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P990728

Luminaire Tested: **ML3ALSFL9FS1E-TIR4D25NFL-TL3SDMB-750LM-3000K**

Issue Date: 5/13/2025

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
Report Number: P990728
Test Lab: Cooper Lighting Solutions
Issue Date: 5/13/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: ML3ALSFL9FS1E-TIR4D25NFL-TL3SDMB-750LM-3000K
Description: 3IN SQUARE ML FLEX ADJUSTABLE, SELECTABLE CCT, WITH 25D TIR, MATTE BLACK TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 681.1 lumens
Efficiency: N/A
Efficacy: 70.2 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.5 / 0.54
Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P990728
CATALOG NUMBER: ML3ALSFL9FS1E-TIR4D25NFL-TL3SDMB-750LM-3000K

Luminous Intensity Polar Plot



TEST NUMBER: P990728

CATALOG NUMBER: ML3ALSFL9FS1E-TIR4D25NFL-TL3SDMB-750LM-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	99	94	90	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	84	98	92	87	84	90	86	83		88	85	82		86
5	96	88	83	79	94	87	82	79	86	81	78		84	80	77		82
6	92	84	79	75	90	83	78	74	82	77	74		80	76	74		79
7	88	80	75	71	87	79	74	71	78	74	70		77	73	70		76
8	85	76	71	67	83	76	71	67	75	70	67		74	70	67		73
9	81	73	68	64	80	72	68	64	72	67	64		71	67	64		70
10	78	70	65	61	78	70	65	61	69	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	300632	300632	300632
5°	276159	275623	276695
10°	220191	220558	218757
15°	156171	157259	157437
20°	103771	106025	105640
25°	65445	68353	68353
30°	40250	42478	43094
35°	24704	26218	26638
40°	14928	16322	15850
45°	8963	10205	9450
50°	5466	6859	5761
55°	3363	4294	3693
60°	2480	3169	2480
65°	1671	2078	2078
70°	1561	1561	1561
75°	665	1331	665
80°	0	0	0
85°	0	0	0

TEST NUMBER: P990728

CATALOG NUMBER: ML3ALSFL9FS1E-TIR4D25NFL-TL3SDMB-750LM-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.5	20.8
10°-20°	242.0	35.5
20°-30°	166.2	24.4
30°-40°	80.1	11.8
40°-50°	32.3	4.7
50°-60°	12.3	1.8
60°-70°	5.1	0.8
70°-80°	1.6	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	549.7	80.7
0°-40°	629.8	92.5
0°-60°	674.4	99.0
0°-90°	681.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	681.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1746	1746	1746	1746	1746	
5°	1597	1599	1594	1602	1600	142
15°	876	875	882	884	883	240
25°	344	350	360	363	360	161
35°	118	119	125	129	127	76
45°	37	39	42	41	39	30
55°	11	12	14	13	12	11
65°	4	5	5	5	5	4
75°	1	1	2	1	1	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P990728

CATALOG NUMBER: ML3ALSFL9FS1E-TIR4D25NFL-TL3SDMB-750LM-3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1745.6	1745.6	1745.6	1745.6	1745.6
1°	1736.4	1736.4	1737.4	1736.4	1740.5
2°	1714.9	1715.9	1719.0	1719.0	1719.0
3°	1686.3	1685.3	1687.3	1690.4	1692.4
4°	1644.4	1643.4	1651.6	1649.5	1651.6
5°	1597.4	1599.4	1594.3	1602.5	1600.5
6°	1544.3	1541.2	1539.1	1545.3	1542.2
7°	1477.8	1480.9	1477.8	1485.0	1472.7
8°	1411.4	1409.3	1405.3	1407.3	1410.4
9°	1339.9	1337.8	1333.7	1333.7	1336.8
10°	1259.1	1255.0	1261.2	1256.0	1250.9
11°	1178.4	1175.3	1181.4	1177.4	1180.4
12°	1095.6	1100.7	1102.7	1101.7	1103.8
13°	1013.8	1023.0	1023.0	1025.1	1022.0
14°	943.3	950.5	950.5	952.5	955.6
15°	875.9	874.8	882.0	884.0	883.0
16°	799.2	805.3	813.5	814.5	813.5
17°	732.8	738.9	752.2	751.2	748.1
18°	672.5	678.6	686.8	684.7	682.7
19°	613.2	617.3	629.6	631.6	625.5
20°	566.2	566.2	578.5	576.4	576.4
22.5°	442.5	446.6	457.9	459.9	457.9
25°	344.4	350.5	359.7	362.8	359.7
27.5°	265.7	268.8	279.0	281.1	282.1
30°	202.4	204.4	213.6	220.8	216.7
32.5°	153.3	157.4	164.5	168.6	167.6
35°	117.5	118.6	124.7	128.8	126.7
37.5°	87.9	91.0	95.0	97.1	94.0
40°	66.4	67.5	72.6	72.6	70.5
42.5°	49.1	51.1	55.2	55.2	52.1
45°	36.8	38.8	41.9	40.9	38.8
47.5°	26.6	29.6	31.7	30.7	28.6
50°	20.4	21.5	25.6	23.5	21.5
52.5°	15.3	16.4	19.4	17.4	16.4
55°	11.2	12.3	14.3	13.3	12.3
57.5°	8.2	9.2	11.2	10.2	9.2
60°	7.2	7.2	9.2	8.2	7.2
62.5°	5.1	6.1	7.2	6.1	6.1
65°	4.1	5.1	5.1	5.1	5.1
67.5°	3.1	4.1	4.1	4.1	4.1
70°	3.1	3.1	3.1	3.1	3.1
72.5°	2.0	2.0	3.1	2.0	2.0
75°	1.0	1.0	2.0	1.0	1.0
77.5°	0.0	1.0	1.0	1.0	1.0
80°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P990728
CATALOG NUMBER: ML3ALSFL9FS1E-TIR4D25NFL-TL3SDMB-750LM-3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)