

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P990869

Luminaire Tested: **ML4ALSFL9FS1E-TIR4D25NFL-TL4RDMW-1000LM-3500K**

Issue Date: 5/13/2025

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P990869
 Test Lab: Cooper Lighting Solutions
 Issue Date: 5/13/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: ML4ALSFL9FS1E-TIR4D25NFL-TL4RDMW-1000LM-3500K
 Description: 4IN ROUND ML FLEX ADJUSTABLE, SELECTABLE CCT, WITH 25D TIR, MATTE WHITE TRIM
 Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 877.8 lumens
 Efficiency: N/A
 Efficacy: 67.5 lumens/watt
 Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.56
 Luminous Opening: Circular (Dia: 0.33' x H: 0')
 CIE Type: Direct

Input Watts (W): 13
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P990869
CATALOG NUMBER: ML4ALSFL9FS1E-TIR4D25NFL-TL4RDMW-1000LM-3500K

Luminous Intensity Polar Plot



TEST NUMBER: P990869

CATALOG NUMBER: ML4ALSFL9FS1E-TIR4D25NFL-TL4RDMW-1000LM-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	114	111	109	107	111	109	107	105		105	103	102			101	100	99			94
2	109	104	100	97	106	102	99	96		99	96	94			96	94	92			88
3	104	98	93	89	102	96	92	88		94	90	87			91	88	86			83
4	99	92	87	83	97	91	86	82		89	85	81			87	83	81			78
5	95	87	82	78	93	86	81	77		84	80	77			83	79	76			74
6	91	82	77	73	89	82	77	73		80	76	72			79	75	72			70
7	87	78	73	69	86	78	73	69		77	72	69			75	71	68			67
8	83	75	69	66	82	74	69	65		73	68	65			72	68	65			63
9	80	71	66	62	79	71	66	62		70	65	62			69	65	62			61
10	77	68	63	60	76	68	63	60		67	63	59			66	62	59			58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	252933
5°	234732
10°	191843
15°	141194
20°	97081
25°	63312
30°	39524
35°	24228
40°	14942
45°	9542
50°	6524
55°	4882
60°	4070
65°	3619
70°	3354
75°	2478
80°	710
85°	0

TEST NUMBER: P990869
 CATALOG NUMBER: ML4ALSFL9FS1E-TIR4D25NFL-TL4RDMW-1000LM-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.0	19.3
10°-20°	304.4	34.7
20°-30°	216.6	24.7
30°-40°	104.6	11.9
40°-50°	44.2	5.0
50°-60°	21.0	2.4
60°-70°	12.4	1.4
70°-80°	5.2	0.6
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	690.0	78.6
0°-40°	794.6	90.5
0°-60°	859.8	98.0
0°-90°	877.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	877.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2051	
5°	1896	169
15°	1106	304
25°	465	217
35°	161	105
45°	55	44
55°	23	21
65°	12	12
75°	5	5
85°	0	0
90°	0	

TEST NUMBER: P990869
CATALOG NUMBER: ML4ALSFL9FS1E-TIR4D25NFL-TL4RDMW-1000LM-3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2050.6
1°	2042.3
2°	2022.7
3°	1989.7
4°	1946.4
5°	1895.8
6°	1833.9
7°	1766.9
8°	1689.5
9°	1613.2
10°	1531.7
11°	1444.1
12°	1357.4
13°	1273.9
14°	1189.3
15°	1105.7
16°	1026.3
17°	950.0
18°	877.8
19°	806.6
20°	739.6
22.5°	591.0
25°	465.2
27.5°	361.0
30°	277.5
32.5°	211.5
35°	160.9
37.5°	122.7
40°	92.8
42.5°	71.2
45°	54.7
47.5°	42.3
50°	34.0
52.5°	26.8
55°	22.7
57.5°	19.6
60°	16.5
62.5°	14.4
65°	12.4
67.5°	10.3
70°	9.3
72.5°	7.2
75°	5.2
77.5°	2.1
80°	1.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



TEST NUMBER: P990869
CATALOG NUMBER: ML4ALSFL9FS1E-TIR4D25NFL-TL4RDMW-1000LM-3500K

CANDELA DISTRIBUTION (continued):

	0°
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)