

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P997175

Luminaire Tested: **SMX4SLSFSD2W-650LM-5000K**

Issue Date: 3/11/2025



Test Information

Test Method: LM-41-14
Report Number: P997175
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (A2410456A001)
Test Lab:
Issue Date: 3/11/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: SMX4SLSFSD2W-650LM-5000K
Description: 4IN SQAURE, 90CRI, DIMMING TO 10%, DAMP LOCATION
Light Source: SELECTABLE CCT 90CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 673.5 lumens
Efficiency: N/A
Efficacy: 97.6 lumens/watt
Spacing Criteria (0/90/45): 1.25 / 1.25 / 1.37
Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 6.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P997175

CATALOG NUMBER: SMX4SLSFSD2W-650LM-5000K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997175

CATALOG NUMBER: SMX4SLSFSD2W-650LM-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	84		
2	99	91	84	78	96	89	83	77	85	80	76	82	78	74	79	76	72	70		
3	90	80	72	65	88	78	71	65	75	69	63	72	67	62	70	65	61	59		
4	83	71	62	55	80	69	61	55	67	60	54	64	58	53	62	57	53	50		
5	76	63	54	48	74	62	54	47	60	52	47	58	51	46	56	50	46	44		
6	70	57	48	41	68	56	47	41	54	47	41	52	46	41	51	45	40	38		
7	65	52	43	37	63	51	42	36	49	42	36	48	41	36	46	40	36	34		
8	61	47	38	33	59	46	38	33	45	38	32	44	37	32	43	36	32	30		
9	57	43	35	29	55	43	35	29	41	34	29	40	34	29	39	33	29	27		
10	53	40	32	27	52	39	32	27	38	31	26	37	31	26	36	30	26	24		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23801	23801	23801	23801
5°	23813	23773	23793	23763
10°	23757	23697	23717	23687
15°	23658	23587	23597	23587
20°	23541	23446	23435	23446
25°	23361	23252	23230	23263
30°	23146	23032	22998	23043
35°	22890	22781	22733	22781
40°	22619	22490	22425	22477
45°	22282	22142	22072	22128
50°	21866	21712	21636	21697
55°	21351	21196	21110	21162
60°	20658	20500	20421	20460
65°	19716	19576	19459	19506
70°	18351	18207	18091	18120
75°	16269	16192	16078	16040
80°	13092	13035	12921	12807
85°	8279	8279	8392	7939

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997175

CATALOG NUMBER: SMX4SLSFSD2W-650LM-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	22.8	3.4
10°-20°	65.1	9.7
20°-30°	98.4	14.6
30°-40°	118.2	17.5
40°-50°	122.2	18.1
50°-60°	109.9	16.3
60°-70°	82.7	12.3
70°-80°	44.8	6.6
80°-90°	9.5	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	186.2	27.7
0°-40°	304.4	45.2
0°-60°	536.5	79.7
0°-90°	673.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	673.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	241	241	241	241	241	
5°	240	240	240	240	240	23
15°	231	230	231	230	231	65
25°	214	213	213	213	214	99
35°	190	189	188	189	190	119
45°	159	158	158	158	159	123
55°	124	123	122	123	124	111
65°	84	84	83	83	84	83
75°	43	42	42	42	43	45
85°	7	7	7	7	7	10
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997175

CATALOG NUMBER: SMX4SLSFSD2W-650LM-5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	240.8	240.8	240.8	240.8	240.8	240.8	240.8	240.8	240.8	240.8	240.8
0.5°	241.3	241.0	240.9	240.7	240.5	240.6	240.9	240.9	241.0	241.0	240.9
1°	241.0	241.1	240.7	240.8	240.6	240.6	240.7	240.9	240.9	241.0	240.7
1.5°	241.1	240.8	240.9	240.6	240.5	240.5	240.8	240.7	241.1	240.8	240.7
2°	241.0	241.0	240.6	240.6	240.2	240.5	240.6	240.6	240.8	240.9	240.6
2.5°	240.8	240.7	240.5	240.1	240.3	240.3	240.5	240.5	240.9	240.7	240.3
3°	240.9	240.7	240.5	240.4	240.2	240.3	240.3	240.4	240.5	240.7	240.3
3.5°	240.8	240.7	240.2	240.1	240.0	240.0	240.2	240.3	240.5	240.5	240.2
4°	240.4	240.4	240.1	239.9	239.9	239.9	239.9	240.0	240.1	240.2	240.0
4.5°	240.3	240.2	239.9	239.7	239.5	239.7	239.9	239.8	240.2	240.1	239.9
5°	240.0	240.0	239.7	239.5	239.6	239.6	239.4	239.7	239.8	239.8	239.6
5.5°	240.0	239.8	239.5	239.4	239.1	239.1	239.5	239.2	239.5	239.6	239.3
6°	239.6	239.6	239.3	239.2	238.9	239.0	239.0	239.1	239.3	239.4	239.2
6.5°	239.4	239.2	238.9	238.7	238.6	238.6	238.9	238.7	239.1	239.1	238.8
7°	238.9	238.9	238.6	238.4	238.5	238.4	238.3	238.6	238.7	238.8	238.6
7.5°	238.9	238.6	238.3	238.0	238.1	237.9	238.2	238.1	238.4	238.3	238.3
8°	238.4	238.3	238.1	237.8	237.6	237.8	237.8	237.8	238.0	238.1	237.8
8.5°	238.2	237.9	237.5	237.2	237.4	237.0	237.3	237.3	237.7	237.5	237.5
9°	237.5	237.5	237.2	237.1	236.8	237.0	236.9	237.0	237.1	237.5	237.0
9.5°	237.3	237.2	236.8	236.4	236.6	236.5	236.6	236.5	236.8	236.7	236.7
10°	236.7	236.8	236.4	236.1	236.1	236.0	235.9	236.0	236.3	236.4	236.2
10.5°	236.4	236.2	235.9	235.5	235.6	235.5	235.8	235.5	235.9	236.0	235.9
11°	235.9	235.8	235.4	235.2	235.1	235.2	234.8	235.2	235.3	235.3	235.1
11.5°	235.5	235.2	234.9	234.7	234.6	234.5	234.6	234.5	234.9	235.0	234.8
12°	234.9	234.7	234.2	234.1	234.1	234.1	234.0	234.0	234.2	234.2	234.1
12.5°	234.3	234.2	233.9	233.6	233.5	233.4	233.4	233.4	233.8	233.8	233.7
13°	233.8	233.6	233.3	232.9	233.0	232.9	232.9	232.8	233.1	233.1	233.1
13.5°	233.3	233.0	232.7	232.3	232.4	232.2	232.4	232.2	232.6	232.7	232.6
14°	232.5	232.4	232.1	231.9	231.8	231.8	231.5	231.7	231.9	232.0	231.9
14.5°	232.2	231.7	231.6	231.0	231.2	231.0	231.2	231.0	231.2	231.3	231.2
15°	231.2	231.3	230.9	230.5	230.5	230.5	230.3	230.4	230.6	230.8	230.8
15.5°	230.6	230.4	230.1	229.7	229.7	229.7	229.8	229.7	229.8	229.9	230.0
16°	230.1	230.0	229.5	229.2	229.2	229.1	228.9	228.9	229.1	229.4	229.3
16.5°	229.4	229.0	228.7	228.3	228.3	228.2	228.3	228.2	228.5	228.7	228.6
17°	228.5	228.4	228.0	227.7	227.8	227.6	227.7	227.5	227.7	227.8	227.8
17.5°	227.8	227.7	227.3	226.7	226.9	226.7	226.8	226.6	227.0	227.1	227.1
18°	226.9	226.9	226.5	226.2	226.2	226.0	226.0	226.0	226.1	226.3	226.3
18.5°	226.3	226.0	225.6	225.2	225.3	225.2	225.3	225.0	225.3	225.6	225.5
19°	225.4	225.4	224.9	224.5	224.5	224.4	224.2	224.5	224.6	224.8	224.7
19.5°	224.6	224.3	224.0	223.5	223.8	223.6	223.7	223.4	223.6	223.8	223.9
20°	223.8	223.7	223.2	222.9	222.9	222.7	222.7	222.6	222.8	223.0	223.1
20.5°	223.0	222.7	222.2	221.9	221.8	221.8	221.7	221.6	222.0	222.2	222.2
21°	222.1	221.8	221.4	221.0	221.0	220.9	220.9	220.8	221.0	221.2	221.2

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997175

CATALOG NUMBER: SMX4SLSFSD2W-650LM-5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
22.5°	219.4	219.0	218.6	218.2	218.2	218.1	218.0	217.9	218.2	218.3	218.4
23°	218.3	218.0	217.7	217.2	217.4	217.2	217.0	217.0	217.2	217.4	217.6
23.5°	217.3	217.0	216.7	216.2	216.2	216.1	216.1	216.0	216.2	216.4	216.5
24°	216.4	216.1	215.6	215.3	215.4	215.1	215.0	214.9	215.1	215.4	215.5
24.5°	215.3	215.1	214.7	214.0	214.3	213.9	214.0	214.0	214.3	214.3	214.5
25°	214.2	214.0	213.6	213.3	213.2	213.0	212.9	212.9	213.0	213.3	213.4
25.5°	213.3	212.8	212.5	211.9	212.1	211.9	212.0	211.8	212.0	212.3	212.3
26°	212.0	211.9	211.5	211.1	211.2	210.8	210.7	210.8	210.9	211.1	211.3
26.5°	211.1	210.8	210.3	209.8	209.9	209.8	209.8	209.7	209.8	210.0	210.2
27°	209.9	209.7	209.2	208.7	208.8	208.7	208.6	208.5	208.7	208.9	209.0
27.5°	208.8	208.4	208.0	207.7	207.7	207.4	207.5	207.3	207.5	207.7	208.0
28°	207.5	207.4	206.9	206.4	206.6	206.5	206.2	206.1	206.4	206.5	206.8
28.5°	206.5	206.2	205.6	205.3	205.4	205.1	205.2	205.0	205.2	205.4	205.6
29°	205.3	205.1	204.6	204.1	204.1	203.9	203.9	203.9	204.0	204.2	204.3
29.5°	204.2	203.8	203.4	202.9	203.0	202.8	202.7	202.6	202.8	203.0	203.4
30°	202.8	202.6	202.2	201.6	201.8	201.6	201.5	201.4	201.5	201.8	201.9
30.5°	201.8	201.3	200.9	200.4	200.5	200.2	200.4	200.0	200.3	200.5	200.7
31°	200.3	200.1	199.7	199.2	199.3	199.1	199.0	198.8	199.1	199.4	199.4
31.5°	199.3	198.8	198.4	197.9	198.0	197.7	197.8	197.7	197.7	198.0	198.2
32°	197.8	197.5	197.1	196.6	196.8	196.4	196.3	196.3	196.5	196.9	197.0
32.5°	196.6	196.3	195.8	195.3	195.4	195.2	195.2	195.1	195.1	195.4	195.6
33°	195.3	194.9	194.5	193.9	194.2	193.9	193.8	193.6	193.9	194.1	194.4
33.5°	194.0	193.7	193.2	192.6	192.8	192.5	192.5	192.4	192.6	192.8	193.0
34°	192.6	192.3	191.7	191.2	191.5	191.1	191.1	191.0	191.1	191.3	191.6
34.5°	191.3	190.9	190.5	189.9	190.0	189.8	189.7	189.6	189.8	190.1	190.3
35°	189.7	189.7	189.0	188.6	188.8	188.4	188.4	188.3	188.4	188.7	188.8
35.5°	188.6	188.2	187.7	187.1	187.3	187.0	187.0	186.8	187.0	187.1	187.6
36°	187.0	186.8	186.3	185.8	186.1	185.8	185.6	185.5	185.7	186.0	186.0
36.5°	185.7	185.3	184.8	184.2	184.4	184.1	184.2	184.0	184.2	184.4	184.8
37°	184.2	184.0	183.4	182.9	183.2	182.8	182.7	182.6	182.8	183.1	183.2
37.5°	182.8	182.4	182.0	181.4	181.5	181.3	181.3	181.1	181.2	181.5	181.8
38°	181.3	181.1	180.5	180.0	180.3	180.0	179.9	179.7	179.9	180.2	180.4
38.5°	179.9	179.6	179.0	178.5	178.7	178.4	178.2	178.2	178.3	178.5	178.8
39°	178.2	178.1	177.5	177.0	177.3	176.9	176.8	176.8	176.8	177.2	177.5
39.5°	177.0	176.5	176.1	175.5	175.7	175.4	175.3	175.2	175.3	175.6	175.9
40°	175.3	175.1	174.4	173.9	174.3	173.9	173.7	173.6	173.8	174.1	174.4
40.5°	173.8	173.4	173.0	172.4	172.6	172.3	172.2	172.1	172.3	172.5	172.8
41°	172.3	172.0	171.3	170.9	171.2	170.8	170.8	170.6	170.7	171.0	171.3
41.5°	170.7	170.3	169.8	169.2	169.5	169.2	169.0	169.0	169.1	169.4	169.7
42°	169.1	169.0	168.3	167.8	168.1	167.7	167.6	167.5	167.6	167.8	168.2
42.5°	167.6	167.2	166.6	166.1	166.4	166.0	165.9	165.8	166.0	166.2	166.5
43°	165.8	165.6	165.1	164.6	164.8	164.6	164.4	164.3	164.5	164.7	165.1
43.5°	164.4	164.0	163.4	162.8	163.2	162.9	162.7	162.6	162.7	163.1	163.4

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997175

CATALOG NUMBER: SMX4SLSFSD2W-650LM-5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
45°	159.4	159.2	158.5	157.9	158.4	158.0	157.8	157.8	157.9	158.1	158.4
45.5°	157.8	157.3	156.9	156.3	156.6	156.2	156.1	156.1	156.1	156.5	156.8
46°	156.1	155.9	155.2	154.7	155.1	154.6	154.5	154.4	154.6	154.8	155.1
46.5°	154.4	154.0	153.5	152.9	153.3	153.0	152.8	152.7	152.9	153.2	153.4
47°	152.7	152.4	151.7	151.3	151.7	151.2	151.1	151.0	151.2	151.4	151.8
47.5°	151.0	150.6	150.2	149.5	150.0	149.5	149.3	149.3	149.4	149.7	150.0
48°	149.3	148.9	148.3	147.8	148.2	147.8	147.7	147.6	147.8	148.0	148.3
48.5°	147.6	147.2	146.7	146.1	146.5	146.0	145.9	145.9	146.0	146.2	146.5
49°	145.8	145.5	145.0	144.4	144.8	144.4	144.2	144.1	144.2	144.5	144.9
49.5°	144.0	143.7	143.1	142.6	142.9	142.6	142.5	142.4	142.5	142.7	143.0
50°	142.2	141.9	141.4	140.8	141.2	140.9	140.8	140.6	140.7	141.0	141.3
50.5°	140.5	140.2	139.6	139.0	139.3	139.0	138.9	138.9	138.9	139.2	139.6
51°	138.6	138.4	137.9	137.3	137.7	137.2	137.1	137.0	137.3	137.3	137.7
51.5°	136.9	136.6	135.9	135.3	135.7	135.5	135.2	135.3	135.3	135.7	136.0
52°	135.1	134.8	134.3	133.7	134.2	133.7	133.5	133.5	133.6	133.8	134.2
52.5°	133.3	132.9	132.3	131.7	132.1	131.9	131.6	131.7	131.7	132.1	132.4
53°	131.4	131.1	130.6	130.0	130.4	130.1	129.9	129.8	129.9	130.1	130.6
53.5°	129.5	129.2	128.6	128.0	128.5	128.2	127.9	128.0	128.0	128.3	128.6
54°	127.7	127.4	126.9	126.3	126.7	126.3	126.3	126.2	126.2	126.5	126.8
54.5°	125.8	125.5	124.9	124.2	124.8	124.4	124.3	124.3	124.3	124.5	125.0
55°	123.9	123.6	123.1	122.7	123.0	122.6	122.5	122.4	122.5	122.8	123.1
55.5°	122.1	121.7	121.2	120.5	121.0	120.7	120.6	120.4	120.5	120.9	121.2
56°	120.1	119.9	119.3	118.8	119.2	118.8	118.7	118.7	118.8	118.9	119.3
56.5°	118.2	117.9	117.4	116.8	117.3	117.0	116.7	116.7	116.8	117.1	117.5
57°	116.3	116.1	115.4	114.9	115.4	115.0	114.9	114.8	114.8	115.1	115.5
57.5°	114.3	114.1	113.5	112.9	113.5	113.1	112.9	112.9	113.0	113.3	113.6
58°	112.5	112.2	111.6	111.1	111.6	111.2	111.1	110.9	111.0	111.2	111.7
58.5°	110.4	110.2	109.6	109.1	109.5	109.2	109.1	109.0	109.1	109.4	109.8
59°	108.5	108.3	107.7	107.2	107.7	107.3	107.2	107.1	107.2	107.4	107.8
59.5°	106.5	106.2	105.7	105.2	105.7	105.4	105.2	105.1	105.1	105.5	105.9
60°	104.5	104.3	103.7	103.2	103.7	103.3	103.3	103.1	103.3	103.5	103.8
60.5°	102.5	102.3	101.8	101.2	101.8	101.4	101.3	101.2	101.2	101.6	101.9
61°	100.6	100.3	99.8	99.2	99.8	99.4	99.3	99.2	99.3	99.5	99.9
61.5°	98.6	98.4	97.8	97.2	97.7	97.5	97.3	97.2	97.3	97.6	98.0
62°	96.6	96.2	95.8	95.2	95.8	95.4	95.3	95.3	95.4	95.5	95.8
62.5°	94.5	94.3	93.7	93.2	93.8	93.5	93.3	93.2	93.2	93.6	94.0
63°	92.5	92.2	91.7	91.2	91.8	91.4	91.3	91.3	91.3	91.6	91.9
63.5°	90.5	90.2	89.7	89.1	89.7	89.4	89.3	89.1	89.2	89.5	89.9
64°	88.4	88.1	87.6	87.1	87.7	87.4	87.3	87.2	87.3	87.5	87.8
64.5°	86.4	86.1	85.6	85.1	85.7	85.3	85.2	85.1	85.2	85.5	85.9
65°	84.3	84.1	83.6	83.1	83.7	83.3	83.2	83.2	83.2	83.4	83.7
65.5°	82.3	82.0	81.5	81.0	81.6	81.3	81.1	81.1	81.1	81.4	81.8
66°	80.2	79.9	79.4	78.9	79.6	79.2	79.1	79.0	79.1	79.3	79.7

TEST NUMBER: P997175

CATALOG NUMBER: SMX4SLSFSD2W-650LM-5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
67.5°	74.0	73.7	73.2	72.8	73.4	73.1	72.9	72.8	72.9	73.1	73.5
68°	71.9	71.6	71.1	70.7	71.3	71.0	70.9	70.8	70.9	71.1	71.4
68.5°	69.8	69.5	69.1	68.5	69.2	68.9	68.8	68.8	68.7	69.0	69.4
69°	67.7	67.5	66.9	66.5	67.1	66.9	66.8	66.7	66.7	66.9	67.3
69.5°	65.5	65.3	64.8	64.4	65.1	64.8	64.7	64.6	64.7	65.0	65.2
70°	63.5	63.2	62.7	62.4	63.0	62.7	62.6	62.5	62.6	62.7	63.1
70.5°	61.4	61.2	60.7	60.2	60.9	60.6	60.5	60.4	60.5	60.8	61.1
71°	59.3	59.1	58.6	58.2	58.9	58.6	58.5	58.5	58.4	58.7	59.0
71.5°	57.2	57.0	56.5	56.1	56.8	56.5	56.4	56.3	56.4	56.6	56.9
72°	55.1	54.9	54.5	54.1	54.7	54.5	54.4	54.4	54.4	54.6	54.9
72.5°	53.0	52.8	52.3	51.9	52.7	52.4	52.4	52.3	52.3	52.5	52.8
73°	51.0	50.7	50.2	49.9	50.6	50.4	50.3	50.3	50.3	50.4	50.7
73.5°	48.8	48.7	48.2	47.8	48.5	48.3	48.3	48.2	48.2	48.4	48.6
74°	46.8	46.6	46.1	45.8	46.4	46.3	46.2	46.1	46.2	46.3	46.5
74.5°	44.7	44.5	44.1	43.7	44.4	44.2	44.1	44.0	44.1	44.3	44.6
75°	42.6	42.4	42.1	41.7	42.4	42.2	42.1	42.0	42.1	42.2	42.5
75.5°	40.6	40.4	40.0	39.6	40.4	40.1	40.1	40.0	40.0	40.2	40.6
76°	38.5	38.4	38.0	37.6	38.3	38.1	38.1	37.9	38.0	38.2	38.5
76.5°	36.5	36.3	36.0	35.6	36.3	36.1	36.1	35.9	36.0	36.2	36.5
77°	34.5	34.3	34.0	33.7	34.4	34.1	34.1	34.0	34.0	34.2	34.5
77.5°	32.6	32.4	32.1	31.7	32.4	32.2	32.1	32.0	32.1	32.3	32.6
78°	30.6	30.4	30.1	29.8	30.5	30.2	30.2	30.1	30.2	30.3	30.6
78.5°	28.6	28.5	28.2	27.8	28.5	28.3	28.2	28.2	28.2	28.4	28.6
79°	26.8	26.6	26.3	26.0	26.6	26.4	26.4	26.3	26.3	26.5	26.8
79.5°	24.8	24.7	24.4	24.1	24.7	24.6	24.5	24.4	24.5	24.7	24.9
80°	23.0	22.8	22.6	22.3	22.9	22.7	22.7	22.7	22.7	22.8	23.0
80.5°	21.3	21.1	20.9	20.6	21.1	20.9	20.9	20.8	20.8	21.0	21.3
81°	19.6	19.4	19.2	18.9	19.4	19.2	19.1	19.1	19.1	19.3	19.5
81.5°	17.9	17.7	17.5	17.2	17.6	17.5	17.4	17.3	17.4	17.6	17.8
82°	16.2	16.0	15.8	15.5	16.0	15.8	15.8	15.7	15.7	15.9	16.1
82.5°	14.5	14.3	14.1	13.9	14.3	14.2	14.1	14.1	14.1	14.3	14.5
83°	12.9	12.8	12.5	12.3	12.8	12.6	12.6	12.6	12.6	12.7	12.9
83.5°	11.4	11.3	11.0	10.8	11.3	11.2	11.1	11.1	11.1	11.3	11.4
84°	10.0	9.8	9.6	9.4	9.9	9.7	9.7	9.7	9.7	9.8	10.0
84.5°	8.6	8.5	8.3	8.1	8.5	8.4	8.4	8.3	8.4	8.5	8.7
85°	7.3	7.2	7.0	6.9	7.3	7.4	7.3	7.3	7.4	7.2	7.4
85.5°	6.1	6.1	5.9	5.7	6.3	6.4	6.2	6.2	6.4	6.3	6.4
86°	5.1	5.0	4.8	4.7	5.3	5.4	5.2	5.1	5.4	5.3	5.4
86.5°	4.0	4.0	3.9	3.7	4.3	4.4	4.1	4.1	4.4	4.4	4.5
87°	3.2	3.1	3.0	2.9	3.4	3.4	3.1	3.0	3.4	3.4	3.5
87.5°	2.4	2.4	2.3	2.2	2.4	2.3	2.3	2.3	2.4	2.4	2.5
88°	1.9	1.9	1.8	1.8	1.8	1.7	1.8	1.8	1.8	1.9	1.9
88.5°	1.4	1.4	1.4	1.3	1.3	1.2	1.3	1.3	1.3	1.4	1.4

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P997175
CATALOG NUMBER: SMX4SLSFSD2W-650LM-5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997175

CATALOG NUMBER: SMX4SLSFSD2W-650LM-5000K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	240.8	240.8	240.8	240.8	240.8	240.8
0.5°	240.7	240.4	240.6	240.8	240.9	241.3
1°	240.7	240.5	240.7	240.8	240.9	241.0
1.5°	240.6	240.4	240.5	240.8	240.8	241.1
2°	240.6	240.4	240.5	240.4	240.9	241.0
2.5°	240.5	240.2	240.3	240.7	240.7	240.8
3°	240.5	240.3	240.4	240.3	240.7	240.9
3.5°	240.2	239.8	240.1	240.3	240.3	240.8
4°	240.1	239.9	240.1	240.1	240.3	240.4
4.5°	239.7	239.5	239.7	240.0	240.1	240.3
5°	239.7	239.5	239.7	239.7	240.1	240.0
5.5°	239.4	239.2	239.1	239.6	239.6	240.0
6°	239.1	238.8	239.2	239.1	239.5	239.6
6.5°	238.9	238.7	238.8	239.0	239.2	239.4
7°	238.6	238.3	238.5	238.7	238.9	238.9
7.5°	238.2	237.9	238.2	238.4	238.5	238.9
8°	238.0	237.7	238.0	237.9	238.3	238.4
8.5°	237.6	237.3	237.4	237.9	237.7	238.2
9°	237.2	236.9	237.1	237.1	237.7	237.5
9.5°	236.7	236.5	236.6	236.9	237.0	237.3
10°	236.4	236.0	236.4	236.4	236.7	236.7
10.5°	235.9	235.4	235.6	236.1	236.2	236.4
11°	235.3	235.3	235.4	235.4	235.6	235.9
11.5°	235.0	234.4	234.8	235.0	235.3	235.5
12°	234.5	234.0	234.3	234.4	234.6	234.9
12.5°	233.9	233.5	233.6	234.1	234.2	234.3
13°	233.3	233.0	233.2	233.5	233.6	233.8
13.5°	232.7	232.3	232.5	232.8	233.1	233.3
14°	232.1	231.8	232.0	232.3	232.6	232.5
14.5°	231.5	231.1	231.2	231.6	231.8	232.2
15°	231.0	230.5	230.7	230.9	231.2	231.2
15.5°	230.1	229.8	230.0	230.4	230.6	230.6
16°	229.4	229.1	229.3	229.4	230.0	230.1
16.5°	228.7	228.5	228.6	229.1	229.1	229.4
17°	228.1	227.7	227.9	228.1	228.5	228.5
17.5°	227.3	226.9	227.1	227.4	227.7	227.8
18°	226.3	226.1	226.5	226.8	226.8	226.9
18.5°	225.8	225.4	225.6	225.9	226.2	226.3
19°	224.8	224.7	224.8	225.0	225.4	225.4
19.5°	224.1	223.7	223.9	224.3	224.6	224.6
20°	223.2	222.9	223.3	223.4	223.7	223.8
20.5°	222.2	222.0	222.1	222.7	222.9	223.0
21°	221.5	221.1	221.5	221.6	221.9	222.1

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997175

CATALOG NUMBER: SMX4SLSFSD2W-650LM-5000K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
22.5°	218.7	218.2	218.4	219.1	219.1	219.4
23°	217.6	217.4	217.8	217.8	218.3	218.3
23.5°	216.8	216.4	216.6	217.1	217.2	217.3
24°	215.7	215.4	215.6	216.0	216.3	216.4
24.5°	214.7	214.2	214.6	215.1	215.2	215.3
25°	213.7	213.3	213.5	213.9	214.3	214.2
25.5°	212.5	212.1	212.5	212.9	213.1	213.3
26°	211.5	211.2	211.5	211.7	212.1	212.0
26.5°	210.4	209.9	210.2	210.8	211.0	211.1
27°	209.3	208.9	209.2	209.6	209.9	209.9
27.5°	208.2	207.6	208.1	208.5	208.7	208.8
28°	207.0	206.6	206.9	207.3	207.6	207.5
28.5°	205.8	205.5	205.7	206.2	206.4	206.5
29°	204.7	204.2	204.6	204.9	205.4	205.3
29.5°	203.4	203.1	203.4	203.9	204.0	204.2
30°	202.3	201.9	202.2	202.4	203.0	202.8
30.5°	200.9	200.6	200.9	201.5	201.4	201.8
31°	199.9	199.4	199.7	200.0	200.6	200.3
31.5°	198.3	198.1	198.4	199.0	199.0	199.3
32°	197.4	196.7	197.2	197.6	197.8	197.8
32.5°	195.8	195.6	195.9	196.3	196.5	196.6
33°	194.7	194.2	194.5	195.0	195.3	195.3
33.5°	193.0	192.8	193.3	193.6	194.0	194.0
34°	192.1	191.6	191.9	192.3	192.6	192.6
34.5°	190.4	190.1	190.5	190.9	191.3	191.3
35°	189.2	188.8	189.2	189.5	189.9	189.7
35.5°	187.7	187.4	187.7	188.2	188.5	188.6
36°	186.5	186.0	186.3	186.7	187.1	187.0
36.5°	185.0	184.5	184.9	185.4	185.6	185.7
37°	183.6	183.1	183.5	183.9	184.2	184.2
37.5°	182.1	181.6	182.0	182.6	182.7	182.8
38°	180.7	180.3	180.6	181.0	181.4	181.3
38.5°	179.2	178.7	179.1	179.6	179.8	179.9
39°	177.8	177.1	177.7	178.0	178.5	178.2
39.5°	176.1	175.7	176.2	176.5	176.9	177.0
40°	174.8	174.2	174.6	175.1	175.4	175.3
40.5°	173.1	172.7	173.0	173.5	173.7	173.8
41°	171.7	171.1	171.6	171.9	172.3	172.3
41.5°	170.1	169.6	170.0	170.4	170.7	170.7
42°	168.5	168.0	168.4	168.8	169.2	169.1
42.5°	166.8	166.4	166.8	167.2	167.4	167.6
43°	165.4	164.9	165.3	165.6	166.0	165.8
43.5°	163.7	163.2	163.6	164.1	164.3	164.4

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997175

CATALOG NUMBER: SMX4SLSFSD2W-650LM-5000K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
45°	158.9	158.3	158.7	159.1	159.4	159.4
45.5°	157.1	156.7	157.1	157.4	157.7	157.8
46°	155.5	155.0	155.3	155.8	156.2	156.1
46.5°	153.7	153.2	153.7	154.0	154.4	154.4
47°	152.2	151.6	151.9	152.4	152.7	152.7
47.5°	150.3	149.9	150.3	150.7	151.0	151.0
48°	148.7	148.1	148.6	149.0	149.3	149.3
48.5°	146.9	146.4	146.8	147.3	147.5	147.6
49°	145.2	144.7	145.1	145.5	145.8	145.8
49.5°	143.3	143.0	143.3	143.7	144.0	144.0
50°	141.8	141.1	141.6	141.9	142.3	142.2
50.5°	139.9	139.4	139.8	140.1	140.4	140.5
51°	138.1	137.5	138.0	138.4	138.6	138.6
51.5°	136.3	135.7	136.3	136.5	136.9	136.9
52°	134.5	134.0	134.4	134.8	135.1	135.1
52.5°	132.8	132.2	132.6	132.9	133.3	133.3
53°	130.8	130.2	130.8	131.1	131.4	131.4
53.5°	129.1	128.5	128.9	129.2	129.6	129.5
54°	127.1	126.6	126.9	127.4	127.6	127.7
54.5°	125.3	124.7	125.2	125.5	125.9	125.8
55°	123.5	122.8	123.2	123.7	123.9	123.9
55.5°	121.6	121.1	121.4	121.7	122.0	122.1
56°	119.7	119.1	119.4	119.9	120.2	120.1
56.5°	117.8	117.2	117.6	117.9	118.2	118.2
57°	115.9	115.3	115.7	116.0	116.4	116.3
57.5°	113.9	113.4	113.7	114.1	114.3	114.3
58°	112.0	111.3	111.7	112.2	112.5	112.5
58.5°	110.1	109.5	109.9	110.2	110.5	110.4
59°	108.2	107.5	107.8	108.2	108.5	108.5
59.5°	106.1	105.5	106.0	106.2	106.6	106.5
60°	104.2	103.5	103.9	104.3	104.6	104.5
60.5°	102.2	101.6	102.0	102.2	102.6	102.5
61°	100.2	99.5	99.9	100.3	100.5	100.6
61.5°	98.2	97.6	98.1	98.3	98.6	98.6
62°	96.3	95.5	96.0	96.3	96.6	96.6
62.5°	94.2	93.6	94.0	94.2	94.5	94.5
63°	92.3	91.6	91.9	92.3	92.6	92.5
63.5°	90.2	89.5	90.0	90.2	90.5	90.5
64°	88.2	87.5	87.8	88.2	88.4	88.4
64.5°	86.1	85.4	85.9	86.1	86.4	86.4
65°	84.2	83.4	83.7	84.0	84.4	84.3
65.5°	82.1	81.4	81.7	82.0	82.3	82.3
66°	80.0	79.3	79.7	79.9	80.2	80.2

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997175

CATALOG NUMBER: SMX4SLSFSD2W-650LM-5000K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
67.5°	73.9	73.1	73.5	73.7	74.0	74.0
68°	71.7	71.0	71.4	71.6	71.8	71.9
68.5°	69.7	68.9	69.3	69.5	69.8	69.8
69°	67.7	66.8	67.2	67.4	67.6	67.7
69.5°	65.5	64.8	65.1	65.4	65.6	65.5
70°	63.5	62.7	63.0	63.3	63.4	63.5
70.5°	61.4	60.6	61.0	61.2	61.4	61.4
71°	59.4	58.6	58.8	59.0	59.3	59.3
71.5°	57.2	56.4	56.8	57.0	57.2	57.2
72°	55.2	54.4	54.7	55.0	55.1	55.1
72.5°	53.2	52.3	52.6	52.8	53.1	53.0
73°	51.1	50.2	50.5	50.7	50.9	51.0
73.5°	49.0	48.1	48.5	48.6	48.9	48.8
74°	47.0	46.1	46.4	46.6	46.7	46.8
74.5°	44.9	44.0	44.3	44.5	44.7	44.7
75°	42.8	42.0	42.3	42.4	42.7	42.6
75.5°	40.8	40.0	40.3	40.4	40.6	40.6
76°	38.8	37.9	38.2	38.4	38.6	38.5
76.5°	36.7	35.9	36.2	36.4	36.6	36.5
77°	34.7	34.0	34.2	34.4	34.6	34.5
77.5°	32.8	32.0	32.3	32.4	32.6	32.6
78°	30.9	30.1	30.3	30.4	30.6	30.6
78.5°	28.9	28.1	28.4	28.5	28.7	28.6
79°	27.0	26.2	26.5	26.6	26.8	26.8
79.5°	25.1	24.4	24.6	24.7	24.9	24.8
80°	23.3	22.5	22.7	22.9	23.0	23.0
80.5°	21.5	20.9	21.0	21.2	21.3	21.3
81°	19.7	19.2	19.3	19.4	19.6	19.6
81.5°	17.9	17.5	17.6	17.7	17.9	17.9
82°	16.3	15.8	15.9	16.0	16.2	16.2
82.5°	14.6	14.1	14.2	14.3	14.5	14.5
83°	13.1	12.5	12.7	12.7	12.9	12.9
83.5°	11.6	11.0	11.2	11.3	11.4	11.4
84°	10.1	9.6	9.8	9.8	10.0	10.0
84.5°	8.8	8.3	8.4	8.5	8.6	8.6
85°	7.5	7.0	7.1	7.2	7.3	7.3
85.5°	6.5	5.9	6.0	6.0	6.1	6.1
86°	5.5	4.8	4.9	4.9	5.0	5.1
86.5°	4.5	3.8	3.9	4.0	4.1	4.0
87°	3.5	3.0	3.1	3.1	3.2	3.2
87.5°	2.6	2.3	2.3	2.4	2.4	2.4
88°	1.9	1.8	1.9	1.9	1.9	1.9
88.5°	1.4	1.4	1.4	1.4	1.5	1.4

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P997175
CATALOG NUMBER: SMX4SLSFSD2W-650LM-5000K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
90°	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270° - · - 135°-315°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





21.5°	221.2	220.9	220.3	220.0	220.1	219.9	220.0	219.8	220.0	220.3	220.5
22°	220.2	220.0	219.6	219.1	219.4	219.1	219.1	218.9	219.1	219.4	219.5



44°	162.5	162.5	161.9	161.3	161.6	161.3	161.0	161.1	161.2	161.4	161.7
44.5°	161.1	160.7	160.2	159.6	159.9	159.5	159.5	159.3	159.5	159.8	160.2



66.5°	78.1	77.9	77.4	76.8	77.5	77.2	77.0	76.9	77.0	77.3	77.6
67°	76.0	75.8	75.3	74.8	75.4	75.1	75.0	74.9	75.0	75.3	75.5

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



89°	1.0	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.0	1.0
89.5°	0.5	0.5	0.5	0.5	0.6	0.6	0.6	0.6	0.7	0.7	0.7

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



21.5°	220.5	220.0	220.3	220.7	221.0	221.2
22°	219.6	219.4	219.7	219.8	220.2	220.2

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



44°	162.2	161.5	161.9	162.4	162.7	162.5
44.5°	160.4	159.9	160.3	160.7	161.1	161.1

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



66.5°	78.0	77.3	77.7	77.8	78.1	78.1
67°	75.9	75.1	75.5	75.7	76.0	76.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



89°	0.9	0.9	1.0	1.0	1.0	1.0
89.5°	0.6	0.5	0.5	0.5	0.5	0.5

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)