

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P991368

Luminaire Tested: **SMD4R07FS5-927**

Issue Date: 05/20/2025



Test Information

Test Method: LM-79-08
Report Number: P991368
Test Lab: THIRD PARTY NVLAP
Issue Date: 05/20/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: SMD4R07FS5-927
Description: HALO SURFACE MOUNT 4 inch 90 CRI COLOR SELECTABLE Round FIXTURE
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 769.9 lumens
Efficiency: N/A
Efficacy: 97.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.36
Luminous Opening: Circular (Dia: 0.3' x H: 0')
CIE Type: Direct

Input Watts (W): 7.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P991368
CATALOG NUMBER: SMD4R07FS5-927

Luminous Intensity Polar Plot



TEST NUMBER: P991368

CATALOG NUMBER: SMD4R07FS5-927

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102
1	109	104	100	96	106	102	98	94	97	94	91	93	91	88	90	88	86
2	99	91	84	78	96	89	82	77	85	80	75	82	77	73	79	75	72
3	90	79	71	65	88	78	70	64	75	68	63	72	67	62	70	65	61
4	82	70	62	55	80	69	61	54	67	59	54	64	58	53	62	57	52
5	76	63	54	47	74	62	53	47	60	52	46	58	51	46	56	50	45
6	70	57	48	41	68	56	47	41	54	46	41	52	45	40	51	45	40
7	65	51	43	36	63	51	42	36	49	41	36	47	41	36	46	40	35
8	60	47	38	32	59	46	38	32	45	37	32	44	37	32	42	36	32
9	56	43	35	29	55	42	34	29	41	34	29	40	34	29	39	33	29
10	53	40	32	26	52	39	32	26	38	31	26	37	31	26	36	30	26

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	41739	41739	41739	41739
5°	41761	41654	41639	41715
10°	41703	41487	41456	41626
15°	41541	41241	41194	41446
20°	41339	40918	40869	41226
25°	41031	40527	40459	40913
30°	40653	40073	40003	40565
35°	40210	39522	39447	40117
40°	39678	38902	38843	39598
45°	39065	38161	38118	39001
50°	38355	37265	37289	38331
55°	37461	36213	36292	37487
60°	36364	34872	35024	36425
65°	34951	33186	33474	35131
70°	33125	31033	31478	33481
75°	30830	28124	28888	31359
80°	27887	24028	25343	28851
85°	22714	16249	19044	25160



TEST NUMBER: P991368
 CATALOG NUMBER: SMD4R07FS5-927

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.9	3.4
10°-20°	74.0	9.6
20°-30°	111.7	14.5
30°-40°	134.0	17.4
40°-50°	138.2	18.0
50°-60°	124.1	16.1
60°-70°	93.9	12.2
70°-80°	53.7	7.0
80°-90°	13.9	1.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.1	0.0
120°-130°	0.1	0.0
130°-140°	0.1	0.0
140°-150°	0.1	0.0
150°-160°	0.1	0.0
160°-170°	0.1	0.0
170°-180°	0.0	0.0
0°-30°	211.7	27.5
0°-40°	345.7	44.9
0°-60°	608.0	79.0
0°-90°	769.4	99.9
90°-120°	0.1	0.0
90°-150°	0.3	0.0
90°-180°	1.0	0.1
0°-180°	769.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	274	274	274	274	274	
5°	273	272	272	273	273	26
15°	264	262	261	263	264	74
25°	244	241	241	244	244	113
35°	216	213	212	216	216	135
45°	181	177	177	181	181	140
55°	141	136	137	141	141	126
65°	97	92	93	98	97	96
75°	52	48	49	53	52	55
85°	13	9	11	14	13	14
90°	0	0	0	1	0	1
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	

TEST NUMBER: P991368

CATALOG NUMBER: SMD4R07FS5-927

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	274.1	274.1	274.1	274.1	274.1	274.1	274.1	274.1	274.1	274.1	274.1
0.5°	274.2	274.2	274.2	274.3	274.0	274.0	273.9	274.0	274.1	274.2	274.2
1°	274.1	274.3	274.2	274.1	273.8	273.9	273.8	273.8	274.0	274.2	274.2
1.5°	274.1	274.2	274.1	274.1	273.9	273.7	273.7	273.8	273.9	274.1	274.1
2°	274.0	274.1	274.0	274.0	273.6	273.6	273.6	273.6	273.7	274.0	274.0
2.5°	274.0	274.0	273.9	273.9	273.6	273.4	273.4	273.5	273.6	273.9	273.9
3°	273.9	273.9	273.8	273.6	273.4	273.3	273.2	273.3	273.4	273.8	273.7
3.5°	273.8	273.6	273.6	273.5	273.3	273.1	273.0	273.1	273.2	273.6	273.6
4°	273.6	273.6	273.4	273.3	273.0	273.0	272.8	272.9	273.0	273.4	273.3
4.5°	273.5	273.3	273.2	273.1	272.8	272.6	272.5	272.6	272.7	273.0	273.1
5°	273.2	273.1	273.0	272.7	272.5	272.4	272.2	272.2	272.4	272.9	272.9
5.5°	273.0	272.8	272.7	272.5	272.3	272.0	271.9	271.9	272.1	272.5	272.6
6°	272.7	272.6	272.4	272.1	271.9	271.7	271.5	271.5	271.8	272.3	272.3
6.5°	272.4	272.2	272.1	271.9	271.6	271.3	271.1	271.2	271.4	271.9	272.0
7°	272.1	271.9	271.7	271.4	271.1	270.9	270.7	270.8	271.0	271.6	271.6
7.5°	271.8	271.5	271.3	271.0	270.7	270.4	270.3	270.4	270.6	271.0	271.2
8°	271.4	271.1	270.9	270.5	270.3	270.0	269.9	270.0	270.2	270.7	270.8
8.5°	271.0	270.6	270.4	270.1	269.9	269.5	269.5	269.5	269.7	270.2	270.4
9°	270.6	270.2	270.0	269.6	269.4	269.1	268.9	268.9	269.2	269.8	269.9
9.5°	270.1	269.7	269.5	269.1	268.8	268.5	268.3	268.4	268.6	269.3	269.4
10°	269.7	269.3	269.0	268.5	268.3	268.0	267.8	267.8	268.1	268.7	268.9
10.5°	269.2	268.7	268.4	268.0	267.8	267.4	267.2	267.3	267.6	268.1	268.4
11°	268.7	268.2	267.9	267.4	267.2	266.9	266.6	266.7	267.0	267.6	267.7
11.5°	268.1	267.6	267.3	266.9	266.6	266.2	266.0	266.1	266.3	267.0	267.2
12°	267.5	267.1	266.7	266.2	265.9	265.6	265.3	265.4	265.7	266.4	266.5
12.5°	267.0	266.4	266.1	265.5	265.2	264.8	264.6	264.7	265.0	265.7	266.0
13°	266.3	265.8	265.5	264.8	264.6	264.2	264.0	264.0	264.3	265.1	265.3
13.5°	265.7	265.1	264.7	264.1	263.9	263.5	263.2	263.4	263.5	264.3	264.6
14°	264.9	264.5	264.1	263.4	263.2	262.8	262.5	262.5	262.9	263.7	263.9
14.5°	264.3	263.7	263.3	262.6	262.3	262.0	261.7	261.8	262.0	262.8	263.2
15°	263.5	263.0	262.6	261.8	261.6	261.2	260.9	261.0	261.3	262.1	262.3
15.5°	262.8	262.2	261.8	261.0	260.8	260.4	260.1	260.2	260.5	261.2	261.7
16°	262.0	261.4	261.1	260.2	260.0	259.6	259.3	259.4	259.7	260.5	260.8
16.5°	261.2	260.6	260.1	259.3	259.1	258.7	258.4	258.5	258.8	259.6	260.0
17°	260.4	259.8	259.3	258.4	258.3	257.8	257.5	257.6	258.0	258.8	259.1
17.5°	259.6	258.9	258.4	257.5	257.4	256.9	256.6	256.7	257.0	257.8	258.3
18°	258.7	258.1	257.6	256.7	256.5	256.1	255.7	255.8	256.1	256.9	257.3
18.5°	257.9	257.1	256.6	255.7	255.5	255.1	254.7	254.8	255.1	255.9	256.4
19°	256.9	256.2	255.7	254.7	254.5	254.2	253.7	253.7	254.2	255.0	255.4
19.5°	256.0	255.3	254.7	253.7	253.5	253.1	252.7	252.8	253.1	254.0	254.6
20°	255.1	254.4	253.8	252.8	252.5	252.2	251.7	251.8	252.2	253.1	253.5
20.5°	254.1	253.3	252.7	251.7	251.5	251.1	250.7	250.8	251.1	252.0	252.6
21°	253.0	252.3	251.7	250.7	250.4	250.0	249.6	249.6	250.1	251.0	251.5
21.5°	252.0	251.3	250.6	249.6	249.4	248.9	248.5	248.6	249.0	249.9	250.5
22°	251.0	250.3	249.6	248.6	248.3	247.8	247.4	247.5	248.0	248.8	249.4



TEST NUMBER: P991368

CATALOG NUMBER: SMD4R07FS5-927

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
22.5°	249.9	249.2	248.4	247.5	247.2	246.7	246.3	246.4	246.7	247.7	248.4
23°	248.8	248.1	247.4	246.4	246.0	245.6	245.2	245.2	245.7	246.6	247.2
23.5°	247.7	246.9	246.2	245.2	244.9	244.3	244.0	244.1	244.4	245.4	246.1
24°	246.5	245.8	245.1	244.0	243.6	243.2	242.8	242.9	243.3	244.3	244.9
24.5°	245.4	244.6	243.9	242.8	242.4	242.0	241.6	241.7	242.0	243.1	243.8
25°	244.2	243.4	242.7	241.6	241.2	240.8	240.3	240.4	240.8	241.9	242.5
25.5°	243.0	242.2	241.5	240.3	239.9	239.5	239.1	239.3	239.5	240.6	241.4
26°	241.8	241.0	240.2	239.0	238.7	238.3	237.7	237.9	238.3	239.3	240.1
26.5°	240.6	239.7	238.8	237.7	237.4	237.0	236.4	236.6	237.0	238.0	238.8
27°	239.3	238.4	237.7	236.4	236.1	235.7	235.1	235.3	235.7	236.8	237.5
27.5°	238.0	237.2	236.3	235.1	234.8	234.3	233.8	234.0	234.4	235.4	236.3
28°	236.6	235.8	235.0	233.8	233.4	233.0	232.5	232.6	233.1	234.1	234.9
28.5°	235.3	234.5	233.6	232.4	232.1	231.6	231.1	231.3	231.6	232.7	233.6
29°	234.0	233.2	232.3	231.0	230.7	230.2	229.7	229.9	230.4	231.5	232.2
29.5°	232.7	231.8	230.9	229.6	229.3	228.8	228.2	228.5	228.8	229.9	230.9
30°	231.2	230.4	229.5	228.2	227.9	227.4	226.8	227.0	227.5	228.6	229.4
30.5°	229.8	229.0	228.1	226.8	226.4	225.9	225.4	225.6	226.0	227.1	228.1
31°	228.4	227.5	226.6	225.3	225.0	224.4	223.9	224.1	224.6	225.7	226.6
31.5°	227.0	226.2	225.1	223.8	223.5	222.9	222.4	222.7	223.0	224.1	225.2
32°	225.4	224.7	223.6	222.3	222.0	221.5	220.9	221.1	221.6	222.7	223.7
32.5°	224.0	223.2	222.2	220.8	220.5	219.9	219.4	219.6	220.1	221.1	222.2
33°	222.5	221.7	220.6	219.3	219.0	218.4	217.8	218.1	218.6	219.7	220.6
33.5°	221.1	220.2	219.1	217.7	217.4	216.8	216.2	216.6	217.0	218.1	219.2
34°	219.5	218.6	217.6	216.2	215.8	215.3	214.7	215.0	215.5	216.6	217.6
34.5°	218.0	217.1	215.9	214.6	214.2	213.6	213.1	213.4	213.8	214.9	216.1
35°	216.3	215.4	214.4	213.0	212.6	212.1	211.5	211.7	212.2	213.4	214.5
35.5°	214.8	213.9	212.7	211.3	211.0	210.4	209.9	210.1	210.6	211.8	213.0
36°	213.1	212.3	211.2	209.7	209.4	208.8	208.2	208.4	209.1	210.2	211.3
36.5°	211.6	210.7	209.5	208.0	207.8	207.1	206.5	206.9	207.3	208.5	209.8
37°	209.8	209.0	207.8	206.4	206.1	205.5	204.9	205.2	205.7	206.9	208.0
37.5°	208.3	207.3	206.1	204.7	204.5	203.7	203.2	203.5	204.0	205.2	206.5
38°	206.5	205.7	204.4	203.1	202.7	202.0	201.5	201.7	202.3	203.5	204.7
38.5°	204.9	204.0	202.7	201.4	201.0	200.3	199.8	200.1	200.6	201.7	203.2
39°	203.1	202.3	201.0	199.6	199.3	198.7	198.0	198.3	198.9	200.1	201.4
39.5°	201.5	200.6	199.3	197.9	197.5	196.8	196.3	196.6	197.1	198.3	199.7
40°	199.6	198.7	197.5	196.1	195.7	195.1	194.5	194.8	195.4	196.6	197.9
40.5°	198.0	197.0	195.7	194.3	194.0	193.2	192.7	193.0	193.6	194.7	196.3
41°	196.1	195.2	193.9	192.6	192.0	191.5	190.9	191.2	191.9	193.0	194.4
41.5°	194.4	193.5	192.1	190.7	190.3	189.6	189.1	189.5	190.0	191.2	192.6
42°	192.5	191.6	190.3	188.9	188.4	187.8	187.2	187.5	188.2	189.4	190.8
42.5°	190.8	189.8	188.4	187.0	186.7	185.9	185.4	185.7	186.4	187.6	189.1
43°	188.9	188.0	186.6	185.1	184.8	184.1	183.5	183.9	184.6	185.8	187.2
43.5°	187.1	186.2	184.7	183.2	182.9	182.2	181.7	182.1	182.7	183.9	185.5
44°	185.2	184.3	182.9	181.4	181.0	180.4	179.8	180.1	180.9	182.0	183.5
44.5°	183.4	182.4	180.9	179.5	179.2	178.4	177.9	178.3	178.9	180.1	181.7

TEST NUMBER: P991368

CATALOG NUMBER: SMD4R07FS5-927

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
45°	181.4	180.5	179.1	177.6	177.2	176.5	175.9	176.3	177.0	178.3	179.7
45.5°	179.6	178.7	177.1	175.7	175.3	174.6	174.0	174.4	175.1	176.3	178.0
46°	177.6	176.7	175.2	173.8	173.3	172.7	172.1	172.5	173.2	174.4	176.0
46.5°	175.7	174.8	173.2	171.8	171.4	170.7	170.2	170.6	171.3	172.4	174.1
47°	173.7	172.7	171.3	169.9	169.4	168.7	168.2	168.6	169.3	170.5	172.1
47.5°	171.9	170.9	169.2	167.9	167.5	166.7	166.2	166.6	167.3	168.5	170.2
48°	169.8	168.9	167.3	165.9	165.4	164.8	164.2	164.6	165.4	166.6	168.2
48.5°	167.9	166.9	165.3	163.8	163.4	162.7	162.3	162.7	163.4	164.6	166.2
49°	165.8	164.9	163.3	161.9	161.4	160.8	160.2	160.6	161.4	162.6	164.2
49.5°	163.9	162.9	161.2	159.8	159.4	158.7	158.2	158.6	159.4	160.6	162.3
50°	161.9	160.8	159.2	157.8	157.3	156.7	156.2	156.5	157.4	158.6	160.2
50.5°	159.9	158.8	157.1	155.7	155.3	154.6	154.1	154.6	155.4	156.6	158.2
51°	157.8	156.8	155.1	153.7	153.3	152.6	152.1	152.5	153.3	154.5	156.1
51.5°	155.8	154.7	153.0	151.6	151.3	150.5	150.0	150.5	151.3	152.5	154.2
52°	153.7	152.7	151.0	149.6	149.1	148.4	147.9	148.4	149.3	150.4	152.2
52.5°	151.7	150.6	148.8	147.4	147.1	146.3	145.9	146.4	147.2	148.4	150.1
53°	149.5	148.4	146.8	145.4	144.9	144.2	143.7	144.2	145.1	146.3	148.0
53.5°	147.5	146.4	144.6	143.2	142.9	142.1	141.6	142.1	143.0	144.2	146.0
54°	145.3	144.2	142.5	141.1	140.7	140.0	139.5	140.0	140.8	142.1	143.8
54.5°	143.2	142.1	140.3	138.9	138.6	137.8	137.4	137.9	138.7	140.0	141.7
55°	141.1	140.0	138.3	136.8	136.4	135.7	135.3	135.7	136.7	137.9	139.6
55.5°	139.0	137.9	136.1	134.6	134.3	133.6	133.1	133.6	134.5	135.7	137.5
56°	136.8	135.6	133.9	132.5	132.1	131.4	130.9	131.4	132.4	133.6	135.3
56.5°	134.7	133.5	131.7	130.3	130.0	129.2	128.8	129.3	130.2	131.4	133.3
57°	132.5	131.3	129.6	128.1	127.7	127.1	126.6	127.0	128.0	129.3	131.1
57.5°	130.4	129.1	127.4	125.9	125.6	124.9	124.5	124.9	125.8	127.1	129.0
58°	128.2	126.9	125.2	123.8	123.3	122.7	122.2	122.7	123.7	125.0	126.8
58.5°	126.0	124.8	122.9	121.5	121.2	120.5	120.1	120.6	121.5	122.8	124.6
59°	123.8	122.5	120.8	119.4	118.9	118.2	117.9	118.4	119.4	120.7	122.4
59.5°	121.6	120.4	118.5	117.1	116.7	116.0	115.6	116.1	117.1	118.5	120.3
60°	119.4	118.1	116.4	114.9	114.5	113.8	113.5	114.0	115.0	116.3	118.1
60.5°	117.2	115.9	114.1	112.6	112.2	111.6	111.2	111.8	112.8	114.1	115.9
61°	114.9	113.6	111.9	110.4	110.0	109.3	109.0	109.5	110.6	111.9	113.7
61.5°	112.8	111.4	109.6	108.2	107.8	107.1	106.8	107.4	108.3	109.7	111.5
62°	110.5	109.1	107.4	106.0	105.6	104.9	104.6	105.1	106.1	107.5	109.3
62.5°	108.3	106.9	105.1	103.7	103.3	102.7	102.4	102.9	103.9	105.3	107.1
63°	106.0	104.6	102.9	101.5	101.0	100.4	100.1	100.6	101.7	103.0	104.8
63.5°	103.8	102.4	100.6	99.1	98.8	98.1	97.9	98.4	99.5	100.8	102.6
64°	101.5	100.2	98.4	96.9	96.6	95.9	95.7	96.2	97.2	98.6	100.4
64.5°	99.3	97.9	96.1	94.7	94.3	93.6	93.4	94.0	95.0	96.4	98.2
65°	97.0	95.6	93.9	92.5	92.1	91.4	91.2	91.8	92.9	94.2	96.0
65.5°	94.7	93.4	91.6	90.2	89.8	89.2	89.0	89.5	90.6	92.0	93.7
66°	92.5	91.1	89.3	87.9	87.6	87.0	86.9	87.3	88.4	89.8	91.5
66.5°	90.2	88.8	87.1	85.6	85.3	84.8	84.6	85.1	86.2	87.5	89.3
67°	88.0	86.5	84.8	83.3	83.1	82.5	82.4	82.9	84.0	85.4	87.1

TEST NUMBER: P991368

CATALOG NUMBER: SMD4R07FS5-927

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
67.5°	85.7	84.3	82.5	81.1	80.9	80.3	80.2	80.7	81.8	83.2	84.9
68°	83.4	82.0	80.3	78.9	78.6	78.1	77.9	78.5	79.6	81.0	82.7
68.5°	81.2	79.8	78.0	76.6	76.4	75.8	75.6	76.3	77.3	78.8	80.4
69°	78.9	77.5	75.8	74.3	74.2	73.6	73.4	74.0	75.2	76.6	78.2
69.5°	76.7	75.3	73.5	72.0	71.9	71.3	71.2	71.8	72.9	74.4	76.1
70°	74.4	73.0	71.3	69.9	69.7	69.1	69.0	69.6	70.7	72.1	73.8
70.5°	72.2	70.8	69.0	67.6	67.4	66.9	66.7	67.4	68.5	69.9	71.6
71°	70.0	68.5	66.8	65.4	65.3	64.7	64.6	65.2	66.4	67.8	69.4
71.5°	67.7	66.3	64.6	63.1	63.0	62.5	62.3	63.0	64.1	65.5	67.2
72°	65.5	64.0	62.4	61.0	60.8	60.3	60.2	60.8	62.0	63.4	65.0
72.5°	63.3	61.8	60.1	58.8	58.6	58.1	58.0	58.6	59.8	61.2	62.9
73°	61.1	59.6	57.9	56.5	56.4	55.9	55.8	56.5	57.6	59.0	60.6
73.5°	58.9	57.5	55.8	54.3	54.2	53.7	53.6	54.3	55.4	56.8	58.5
74°	56.7	55.2	53.5	52.2	52.1	51.6	51.5	52.1	53.4	54.7	56.4
74.5°	54.5	53.1	51.4	50.0	49.9	49.4	49.4	50.0	51.2	52.6	54.3
75°	52.4	50.9	49.3	47.9	47.8	47.3	47.3	47.9	49.1	50.5	52.1
75.5°	50.2	48.8	47.2	45.8	45.6	45.2	45.1	45.8	47.0	48.4	50.0
76°	48.1	46.6	45.0	43.7	43.6	43.1	43.1	43.7	44.9	46.3	47.9
76.5°	45.9	44.6	42.9	41.6	41.4	41.0	40.9	41.7	42.8	44.2	45.8
77°	43.9	42.4	40.8	39.5	39.4	39.0	38.9	39.6	40.8	42.1	43.7
77.5°	41.8	40.4	38.7	37.4	37.4	36.9	36.9	37.6	38.7	40.1	41.6
78°	39.7	38.3	36.7	35.5	35.3	34.9	34.9	35.6	36.8	38.1	39.6
78.5°	37.7	36.1	34.8	33.5	33.3	32.9	32.9	33.6	34.7	36.1	37.6
79°	35.7	34.2	32.8	31.5	31.3	30.9	30.9	31.6	32.7	34.1	35.6
79.5°	33.7	32.3	30.8	29.5	29.3	28.9	29.0	29.7	30.8	32.1	33.6
80°	31.8	30.4	28.9	27.5	27.4	27.0	27.1	27.8	28.9	30.2	31.6
80.5°	29.8	28.4	26.9	25.7	25.4	25.1	25.1	25.8	26.9	28.3	29.7
81°	27.8	26.5	25.0	23.8	23.6	23.2	23.3	23.9	25.1	26.4	27.8
81.5°	25.9	24.5	23.0	21.8	21.6	21.3	21.4	22.1	23.2	24.5	25.9
82°	24.0	22.6	21.1	19.9	19.8	19.5	19.6	20.2	21.3	22.6	24.0
82.5°	22.1	20.8	19.3	18.1	17.9	17.6	17.8	18.4	19.5	20.8	22.2
83°	20.2	18.9	17.4	16.3	16.1	15.9	15.9	16.6	17.7	19.0	20.4
83.5°	18.4	17.1	15.6	14.5	14.3	14.0	14.2	14.9	16.0	17.2	18.6
84°	16.6	15.3	13.9	12.7	12.6	12.4	12.5	13.1	14.2	15.5	16.8
84.5°	14.8	13.5	12.1	11.0	10.9	10.7	10.8	11.5	12.5	13.8	15.1
85°	13.0	11.7	10.4	9.3	9.3	9.1	9.2	9.9	10.9	12.0	13.3
85.5°	11.3	10.1	8.7	7.6	7.6	7.4	7.6	8.3	9.2	10.4	11.7
86°	9.6	8.4	7.0	6.0	6.0	5.8	5.9	6.6	7.6	8.7	10.0
86.5°	7.9	6.7	5.4	4.4	4.4	4.1	4.3	5.0	5.9	7.1	8.4
87°	6.3	5.1	3.9	3.5	2.9	2.7	2.8	3.4	4.3	5.5	6.8
87.5°	4.7	3.6	3.0	2.7	1.6	1.5	1.6	2.0	2.8	3.8	5.2
88°	3.2	2.7	2.0	1.8	0.8	0.7	0.8	1.1	1.5	2.4	3.5
88.5°	2.4	1.8	1.0	0.9	0.3	0.2	0.2	0.4	0.8	1.2	2.1
89°	1.6	0.9	0.1	0.1	0.0	0.0	0.0	0.1	0.2	0.6	1.1
89.5°	0.8	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.5



TEST NUMBER: P991368

CATALOG NUMBER: SMD4R07FS5-927

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1
90.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
91°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
91.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P991368

CATALOG NUMBER: SMD4R07FS5-927

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.1	0.1	0.1	0.1	0.0	0.0	0.1	0.0	0.0	0.0	0.0
113.5°	0.1	0.1	0.1	0.1	0.0	0.0	0.1	0.1	0.0	0.0	0.0
114°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0
114.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0
115°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0
115.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
116°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
116.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
117°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
117.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
118°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
118.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
119°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
119.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
120°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
120.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
121°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
121.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
122°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
122.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
123°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
123.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
124°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
124.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
125°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
125.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
126°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
126.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
127°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
127.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
128°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
128.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
129°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
129.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
130°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
130.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
131°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
131.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
132°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
132.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
133°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
133.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
134°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
134.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1

TEST NUMBER: P991368

CATALOG NUMBER: SMD4R07FS5-927

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
135°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
135.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
136°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
136.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
138°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
138.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.1	0.1	0.1
139°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.1	0.1
139.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.1	0.1
140°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.1	0.1
140.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.1	0.1
141°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.1	0.1
141.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.1
142°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.1
142.5°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.1
143°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.1
143.5°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
144°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
144.5°	0.1	0.2	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145°	0.1	0.2	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
145.5°	0.1	0.2	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
146°	0.1	0.2	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
146.5°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
147°	0.2	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
147.5°	0.2	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
148°	0.2	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
148.5°	0.2	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
149°	0.2	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
149.5°	0.2	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
150°	0.2	0.2	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
150.5°	0.2	0.2	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
151°	0.2	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
151.5°	0.2	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
152°	0.2	0.1	0.2	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
152.5°	0.2	0.1	0.2	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
153°	0.2	0.1	0.2	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
153.5°	0.2	0.1	0.2	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
154°	0.2	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
154.5°	0.2	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.3	0.2	0.2
155°	0.2	0.1	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.2	0.2
155.5°	0.2	0.1	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.2	0.2
156°	0.2	0.1	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.2	0.2
156.5°	0.2	0.1	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.2	0.2
157°	0.2	0.1	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.2	0.2

TEST NUMBER: P991368

CATALOG NUMBER: SMD4R07FS5-927

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
157.5°	0.2	0.1	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.2	0.2
158°	0.2	0.1	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.2	0.2
158.5°	0.2	0.1	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.2	0.2
159°	0.2	0.1	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.2	0.2
159.5°	0.2	0.1	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.2	0.2
160°	0.2	0.1	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.2	0.2
160.5°	0.2	0.1	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.2	0.2
161°	0.2	0.1	0.2	0.2	0.2	0.2	0.3	0.4	0.3	0.2	0.2
161.5°	0.2	0.1	0.2	0.2	0.2	0.2	0.3	0.4	0.3	0.3	0.2
162°	0.2	0.1	0.2	0.2	0.3	0.3	0.3	0.4	0.3	0.3	0.2
162.5°	0.2	0.1	0.2	0.2	0.3	0.3	0.3	0.4	0.3	0.3	0.2
163°	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.4	0.3	0.3	0.2
163.5°	0.2	0.2	0.2	0.2	0.3	0.3	0.4	0.3	0.3	0.3	0.2
164°	0.2	0.2	0.2	0.2	0.3	0.3	0.4	0.3	0.3	0.3	0.2
164.5°	0.2	0.2	0.2	0.2	0.3	0.3	0.4	0.3	0.3	0.3	0.2
165°	0.2	0.2	0.2	0.2	0.3	0.3	0.4	0.4	0.3	0.3	0.2
165.5°	0.2	0.2	0.2	0.2	0.3	0.3	0.4	0.4	0.3	0.3	0.2
166°	0.2	0.2	0.2	0.2	0.3	0.3	0.4	0.4	0.3	0.3	0.2
166.5°	0.2	0.2	0.2	0.2	0.3	0.3	0.4	0.4	0.3	0.3	0.2
167°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.3	0.2
167.5°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.3	0.2
168°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.3	0.2
168.5°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.3	0.3
169°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.3	0.3
169.5°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.2	0.3
170°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.2	0.3
170.5°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.2	0.2
171°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.2	0.2
171.5°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.2	0.2	0.2
172°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.2	0.2	0.2
172.5°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.2	0.2	0.2
173°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.2	0.2	0.2	0.2
173.5°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.2	0.2	0.2	0.2
174°	0.2	0.2	0.2	0.2	0.2	0.2	0.3	0.2	0.2	0.2	0.2
174.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
175°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
175.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
176°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
176.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
177°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
177.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
178°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
178.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
179°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
179.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2



TEST NUMBER: P991368
CATALOG NUMBER: SMD4R07FS5-927

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
180°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2



TEST NUMBER: P991368

CATALOG NUMBER: SMD4R07FS5-927

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	274.1	274.1	274.1	274.1	274.1	274.1
0.5°	274.3	274.1	274.0	273.9	274.0	274.2
1°	274.2	273.9	274.0	274.0	274.0	274.1
1.5°	274.2	274.0	274.0	273.9	274.1	274.1
2°	274.1	273.9	273.9	273.9	273.9	274.0
2.5°	274.1	273.8	273.8	273.8	273.8	274.0
3°	273.9	273.7	273.7	273.8	273.7	273.9
3.5°	273.8	273.6	273.6	273.6	273.6	273.8
4°	273.5	273.2	273.5	273.5	273.4	273.6
4.5°	273.4	273.2	273.2	273.3	273.3	273.5
5°	273.1	272.9	273.1	273.1	273.1	273.2
5.5°	272.9	272.7	272.8	272.8	272.9	273.0
6°	272.5	272.3	272.5	272.6	272.6	272.7
6.5°	272.3	272.1	272.2	272.3	272.3	272.4
7°	271.9	271.7	271.9	272.0	272.0	272.1
7.5°	271.6	271.3	271.5	271.7	271.6	271.8
8°	271.2	270.9	271.2	271.3	271.3	271.4
8.5°	270.8	270.6	270.7	270.9	270.9	271.0
9°	270.2	270.1	270.3	270.5	270.5	270.6
9.5°	269.8	269.7	269.8	270.1	270.1	270.1
10°	269.2	269.2	269.4	269.6	269.6	269.7
10.5°	268.8	268.7	268.9	269.1	269.1	269.2
11°	268.2	268.1	268.3	268.5	268.6	268.7
11.5°	267.7	267.6	267.7	268.0	268.0	268.1
12°	267.1	266.9	267.2	267.4	267.4	267.5
12.5°	266.6	266.4	266.6	266.9	266.9	267.0
13°	265.9	265.7	266.0	266.2	266.3	266.3
13.5°	265.3	265.1	265.3	265.6	265.6	265.7
14°	264.5	264.4	264.7	264.9	264.9	264.9
14.5°	263.8	263.7	264.0	264.3	264.2	264.3
15°	263.0	262.9	263.3	263.5	263.5	263.5
15.5°	262.3	262.1	262.5	262.9	262.8	262.8
16°	261.4	261.4	261.8	262.0	262.1	262.0
16.5°	260.7	260.7	261.0	261.2	261.3	261.2
17°	259.9	259.8	260.2	260.4	260.5	260.4
17.5°	259.0	258.9	259.3	259.6	259.7	259.6
18°	258.1	258.0	258.5	258.7	258.8	258.7
18.5°	257.2	257.2	257.5	257.9	257.9	257.9
19°	256.2	256.3	256.6	257.0	257.0	256.9
19.5°	255.4	255.4	255.7	256.2	256.1	256.0
20°	254.4	254.4	254.9	255.1	255.2	255.1
20.5°	253.4	253.3	253.8	254.2	254.1	254.1
21°	252.3	252.4	252.9	253.1	253.2	253.0
21.5°	251.3	251.3	251.8	252.2	252.1	252.0
22°	250.2	250.3	250.8	251.1	251.1	251.0



TEST NUMBER: P991368

CATALOG NUMBER: SMD4R07FS5-927

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
22.5°	249.1	249.2	249.7	250.1	250.1	249.9
23°	248.1	248.1	248.7	248.9	249.0	248.8
23.5°	247.0	247.0	247.5	247.9	247.8	247.7
24°	245.8	245.8	246.4	246.7	246.7	246.5
24.5°	244.7	244.6	245.2	245.7	245.6	245.4
25°	243.4	243.5	244.1	244.4	244.5	244.2
25.5°	242.2	242.3	242.8	243.3	243.3	243.0
26°	241.0	241.1	241.7	242.0	242.1	241.8
26.5°	239.8	239.8	240.4	240.9	240.8	240.6
27°	238.5	238.6	239.2	239.6	239.6	239.3
27.5°	237.2	237.3	237.9	238.4	238.3	238.0
28°	235.9	235.9	236.6	237.0	237.0	236.6
28.5°	234.6	234.7	235.3	235.8	235.7	235.3
29°	233.2	233.3	234.0	234.4	234.4	234.0
29.5°	231.8	232.0	232.6	233.2	233.0	232.7
30°	230.4	230.7	231.2	231.7	231.7	231.2
30.5°	229.0	229.3	229.8	230.4	230.3	229.8
31°	227.6	227.8	228.5	228.9	228.9	228.4
31.5°	226.2	226.4	227.0	227.5	227.4	227.0
32°	224.7	224.9	225.6	226.0	226.0	225.4
32.5°	223.2	223.5	224.1	224.6	224.5	224.0
33°	221.8	222.0	222.7	223.1	223.0	222.5
33.5°	220.2	220.5	221.2	221.6	221.5	221.1
34°	218.7	218.9	219.7	220.1	220.0	219.5
34.5°	217.1	217.4	218.0	218.6	218.4	218.0
35°	215.6	215.8	216.5	217.0	216.9	216.3
35.5°	214.0	214.2	214.9	215.4	215.4	214.8
36°	212.4	212.6	213.4	213.8	213.8	213.1
36.5°	210.8	211.0	211.7	212.2	212.1	211.6
37°	209.2	209.4	210.1	210.5	210.5	209.8
37.5°	207.5	207.7	208.5	208.9	208.8	208.3
38°	205.9	206.0	206.9	207.2	207.2	206.5
38.5°	204.2	204.4	205.1	205.6	205.5	204.9
39°	202.5	202.6	203.6	203.9	203.9	203.1
39.5°	200.8	201.0	201.8	202.2	202.1	201.5
40°	199.1	199.2	200.1	200.4	200.4	199.6
40.5°	197.4	197.5	198.3	198.7	198.6	198.0
41°	195.5	195.7	196.6	197.0	197.0	196.1
41.5°	193.7	194.0	194.7	195.3	195.1	194.4
42°	191.9	192.1	193.0	193.4	193.4	192.5
42.5°	190.2	190.4	191.2	191.6	191.5	190.8
43°	188.4	188.6	189.4	189.8	189.8	188.9
43.5°	186.5	186.8	187.5	188.0	187.8	187.1
44°	184.7	184.9	185.7	186.1	186.1	185.2
44.5°	182.8	183.1	183.8	184.3	184.1	183.4



TEST NUMBER: P991368

CATALOG NUMBER: SMD4R07FS5-927

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
45°	181.0	181.1	182.0	182.4	182.3	181.4
45.5°	179.1	179.3	180.1	180.6	180.4	179.6
46°	177.2	177.4	178.2	178.7	178.5	177.6
46.5°	175.3	175.5	176.3	176.7	176.5	175.7
47°	173.5	173.6	174.4	174.8	174.7	173.7
47.5°	171.4	171.7	172.4	172.9	172.7	171.9
48°	169.4	169.7	170.6	170.9	170.8	169.8
48.5°	167.5	167.7	168.6	169.0	168.7	167.9
49°	165.6	165.7	166.6	167.0	166.8	165.8
49.5°	163.6	163.8	164.6	165.0	164.8	163.9
50°	161.6	161.8	162.7	163.0	162.8	161.9
50.5°	159.6	159.8	160.6	160.9	160.8	159.9
51°	157.6	157.7	158.5	158.9	158.7	157.8
51.5°	155.5	155.7	156.5	156.9	156.7	155.8
52°	153.5	153.7	154.5	154.8	154.6	153.7
52.5°	151.5	151.6	152.5	152.8	152.6	151.7
53°	149.4	149.5	150.5	150.7	150.5	149.5
53.5°	147.3	147.5	148.3	148.6	148.4	147.5
54°	145.3	145.4	146.2	146.5	146.3	145.3
54.5°	143.1	143.3	144.1	144.4	144.2	143.2
55°	141.1	141.2	142.0	142.3	142.2	141.1
55.5°	138.9	139.1	139.9	140.2	139.9	139.0
56°	136.8	136.9	137.7	138.0	137.8	136.8
56.5°	134.6	134.8	135.6	135.9	135.6	134.7
57°	132.6	132.7	133.5	133.7	133.6	132.5
57.5°	130.4	130.5	131.3	131.6	131.4	130.4
58°	128.2	128.3	129.2	129.4	129.2	128.2
58.5°	126.1	126.2	127.0	127.2	127.0	126.0
59°	123.9	124.0	124.8	125.1	124.8	123.8
59.5°	121.7	121.8	122.7	122.9	122.6	121.6
60°	119.6	119.6	120.4	120.7	120.4	119.4
60.5°	117.4	117.4	118.3	118.5	118.1	117.2
61°	115.2	115.3	116.1	116.2	116.0	114.9
61.5°	112.9	113.1	113.9	114.1	113.7	112.8
62°	110.9	110.8	111.7	111.8	111.5	110.5
62.5°	108.6	108.6	109.4	109.6	109.3	108.3
63°	106.4	106.4	107.2	107.4	107.0	106.0
63.5°	104.2	104.2	105.0	105.2	104.8	103.8
64°	102.0	102.0	102.7	102.9	102.6	101.5
64.5°	99.7	99.8	100.5	100.7	100.3	99.3
65°	97.6	97.5	98.3	98.4	98.1	97.0
65.5°	95.3	95.3	96.0	96.2	95.8	94.7
66°	93.1	93.0	93.8	93.9	93.6	92.5
66.5°	90.8	90.8	91.5	91.7	91.3	90.2
67°	88.7	88.5	89.2	89.4	89.0	88.0



TEST NUMBER: P991368

CATALOG NUMBER: SMD4R07FS5-927

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
67.5°	86.4	86.3	87.0	87.2	86.8	85.7
68°	84.2	84.1	84.8	84.9	84.5	83.4
68.5°	82.0	81.9	82.6	82.7	82.2	81.2
69°	79.7	79.6	80.3	80.4	80.0	78.9
69.5°	77.5	77.4	78.1	78.2	77.7	76.7
70°	75.3	75.2	75.9	75.9	75.5	74.4
70.5°	73.1	72.9	73.6	73.7	73.3	72.2
71°	70.9	70.7	71.5	71.5	71.0	70.0
71.5°	68.7	68.6	69.2	69.3	68.8	67.7
72°	66.5	66.3	67.0	67.0	66.6	65.5
72.5°	64.3	64.1	64.8	64.8	64.3	63.3
73°	62.1	61.9	62.6	62.6	62.1	61.1
73.5°	59.9	59.8	60.4	60.4	59.9	58.9
74°	57.8	57.5	58.2	58.3	57.8	56.7
74.5°	55.6	55.4	56.0	56.1	55.6	54.5
75°	53.5	53.3	53.9	53.9	53.5	52.4
75.5°	51.3	51.2	51.8	51.8	51.3	50.2
76°	49.2	49.0	49.6	49.7	49.1	48.1
76.5°	47.1	47.0	47.5	47.5	47.0	45.9
77°	45.0	44.9	45.4	45.4	44.9	43.9
77.5°	43.0	42.8	43.3	43.3	42.8	41.8
78°	40.9	40.7	41.3	41.3	40.8	39.7
78.5°	38.9	38.7	39.2	39.2	38.7	37.7
79°	36.8	36.7	37.2	37.2	36.6	35.7
79.5°	34.8	34.8	35.3	35.3	34.7	33.7
80°	32.9	32.9	33.3	33.3	32.7	31.8
80.5°	30.9	30.9	31.4	31.4	30.8	29.8
81°	29.0	29.0	29.4	29.4	28.8	27.8
81.5°	27.1	27.1	27.5	27.4	26.9	25.9
82°	25.2	25.2	25.6	25.6	25.0	24.0
82.5°	23.3	23.4	23.7	23.7	23.1	22.1
83°	21.5	21.5	21.9	21.8	21.2	20.2
83.5°	19.7	19.7	20.1	20.0	19.4	18.4
84°	17.9	17.9	18.3	18.2	17.6	16.6
84.5°	16.2	16.2	16.5	16.4	15.8	14.8
85°	14.4	14.4	14.7	14.6	14.0	13.0
85.5°	12.7	12.7	13.0	12.9	12.3	11.3
86°	11.0	11.0	11.3	11.2	10.6	9.6
86.5°	9.4	9.3	9.6	9.4	8.9	7.9
87°	7.7	7.7	8.0	7.8	7.2	6.3
87.5°	6.1	6.0	6.3	6.2	5.6	4.7
88°	4.5	4.4	4.7	4.6	4.0	3.2
88.5°	2.9	3.6	3.1	3.0	3.0	2.4
89°	1.6	2.7	2.3	2.2	2.1	1.6
89.5°	0.8	1.8	1.6	1.5	1.1	0.8



TEST NUMBER: P991368

CATALOG NUMBER: SMD4R07FS5-927

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
90°	0.3	0.9	0.8	0.7	0.1	0.0
90.5°	0.0	0.0	0.0	0.0	0.0	0.0
91°	0.0	0.0	0.0	0.0	0.0	0.0
91.5°	0.0	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.1
111.5°	0.0	0.0	0.0	0.0	0.1	0.1
112°	0.0	0.0	0.0	0.0	0.1	0.1



TEST NUMBER: P991368

CATALOG NUMBER: SMD4R07FS5-927

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	0.0	0.1	0.1	0.1	0.1	0.1
113°	0.0	0.1	0.1	0.1	0.1	0.1
113.5°	0.0	0.1	0.1	0.1	0.1	0.1
114°	0.0	0.1	0.1	0.1	0.1	0.1
114.5°	0.0	0.1	0.1	0.1	0.1	0.1
115°	0.0	0.1	0.1	0.1	0.1	0.1
115.5°	0.0	0.1	0.1	0.1	0.1	0.1
116°	0.1	0.1	0.1	0.1	0.1	0.1
116.5°	0.1	0.1	0.1	0.1	0.1	0.1
117°	0.1	0.1	0.1	0.1	0.1	0.1
117.5°	0.1	0.1	0.1	0.1	0.1	0.1
118°	0.1	0.1	0.1	0.1	0.1	0.1
118.5°	0.1	0.1	0.1	0.1	0.1	0.1
119°	0.1	0.1	0.1	0.1	0.1	0.1
119.5°	0.1	0.1	0.1	0.1	0.1	0.1
120°	0.1	0.1	0.1	0.1	0.1	0.1
120.5°	0.1	0.1	0.1	0.1	0.1	0.1
121°	0.1	0.1	0.1	0.1	0.1	0.1
121.5°	0.1	0.1	0.1	0.1	0.1	0.1
122°	0.1	0.1	0.1	0.1	0.1	0.1
122.5°	0.1	0.1	0.1	0.1	0.1	0.1
123°	0.1	0.1	0.1	0.1	0.1	0.1
123.5°	0.1	0.1	0.1	0.1	0.1	0.1
124°	0.1	0.1	0.1	0.1	0.1	0.1
124.5°	0.1	0.1	0.1	0.1	0.1	0.1
125°	0.1	0.1	0.1	0.1	0.1	0.1
125.5°	0.1	0.1	0.1	0.1	0.1	0.1
126°	0.1	0.1	0.1	0.1	0.1	0.1
126.5°	0.1	0.1	0.1	0.1	0.1	0.1
127°	0.1	0.1	0.1	0.1	0.1	0.1
127.5°	0.1	0.1	0.1	0.1	0.1	0.1
128°	0.1	0.1	0.1	0.1	0.1	0.1
128.5°	0.1	0.1	0.1	0.1	0.1	0.1
129°	0.1	0.1	0.1	0.1	0.1	0.1
129.5°	0.1	0.1	0.1	0.1	0.1	0.1
130°	0.1	0.1	0.1	0.1	0.1	0.1
130.5°	0.1	0.1	0.1	0.1	0.1	0.1
131°	0.1	0.1	0.1	0.1	0.1	0.1
131.5°	0.1	0.1	0.1	0.1	0.1	0.1
132°	0.1	0.1	0.1	0.1	0.1	0.1
132.5°	0.1	0.1	0.1	0.1	0.1	0.1
133°	0.1	0.1	0.1	0.1	0.1	0.1
133.5°	0.1	0.1	0.1	0.1	0.1	0.1
134°	0.1	0.1	0.1	0.1	0.1	0.1
134.5°	0.1	0.1	0.1	0.1	0.1	0.1



TEST NUMBER: P991368

CATALOG NUMBER: SMD4R07FS5-927

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
135°	0.1	0.1	0.1	0.1	0.1	0.1
135.5°	0.1	0.1	0.1	0.1	0.1	0.1
136°	0.1	0.1	0.1	0.1	0.1	0.1
136.5°	0.1	0.1	0.1	0.1	0.1	0.1
137°	0.1	0.1	0.1	0.1	0.1	0.1
137.5°	0.1	0.1	0.1	0.1	0.1	0.1
138°	0.1	0.1	0.1	0.1	0.1	0.1
138.5°	0.1	0.1	0.1	0.1	0.1	0.1
139°	0.1	0.1	0.1	0.1	0.1	0.1
139.5°	0.1	0.1	0.1	0.1	0.1	0.1
140°	0.1	0.1	0.1	0.1	0.1	0.1
140.5°	0.1	0.1	0.1	0.1	0.1	0.1
141°	0.1	0.1	0.1	0.1	0.1	0.1
141.5°	0.1	0.1	0.1	0.1	0.1	0.1
142°	0.1	0.1	0.1	0.1	0.1	0.1
142.5°	0.2	0.1	0.1	0.1	0.1	0.1
143°	0.2	0.1	0.1	0.1	0.1	0.1
143.5°	0.2	0.1	0.1	0.1	0.1	0.1
144°	0.2	0.1	0.1	0.1	0.1	0.1
144.5°	0.2	0.1	0.1	0.1	0.1	0.1
145°	0.2	0.1	0.1	0.1	0.1	0.1
145.5°	0.2	0.1	0.1	0.1	0.1	0.1
146°	0.2	0.1	0.1	0.1	0.1	0.1
146.5°	0.2	0.1	0.1	0.1	0.1	0.1
147°	0.2	0.1	0.1	0.1	0.1	0.2
147.5°	0.2	0.1	0.1	0.1	0.1	0.2
148°	0.2	0.1	0.1	0.1	0.1	0.2
148.5°	0.2	0.1	0.1	0.1	0.2	0.2
149°	0.2	0.1	0.1	0.1	0.2	0.2
149.5°	0.2	0.1	0.1	0.1	0.2	0.2
150°	0.2	0.1	0.1	0.1	0.2	0.2
150.5°	0.2	0.1	0.1	0.1	0.2	0.2
151°	0.2	0.1	0.1	0.1	0.2	0.2
151.5°	0.2	0.1	0.1	0.1	0.2	0.2
152°	0.2	0.1	0.1	0.1	0.2	0.2
152.5°	0.2	0.1	0.1	0.1	0.2	0.2
153°	0.2	0.1	0.1	0.1	0.2	0.2
153.5°	0.2	0.1	0.1	0.1	0.2	0.2
154°	0.2	0.1	0.1	0.1	0.2	0.2
154.5°	0.2	0.1	0.1	0.1	0.2	0.2
155°	0.2	0.1	0.1	0.1	0.2	0.2
155.5°	0.2	0.1	0.1	0.1	0.2	0.2
156°	0.2	0.1	0.1	0.1	0.2	0.2
156.5°	0.2	0.1	0.1	0.1	0.2	0.2
157°	0.2	0.1	0.1	0.1	0.2	0.2



TEST NUMBER: P991368

CATALOG NUMBER: SMD4R07FS5-927

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
157.5°	0.2	0.1	0.1	0.2	0.2	0.2
158°	0.2	0.1	0.1	0.2	0.2	0.2
158.5°	0.2	0.1	0.1	0.2	0.2	0.2
159°	0.2	0.1	0.1	0.2	0.2	0.2
159.5°	0.2	0.1	0.1	0.2	0.2	0.2
160°	0.2	0.1	0.2	0.2	0.2	0.2
160.5°	0.2	0.1	0.2	0.2	0.2	0.2
161°	0.2	0.2	0.2	0.2	0.2	0.2
161.5°	0.2	0.2	0.2	0.2	0.2	0.2
162°	0.2	0.2	0.2	0.2	0.2	0.2
162.5°	0.2	0.2	0.2	0.2	0.2	0.2
163°	0.2	0.2	0.2	0.2	0.2	0.2
163.5°	0.2	0.2	0.2	0.2	0.2	0.2
164°	0.2	0.2	0.2	0.2	0.2	0.2
164.5°	0.2	0.2	0.2	0.2	0.2	0.2
165°	0.2	0.2	0.2	0.2	0.2	0.2
165.5°	0.2	0.2	0.2	0.2	0.2	0.2
166°	0.2	0.2	0.2	0.2	0.2	0.2
166.5°	0.2	0.2	0.2	0.2	0.2	0.2
167°	0.3	0.2	0.2	0.2	0.2	0.2
167.5°	0.3	0.2	0.2	0.2	0.2	0.2
168°	0.3	0.2	0.2	0.2	0.2	0.2
168.5°	0.2	0.2	0.2	0.2	0.2	0.2
169°	0.2	0.2	0.2	0.2	0.2	0.2
169.5°	0.2	0.2	0.2	0.2	0.2	0.2
170°	0.2	0.2	0.2	0.2	0.2	0.2
170.5°	0.2	0.2	0.2	0.2	0.2	0.2
171°	0.2	0.2	0.2	0.2	0.2	0.2
171.5°	0.2	0.2	0.2	0.2	0.2	0.2
172°	0.2	0.2	0.2	0.2	0.2	0.2
172.5°	0.2	0.2	0.2	0.2	0.2	0.2
173°	0.2	0.2	0.2	0.2	0.2	0.2
173.5°	0.2	0.2	0.2	0.2	0.2	0.2
174°	0.2	0.2	0.2	0.2	0.2	0.2
174.5°	0.2	0.2	0.2	0.2	0.2	0.2
175°	0.2	0.2	0.2	0.2	0.2	0.2
175.5°	0.2	0.2	0.2	0.2	0.2	0.2
176°	0.2	0.2	0.2	0.2	0.2	0.2
176.5°	0.2	0.2	0.2	0.2	0.2	0.2
177°	0.2	0.2	0.2	0.2	0.2	0.2
177.5°	0.2	0.2	0.2	0.2	0.2	0.2
178°	0.2	0.2	0.2	0.2	0.2	0.2
178.5°	0.2	0.2	0.2	0.2	0.2	0.2
179°	0.2	0.2	0.2	0.2	0.2	0.2
179.5°	0.2	0.2	0.2	0.2	0.2	0.2



TEST NUMBER: P991368
CATALOG NUMBER: SMD4R07FS5-927

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
180°	0.2	0.2	0.2	0.2	0.2	0.2

(END OF REPORT)