

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P990593

Luminaire Tested: **ML2ALSFL9FS1E-TIR1D40FL-TL2RDMB-550LM-3000K**

Issue Date: 5/13/2025

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P990593
 Test Lab: Cooper Lighting Solutions
 Issue Date: 5/13/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: ML2ALSFL9FS1E-TIR1D40FL-TL2RDMB-550LM-3000K
 Description: 2IN ROUND ML FLEX ADJUSTABLE, SELECTABLE CCT, WITH 40D TIR, MATTE BLACK TRIM
 Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 523.7 lumens
 Efficiency: N/A
 Efficacy: 68.9 lumens/watt
 Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.69
 Luminous Opening: Circular (Dia: 0.17' x H: 0')
 CIE Type: Direct

Input Watts (W): 7.6
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P990593
CATALOG NUMBER: ML2ALSFL9FS1E-TIR1D40FL-TL2RDMB-550LM-3000K

Luminous Intensity Polar Plot



TEST NUMBER: P990593

CATALOG NUMBER: ML2ALSFL9FS1E-TIR1D40FL-TL2RDMB-550LM-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			0
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			100
1	114	111	108	106	111	109	106	104		105	103	101			101	99	98			94
2	108	103	99	96	106	101	98	95		98	95	93			95	93	91			87
3	103	96	92	88	101	95	91	87		92	89	86			90	87	84			81
4	98	90	85	81	96	89	84	80		87	83	79			85	81	78			76
5	93	85	79	75	91	84	79	75		82	78	74			81	77	73			71
6	89	80	74	70	87	79	74	70		78	73	69			76	72	69			67
7	85	76	70	66	83	75	70	66		74	69	65			73	68	65			63
8	81	72	66	62	80	71	66	62		70	65	62			69	65	61			60
9	77	68	62	59	76	68	62	59		67	62	58			66	61	58			57
10	74	65	59	56	73	64	59	56		64	59	55			63	58	55			54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	422530
5°	409633
10°	370833
15°	310710
20°	240207
25°	171535
30°	116334
35°	74385
40°	45857
45°	28468
50°	18498
55°	12645
60°	9276
65°	8522
70°	6059
75°	4003
80°	0
85°	0

TEST NUMBER: P990593

CATALOG NUMBER: ML2ALSFL9FS1E-TIR1D40FL-TL2RDDB-550LM-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.2	14.5
10°-20°	167.3	31.9
20°-30°	145.3	27.8
30°-40°	79.2	15.1
40°-50°	33.1	6.3
50°-60°	13.7	2.6
60°-70°	6.8	1.3
70°-80°	2.2	0.4
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	388.8	74.2
0°-40°	467.9	89.3
0°-60°	514.7	98.3
0°-90°	523.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	523.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	856	
5°	827	76
15°	608	167
25°	315	145
35°	124	79
45°	41	33
55°	15	14
65°	7	7
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P990593
CATALOG NUMBER: ML2ALSFL9FS1E-TIR1D40FL-TL2RDMB-550LM-3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	856.4
2.5°	850.1
5°	827.1
7.5°	789.4
10°	740.2
12.5°	678.4
15°	608.3
17.5°	532.9
20°	457.5
22.5°	383.2
25°	315.1
27.5°	256.5
30°	204.2
32.5°	159.1
35°	123.5
37.5°	94.2
40°	71.2
42.5°	53.4
45°	40.8
47.5°	31.4
50°	24.1
52.5°	18.8
55°	14.7
57.5°	11.5
60°	9.4
62.5°	8.4
65°	7.3
67.5°	5.2
70°	4.2
72.5°	3.1
75°	2.1
77.5°	1.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)