

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P990640

Luminaire Tested: **ML2ALSFL9FS1E-TIR1D55WFL-TL2RDMW-550LM-4000K**

Issue Date: 5/13/2025

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P990640
 Test Lab: Cooper Lighting Solutions
 Issue Date: 5/13/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: ML2ALSFL9FS1E-TIR1D55WFL-TL2RDMW-550LM-4000K
 Description: 2IN ROUND ML FLEX ADJUSTABLE, SELECTABLE CCT, WITH 55D TIR, MATTE WHITE TRIM
 Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 4000K CCT
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 547.8 lumens
 Efficiency: N/A
 Efficacy: 72.1 lumens/watt
 Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.81
 Luminous Opening: Circular (Dia: 0.17' x H: 0')
 CIE Type: Direct

Input Watts (W): 7.6
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P990640
CATALOG NUMBER: ML2ALSFL9FS1E-TIR1D55WFL-TL2RDMW-550LM-4000K

Luminous Intensity Polar Plot



TEST NUMBER: P990640

CATALOG NUMBER: ML2ALSFL9FS1E-TIR1D55WFL-TL2RDMW-550LM-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86
4	96	88	82	78	94	87	82	77	85	80	77		83	79	76		81
5	91	82	76	72	89	81	76	71	80	75	71		78	74	70		76
6	86	77	71	66	85	76	71	66	75	70	66		73	69	65		72
7	82	72	66	62	81	72	66	62	70	65	61		69	65	61		68
8	78	68	62	58	77	68	62	58	67	61	57		66	61	57		65
9	74	64	58	54	73	64	58	54	63	58	54		62	57	54		61
10	71	61	55	51	70	61	55	51	60	54	51		59	54	51		58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	323213
5°	318455
10°	304502
15°	280165
20°	242360
25°	193855
30°	140262
35°	94682
40°	60155
45°	36841
50°	23641
55°	16085
60°	13025
65°	11558
70°	9521
75°	6291
80°	3125
85°	0

TEST NUMBER: P990640
 CATALOG NUMBER: ML2ALSFL9FS1E-TIR1D55WFL-TL2RDMW-550LM-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.3	11.0
10°-20°	151.8	27.7
20°-30°	161.5	29.5
30°-40°	99.9	18.2
40°-50°	42.7	7.8
50°-60°	17.9	3.3
60°-70°	9.5	1.7
70°-80°	3.9	0.7
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	373.6	68.2
0°-40°	473.4	86.4
0°-60°	534.0	97.5
0°-90°	547.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	547.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	655	
5°	643	60
15°	548	152
25°	356	162
35°	157	100
45°	53	43
55°	19	18
65°	10	10
75°	3	4
85°	0	0
90°	0	

TEST NUMBER: P990640
CATALOG NUMBER: ML2ALSFL9FS1E-TIR1D55WFL-TL2RDMW-550LM-4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	655.1
2.5°	651.8
5°	643.0
7.5°	628.7
10°	607.8
12.5°	580.4
15°	548.5
17.5°	507.8
20°	461.6
22.5°	411.1
25°	356.1
27.5°	300.1
30°	246.2
32.5°	198.9
35°	157.2
37.5°	122.0
40°	93.4
42.5°	69.2
45°	52.8
47.5°	39.6
50°	30.8
52.5°	24.2
55°	18.7
57.5°	15.4
60°	13.2
62.5°	11.0
65°	9.9
67.5°	7.7
70°	6.6
72.5°	5.5
75°	3.3
77.5°	2.2
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)