

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P30068

Luminaire Tested: **ML706840-492PS06**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P30068
Test Lab: METALUX RESEARCH LABS
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: ML706840-492PS06
Description: HALO RECESSED LED RETROFIT MODULE WITH WHITE TRIM RING &
LENSED SHOWER TRIM
Light Source: HIGH OUPUT LED PACKAGE
LED 14 WATTS
Ballast/Driver: 120V ELECTRONIC DRIVER

Summary


Lumens per Lamp: 499 (1 lamp)
Luminaire Lumens: 500.0 lumens
Efficiency: 100.2%
Efficacy: 36.2 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.23
Luminous Opening: Circular (Dia: 0.4' x H: 0')
CIE Type: Direct

Input Watts (W): 13.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P30068
CATALOG NUMBER: ML706840-492PS06

Luminous Intensity Polar Plot





TEST NUMBER: P30068

CATALOG NUMBER: ML706840-492PS06

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	117	117	117	117	111	111	111		107	107	107		102	102	102	100
1	112	108	105	102	109	106	103	100	101	99	97		98	96	94		94	93	91	89
2	104	97	92	87	101	95	90	86	92	88	84		89	85	82		86	83	81	79
3	96	88	81	76	94	86	80	75	83	78	74		81	76	73		78	75	71	70
4	89	79	72	67	87	78	71	66	76	70	65		74	69	64		72	67	64	62
5	83	72	65	59	81	71	64	59	69	63	58		67	62	58		66	61	57	55
6	78	66	58	53	76	65	58	53	63	57	52		62	56	52		60	55	51	50
7	72	61	53	48	71	60	53	47	58	52	47		57	51	47		56	51	46	45
8	68	56	48	43	66	55	48	43	54	47	43		53	47	43		52	46	42	41
9	64	52	44	39	62	51	44	39	50	44	39		49	43	39		48	43	39	37
10	60	48	41	36	59	47	41	36	47	40	36		46	40	36		45	39	36	34

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	23967
5°	23795
10°	23537
15°	23001
20°	22619
25°	21908
30°	21210
35°	20182
40°	18840
45°	16700
50°	12383
55°	6557
60°	4548
65°	4346
70°	4092
75°	3718
80°	3022
85°	2007



TEST NUMBER: P30068

CATALOG NUMBER: ML706840-492PS06

ZONAL LUMENS:

Zone	Lumens	% Fixture	% Lamp
0°-10°	25.7	5.1	5.2
10°-20°	71.8	14.4	14.4
20°-30°	104.6	20.9	21.0
30°-40°	117.8	23.6	23.6
40°-50°	101.9	20.4	20.4
50°-60°	43.7	8.7	8.8
60°-70°	20.5	4.1	4.1
70°-80°	11.6	2.3	2.3
80°-90°	2.4	0.5	0.5
90°-100°	0.0	0.0	0.0
100°-110°	0.0	0.0	0.0
110°-120°	0.0	0.0	0.0
120°-130°	0.0	0.0	0.0
130°-140°	0.0	0.0	0.0
140°-150°	0.0	0.0	0.0
150°-160°	0.0	0.0	0.0
160°-170°	0.0	0.0	0.0
170°-180°	0.0	0.0	0.0
0°-30°	202.0	40.4	40.5
0°-40°	319.8	64.0	64.1
0°-60°	465.4	93.1	93.3
0°-90°	500.0	100.0	100.2
90°-120°	0.0	0.0	0.0
90°-150°	0.0	0.0	0.0
90°-180°	0.0	0.0	0.0
0°-180°	500.0	100.0	100.2

CANDELA DISTRIBUTION:

0°	Flux
0°	274
5°	271
15°	254
25°	227
35°	189
45°	135
55°	43
65°	21
75°	11
85°	2
90°	0
95°	0
105°	0
115°	0
125°	0
135°	0
145°	0
155°	0
165°	0
175°	0
180°	0



TEST NUMBER: P30068

CATALOG NUMBER: ML706840-492PS06

CANDELA DISTRIBUTION (FULL):

	0°
0°	274
2.5°	274
5°	271
7.5°	269
10°	265
12.5°	260
15°	254
17.5°	249
20°	243
22.5°	235
25°	227
27.5°	219
30°	210
32.5°	200
35°	189
37.5°	177
40°	165
42.5°	151
45°	135
47.5°	116
50°	91
52.5°	64
55°	43
57.5°	32
60°	26
62.5°	23
65°	21
67.5°	18
70°	16
72.5°	14
75°	11
77.5°	8
80°	6
82.5°	4
85°	2
87.5°	0
90°	0
92.5°	0
95°	0
97.5°	0
100°	0
102.5°	0
105°	0
107.5°	0
110°	0



TEST NUMBER: P30068

CATALOG NUMBER: ML706840-492PS06

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0
115°	0
117.5°	0
120°	0
122.5°	0
125°	0
127.5°	0
130°	0
132.5°	0
135°	0
137.5°	0
140°	0
142.5°	0
145°	0
147.5°	0
150°	0
152.5°	0
155°	0
157.5°	0
160°	0
162.5°	0
165°	0
167.5°	0
170°	0
172.5°	0
175°	0
177.5°	0
180°	0

(END OF REPORT)