

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P20232

Luminaire Tested: **ML709835T120DEM – 494SC06 – H750TEM912**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P20232
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (P20232)
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: ML709835T120DEM – 494SC06 – H750TEM912
Description: HALO 6" RECESSED LED DOWNLIGHT WITH SPECULAR CLEAR TRIM
Light Source: HIGHT OUTPUT LED
Ballast/Driver: IOTA BATTERY PACK

Summary

Lumens per Lamp: 600 (1 lamp)
Luminaire Lumens: 599.9 lumens
Efficiency: 100.0%
Efficacy: 64.5 lumens/watt
Spacing Criteria (0/90/45): 1.57 / 1.57 / 1.4
Luminous Opening: Vertical Cylinder (Dia: 0.5' x H: 0.1')
CIE Type: Direct


Input Watts (W): 9.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P20232

CATALOG NUMBER: ML709835T120DEM – 494SC06 – H750TEM912

Luminous Intensity Polar Plot





TEST NUMBER: P20232

CATALOG NUMBER: ML709835T120DEM – 494SC06 – H750TEM912

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75
4	93	84	77	72	91	82	76	72	80	75	71	78	73	70	76	72	69	67
5	87	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62	61
6	81	70	63	58	79	69	63	58	68	62	57	66	61	57	65	60	57	55
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50
8	71	60	52	48	70	59	52	47	58	52	47	57	51	47	56	51	47	45
9	66	55	48	43	65	55	48	43	53	47	43	52	47	43	52	46	43	41
10	63	51	44	40	61	51	44	40	50	44	39	49	43	39	48	43	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	15580
5°	15788
10°	16701
15°	17320
20°	16845
25°	16534
30°	17141
35°	17487
40°	16262
45°	11994
50°	3428
55°	98
60°	53
65°	59
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P20232

CATALOG NUMBER: ML709835T120DEM – 494SC06 – H750TEM912

ZONAL LUMENS:

Zone	Lumens	% Fixture	% Lamp
0°-10°	28.7	4.8	4.8
10°-20°	91.1	15.2	15.2
20°-30°	143.0	23.8	23.8
30°-40°	189.7	31.6	31.6
40°-50°	137.0	22.8	22.8
50°-60°	9.8	1.6	1.6
60°-70°	0.6	0.1	0.1
70°-80°	0.0	0.0	0.0
80°-90°	0.0	0.0	0.0
90°-100°	0.0	0.0	0.0
100°-110°	0.0	0.0	0.0
110°-120°	0.0	0.0	0.0
120°-130°	0.0	0.0	0.0
130°-140°	0.0	0.0	0.0
140°-150°	0.0	0.0	0.0
150°-160°	0.0	0.0	0.0
160°-170°	0.0	0.0	0.0
170°-180°	0.0	0.0	0.0
0°-30°	262.8	43.8	43.8
0°-40°	452.5	75.4	75.4
0°-60°	599.3	99.9	99.9
0°-90°	599.9	100.0	100.0
90°-120°	0.0	0.0	0.0
90°-150°	0.0	0.0	0.0
90°-180°	0.0	0.0	0.0
0°-180°	599.9	100.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	284	
5°	293	29
15°	326	91
25°	306	143
35°	308	190
45°	194	137
55°	1	10
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P20232

CATALOG NUMBER: ML709835T120DEM – 494SC06 – H750TEM912

CANDELA DISTRIBUTION (FULL):

	0°
0°	284.2
2.5°	286.9
5°	293.3
7.5°	305.1
10°	313.5
12.5°	322.5
15°	326.0
17.5°	321.8
20°	315.5
22.5°	309.2
25°	305.8
27.5°	307.9
30°	310.6
32.5°	312.1
35°	307.9
37.5°	297.4
40°	275.8
42.5°	244.3
45°	194.1
47.5°	117.9
50°	52.4
52.5°	16.7
55°	1.4
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)