

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P20265

Luminaire Tested: **ML709840ICAT120D-494SC06**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P20265
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: ML709840ICAT120D-494SC06
Description: HALO 6" RECESSED LED DOWNLIGHT WITH SPECULAR CLEAR TRIM
REFLECTOR WITH MODULE
Light Source: HIGHT OUTPUT LED
LED 14 WATTS
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: 923 (1 lamp)
Luminaire Lumens: 923.8 lumens
Efficiency: 100.1%
Efficacy: 66.0 lumens/watt
Spacing Criteria (0/90/45): 1.58 / 1.58 / 1.41
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P20265

CATALOG NUMBER: ML709840ICAT120D-494SC06

Luminous Intensity Polar Plot





TEST NUMBER: P20265

CATALOG NUMBER: ML709840ICAT120D-494SC06

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96	95	93	92
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	87	85	83
3	99	91	86	81	97	90	85	80	87	83	79		85	81	78		82	79	76	75
4	93	84	77	72	91	82	76	72	80	75	71		78	74	70		76	72	69	67
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70	66	62	61
6	81	70	63	58	79	69	63	58	68	62	57		66	61	57		65	60	57	55
7	76	65	57	52	74	64	57	52	63	56	52		61	56	52		60	55	51	50
8	71	60	52	48	70	59	52	47	58	52	47		57	51	47		56	51	47	45
9	67	55	48	43	65	55	48	43	54	47	43		53	47	43		52	46	43	41
10	63	51	44	40	61	51	44	40	50	44	39		49	43	39		48	43	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	23902
5°	24763
10°	26831
15°	28320
20°	28294
25°	28490
30°	30258
35°	31922
40°	30414
45°	23336
50°	6738
55°	191
60°	110
65°	130
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P20265

CATALOG NUMBER: ML709840ICAT120D-494SC06

ZONAL LUMENS:

Zone	Lumens	% Fixture	% Lamp
0°-10°	44.1	4.8	4.8
10°-20°	139.7	15.1	15.1
20°-30°	220.0	23.8	23.8
30°-40°	293.3	31.8	31.8
40°-50°	210.9	22.8	22.8
50°-60°	14.9	1.6	1.6
60°-70°	0.9	0.1	0.1
70°-80°	0.0	0.0	0.0
80°-90°	0.0	0.0	0.0
90°-100°	0.0	0.0	0.0
100°-110°	0.0	0.0	0.0
110°-120°	0.0	0.0	0.0
120°-130°	0.0	0.0	0.0
130°-140°	0.0	0.0	0.0
140°-150°	0.0	0.0	0.0
150°-160°	0.0	0.0	0.0
160°-170°	0.0	0.0	0.0
170°-180°	0.0	0.0	0.0
0°-30°	403.8	43.7	43.8
0°-40°	697.2	75.5	75.5
0°-60°	922.9	99.9	100.0
0°-90°	923.8	100.0	100.1
90°-120°	0.0	0.0	0.0
90°-150°	0.0	0.0	0.0
90°-180°	0.0	0.0	0.0
0°-180°	923.8	100.0	100.1

CANDELA DISTRIBUTION:

	0°	Flux
0°	436	
5°	450	44
15°	499	140
25°	471	220
35°	477	293
45°	301	211
55°	2	15
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P20265

CATALOG NUMBER: ML709840ICAT120D-494SC06

CANDELA DISTRIBUTION (FULL):

	0°
0°	436
2.5°	440
5°	450
7.5°	469
10°	482
12.5°	495
15°	499
17.5°	494
20°	485
22.5°	475
25°	471
27.5°	474
30°	478
32.5°	482
35°	477
37.5°	461
40°	425
42.5°	377
45°	301
47.5°	179
50°	79
52.5°	25
55°	2
57.5°	2
60°	1
62.5°	1
65°	1
67.5°	1
70°	0
72.5°	0
75°	0
77.5°	0
80°	0
82.5°	0
85°	0
87.5°	0
90°	0

(END OF REPORT)