

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P601318

Luminaire Tested: **ML410LSWFL9FS1E - TIR4D55WFL - TL43R2G_ TL44S2G_ 5000K**

Issue Date: 7/29/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P601318
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 7/29/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: ML410LSWFL9FS1E - TIR4D55WFL - TL43R2G_ TL44S2G_ 5000K
 Description: RETROFIT, 55D OPTIC, DIFFUSE CLEAR LENS TRIM
 Light Source: (1) SELECTABLE LUMEN LED 90CRI / 5000K CCT
 Ballast/Driver: -

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 1207.8 lumens
 Efficiency: N/A
 Efficacy: 100.6 lumens/watt
 Spacing Criteria (0/90/45): 0.9 / 0.9 / 0.83
 Luminous Opening: Circular (Dia: 0.21' x H: 0')
 CIE Type: Direct


Input Watts (W): 12
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



Meas			
Instrument	Identificatio		Calibration Due Date
Photometer	GONIO 1 11111111	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P601318
CATALOG NUMBER: ML410LSWFL9FS1E - TIR4D55WFL - TL43R2G_ TL44S2G_ 5000K

Luminous Intensity Polar Plot



TEST NUMBER: P601318

CATALOG NUMBER: ML410LSWFL9FS1E - TIR4D55WFL - TL43R2G_ TL44S2G_ 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88
3	103	97	92	89	101	96	91	88	93	89	86	91	88	85	89	86	84	82
4	98	91	86	82	97	90	85	81	88	84	80	86	82	79	84	81	79	77
5	94	86	80	76	92	85	80	76	83	78	75	81	77	74	80	76	74	72
6	89	81	75	71	88	80	75	71	78	74	70	77	73	70	76	72	69	68
7	85	76	70	66	84	76	70	66	74	69	66	73	69	66	72	68	65	64
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60
9	77	68	63	59	76	68	62	59	67	62	58	66	61	58	65	61	58	57
10	74	65	59	55	73	64	59	55	64	59	55	63	58	55	62	58	55	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	471627
5°	468642
10°	462454
15°	439915
20°	399977
25°	328514
30°	224967
35°	119807
40°	57832
45°	26258
50°	11839
55°	5836
60°	2842
65°	1121
70°	1385
75°	1830
80°	0
85°	0

TEST NUMBER: P601318

CATALOG NUMBER: ML410LSWFL9FS1E - TIR4D55WFL - TL43R2G_ TL44S2G_ 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	140.0	11.6
10°-20°	375.6	31.1
20°-30°	421.2	34.9
30°-40°	206.6	17.1
40°-50°	50.9	4.2
50°-60°	10.2	0.8
60°-70°	2.2	0.2
70°-80°	1.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	936.9	77.6
0°-40°	1143.5	94.7
0°-60°	1204.6	99.7
0°-90°	1207.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1207.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1494	
5°	1478	140
15°	1346	376
25°	943	421
35°	311	207
45°	59	51
55°	11	10
65°	2	2
75°	2	1
85°	0	0
90°	0	

TEST NUMBER: P601318
CATALOG NUMBER: ML410LSWFL9FS1E - TIR4D55WFL - TL43R2G_ TL44S2G_ 5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1493.6
2.5°	1481.5
5°	1478.5
7.5°	1466.4
10°	1442.3
12.5°	1404.6
15°	1345.7
17.5°	1283.9
20°	1190.3
22.5°	1078.7
25°	942.9
27.5°	783.0
30°	617.0
32.5°	454.1
35°	310.8
37.5°	209.7
40°	140.3
42.5°	92.0
45°	58.8
47.5°	36.2
50°	24.1
52.5°	15.1
55°	10.6
57.5°	6.0
60°	4.5
62.5°	3.0
65°	1.5
67.5°	1.5
70°	1.5
72.5°	1.5
75°	1.5
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)