

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P601248

Luminaire Tested: **ML408LSFL95FS1E - TIR4D40FL - TL41R_ TL42S_ 5000K**

Issue Date: 7/29/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P601248
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 7/29/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: ML408LSFL95FS1E - TIR4D40FL - TL41R_ TL42S_ 5000K
 Description: RETROFIT, 40D OPTIC, OPEN TRIM
 Light Source: (1) SELECTABLE LUMEN LED 95CRI / 5000K CCT
 Ballast/Driver: -

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 1098.6 lumens
 Efficiency: N/A
 Efficacy: 106.7 lumens/watt
 Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.63
 Luminous Opening: Circular (Dia: 0.21' x H: 0')
 CIE Type: Direct


Input Watts (W): 10.3
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



Meas		Calibration Due Date	
Instrument	Identificatio		
Photometer	GONIO 1 11111111	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P601248
CATALOG NUMBER: ML408LSFL95FS1E - TIR4D40FL - TL41R_ TL42S_ 5000K

Luminous Intensity Polar Plot





TEST NUMBER: P601248
 CATALOG NUMBER: ML408LSFL95FS1E - TIR4D40FL - TL41R_ TL42S_ 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	93	92	95
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90	91	89	87	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	88	85	83	86
4	101	95	90	86	99	94	89	86	92	88	85	90	87	84	88	85	83	82	86	82	80	82
5	97	90	85	81	96	89	85	81	87	83	80	86	82	80	84	81	79	78	84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76	82	79	76	81	78	75	74	81	78	75	74
7	90	82	77	73	89	81	77	73	80	76	73	79	75	72	78	75	72	71	78	75	72	71
8	86	78	73	70	85	78	73	70	77	73	69	76	72	69	75	72	69	68	75	72	69	68
9	83	75	70	67	82	75	70	67	74	69	66	73	69	66	72	69	66	65	72	69	66	65
10	80	72	67	64	79	72	67	64	71	67	64	70	66	63	70	66	63	62	70	66	63	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	728281
5°	706022
10°	646178
15°	549853
20°	398801
25°	227162
30°	108072
35°	56357
40°	28236
45°	13531
50°	7762
55°	3633
60°	821
65°	971
70°	0
75°	0
80°	0
85°	0

TEST NUMBER: P601248
 CATALOG NUMBER: ML408LSFL95FS1E - TIR4D40FL - TL41R_ TL42S_ 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	206.2	18.8
10°-20°	456.5	41.6
20°-30°	304.5	27.7
30°-40°	97.6	8.9
40°-50°	26.5	2.4
50°-60°	6.5	0.6
60°-70°	0.8	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	967.2	88.0
0°-40°	1064.8	96.9
0°-60°	1097.8	99.9
0°-90°	1098.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1098.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2306	
5°	2227	206
15°	1682	456
25°	652	305
35°	146	98
45°	30	27
55°	7	7
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P601248
CATALOG NUMBER: ML408LSFL95FS1E - TIR4D40FL - TL41R_ TL42S_ 5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2306.4
1°	2305.1
2°	2310.3
3°	2280.1
4°	2261.6
5°	2227.4
6°	2199.7
7°	2157.6
8°	2123.3
9°	2068.0
10°	2015.3
11°	1967.9
12°	1898.1
13°	1833.5
14°	1761.1
15°	1682.0
17.5°	1456.8
20°	1186.8
22.5°	901.0
25°	652.0
27.5°	442.6
30°	296.4
32.5°	205.5
35°	146.2
37.5°	104.1
40°	68.5
42.5°	44.8
45°	30.3
47.5°	22.4
50°	15.8
52.5°	10.5
55°	6.6
57.5°	4.0
60°	1.3
62.5°	1.3
65°	1.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0


Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


NVLAP Lab Code: 200050-0



TEST NUMBER: P601248
CATALOG NUMBER: ML408LSFL95FS1E - TIR4D40FL - TL41R_ TL42S_ 5000K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)