

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P997191

Luminaire Tested: **SMX6RLSFS010-900LM-2700K**

Issue Date: 3/11/2025

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P997191
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (A2410866A001)
Test Lab:
Issue Date: 3/11/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: SMX6RLSFS010-900LM-2700K
Description: 6IN ROUND, 90CRI, 0-10V DIMMING, DAMP LOCATION
Light Source: SELECTABLE CCT 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 891.5 lumens
Efficiency: N/A
Efficacy: 103.7 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.39
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P997191

CATALOG NUMBER: SMX6RLSFS010-900LM-2700K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997191

CATALOG NUMBER: SMX6RLSFS010-900LM-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	109	104	100	96	106	102	98	94	97	94	91	93	91	88	90	88	86	84		
2	99	90	83	78	96	88	82	77	85	80	75	82	77	73	79	75	72	69		
3	90	79	71	64	87	78	70	64	75	68	63	72	66	61	69	64	60	58		
4	82	70	61	54	80	69	60	54	66	59	53	64	58	52	62	56	52	50		
5	75	62	53	47	73	61	53	46	59	52	46	57	51	45	55	50	45	43		
6	70	56	47	41	68	55	47	40	53	46	40	52	45	40	50	44	39	37		
7	65	51	42	36	63	50	42	36	49	41	35	47	40	35	46	40	35	33		
8	60	46	38	32	58	46	37	32	44	37	32	43	36	31	42	36	31	29		
9	56	43	34	29	55	42	34	29	41	34	28	40	33	28	39	33	28	26		
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	16780	16780	16780	16780
5°	16790	16784	16790	16784
10°	16767	16767	16767	16767
15°	16725	16731	16725	16731
20°	16679	16679	16679	16679
25°	16610	16604	16610	16604
30°	16528	16528	16528	16528
35°	16423	16423	16423	16423
40°	16309	16302	16309	16302
45°	16164	16164	16164	16164
50°	15974	15965	15974	15965
55°	15713	15732	15713	15732
60°	15361	15361	15361	15361
65°	14852	14839	14852	14839
70°	14025	14025	14025	14025
75°	12772	12814	12772	12814
80°	10828	10797	10828	10797
85°	7737	7674	7737	7674



TEST NUMBER: P997191
CATALOG NUMBER: SMX6RLSFS010-900LM-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.0	3.3
10°-20°	83.1	9.3
20°-30°	126.5	14.2
30°-40°	153.5	17.2
40°-50°	160.7	18.0
50°-60°	146.8	16.5
60°-70°	112.9	12.7
70°-80°	63.8	7.2
80°-90°	15.3	1.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	238.6	26.8
0°-40°	392.1	44.0
0°-60°	699.6	78.5
0°-90°	891.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	891.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	306	306	306	306	306	
5°	305	305	305	305	305	29
15°	295	295	295	295	295	83
25°	275	274	275	274	275	127
35°	245	245	245	245	245	154
45°	208	208	208	208	208	161
55°	164	165	164	165	164	147
65°	114	114	114	114	114	113
75°	60	60	60	60	60	64
85°	12	12	12	12	12	15
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997191

CATALOG NUMBER: SMX6RLSFS010-900LM-2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	306.1	306.1	306.1	306.1	306.1	306.1	306.1	306.1	306.1	306.1	306.1
0.5°	306.2	305.9	306.2	306.1	306.2	306.1	306.2	305.9	306.2	305.9	306.2
1°	306.1	305.9	306.1	306.2	306.2	306.2	306.1	305.9	306.1	305.9	306.1
1.5°	306.0	305.9	306.0	306.1	306.2	306.1	306.0	305.9	306.0	305.9	306.0
2°	306.2	305.8	306.0	306.0	306.0	306.0	306.0	305.8	306.2	305.8	306.0
2.5°	306.0	305.6	305.8	305.9	305.9	305.9	305.8	305.6	306.0	305.6	305.8
3°	305.9	305.6	305.6	305.8	305.7	305.8	305.6	305.6	305.9	305.6	305.6
3.5°	305.6	305.4	305.5	305.6	305.7	305.6	305.5	305.4	305.6	305.4	305.5
4°	305.3	305.2	305.3	305.4	305.5	305.4	305.3	305.2	305.3	305.2	305.3
4.5°	305.3	305.0	305.0	305.1	305.2	305.1	305.0	305.0	305.3	305.0	305.0
5°	305.1	304.7	304.8	305.0	305.0	305.0	304.8	304.7	305.1	304.7	304.8
5.5°	304.8	304.5	304.7	304.6	304.8	304.6	304.7	304.5	304.8	304.5	304.7
6°	304.4	304.1	304.2	304.3	304.5	304.3	304.2	304.1	304.4	304.1	304.2
6.5°	304.0	303.9	303.8	304.1	304.2	304.1	303.8	303.9	304.0	303.9	303.8
7°	303.5	303.5	303.5	303.6	303.8	303.6	303.5	303.5	303.5	303.5	303.5
7.5°	303.2	303.2	303.1	303.2	303.6	303.2	303.1	303.2	303.2	303.2	303.1
8°	302.8	302.8	302.7	302.8	303.0	302.8	302.7	302.8	302.8	302.8	302.7
8.5°	302.4	302.4	302.3	302.4	302.6	302.4	302.3	302.4	302.4	302.4	302.3
9°	302.1	302.0	301.9	302.0	302.2	302.0	301.9	302.0	302.1	302.0	301.9
9.5°	301.4	301.4	301.4	301.5	301.7	301.5	301.4	301.4	301.4	301.4	301.4
10°	301.2	300.9	300.9	301.0	301.2	301.0	300.9	300.9	301.2	300.9	300.9
10.5°	300.5	300.4	300.3	300.4	300.8	300.4	300.3	300.4	300.5	300.4	300.3
11°	300.2	299.8	299.8	299.9	300.0	299.9	299.8	299.8	300.2	299.8	299.8
11.5°	299.5	299.3	299.3	299.2	299.5	299.2	299.3	299.3	299.5	299.3	299.3
12°	298.9	298.6	298.6	298.7	298.9	298.7	298.6	298.6	298.9	298.6	298.6
12.5°	298.1	297.9	298.1	298.0	298.3	298.0	298.1	297.9	298.1	297.9	298.1
13°	297.5	297.3	297.4	297.4	297.6	297.4	297.4	297.3	297.5	297.3	297.4
13.5°	296.9	296.6	296.7	296.8	297.0	296.8	296.7	296.6	296.9	296.6	296.7
14°	296.2	295.9	295.9	296.0	296.3	296.0	295.9	295.9	296.2	295.9	295.9
14.5°	295.3	295.1	295.2	295.2	295.6	295.2	295.2	295.1	295.3	295.1	295.2
15°	294.7	294.3	294.5	294.5	294.8	294.5	294.5	294.3	294.7	294.3	294.5
15.5°	293.8	293.7	293.7	293.8	294.0	293.8	293.7	293.7	293.8	293.7	293.7
16°	293.2	293.0	292.9	293.1	293.2	293.1	292.9	293.0	293.2	293.0	292.9
16.5°	292.3	292.2	292.1	292.3	292.5	292.3	292.1	292.2	292.3	292.2	292.1
17°	291.6	291.1	291.2	291.4	291.5	291.4	291.2	291.1	291.6	291.1	291.2
17.5°	290.6	290.3	290.4	290.5	290.7	290.5	290.4	290.3	290.6	290.3	290.4
18°	289.7	289.5	289.4	289.6	289.8	289.6	289.4	289.5	289.7	289.5	289.4
18.5°	288.8	288.5	288.7	288.6	288.9	288.6	288.7	288.5	288.8	288.5	288.7
19°	287.8	287.5	287.6	287.8	287.9	287.8	287.6	287.5	287.8	287.5	287.6
19.5°	286.8	286.6	286.6	286.7	286.8	286.7	286.6	286.6	286.8	286.6	286.6
20°	285.9	285.5	285.6	285.7	285.9	285.7	285.6	285.5	285.9	285.5	285.6
20.5°	284.7	284.5	284.6	284.7	284.9	284.7	284.6	284.5	284.7	284.5	284.6
21°	283.8	283.5	283.6	283.7	283.8	283.7	283.6	283.5	283.8	283.5	283.6

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997191

CATALOG NUMBER: SMX6RLSFS010-900LM-2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
22.5°	280.4	280.2	280.3	280.3	280.5	280.3	280.3	280.2	280.4	280.2	280.3
23°	279.3	279.1	279.1	279.2	279.4	279.2	279.1	279.1	279.3	279.1	279.1
23.5°	278.1	278.0	277.9	278.0	278.2	278.0	277.9	278.0	278.1	278.0	277.9
24°	277.0	276.7	276.8	276.8	277.0	276.8	276.8	276.7	277.0	276.7	276.8
24.5°	275.7	275.6	275.6	275.6	275.8	275.6	275.6	275.6	275.7	275.6	275.6
25°	274.6	274.4	274.4	274.3	274.5	274.3	274.4	274.4	274.6	274.4	274.4
25.5°	273.3	273.1	273.1	273.1	273.3	273.1	273.1	273.1	273.3	273.1	273.1
26°	272.1	271.9	271.9	271.8	272.2	271.8	271.9	271.9	272.1	271.9	271.9
26.5°	270.7	270.5	270.6	270.5	270.8	270.5	270.6	270.5	270.7	270.5	270.6
27°	269.4	269.2	269.2	269.3	269.4	269.3	269.2	269.2	269.4	269.2	269.2
27.5°	268.0	267.9	267.9	268.0	268.1	268.0	267.9	267.9	268.0	267.9	267.9
28°	266.7	266.5	266.5	266.6	266.8	266.6	266.5	266.5	266.7	266.5	266.5
28.5°	265.3	265.0	265.2	265.2	265.3	265.2	265.2	265.0	265.3	265.0	265.2
29°	263.9	263.7	263.8	263.8	263.9	263.8	263.8	263.7	263.9	263.7	263.8
29.5°	262.5	262.3	262.3	262.4	262.6	262.4	262.3	262.3	262.5	262.3	262.3
30°	261.1	260.8	260.9	261.0	261.1	261.0	260.9	260.8	261.1	260.8	260.9
30.5°	259.6	259.4	259.4	259.5	259.6	259.5	259.4	259.4	259.6	259.4	259.4
31°	258.1	257.9	257.9	258.0	258.2	258.0	257.9	257.9	258.1	257.9	257.9
31.5°	256.5	256.3	256.4	256.4	256.7	256.4	256.4	256.3	256.5	256.3	256.4
32°	255.0	254.8	254.8	254.9	255.0	254.9	254.8	254.8	255.0	254.8	254.8
32.5°	253.4	253.3	253.4	253.3	253.5	253.3	253.4	253.3	253.4	253.3	253.4
33°	251.8	251.7	251.8	251.8	251.9	251.8	251.8	251.7	251.8	251.7	251.8
33.5°	250.3	250.1	250.1	250.2	250.3	250.2	250.1	250.1	250.3	250.1	250.1
34°	248.6	248.5	248.5	248.6	248.7	248.6	248.5	248.5	248.6	248.5	248.5
34.5°	247.0	246.8	246.8	246.9	247.0	246.9	246.8	246.8	247.0	246.8	246.8
35°	245.4	245.1	245.2	245.3	245.4	245.3	245.2	245.1	245.4	245.1	245.2
35.5°	243.7	243.5	243.5	243.7	243.8	243.7	243.5	243.5	243.7	243.5	243.5
36°	242.0	241.7	241.9	242.0	242.1	242.0	241.9	241.7	242.0	241.7	241.9
36.5°	240.4	240.1	240.2	240.3	240.4	240.3	240.2	240.1	240.4	240.1	240.2
37°	238.8	238.4	238.5	238.6	238.7	238.6	238.5	238.4	238.8	238.4	238.5
37.5°	237.0	236.7	236.8	236.8	236.9	236.8	236.8	236.7	237.0	236.7	236.8
38°	235.1	235.0	235.0	235.1	235.2	235.1	235.0	235.0	235.1	235.0	235.0
38.5°	233.4	233.2	233.2	233.3	233.4	233.3	233.2	233.2	233.4	233.2	233.2
39°	231.5	231.5	231.4	231.5	231.7	231.5	231.4	231.5	231.5	231.5	231.4
39.5°	229.8	229.7	229.5	229.8	229.8	229.8	229.5	229.7	229.8	229.7	229.5
40°	227.9	227.8	227.7	227.8	227.8	227.8	227.7	227.8	227.9	227.8	227.7
40.5°	226.0	225.9	225.8	225.9	225.9	225.9	225.8	225.9	226.0	225.9	225.8
41°	224.2	224.0	224.0	224.0	224.0	224.0	224.0	224.0	224.2	224.0	224.0
41.5°	222.4	222.1	222.1	222.1	222.2	222.1	222.1	222.1	222.4	222.1	222.1
42°	220.5	220.2	220.2	220.2	220.3	220.2	220.2	220.2	220.5	220.2	220.2
42.5°	218.4	218.2	218.2	218.2	218.3	218.2	218.2	218.2	218.4	218.2	218.2
43°	216.5	216.3	216.2	216.3	216.3	216.3	216.2	216.3	216.5	216.3	216.2
43.5°	214.4	214.2	214.2	214.4	214.4	214.4	214.2	214.2	214.4	214.2	214.2

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997191

CATALOG NUMBER: SMX6RLSFS010-900LM-2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
45°	208.5	208.3	208.3	208.3	208.5	208.3	208.3	208.3	208.5	208.3	208.3
45.5°	206.3	206.2	206.2	206.3	206.4	206.3	206.2	206.2	206.3	206.2	206.2
46°	204.2	204.2	204.2	204.3	204.3	204.3	204.2	204.2	204.2	204.2	204.2
46.5°	202.2	202.1	202.1	202.2	202.3	202.2	202.1	202.1	202.2	202.1	202.1
47°	200.1	200.1	200.0	200.1	200.2	200.1	200.0	200.1	200.1	200.1	200.0
47.5°	198.1	197.9	197.8	198.0	198.0	198.0	197.8	197.9	198.1	197.9	197.8
48°	195.8	195.6	195.8	195.8	195.9	195.8	195.8	195.6	195.8	195.6	195.8
48.5°	193.7	193.6	193.6	193.7	193.8	193.7	193.6	193.6	193.7	193.6	193.6
49°	191.5	191.4	191.5	191.5	191.6	191.5	191.5	191.4	191.5	191.4	191.5
49.5°	189.4	189.3	189.4	189.3	189.4	189.3	189.4	189.3	189.4	189.3	189.4
50°	187.3	187.0	187.1	187.1	187.2	187.1	187.1	187.0	187.3	187.0	187.1
50.5°	185.1	184.9	184.9	185.0	185.0	185.0	184.9	184.9	185.1	184.9	184.9
51°	182.8	182.7	182.8	182.8	182.9	182.8	182.8	182.7	182.8	182.7	182.8
51.5°	180.7	180.6	180.5	180.5	180.7	180.5	180.5	180.6	180.7	180.6	180.5
52°	178.5	178.3	178.3	178.3	178.5	178.3	178.3	178.3	178.5	178.3	178.3
52.5°	176.2	176.0	176.0	176.0	176.2	176.0	176.0	176.0	176.2	176.0	176.0
53°	173.9	173.7	173.7	173.8	173.8	173.8	173.7	173.7	173.9	173.7	173.7
53.5°	171.5	171.5	171.4	171.4	171.5	171.4	171.4	171.5	171.5	171.5	171.4
54°	169.2	169.1	169.0	169.0	169.2	169.0	169.0	169.1	169.2	169.1	169.0
54.5°	166.8	166.7	166.7	166.7	166.9	166.7	166.7	166.7	166.8	166.7	166.7
55°	164.4	164.3	164.4	164.3	164.6	164.3	164.4	164.3	164.4	164.3	164.4
55.5°	162.0	161.9	162.0	161.9	162.2	161.9	162.0	161.9	162.0	161.9	162.0
56°	159.6	159.5	159.7	159.7	159.9	159.7	159.7	159.5	159.6	159.5	159.7
56.5°	157.2	157.1	157.2	157.2	157.5	157.2	157.2	157.1	157.2	157.1	157.2
57°	154.8	154.8	154.9	154.8	154.9	154.8	154.9	154.8	154.8	154.8	154.9
57.5°	152.4	152.5	152.4	152.4	152.5	152.4	152.4	152.5	152.4	152.5	152.4
58°	150.1	149.9	150.0	150.0	150.1	150.0	150.0	149.9	150.1	149.9	150.0
58.5°	147.6	147.5	147.5	147.5	147.7	147.5	147.5	147.5	147.6	147.5	147.5
59°	145.1	145.0	145.0	145.0	145.2	145.0	145.0	145.0	145.1	145.0	145.0
59.5°	142.6	142.5	142.5	142.5	142.6	142.5	142.5	142.5	142.6	142.5	142.5
60°	140.1	140.0	140.0	140.0	140.1	140.0	140.0	140.0	140.1	140.0	140.0
60.5°	137.5	137.5	137.5	137.5	137.5	137.5	137.5	137.5	137.5	137.5	137.5
61°	134.9	134.9	134.9	134.9	135.0	134.9	134.9	134.9	134.9	134.9	134.9
61.5°	132.5	132.4	132.4	132.4	132.5	132.4	132.4	132.4	132.5	132.4	132.4
62°	130.0	129.8	129.9	129.8	130.0	129.8	129.9	129.8	130.0	129.8	129.9
62.5°	127.4	127.3	127.2	127.3	127.3	127.3	127.2	127.3	127.4	127.3	127.2
63°	124.8	124.8	124.7	124.7	124.8	124.7	124.7	124.8	124.8	124.8	124.7
63.5°	122.3	122.1	122.2	122.1	122.2	122.1	122.2	122.1	122.3	122.1	122.2
64°	119.7	119.5	119.5	119.5	119.6	119.5	119.5	119.5	119.7	119.5	119.5
64.5°	117.1	116.9	116.9	116.9	117.0	116.9	116.9	116.9	117.1	116.9	116.9
65°	114.5	114.3	114.2	114.3	114.4	114.3	114.2	114.3	114.5	114.3	114.2
65.5°	111.8	111.7	111.6	111.6	111.7	111.6	111.6	111.7	111.8	111.7	111.6
66°	109.1	108.9	108.9	109.0	109.1	109.0	108.9	108.9	109.1	108.9	108.9

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997191

CATALOG NUMBER: SMX6RLSFS010-900LM-2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
67.5°	100.9	101.0	100.9	100.9	101.0	100.9	100.9	101.0	100.9	101.0	100.9
68°	98.4	98.4	98.2	98.2	98.3	98.2	98.2	98.4	98.4	98.4	98.2
68.5°	95.7	95.6	95.5	95.6	95.7	95.6	95.5	95.6	95.7	95.6	95.5
69°	92.9	92.8	92.8	92.9	93.0	92.9	92.8	92.8	92.9	92.8	92.8
69.5°	90.2	90.1	90.1	90.1	90.2	90.1	90.1	90.1	90.2	90.1	90.1
70°	87.5	87.4	87.5	87.4	87.5	87.4	87.5	87.4	87.5	87.4	87.5
70.5°	84.8	84.7	84.7	84.6	84.8	84.6	84.7	84.7	84.8	84.7	84.7
71°	82.0	82.0	82.0	82.0	82.1	82.0	82.0	82.0	82.0	82.0	82.0
71.5°	79.3	79.2	79.3	79.2	79.4	79.2	79.3	79.2	79.3	79.2	79.3
72°	76.6	76.5	76.5	76.5	76.7	76.5	76.5	76.5	76.6	76.5	76.5
72.5°	73.9	73.8	73.8	73.8	73.9	73.8	73.8	73.8	73.9	73.8	73.8
73°	71.2	71.1	71.2	71.0	71.2	71.0	71.2	71.1	71.2	71.1	71.2
73.5°	68.4	68.5	68.5	68.4	68.5	68.4	68.5	68.5	68.4	68.5	68.5
74°	65.8	65.8	65.8	65.7	65.9	65.7	65.8	65.8	65.8	65.8	65.8
74.5°	63.1	63.1	63.1	63.0	63.1	63.0	63.1	63.1	63.1	63.1	63.1
75°	60.3	60.4	60.4	60.3	60.5	60.3	60.4	60.4	60.3	60.4	60.4
75.5°	57.6	57.7	57.7	57.7	57.8	57.7	57.7	57.7	57.6	57.7	57.7
76°	55.0	55.0	55.0	55.0	55.1	55.0	55.0	55.0	55.0	55.0	55.0
76.5°	52.3	52.3	52.3	52.3	52.4	52.3	52.3	52.3	52.3	52.3	52.3
77°	49.7	49.7	49.7	49.7	49.8	49.7	49.7	49.7	49.7	49.7	49.7
77.5°	47.1	47.0	47.1	47.0	47.1	47.0	47.1	47.0	47.1	47.0	47.1
78°	44.5	44.4	44.5	44.4	44.5	44.4	44.5	44.4	44.5	44.4	44.5
78.5°	41.9	41.9	41.9	41.8	41.9	41.8	41.9	41.9	41.9	41.9	41.9
79°	39.3	39.3	39.3	39.2	39.3	39.2	39.3	39.3	39.3	39.3	39.3
79.5°	36.7	36.7	36.7	36.7	36.8	36.7	36.7	36.7	36.7	36.7	36.7
80°	34.3	34.1	34.1	34.1	34.2	34.1	34.1	34.1	34.3	34.1	34.1
80.5°	31.7	31.7	31.7	31.7	31.7	31.7	31.7	31.7	31.7	31.7	31.7
81°	29.3	29.3	29.3	29.3	29.2	29.3	29.3	29.3	29.3	29.3	29.3
81.5°	26.8	26.9	26.9	26.9	26.9	26.9	26.9	26.9	26.8	26.9	26.9
82°	24.6	24.6	24.6	24.6	24.6	24.6	24.6	24.6	24.6	24.6	24.6
82.5°	22.4	22.3	22.4	22.4	22.3	22.4	22.4	22.3	22.4	22.3	22.4
83°	20.3	20.2	20.2	20.2	20.2	20.2	20.2	20.2	20.3	20.2	20.2
83.5°	18.1	18.0	18.1	18.1	18.1	18.1	18.1	18.0	18.1	18.0	18.1
84°	16.1	16.1	16.1	16.1	16.1	16.1	16.1	16.1	16.1	16.1	16.1
84.5°	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2
85°	12.3	12.3	12.3	12.3	12.2	12.3	12.3	12.3	12.3	12.3	12.3
85.5°	10.5	10.6	10.6	10.6	10.6	10.6	10.6	10.6	10.5	10.6	10.6
86°	9.0	9.0	9.0	8.9	8.9	8.9	9.0	9.0	9.0	9.0	9.0
86.5°	7.4	7.4	7.4	7.5	7.4	7.5	7.4	7.4	7.4	7.4	7.4
87°	6.0	6.1	6.1	6.1	6.0	6.1	6.1	6.1	6.0	6.1	6.1
87.5°	4.8	4.8	4.9	4.8	4.7	4.8	4.9	4.8	4.8	4.8	4.9
88°	3.7	3.8	3.8	3.7	3.7	3.7	3.8	3.8	3.7	3.8	3.8
88.5°	2.8	2.8	2.8	2.8	2.7	2.8	2.8	2.8	2.8	2.8	2.8

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P997191
CATALOG NUMBER: SMX6RLSFS010-900LM-2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997191

CATALOG NUMBER: SMX6RLSFS010-900LM-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	306.1	306.1	306.1	306.1	306.1	306.1
0.5°	306.1	306.2	306.1	306.2	305.9	306.2
1°	306.2	306.2	306.2	306.1	305.9	306.1
1.5°	306.1	306.2	306.1	306.0	305.9	306.0
2°	306.0	306.0	306.0	306.0	305.8	306.2
2.5°	305.9	305.9	305.9	305.8	305.6	306.0
3°	305.8	305.7	305.8	305.6	305.6	305.9
3.5°	305.6	305.7	305.6	305.5	305.4	305.6
4°	305.4	305.5	305.4	305.3	305.2	305.3
4.5°	305.1	305.2	305.1	305.0	305.0	305.3
5°	305.0	305.0	305.0	304.8	304.7	305.1
5.5°	304.6	304.8	304.6	304.7	304.5	304.8
6°	304.3	304.5	304.3	304.2	304.1	304.4
6.5°	304.1	304.2	304.1	303.8	303.9	304.0
7°	303.6	303.8	303.6	303.5	303.5	303.5
7.5°	303.2	303.6	303.2	303.1	303.2	303.2
8°	302.8	303.0	302.8	302.7	302.8	302.8
8.5°	302.4	302.6	302.4	302.3	302.4	302.4
9°	302.0	302.2	302.0	301.9	302.0	302.1
9.5°	301.5	301.7	301.5	301.4	301.4	301.4
10°	301.0	301.2	301.0	300.9	300.9	301.2
10.5°	300.4	300.8	300.4	300.3	300.4	300.5
11°	299.9	300.0	299.9	299.8	299.8	300.2
11.5°	299.2	299.5	299.2	299.3	299.3	299.5
12°	298.7	298.9	298.7	298.6	298.6	298.9
12.5°	298.0	298.3	298.0	298.1	297.9	298.1
13°	297.4	297.6	297.4	297.4	297.3	297.5
13.5°	296.8	297.0	296.8	296.7	296.6	296.9
14°	296.0	296.3	296.0	295.9	295.9	296.2
14.5°	295.2	295.6	295.2	295.2	295.1	295.3
15°	294.5	294.8	294.5	294.5	294.3	294.7
15.5°	293.8	294.0	293.8	293.7	293.7	293.8
16°	293.1	293.2	293.1	292.9	293.0	293.2
16.5°	292.3	292.5	292.3	292.1	292.2	292.3
17°	291.4	291.5	291.4	291.2	291.1	291.6
17.5°	290.5	290.7	290.5	290.4	290.3	290.6
18°	289.6	289.8	289.6	289.4	289.5	289.7
18.5°	288.6	288.9	288.6	288.7	288.5	288.8
19°	287.8	287.9	287.8	287.6	287.5	287.8
19.5°	286.7	286.8	286.7	286.6	286.6	286.8
20°	285.7	285.9	285.7	285.6	285.5	285.9
20.5°	284.7	284.9	284.7	284.6	284.5	284.7
21°	283.7	283.8	283.7	283.6	283.5	283.8

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997191

CATALOG NUMBER: SMX6RLSFS010-900LM-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
22.5°	280.3	280.5	280.3	280.3	280.2	280.4
23°	279.2	279.4	279.2	279.1	279.1	279.3
23.5°	278.0	278.2	278.0	277.9	278.0	278.1
24°	276.8	277.0	276.8	276.8	276.7	277.0
24.5°	275.6	275.8	275.6	275.6	275.6	275.7
25°	274.3	274.5	274.3	274.4	274.4	274.6
25.5°	273.1	273.3	273.1	273.1	273.1	273.3
26°	271.8	272.2	271.8	271.9	271.9	272.1
26.5°	270.5	270.8	270.5	270.6	270.5	270.7
27°	269.3	269.4	269.3	269.2	269.2	269.4
27.5°	268.0	268.1	268.0	267.9	267.9	268.0
28°	266.6	266.8	266.6	266.5	266.5	266.7
28.5°	265.2	265.3	265.2	265.2	265.0	265.3
29°	263.8	263.9	263.8	263.8	263.7	263.9
29.5°	262.4	262.6	262.4	262.3	262.3	262.5
30°	261.0	261.1	261.0	260.9	260.8	261.1
30.5°	259.5	259.6	259.5	259.4	259.4	259.6
31°	258.0	258.2	258.0	257.9	257.9	258.1
31.5°	256.4	256.7	256.4	256.4	256.3	256.5
32°	254.9	255.0	254.9	254.8	254.8	255.0
32.5°	253.3	253.5	253.3	253.4	253.3	253.4
33°	251.8	251.9	251.8	251.8	251.7	251.8
33.5°	250.2	250.3	250.2	250.1	250.1	250.3
34°	248.6	248.7	248.6	248.5	248.5	248.6
34.5°	246.9	247.0	246.9	246.8	246.8	247.0
35°	245.3	245.4	245.3	245.2	245.1	245.4
35.5°	243.7	243.8	243.7	243.5	243.5	243.7
36°	242.0	242.1	242.0	241.9	241.7	242.0
36.5°	240.3	240.4	240.3	240.2	240.1	240.4
37°	238.6	238.7	238.6	238.5	238.4	238.8
37.5°	236.8	236.9	236.8	236.8	236.7	237.0
38°	235.1	235.2	235.1	235.0	235.0	235.1
38.5°	233.3	233.4	233.3	233.2	233.2	233.4
39°	231.5	231.7	231.5	231.4	231.5	231.5
39.5°	229.8	229.8	229.8	229.5	229.7	229.8
40°	227.8	227.8	227.8	227.7	227.8	227.9
40.5°	225.9	225.9	225.9	225.8	225.9	226.0
41°	224.0	224.0	224.0	224.0	224.0	224.2
41.5°	222.1	222.2	222.1	222.1	222.1	222.4
42°	220.2	220.3	220.2	220.2	220.2	220.5
42.5°	218.2	218.3	218.2	218.2	218.2	218.4
43°	216.3	216.3	216.3	216.2	216.3	216.5
43.5°	214.4	214.4	214.4	214.2	214.2	214.4

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997191

CATALOG NUMBER: SMX6RLSFS010-900LM-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
45°	208.3	208.5	208.3	208.3	208.3	208.5
45.5°	206.3	206.4	206.3	206.2	206.2	206.3
46°	204.3	204.3	204.3	204.2	204.2	204.2
46.5°	202.2	202.3	202.2	202.1	202.1	202.2
47°	200.1	200.2	200.1	200.0	200.1	200.1
47.5°	198.0	198.0	198.0	197.8	197.9	198.1
48°	195.8	195.9	195.8	195.8	195.6	195.8
48.5°	193.7	193.8	193.7	193.6	193.6	193.7
49°	191.5	191.6	191.5	191.5	191.4	191.5
49.5°	189.3	189.4	189.3	189.4	189.3	189.4
50°	187.1	187.2	187.1	187.1	187.0	187.3
50.5°	185.0	185.0	185.0	184.9	184.9	185.1
51°	182.8	182.9	182.8	182.8	182.7	182.8
51.5°	180.5	180.7	180.5	180.5	180.6	180.7
52°	178.3	178.5	178.3	178.3	178.3	178.5
52.5°	176.0	176.2	176.0	176.0	176.0	176.2
53°	173.8	173.8	173.8	173.7	173.7	173.9
53.5°	171.4	171.5	171.4	171.4	171.5	171.5
54°	169.0	169.2	169.0	169.0	169.1	169.2
54.5°	166.7	166.9	166.7	166.7	166.7	166.8
55°	164.3	164.6	164.3	164.4	164.3	164.4
55.5°	161.9	162.2	161.9	162.0	161.9	162.0
56°	159.7	159.9	159.7	159.7	159.5	159.6
56.5°	157.2	157.5	157.2	157.2	157.1	157.2
57°	154.8	154.9	154.8	154.9	154.8	154.8
57.5°	152.4	152.5	152.4	152.4	152.5	152.4
58°	150.0	150.1	150.0	150.0	149.9	150.1
58.5°	147.5	147.7	147.5	147.5	147.5	147.6
59°	145.0	145.2	145.0	145.0	145.0	145.1
59.5°	142.5	142.6	142.5	142.5	142.5	142.6
60°	140.0	140.1	140.0	140.0	140.0	140.1
60.5°	137.5	137.5	137.5	137.5	137.5	137.5
61°	134.9	135.0	134.9	134.9	134.9	134.9
61.5°	132.4	132.5	132.4	132.4	132.4	132.5
62°	129.8	130.0	129.8	129.9	129.8	130.0
62.5°	127.3	127.3	127.3	127.2	127.3	127.4
63°	124.7	124.8	124.7	124.7	124.8	124.8
63.5°	122.1	122.2	122.1	122.2	122.1	122.3
64°	119.5	119.6	119.5	119.5	119.5	119.7
64.5°	116.9	117.0	116.9	116.9	116.9	117.1
65°	114.3	114.4	114.3	114.2	114.3	114.5
65.5°	111.6	111.7	111.6	111.6	111.7	111.8
66°	109.0	109.1	109.0	108.9	108.9	109.1

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997191

CATALOG NUMBER: SMX6RLSFS010-900LM-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
67.5°	100.9	101.0	100.9	100.9	101.0	100.9
68°	98.2	98.3	98.2	98.2	98.4	98.4
68.5°	95.6	95.7	95.6	95.5	95.6	95.7
69°	92.9	93.0	92.9	92.8	92.8	92.9
69.5°	90.1	90.2	90.1	90.1	90.1	90.2
70°	87.4	87.5	87.4	87.5	87.4	87.5
70.5°	84.6	84.8	84.6	84.7	84.7	84.8
71°	82.0	82.1	82.0	82.0	82.0	82.0
71.5°	79.2	79.4	79.2	79.3	79.2	79.3
72°	76.5	76.7	76.5	76.5	76.5	76.6
72.5°	73.8	73.9	73.8	73.8	73.8	73.9
73°	71.0	71.2	71.0	71.2	71.1	71.2
73.5°	68.4	68.5	68.4	68.5	68.5	68.4
74°	65.7	65.9	65.7	65.8	65.8	65.8
74.5°	63.0	63.1	63.0	63.1	63.1	63.1
75°	60.3	60.5	60.3	60.4	60.4	60.3
75.5°	57.7	57.8	57.7	57.7	57.7	57.6
76°	55.0	55.1	55.0	55.0	55.0	55.0
76.5°	52.3	52.4	52.3	52.3	52.3	52.3
77°	49.7	49.8	49.7	49.7	49.7	49.7
77.5°	47.0	47.1	47.0	47.1	47.0	47.1
78°	44.4	44.5	44.4	44.5	44.4	44.5
78.5°	41.8	41.9	41.8	41.9	41.9	41.9
79°	39.2	39.3	39.2	39.3	39.3	39.3
79.5°	36.7	36.8	36.7	36.7	36.7	36.7
80°	34.1	34.2	34.1	34.1	34.1	34.3
80.5°	31.7	31.7	31.7	31.7	31.7	31.7
81°	29.3	29.2	29.3	29.3	29.3	29.3
81.5°	26.9	26.9	26.9	26.9	26.9	26.8
82°	24.6	24.6	24.6	24.6	24.6	24.6
82.5°	22.4	22.3	22.4	22.4	22.3	22.4
83°	20.2	20.2	20.2	20.2	20.2	20.3
83.5°	18.1	18.1	18.1	18.1	18.0	18.1
84°	16.1	16.1	16.1	16.1	16.1	16.1
84.5°	14.2	14.2	14.2	14.2	14.2	14.2
85°	12.3	12.2	12.3	12.3	12.3	12.3
85.5°	10.6	10.6	10.6	10.6	10.6	10.5
86°	8.9	8.9	8.9	9.0	9.0	9.0
86.5°	7.5	7.4	7.5	7.4	7.4	7.4
87°	6.1	6.0	6.1	6.1	6.1	6.0
87.5°	4.8	4.7	4.8	4.9	4.8	4.8
88°	3.7	3.7	3.7	3.8	3.8	3.7
88.5°	2.8	2.7	2.8	2.8	2.8	2.8

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P997191
CATALOG NUMBER: SMX6RLSFS010-900LM-2700K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
90°	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270° - · - 135°-315°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





21.5°	282.6	282.4	282.4	282.6	282.8	282.6	282.4	282.4	282.6	282.4	282.4
22°	281.5	281.3	281.4	281.5	281.6	281.5	281.4	281.3	281.5	281.3	281.4



44°	212.4	212.3	212.2	212.4	212.5	212.4	212.2	212.3	212.4	212.3	212.2
44.5°	210.4	210.4	210.3	210.4	210.5	210.4	210.3	210.4	210.4	210.4	210.3



66.5°	106.3	106.2	106.2	106.3	106.4	106.3	106.2	106.2	106.3	106.2	106.2
67°	103.6	103.6	103.6	103.6	103.7	103.6	103.6	103.6	103.6	103.6	103.6



89°	2.0	2.0	2.1	2.1	1.9	2.1	2.1	2.0	2.0	2.0	2.1
89.5°	1.4	1.4	1.3	1.4	1.4	1.4	1.3	1.4	1.4	1.4	1.3

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



21.5°	282.6	282.8	282.6	282.4	282.4	282.6
22°	281.5	281.6	281.5	281.4	281.3	281.5

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



44°	212.4	212.5	212.4	212.2	212.3	212.4
44.5°	210.4	210.5	210.4	210.3	210.4	210.4

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



66.5°	106.3	106.4	106.3	106.2	106.2	106.3
67°	103.6	103.7	103.6	103.6	103.6	103.6

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



89°	2.1	1.9	2.1	2.1	2.0	2.0
89.5°	1.4	1.4	1.4	1.3	1.4	1.4

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)