

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO

Report Number: P601258

Luminaire Tested: **ML408LSNFL95FS1E - TIR4D25NFL - TL41R\_ TL42S\_ 5000K**

Issue Date: 7/29/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

**Test Information**

Test Method: LM-79-08  
 Report Number: P601258  
 Test Lab: COOPER LIGHTING SOLUTIONS  
 Issue Date: 7/29/2022  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: HALO  
 Catalog Number: ML408LSNFL95FS1E - TIR4D25NFL - TL41R\_ TL42S\_ 5000K  
 Description: RETROFIT, 25D OPTIC, OPEN TRIM  
 Light Source: (1) SELECTABLE LUMEN LED 95CRI / 5000K CCT  
 Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
 Luminaire Lumens: 1105.1 lumens  
 Efficiency: N/A  
 Efficacy: 107.3 lumens/watt  
 Spacing Criteria (0/90/45): 0.43 / 0.43 / 0.46  
 Luminous Opening: Circular (Dia: 0.21' x H: 0')  
 CIE Type: Direct


Input Watts (W): 10.3  
 Input Voltage (V): NR  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT



Meas		Calibration Due Date	
Instrument	Identificatio		
Photometer	GONIO 1 11111111	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P601258  
CATALOG NUMBER: ML408LSNFL95FS1E - TIR4D25NFL - TL41R\_TL42S\_5000K

### Luminous Intensity Polar Plot



TEST NUMBER: P601258  
 CATALOG NUMBER: ML408LSNFL95FS1E - TIR4D25NFL - TL41R\_ TL42S\_ 5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	96
1	115	112	110	108	112	110	108	107	106	105	103	102	101	100	99	98	97	96	95	94	93	91
2	110	106	103	100	108	105	102	99	101	99	97	98	97	95	96	94	93	91	93	90	89	87
3	106	101	97	94	104	100	96	93	97	94	91	95	92	90	93	90	89	87	93	90	89	87
4	102	96	92	88	101	95	91	88	93	90	87	91	88	86	89	87	85	84	89	87	85	84
5	98	92	87	84	97	91	87	83	89	86	83	88	84	82	86	84	81	80	86	84	81	80
6	95	88	83	80	94	87	83	80	86	82	79	85	81	79	83	80	78	77	83	80	78	77
7	92	84	80	76	91	84	79	76	83	79	76	82	78	75	81	77	75	74	81	77	75	74
8	89	81	76	73	88	81	76	73	80	76	73	79	75	72	78	75	72	71	78	75	72	71
9	86	78	74	70	85	78	73	70	77	73	70	76	72	70	75	72	70	69	75	72	70	69
10	83	75	71	68	82	75	71	68	74	70	68	74	70	67	73	70	67	66	73	70	67	66

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1198960
5°	1113932
10°	818937
15°	477672
20°	301419
25°	185597
30°	105993
35°	57282
40°	27123
45°	13486
50°	7762
55°	3633
60°	1642
65°	971
70°	1200
75°	0
80°	0
85°	0

TEST NUMBER: P601258  
 CATALOG NUMBER: ML408LSNFL95FS1E - TIR4D25NFL - TL41R\_TL42S\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	304.4	27.5
10°-20°	420.0	38.0
20°-30°	248.8	22.5
30°-40°	97.3	8.8
40°-50°	26.0	2.4
50°-60°	6.7	0.6
60°-70°	1.8	0.2
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	973.2	88.1
0°-40°	1070.5	96.9
0°-60°	1103.2	99.8
0°-90°	1105.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1105.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3797	
5°	3514	304
15°	1461	420
25°	533	249
35°	149	97
45°	30	26
55°	7	7
65°	1	2
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P601258  
CATALOG NUMBER: ML408LSNFL95FS1E - TIR4D25NFL - TL41R\_ TL42S\_ 5000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3797.0
1°	3810.2
2°	3768.1
3°	3702.3
4°	3632.6
5°	3514.3
6°	3360.4
7°	3230.2
8°	3001.3
9°	2780.4
10°	2554.1
12.5°	1939.9
15°	1461.2
17.5°	1133.7
20°	897.0
22.5°	695.7
25°	532.7
27.5°	398.5
30°	290.7
32.5°	211.7
35°	148.6
37.5°	98.6
40°	65.8
42.5°	43.4
45°	30.2
47.5°	22.4
50°	15.8
52.5°	10.5
55°	6.6
57.5°	3.9
60°	2.6
62.5°	2.6
65°	1.3
67.5°	1.3
70°	1.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)