

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P990727

Luminaire Tested: **ML3ALSFL9FS1E-TIR4D25NFL-TL3SDMB-750LM-2700K**

Issue Date: 5/13/2025

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P990727
 Test Lab: Cooper Lighting Solutions
 Issue Date: 5/13/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: ML3ALSFL9FS1E-TIR4D25NFL-TL3SDMB-750LM-2700K
 Description: 3IN SQUARE ML FLEX ADJUSTABLE, SELECTABLE CCT, WITH 25D TIR, MATTE BLACK TRIM
 Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 2700K CCT
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 666.6 lumens
 Efficiency: N/A
 Efficacy: 68.7 lumens/watt
 Spacing Criteria (0/90/45): 0.49 / 0.5 / 0.54
 Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
 CIE Type: Direct

Input Watts (W): 9.7
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P990727
CATALOG NUMBER: ML3ALSFL9FS1E-TIR4D25NFL-TL3SDMB-750LM-2700K

Luminous Intensity Polar Plot



TEST NUMBER: P990727

CATALOG NUMBER: ML3ALSFL9FS1E-TIR4D25NFL-TL3SDMB-750LM-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	112	109	107	105	105	104	102		102	100	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	104	99	94	90	102	97	93	90	95	91	88		92	89	87		90
4	100	93	88	84	98	92	87	84	90	86	83		88	85	82		86
5	96	88	83	79	94	87	82	79	86	81	78		84	80	78		83
6	92	84	79	75	90	83	78	74	82	77	74		80	76	74		79
7	88	80	75	71	87	79	74	71	78	74	70		77	73	70		76
8	85	76	71	67	84	76	71	67	75	70	67		74	70	67		73
9	81	73	68	64	80	72	68	64	72	67	64		71	67	64		70
10	78	70	65	61	78	70	65	61	69	64	61		68	64	61		67

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	294225	294225	294225
5°	270281	269763	270800
10°	215504	215854	214105
15°	152837	153907	154085
20°	101553	103752	103386
25°	64058	66908	66908
30°	39375	41583	42179
35°	24178	25650	26070
40°	14613	15962	15513
45°	8768	9986	9255
50°	5359	6698	5627
55°	3303	4204	3603
60°	2411	3100	2411
65°	1630	2038	2038
70°	1511	1511	1511
75°	665	1331	665
80°	0	0	0
85°	0	0	0

TEST NUMBER: P990727

CATALOG NUMBER: ML3ALSFL9FS1E-TIR4D25NFL-TL3SDMB-750LM-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.5	20.8
10°-20°	236.9	35.5
20°-30°	162.7	24.4
30°-40°	78.4	11.8
40°-50°	31.6	4.7
50°-60°	12.0	1.8
60°-70°	5.0	0.7
70°-80°	1.5	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	538.0	80.7
0°-40°	616.4	92.5
0°-60°	660.0	99.0
0°-90°	666.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	666.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1708	1708	1708	1708	1708	
5°	1563	1565	1560	1568	1566	139
15°	857	856	863	865	864	235
25°	337	343	352	355	352	158
35°	115	116	122	126	124	74
45°	36	38	41	40	38	29
55°	11	12	14	13	12	11
65°	4	5	5	5	5	4
75°	1	1	2	1	1	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P990727

CATALOG NUMBER: ML3ALSFL9FS1E-TIR4D25NFL-TL3SDMB-750LM-2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1708.4	1708.4	1708.4	1708.4	1708.4
1°	1699.4	1699.4	1700.4	1699.4	1703.4
2°	1678.4	1679.4	1682.4	1682.4	1682.4
3°	1650.4	1649.4	1651.4	1654.4	1656.4
4°	1609.4	1608.4	1616.4	1614.4	1616.4
5°	1563.4	1565.4	1560.4	1568.4	1566.4
6°	1511.4	1508.4	1506.4	1512.4	1509.4
7°	1446.4	1449.4	1446.4	1453.4	1441.4
8°	1381.3	1379.3	1375.3	1377.3	1380.3
9°	1311.3	1309.3	1305.3	1305.3	1308.3
10°	1232.3	1228.3	1234.3	1229.3	1224.3
11°	1153.3	1150.3	1156.3	1152.3	1155.3
12°	1072.3	1077.3	1079.3	1078.3	1080.3
13°	992.2	1001.2	1001.2	1003.2	1000.2
14°	923.2	930.2	930.2	932.2	935.2
15°	857.2	856.2	863.2	865.2	864.2
16°	782.2	788.2	796.2	797.2	796.2
17°	717.2	723.2	736.2	735.2	732.2
18°	658.2	664.2	672.2	670.2	668.2
19°	600.1	604.2	616.2	618.2	612.2
20°	554.1	554.1	566.1	564.1	564.1
22.5°	433.1	437.1	448.1	450.1	448.1
25°	337.1	343.1	352.1	355.1	352.1
27.5°	260.1	263.1	273.1	275.1	276.1
30°	198.0	200.0	209.1	216.1	212.1
32.5°	150.0	154.0	161.0	165.0	164.0
35°	115.0	116.0	122.0	126.0	124.0
37.5°	86.0	89.0	93.0	95.0	92.0
40°	65.0	66.0	71.0	71.0	69.0
42.5°	48.0	50.0	54.0	54.0	51.0
45°	36.0	38.0	41.0	40.0	38.0
47.5°	26.0	29.0	31.0	30.0	28.0
50°	20.0	21.0	25.0	23.0	21.0
52.5°	15.0	16.0	19.0	17.0	16.0
55°	11.0	12.0	14.0	13.0	12.0
57.5°	8.0	9.0	11.0	10.0	9.0
60°	7.0	7.0	9.0	8.0	7.0
62.5°	5.0	6.0	7.0	6.0	6.0
65°	4.0	5.0	5.0	5.0	5.0
67.5°	3.0	4.0	4.0	4.0	4.0
70°	3.0	3.0	3.0	3.0	3.0
72.5°	2.0	2.0	3.0	2.0	2.0
75°	1.0	1.0	2.0	1.0	1.0
77.5°	0.0	1.0	1.0	1.0	1.0
80°	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P990727

CATALOG NUMBER: ML3ALSFL9FS1E-TIR4D25NFL-TL3SDMB-750LM-2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)