

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P997223

Luminaire Tested: **SMX6SLSFSD2W-900LM-3500K**

Issue Date: 3/11/2025

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

**Test Information**

Test Method: LM-41-14
Report Number: P997223
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (A2410656A001)
Test Lab:
Issue Date: 3/11/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: SMX6SLSFSD2W-900LM-3500K
Description: 6IN SQAURE, 90CRI, DIMMING TO 10%, DAMP LOCATION
Light Source: SELECTABLE CCT 90CRI / 3500K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 980.5 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.27 / 1.38
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P997223

CATALOG NUMBER: SMX6SLSFSD2W-900LM-3500K

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997223

CATALOG NUMBER: SMX6SLSFSD2W-900LM-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	109	104	100	96	106	102	98	94	97	94	91	93	91	88	90	88	86	84		
2	99	90	84	78	96	89	82	77	85	80	75	82	77	73	79	75	72	69		
3	90	79	71	64	87	78	70	64	75	68	63	72	66	62	69	65	61	58		
4	82	70	61	54	80	69	60	54	66	59	53	64	58	53	62	56	52	50		
5	76	63	53	47	73	61	53	47	59	52	46	57	51	45	55	50	45	43		
6	70	56	47	41	68	55	47	41	53	46	40	52	45	40	50	44	39	37		
7	65	51	42	36	63	50	42	36	49	41	36	47	40	35	46	40	35	33		
8	60	46	38	32	59	46	38	32	44	37	32	43	36	31	42	36	31	29		
9	56	43	34	29	55	42	34	29	41	34	29	40	33	28	39	33	28	26		
10	53	39	31	26	51	39	31	26	38	31	26	37	30	26	36	30	26	24		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14579	14579	14579	14579
5°	14578	14574	14578	14574
10°	14528	14581	14528	14581
15°	14518	14536	14518	14536
20°	14474	14483	14474	14483
25°	14395	14423	14395	14423
30°	14298	14338	14298	14338
35°	14218	14234	14218	14234
40°	14096	14130	14096	14130
45°	13974	13980	13974	13980
50°	13792	13819	13792	13819
55°	13564	13587	13564	13587
60°	13235	13253	13235	13253
65°	12765	12796	12765	12796
70°	12060	12060	12060	12060
75°	10929	10946	10929	10946
80°	9199	9224	9199	9224
85°	6323	6521	6323	6521



TEST NUMBER: P997223

CATALOG NUMBER: SMX6SLSFSD2W-900LM-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.1	3.3
10°-20°	91.9	9.4
20°-30°	139.7	14.2
30°-40°	169.2	17.3
40°-50°	176.9	18.0
50°-60°	161.3	16.4
60°-70°	123.7	12.6
70°-80°	69.5	7.1
80°-90°	16.1	1.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	263.7	26.9
0°-40°	432.9	44.2
0°-60°	771.1	78.6
0°-90°	980.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	980.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	339	339	339	339	339	
5°	337	337	337	337	337	32
15°	326	326	326	326	326	92
25°	303	304	303	304	303	140
35°	270	271	270	271	270	169
45°	230	230	230	230	230	177
55°	181	181	181	181	181	161
65°	125	126	125	126	125	124
75°	66	66	66	66	66	70
85°	13	13	13	13	13	16
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997223

CATALOG NUMBER: SMX6SLSFSD2W-900LM-3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	338.6	338.6	338.6	338.6	338.6	338.6	338.6	338.6	338.6	338.6	338.6
0.5°	338.6	338.5	338.4	338.9	339.2	338.9	338.4	338.5	338.6	338.5	338.4
1°	338.5	338.4	338.5	338.9	339.2	338.9	338.5	338.4	338.5	338.4	338.5
1.5°	338.8	338.2	338.6	338.8	339.2	338.8	338.6	338.2	338.8	338.2	338.6
2°	338.8	338.1	338.5	338.9	339.2	338.9	338.5	338.1	338.8	338.1	338.5
2.5°	338.4	338.1	338.2	338.7	338.5	338.7	338.2	338.1	338.4	338.1	338.2
3°	338.3	337.7	338.1	338.6	338.3	338.6	338.1	337.7	338.3	337.7	338.1
3.5°	338.2	337.6	338.1	338.3	338.1	338.3	338.1	337.6	338.2	337.6	338.1
4°	337.8	337.6	337.9	338.0	338.3	338.0	337.9	337.6	337.8	337.6	337.9
4.5°	337.7	337.1	337.6	337.5	337.8	337.5	337.6	337.1	337.7	337.1	337.6
5°	337.3	336.7	337.4	337.3	337.2	337.3	337.4	336.7	337.3	336.7	337.4
5.5°	337.4	336.7	336.9	336.9	337.4	336.9	336.9	336.7	337.4	336.7	336.9
6°	336.4	336.2	336.5	336.9	337.3	336.9	336.5	336.2	336.4	336.2	336.5
6.5°	336.3	335.9	336.1	336.2	336.6	336.2	336.1	335.9	336.3	335.9	336.1
7°	335.9	335.6	335.7	336.0	336.6	336.0	335.7	335.6	335.9	335.6	335.7
7.5°	335.4	335.1	335.5	335.3	335.7	335.3	335.5	335.1	335.4	335.1	335.5
8°	335.1	334.3	335.2	335.1	335.8	335.1	335.2	334.3	335.1	334.3	335.2
8.5°	334.4	334.2	334.4	334.6	335.0	334.6	334.4	334.2	334.4	334.2	334.4
9°	333.2	333.6	333.8	334.3	334.5	334.3	333.8	333.6	333.2	333.6	333.8
9.5°	332.9	333.3	333.2	334.0	333.8	334.0	333.2	333.3	332.9	333.3	333.2
10°	332.3	332.8	332.7	333.3	333.5	333.3	332.7	332.8	332.3	332.8	332.7
10.5°	331.8	331.9	332.3	332.6	332.8	332.6	332.3	331.9	331.8	331.9	332.3
11°	331.4	331.2	331.7	332.2	331.7	332.2	331.7	331.2	331.4	331.2	331.7
11.5°	330.8	330.6	331.2	331.1	331.4	331.1	331.2	330.6	330.8	330.6	331.2
12°	330.2	329.8	330.2	330.7	331.1	330.7	330.2	329.8	330.2	329.8	330.2
12.5°	329.4	329.3	329.7	330.0	330.0	330.0	329.7	329.3	329.4	329.3	329.7
13°	329.0	328.5	328.9	329.0	329.3	329.0	328.9	328.5	329.0	328.5	328.9
13.5°	328.2	327.7	328.4	328.1	328.3	328.1	328.4	327.7	328.2	327.7	328.4
14°	327.1	327.1	327.4	327.5	328.0	327.5	327.4	327.1	327.1	327.1	327.4
14.5°	326.6	326.3	326.7	326.7	327.1	326.7	326.7	326.3	326.6	326.3	326.7
15°	325.7	325.5	326.0	325.9	326.1	325.9	326.0	325.5	325.7	325.5	326.0
15.5°	324.8	324.5	324.7	325.0	325.5	325.0	324.7	324.5	324.8	324.5	324.7
16°	323.7	323.8	323.9	324.2	323.9	324.2	323.9	323.8	323.7	323.8	323.9
16.5°	323.0	322.7	323.0	323.2	323.4	323.2	323.0	322.7	323.0	322.7	323.0
17°	322.1	321.8	322.2	322.5	322.0	322.5	322.2	321.8	322.1	321.8	322.2
17.5°	321.0	320.7	321.0	321.1	321.3	321.1	321.0	320.7	321.0	320.7	321.0
18°	319.7	319.6	320.0	320.2	320.3	320.2	320.0	319.6	319.7	319.6	320.0
18.5°	319.0	318.9	318.8	319.1	319.6	319.1	318.8	318.9	319.0	318.9	318.8
19°	317.9	317.8	318.2	318.1	318.7	318.1	318.2	317.8	317.9	317.8	318.2
19.5°	316.7	316.3	317.1	316.8	316.9	316.8	317.1	316.3	316.7	316.3	317.1
20°	315.9	315.6	315.8	316.0	316.1	316.0	315.8	315.6	315.9	315.6	315.8
20.5°	314.6	314.0	314.4	314.6	315.0	314.6	314.4	314.0	314.6	314.0	314.4
21°	313.1	313.2	313.2	313.6	314.0	313.6	313.2	313.2	313.1	313.2	313.2

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997223

CATALOG NUMBER: SMX6SLSFSD2W-900LM-3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
22.5°	310.0	309.0	309.2	310.3	310.0	310.3	309.2	309.0	310.0	309.0	309.2
23°	308.6	308.0	308.2	309.1	308.8	309.1	308.2	308.0	308.6	308.0	308.2
23.5°	307.2	306.6	307.0	307.6	307.5	307.6	307.0	306.6	307.2	306.6	307.0
24°	306.2	305.4	305.8	306.1	306.4	306.1	305.8	305.4	306.2	305.4	305.8
24.5°	304.6	304.2	304.3	304.5	304.9	304.5	304.3	304.2	304.6	304.2	304.3
25°	303.0	303.0	303.2	303.3	303.6	303.3	303.2	303.0	303.0	303.0	303.2
25.5°	301.7	301.5	301.9	302.0	301.9	302.0	301.9	301.5	301.7	301.5	301.9
26°	300.2	300.1	300.3	300.5	300.7	300.5	300.3	300.1	300.2	300.1	300.3
26.5°	299.0	298.5	298.9	299.0	299.1	299.0	298.9	298.5	299.0	298.5	298.9
27°	297.4	297.1	297.2	297.6	297.9	297.6	297.2	297.1	297.4	297.1	297.2
27.5°	296.0	295.5	295.7	296.1	296.4	296.1	295.7	295.5	296.0	295.5	295.7
28°	294.5	294.2	294.5	294.7	295.0	294.7	294.5	294.2	294.5	294.2	294.5
28.5°	293.0	292.4	293.0	293.1	293.5	293.1	293.0	292.4	293.0	292.4	293.0
29°	291.0	290.9	291.2	291.3	291.7	291.3	291.2	290.9	291.0	290.9	291.2
29.5°	289.6	289.3	289.8	289.8	290.1	289.8	289.8	289.3	289.6	289.3	289.8
30°	287.6	287.8	288.0	288.1	288.4	288.1	288.0	287.8	287.6	287.8	288.0
30.5°	286.3	285.9	286.4	286.6	287.2	286.6	286.4	285.9	286.3	285.9	286.4
31°	284.6	284.2	284.7	284.9	285.4	284.9	284.7	284.2	284.6	284.2	284.7
31.5°	283.0	282.5	283.0	283.2	283.7	283.2	283.0	282.5	283.0	282.5	283.0
32°	281.0	280.8	281.1	281.4	281.6	281.4	281.1	280.8	281.0	280.8	281.1
32.5°	279.5	278.9	279.7	279.8	279.9	279.8	279.7	278.9	279.5	278.9	279.7
33°	277.6	277.6	277.8	278.1	278.1	278.1	277.8	277.6	277.6	277.6	277.8
33.5°	276.2	275.5	276.2	276.2	276.1	276.2	276.2	275.5	276.2	275.5	276.2
34°	274.3	274.3	273.9	274.5	274.4	274.5	273.9	274.3	274.3	274.3	273.9
34.5°	272.1	272.2	272.4	272.6	272.8	272.6	272.4	272.2	272.1	272.2	272.4
35°	270.5	270.4	270.3	270.7	270.8	270.7	270.3	270.4	270.5	270.4	270.3
35.5°	268.4	268.6	268.5	269.0	268.7	269.0	268.5	268.6	268.4	268.6	268.5
36°	266.8	266.6	266.7	267.2	266.8	267.2	266.7	266.6	266.8	266.6	266.7
36.5°	264.4	264.4	264.8	265.1	264.9	265.1	264.8	264.4	264.4	264.4	264.8
37°	263.2	262.6	262.8	263.0	263.2	263.0	262.8	262.6	263.2	262.6	262.8
37.5°	260.3	260.6	261.2	261.5	261.4	261.5	261.2	260.6	260.3	260.6	261.2
38°	258.7	258.9	259.0	259.4	259.3	259.4	259.0	258.9	258.7	258.9	259.0
38.5°	256.6	256.6	256.8	257.4	257.3	257.4	256.8	256.6	256.6	256.6	256.8
39°	254.8	254.9	255.2	255.2	255.6	255.2	255.2	254.9	254.8	254.9	255.2
39.5°	252.8	252.7	253.2	253.2	253.3	253.2	253.2	252.7	252.8	252.7	253.2
40°	250.8	250.6	250.9	251.3	251.4	251.3	250.9	250.6	250.8	250.6	250.9
40.5°	248.7	248.5	248.8	249.3	249.3	249.3	248.8	248.5	248.7	248.5	248.8
41°	246.8	246.7	246.7	247.0	247.1	247.0	246.7	246.7	246.8	246.7	246.7
41.5°	244.6	244.3	244.7	244.9	245.1	244.9	244.7	244.3	244.6	244.3	244.7
42°	242.5	242.1	242.6	242.9	242.5	242.9	242.6	242.1	242.5	242.1	242.6
42.5°	240.4	240.0	240.4	240.9	240.5	240.9	240.4	240.0	240.4	240.0	240.4
43°	238.2	238.2	238.3	238.5	238.6	238.5	238.3	238.2	238.2	238.2	238.3
43.5°	236.1	235.8	235.9	236.3	236.3	236.3	235.9	235.8	236.1	235.8	235.9

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997223

CATALOG NUMBER: SMX6SLSFSD2W-900LM-3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
45°	229.5	229.1	229.3	229.7	229.6	229.7	229.3	229.1	229.5	229.1	229.3
45.5°	227.1	226.6	226.9	227.3	227.3	227.3	226.9	226.6	227.1	226.6	226.9
46°	224.7	224.5	224.7	225.1	225.0	225.1	224.7	224.5	224.7	224.5	224.7
46.5°	222.4	222.1	222.3	222.5	222.7	222.5	222.3	222.1	222.4	222.1	222.3
47°	220.2	219.9	220.1	220.3	220.4	220.3	220.1	219.9	220.2	219.9	220.1
47.5°	217.9	217.5	217.9	218.1	218.2	218.1	217.9	217.5	217.9	217.5	217.9
48°	215.4	215.2	215.5	215.8	216.0	215.8	215.5	215.2	215.4	215.2	215.5
48.5°	213.2	212.9	213.1	213.2	213.4	213.2	213.1	212.9	213.2	212.9	213.1
49°	211.0	210.5	210.7	211.1	210.9	211.1	210.7	210.5	211.0	210.5	210.7
49.5°	208.4	208.1	208.2	208.5	208.8	208.5	208.2	208.1	208.4	208.1	208.2
50°	205.9	205.6	205.6	206.2	206.3	206.2	205.6	205.6	205.9	205.6	205.6
50.5°	203.5	203.1	203.1	203.6	203.8	203.6	203.1	203.1	203.5	203.1	203.1
51°	201.1	200.7	200.6	201.2	201.2	201.2	200.6	200.7	201.1	200.7	200.6
51.5°	198.5	198.3	198.3	198.6	198.9	198.6	198.3	198.3	198.5	198.3	198.3
52°	195.9	195.7	195.6	196.1	196.4	196.1	195.6	195.7	195.9	195.7	195.6
52.5°	193.2	193.2	193.4	193.6	193.8	193.6	193.4	193.2	193.2	193.2	193.4
53°	190.9	190.7	190.9	191.0	191.1	191.0	190.9	190.7	190.9	190.7	190.9
53.5°	188.5	188.1	188.4	188.2	188.7	188.2	188.4	188.1	188.5	188.1	188.4
54°	185.9	185.5	185.7	186.0	186.1	186.0	185.7	185.5	185.9	185.5	185.7
54.5°	183.3	182.9	183.1	183.5	183.5	183.5	183.1	182.9	183.3	182.9	183.1
55°	180.7	180.4	180.5	180.8	181.0	180.8	180.5	180.4	180.7	180.4	180.5
55.5°	178.2	177.8	177.9	178.1	178.4	178.1	177.9	177.8	178.2	177.8	177.9
56°	175.4	175.1	175.2	175.4	175.6	175.4	175.2	175.1	175.4	175.1	175.2
56.5°	172.8	172.4	172.6	172.8	172.8	172.8	172.6	172.4	172.8	172.4	172.6
57°	170.0	169.7	169.9	170.2	170.3	170.2	169.9	169.7	170.0	169.7	169.9
57.5°	167.3	167.0	167.2	167.6	167.6	167.6	167.2	167.0	167.3	167.0	167.2
58°	164.6	164.3	164.6	164.8	164.9	164.8	164.6	164.3	164.6	164.3	164.6
58.5°	162.0	161.7	161.9	162.0	162.1	162.0	161.9	161.7	162.0	161.7	161.9
59°	159.4	159.0	158.9	159.2	159.5	159.2	158.9	159.0	159.4	159.0	158.9
59.5°	156.5	156.2	156.1	156.5	156.7	156.5	156.1	156.2	156.5	156.2	156.1
60°	153.7	153.5	153.4	153.7	153.9	153.7	153.4	153.5	153.7	153.5	153.4
60.5°	151.0	150.7	150.7	151.0	151.2	151.0	150.7	150.7	151.0	150.7	150.7
61°	148.0	147.9	147.9	148.2	148.3	148.2	147.9	147.9	148.0	147.9	147.9
61.5°	145.2	145.0	145.1	145.4	145.5	145.4	145.1	145.0	145.2	145.0	145.1
62°	142.3	142.3	142.2	142.6	142.7	142.6	142.2	142.3	142.3	142.3	142.2
62.5°	139.4	139.5	139.5	139.8	139.8	139.8	139.5	139.5	139.4	139.5	139.5
63°	136.7	136.6	136.7	137.0	137.0	137.0	136.7	136.6	136.7	136.6	136.7
63.5°	133.8	133.8	133.9	134.0	134.3	134.0	133.9	133.8	133.8	133.8	133.9
64°	131.0	130.8	131.0	131.1	131.5	131.1	131.0	130.8	131.0	130.8	131.0
64.5°	128.1	128.0	128.2	128.2	128.5	128.2	128.2	128.0	128.1	128.0	128.2
65°	125.3	125.1	125.2	125.3	125.6	125.3	125.2	125.1	125.3	125.1	125.2
65.5°	122.2	122.1	122.3	122.4	122.5	122.4	122.3	122.1	122.2	122.1	122.3
66°	119.3	119.2	119.2	119.6	119.6	119.6	119.2	119.2	119.3	119.2	119.2

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997223

CATALOG NUMBER: SMX6SLSFSD2W-900LM-3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
67.5°	110.7	110.3	110.4	110.6	110.8	110.6	110.4	110.3	110.7	110.3	110.4
68°	107.7	107.5	107.5	107.7	107.9	107.7	107.5	107.5	107.7	107.5	107.5
68.5°	104.7	104.5	104.7	104.8	104.8	104.8	104.7	104.5	104.7	104.5	104.7
69°	101.7	101.5	101.4	101.8	101.8	101.8	101.4	101.5	101.7	101.5	101.4
69.5°	98.7	98.5	98.6	98.8	98.9	98.8	98.6	98.5	98.7	98.5	98.6
70°	95.8	95.6	95.7	95.8	95.8	95.8	95.7	95.6	95.8	95.6	95.7
70.5°	92.7	92.5	92.6	92.9	92.8	92.9	92.6	92.5	92.7	92.5	92.6
71°	89.7	89.6	89.6	89.8	89.8	89.8	89.6	89.6	89.7	89.6	89.6
71.5°	86.6	86.5	86.6	86.8	86.7	86.8	86.6	86.5	86.6	86.5	86.6
72°	83.6	83.5	83.5	83.8	83.8	83.8	83.5	83.5	83.6	83.5	83.5
72.5°	80.6	80.5	80.6	80.9	80.8	80.9	80.6	80.5	80.6	80.5	80.6
73°	77.5	77.5	77.6	77.8	77.8	77.8	77.6	77.5	77.5	77.5	77.6
73.5°	74.7	74.5	74.6	74.8	74.8	74.8	74.6	74.5	74.7	74.5	74.6
74°	71.8	71.7	71.7	71.7	71.9	71.7	71.7	71.7	71.8	71.7	71.7
74.5°	68.7	68.7	68.7	68.8	68.8	68.8	68.7	68.7	68.7	68.7	68.7
75°	65.7	65.7	65.7	65.8	65.8	65.8	65.7	65.7	65.7	65.7	65.7
75.5°	62.7	62.7	62.7	62.9	62.9	62.9	62.7	62.7	62.7	62.7	62.7
76°	59.8	59.7	59.7	59.8	59.9	59.8	59.7	59.7	59.8	59.7	59.7
76.5°	56.8	56.7	56.8	56.9	56.9	56.9	56.8	56.7	56.8	56.7	56.8
77°	53.9	53.9	53.9	54.1	54.1	54.1	53.9	53.9	53.9	53.9	53.9
77.5°	51.1	51.0	51.1	51.2	51.2	51.2	51.1	51.0	51.1	51.0	51.1
78°	48.3	48.2	48.3	48.4	48.4	48.4	48.3	48.2	48.3	48.2	48.3
78.5°	45.5	45.4	45.4	45.6	45.6	45.6	45.4	45.4	45.5	45.4	45.4
79°	42.7	42.6	42.6	42.8	42.8	42.8	42.6	42.6	42.7	42.6	42.6
79.5°	39.9	39.8	39.8	40.0	40.0	40.0	39.8	39.8	39.9	39.8	39.8
80°	37.1	37.0	37.1	37.2	37.2	37.2	37.1	37.0	37.1	37.0	37.1
80.5°	34.3	34.3	34.3	34.5	34.5	34.5	34.3	34.3	34.3	34.3	34.3
81°	31.7	31.7	31.7	31.8	31.8	31.8	31.7	31.7	31.7	31.7	31.7
81.5°	29.1	29.0	29.1	29.1	29.2	29.1	29.1	29.0	29.1	29.0	29.1
82°	26.4	26.3	26.4	26.6	26.6	26.6	26.4	26.3	26.4	26.3	26.4
82.5°	23.8	23.8	24.0	24.1	24.2	24.1	24.0	23.8	23.8	23.8	24.0
83°	21.5	21.5	21.5	21.7	21.9	21.7	21.5	21.5	21.5	21.5	21.5
83.5°	19.1	19.1	19.2	19.4	19.5	19.4	19.2	19.1	19.1	19.1	19.2
84°	16.9	16.9	17.1	17.2	17.2	17.2	17.1	16.9	16.9	16.9	17.1
84.5°	14.9	14.9	14.9	15.0	15.2	15.0	14.9	14.9	14.9	14.9	14.9
85°	12.8	12.8	12.8	13.0	13.2	13.0	12.8	12.8	12.8	12.8	12.8
85.5°	10.8	10.8	11.0	11.1	11.3	11.1	11.0	10.8	10.8	10.8	11.0
86°	9.0	9.0	9.2	9.3	9.5	9.3	9.2	9.0	9.0	9.0	9.2
86.5°	7.3	7.4	7.5	7.7	7.9	7.7	7.5	7.4	7.3	7.4	7.5
87°	5.8	5.9	6.0	6.1	6.4	6.1	6.0	5.9	5.8	5.9	6.0
87.5°	4.4	4.5	4.7	4.8	5.1	4.8	4.7	4.5	4.4	4.5	4.7
88°	3.3	3.3	3.4	3.6	3.9	3.6	3.4	3.3	3.3	3.3	3.4
88.5°	2.2	2.2	2.4	2.6	2.9	2.6	2.4	2.2	2.2	2.2	2.4

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P997223
CATALOG NUMBER: SMX6SLSFSD2W-900LM-3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997223

CATALOG NUMBER: SMX6SLSFSD2W-900LM-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	338.6	338.6	338.6	338.6	338.6	338.6
0.5°	338.9	339.2	338.9	338.4	338.5	338.6
1°	338.9	339.2	338.9	338.5	338.4	338.5
1.5°	338.8	339.2	338.8	338.6	338.2	338.8
2°	338.9	339.2	338.9	338.5	338.1	338.8
2.5°	338.7	338.5	338.7	338.2	338.1	338.4
3°	338.6	338.3	338.6	338.1	337.7	338.3
3.5°	338.3	338.1	338.3	338.1	337.6	338.2
4°	338.0	338.3	338.0	337.9	337.6	337.8
4.5°	337.5	337.8	337.5	337.6	337.1	337.7
5°	337.3	337.2	337.3	337.4	336.7	337.3
5.5°	336.9	337.4	336.9	336.9	336.7	337.4
6°	336.9	337.3	336.9	336.5	336.2	336.4
6.5°	336.2	336.6	336.2	336.1	335.9	336.3
7°	336.0	336.6	336.0	335.7	335.6	335.9
7.5°	335.3	335.7	335.3	335.5	335.1	335.4
8°	335.1	335.8	335.1	335.2	334.3	335.1
8.5°	334.6	335.0	334.6	334.4	334.2	334.4
9°	334.3	334.5	334.3	333.8	333.6	333.2
9.5°	334.0	333.8	334.0	333.2	333.3	332.9
10°	333.3	333.5	333.3	332.7	332.8	332.3
10.5°	332.6	332.8	332.6	332.3	331.9	331.8
11°	332.2	331.7	332.2	331.7	331.2	331.4
11.5°	331.1	331.4	331.1	331.2	330.6	330.8
12°	330.7	331.1	330.7	330.2	329.8	330.2
12.5°	330.0	330.0	330.0	329.7	329.3	329.4
13°	329.0	329.3	329.0	328.9	328.5	329.0
13.5°	328.1	328.3	328.1	328.4	327.7	328.2
14°	327.5	328.0	327.5	327.4	327.1	327.1
14.5°	326.7	327.1	326.7	326.7	326.3	326.6
15°	325.9	326.1	325.9	326.0	325.5	325.7
15.5°	325.0	325.5	325.0	324.7	324.5	324.8
16°	324.2	323.9	324.2	323.9	323.8	323.7
16.5°	323.2	323.4	323.2	323.0	322.7	323.0
17°	322.5	322.0	322.5	322.2	321.8	322.1
17.5°	321.1	321.3	321.1	321.0	320.7	321.0
18°	320.2	320.3	320.2	320.0	319.6	319.7
18.5°	319.1	319.6	319.1	318.8	318.9	319.0
19°	318.1	318.7	318.1	318.2	317.8	317.9
19.5°	316.8	316.9	316.8	317.1	316.3	316.7
20°	316.0	316.1	316.0	315.8	315.6	315.9
20.5°	314.6	315.0	314.6	314.4	314.0	314.6
21°	313.6	314.0	313.6	313.2	313.2	313.1

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997223

CATALOG NUMBER: SMX6SLSFSD2W-900LM-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
22.5°	310.3	310.0	310.3	309.2	309.0	310.0
23°	309.1	308.8	309.1	308.2	308.0	308.6
23.5°	307.6	307.5	307.6	307.0	306.6	307.2
24°	306.1	306.4	306.1	305.8	305.4	306.2
24.5°	304.5	304.9	304.5	304.3	304.2	304.6
25°	303.3	303.6	303.3	303.2	303.0	303.0
25.5°	302.0	301.9	302.0	301.9	301.5	301.7
26°	300.5	300.7	300.5	300.3	300.1	300.2
26.5°	299.0	299.1	299.0	298.9	298.5	299.0
27°	297.6	297.9	297.6	297.2	297.1	297.4
27.5°	296.1	296.4	296.1	295.7	295.5	296.0
28°	294.7	295.0	294.7	294.5	294.2	294.5
28.5°	293.1	293.5	293.1	293.0	292.4	293.0
29°	291.3	291.7	291.3	291.2	290.9	291.0
29.5°	289.8	290.1	289.8	289.8	289.3	289.6
30°	288.1	288.4	288.1	288.0	287.8	287.6
30.5°	286.6	287.2	286.6	286.4	285.9	286.3
31°	284.9	285.4	284.9	284.7	284.2	284.6
31.5°	283.2	283.7	283.2	283.0	282.5	283.0
32°	281.4	281.6	281.4	281.1	280.8	281.0
32.5°	279.8	279.9	279.8	279.7	278.9	279.5
33°	278.1	278.1	278.1	277.8	277.6	277.6
33.5°	276.2	276.1	276.2	276.2	275.5	276.2
34°	274.5	274.4	274.5	273.9	274.3	274.3
34.5°	272.6	272.8	272.6	272.4	272.2	272.1
35°	270.7	270.8	270.7	270.3	270.4	270.5
35.5°	269.0	268.7	269.0	268.5	268.6	268.4
36°	267.2	266.8	267.2	266.7	266.6	266.8
36.5°	265.1	264.9	265.1	264.8	264.4	264.4
37°	263.0	263.2	263.0	262.8	262.6	263.2
37.5°	261.5	261.4	261.5	261.2	260.6	260.3
38°	259.4	259.3	259.4	259.0	258.9	258.7
38.5°	257.4	257.3	257.4	256.8	256.6	256.6
39°	255.2	255.6	255.2	255.2	254.9	254.8
39.5°	253.2	253.3	253.2	253.2	252.7	252.8
40°	251.3	251.4	251.3	250.9	250.6	250.8
40.5°	249.3	249.3	249.3	248.8	248.5	248.7
41°	247.0	247.1	247.0	246.7	246.7	246.8
41.5°	244.9	245.1	244.9	244.7	244.3	244.6
42°	242.9	242.5	242.9	242.6	242.1	242.5
42.5°	240.9	240.5	240.9	240.4	240.0	240.4
43°	238.5	238.6	238.5	238.3	238.2	238.2
43.5°	236.3	236.3	236.3	235.9	235.8	236.1

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997223

CATALOG NUMBER: SMX6SLSFSD2W-900LM-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
45°	229.7	229.6	229.7	229.3	229.1	229.5
45.5°	227.3	227.3	227.3	226.9	226.6	227.1
46°	225.1	225.0	225.1	224.7	224.5	224.7
46.5°	222.5	222.7	222.5	222.3	222.1	222.4
47°	220.3	220.4	220.3	220.1	219.9	220.2
47.5°	218.1	218.2	218.1	217.9	217.5	217.9
48°	215.8	216.0	215.8	215.5	215.2	215.4
48.5°	213.2	213.4	213.2	213.1	212.9	213.2
49°	211.1	210.9	211.1	210.7	210.5	211.0
49.5°	208.5	208.8	208.5	208.2	208.1	208.4
50°	206.2	206.3	206.2	205.6	205.6	205.9
50.5°	203.6	203.8	203.6	203.1	203.1	203.5
51°	201.2	201.2	201.2	200.6	200.7	201.1
51.5°	198.6	198.9	198.6	198.3	198.3	198.5
52°	196.1	196.4	196.1	195.6	195.7	195.9
52.5°	193.6	193.8	193.6	193.4	193.2	193.2
53°	191.0	191.1	191.0	190.9	190.7	190.9
53.5°	188.2	188.7	188.2	188.4	188.1	188.5
54°	186.0	186.1	186.0	185.7	185.5	185.9
54.5°	183.5	183.5	183.5	183.1	182.9	183.3
55°	180.8	181.0	180.8	180.5	180.4	180.7
55.5°	178.1	178.4	178.1	177.9	177.8	178.2
56°	175.4	175.6	175.4	175.2	175.1	175.4
56.5°	172.8	172.8	172.8	172.6	172.4	172.8
57°	170.2	170.3	170.2	169.9	169.7	170.0
57.5°	167.6	167.6	167.6	167.2	167.0	167.3
58°	164.8	164.9	164.8	164.6	164.3	164.6
58.5°	162.0	162.1	162.0	161.9	161.7	162.0
59°	159.2	159.5	159.2	158.9	159.0	159.4
59.5°	156.5	156.7	156.5	156.1	156.2	156.5
60°	153.7	153.9	153.7	153.4	153.5	153.7
60.5°	151.0	151.2	151.0	150.7	150.7	151.0
61°	148.2	148.3	148.2	147.9	147.9	148.0
61.5°	145.4	145.5	145.4	145.1	145.0	145.2
62°	142.6	142.7	142.6	142.2	142.3	142.3
62.5°	139.8	139.8	139.8	139.5	139.5	139.4
63°	137.0	137.0	137.0	136.7	136.6	136.7
63.5°	134.0	134.3	134.0	133.9	133.8	133.8
64°	131.1	131.5	131.1	131.0	130.8	131.0
64.5°	128.2	128.5	128.2	128.2	128.0	128.1
65°	125.3	125.6	125.3	125.2	125.1	125.3
65.5°	122.4	122.5	122.4	122.3	122.1	122.2
66°	119.6	119.6	119.6	119.2	119.2	119.3

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



TEST NUMBER: P997223

CATALOG NUMBER: SMX6SLSFSD2W-900LM-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
67.5°	110.6	110.8	110.6	110.4	110.3	110.7
68°	107.7	107.9	107.7	107.5	107.5	107.7
68.5°	104.8	104.8	104.8	104.7	104.5	104.7
69°	101.8	101.8	101.8	101.4	101.5	101.7
69.5°	98.8	98.9	98.8	98.6	98.5	98.7
70°	95.8	95.8	95.8	95.7	95.6	95.8
70.5°	92.9	92.8	92.9	92.6	92.5	92.7
71°	89.8	89.8	89.8	89.6	89.6	89.7
71.5°	86.8	86.7	86.8	86.6	86.5	86.6
72°	83.8	83.8	83.8	83.5	83.5	83.6
72.5°	80.9	80.8	80.9	80.6	80.5	80.6
73°	77.8	77.8	77.8	77.6	77.5	77.5
73.5°	74.8	74.8	74.8	74.6	74.5	74.7
74°	71.7	71.9	71.7	71.7	71.7	71.8
74.5°	68.8	68.8	68.8	68.7	68.7	68.7
75°	65.8	65.8	65.8	65.7	65.7	65.7
75.5°	62.9	62.9	62.9	62.7	62.7	62.7
76°	59.8	59.9	59.8	59.7	59.7	59.8
76.5°	56.9	56.9	56.9	56.8	56.7	56.8
77°	54.1	54.1	54.1	53.9	53.9	53.9
77.5°	51.2	51.2	51.2	51.1	51.0	51.1
78°	48.4	48.4	48.4	48.3	48.2	48.3
78.5°	45.6	45.6	45.6	45.4	45.4	45.5
79°	42.8	42.8	42.8	42.6	42.6	42.7
79.5°	40.0	40.0	40.0	39.8	39.8	39.9
80°	37.2	37.2	37.2	37.1	37.0	37.1
80.5°	34.5	34.5	34.5	34.3	34.3	34.3
81°	31.8	31.8	31.8	31.7	31.7	31.7
81.5°	29.1	29.2	29.1	29.1	29.0	29.1
82°	26.6	26.6	26.6	26.4	26.3	26.4
82.5°	24.1	24.2	24.1	24.0	23.8	23.8
83°	21.7	21.9	21.7	21.5	21.5	21.5
83.5°	19.4	19.5	19.4	19.2	19.1	19.1
84°	17.2	17.2	17.2	17.1	16.9	16.9
84.5°	15.0	15.2	15.0	14.9	14.9	14.9
85°	13.0	13.2	13.0	12.8	12.8	12.8
85.5°	11.1	11.3	11.1	11.0	10.8	10.8
86°	9.3	9.5	9.3	9.2	9.0	9.0
86.5°	7.7	7.9	7.7	7.5	7.4	7.3
87°	6.1	6.4	6.1	6.0	5.9	5.8
87.5°	4.8	5.1	4.8	4.7	4.5	4.4
88°	3.6	3.9	3.6	3.4	3.3	3.3
88.5°	2.6	2.9	2.6	2.4	2.2	2.2

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



TEST NUMBER: P997223

CATALOG NUMBER: SMX6SLSFSD2W-900LM-3500K

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
90°	0.0	0.0	0.0	0.0	0.0	0.0

Classified

Scaled Data Report

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270° - · - 135°-315°

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report





21.5°	312.5	311.7	311.8	312.2	312.5	312.2	311.8	311.7	312.5	311.7	311.8
22°	311.2	310.4	311.0	311.4	311.0	311.4	311.0	310.4	311.2	310.4	311.0



44°	234.0	233.5	233.8	234.3	234.1	234.3	233.8	233.5	234.0	233.5	233.8
44.5°	231.5	231.2	231.5	231.9	231.9	231.9	231.5	231.2	231.5	231.2	231.5



66.5°	116.5	116.2	116.3	116.6	116.6	116.3	116.2	116.5	116.2	116.3
67°	113.6	113.3	113.4	113.5	113.5	113.4	113.3	113.6	113.3	113.4

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



89°	1.3	1.4	1.6	1.8	2.1	1.8	1.6	1.4	1.3	1.4	1.6
89.5°	0.7	0.8	1.0	1.2	1.4	1.2	1.0	0.8	0.7	0.8	1.0

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



21.5°	312.2	312.5	312.2	311.8	311.7	312.5
22°	311.4	311.0	311.4	311.0	310.4	311.2

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



44°	234.3	234.1	234.3	233.8	233.5	234.0
44.5°	231.9	231.9	231.9	231.5	231.2	231.5

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



66.5°	116.6	116.6	116.6	116.3	116.2	116.5
67°	113.5	113.8	113.5	113.4	113.3	113.6

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



89°	1.8	2.1	1.8	1.6	1.4	1.3
89.5°	1.2	1.4	1.2	1.0	0.8	0.7

Classified

Cooper Lighting Solutions Photometric Lab

1121 Highway 74 South

Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)