

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P990773

Luminaire Tested: **ML3ALSFL9FS1E-TIR4D40FL-TL3SDMW-750LM-3000K**

Issue Date: 5/13/2025

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P990773
 Test Lab: Cooper Lighting Solutions
 Issue Date: 5/13/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: ML3ALSFL9FS1E-TIR4D40FL-TL3SDMW-750LM-3000K
 Description: 3IN SQUARE ML FLEX ADJUSTABLE, SELECTABLE CCT, WITH 40D TIR, MATTE WHITE TRIM
 Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 771.0 lumens
 Efficiency: N/A
 Efficacy: 79.5 lumens/watt
 Spacing Criteria (0/90/45): 0.62 / 0.63 / 0.64
 Luminous Opening: Rectangular (W 0.25' x L: 0.25' x H: 0')
 CIE Type: Direct

Input Watts (W): 9.7
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P990773
CATALOG NUMBER: ML3ALSFL9FS1E-TIR4D40FL-TL3SDMW-750LM-3000K

Luminous Intensity Polar Plot



TEST NUMBER: P990773

CATALOG NUMBER: ML3ALSFL9FS1E-TIR4D40FL-TL3SDMW-750LM-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	81		85
5	95	87	81	78	93	86	81	77	84	80	76		83	79	76		81
6	91	82	77	73	89	82	76	73	80	76	72		79	75	72		77
7	87	78	73	69	85	78	72	69	76	72	68		75	71	68		74
8	83	74	69	65	82	74	69	65	73	68	65		72	68	65		71
9	80	71	66	62	79	71	65	62	70	65	62		69	65	61		68
10	77	68	63	59	76	67	62	59	67	62	59		66	62	59		65

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	258920	258920	258920
5°	247012	247185	247720
10°	218582	218949	218232
15°	178209	178405	179314
20°	130181	131683	131867
25°	85265	86614	86804
30°	50412	52023	52023
35°	28152	30086	30507
40°	16075	17918	17918
45°	9962	10960	10692
50°	6296	7395	6859
55°	4594	5525	4594
60°	3513	4237	3858
65°	2934	3749	3342
70°	2568	3072	2568
75°	2063	2728	2063
80°	992	992	992
85°	0	0	0

TEST NUMBER: P990773

CATALOG NUMBER: ML3ALSFL9FS1E-TIR4D40FL-TL3SDMW-750LM-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.7	16.9
10°-20°	273.8	35.5
20°-30°	210.0	27.2
30°-40°	92.9	12.1
40°-50°	35.8	4.6
50°-60°	15.5	2.0
60°-70°	8.4	1.1
70°-80°	3.5	0.5
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	614.5	79.7
0°-40°	707.4	91.8
0°-60°	758.7	98.4
0°-90°	771.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	771.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1503	1503	1503	1503	1503	
5°	1429	1428	1430	1430	1433	131
15°	1000	1000	1001	1004	1006	273
25°	449	451	456	458	457	207
35°	134	137	143	145	145	88
45°	41	43	45	45	44	33
55°	15	16	18	16	15	14
65°	7	8	9	8	8	8
75°	3	3	4	3	3	3
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P990773

CATALOG NUMBER: ML3ALSFL9FS1E-TIR4D40FL-TL3SDMW-750LM-3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1503.4	1503.4	1503.4	1503.4	1503.4
1°	1499.3	1499.3	1500.3	1498.3	1500.3
2°	1491.1	1488.1	1490.1	1489.1	1492.2
3°	1474.8	1470.7	1474.8	1474.8	1478.9
4°	1454.3	1451.3	1454.3	1456.4	1459.4
5°	1428.8	1427.8	1429.8	1429.8	1432.9
6°	1397.1	1400.2	1400.2	1401.2	1404.3
7°	1368.5	1368.5	1368.5	1368.5	1369.5
8°	1327.6	1332.7	1331.7	1331.7	1329.7
9°	1287.7	1291.8	1294.9	1289.8	1289.8
10°	1249.9	1247.9	1252.0	1247.9	1247.9
11°	1201.9	1205.0	1205.0	1201.9	1201.9
12°	1149.8	1155.9	1156.9	1158.0	1154.9
13°	1106.9	1104.8	1109.9	1106.9	1112.0
14°	1048.6	1053.7	1056.8	1054.7	1054.7
15°	999.5	999.5	1000.6	1003.6	1005.7
16°	944.3	942.3	945.4	948.4	946.4
17°	883.0	888.1	890.2	891.2	892.2
18°	826.8	834.0	834.0	835.0	835.0
19°	775.7	773.7	774.7	775.7	771.6
20°	710.3	715.4	718.5	718.5	719.5
22.5°	572.3	578.5	579.5	583.6	584.6
25°	448.7	450.7	455.8	457.9	456.8
27.5°	337.3	342.4	347.5	351.6	349.5
30°	253.5	255.5	261.6	264.7	261.6
32.5°	181.9	186.0	195.2	196.2	197.3
35°	133.9	137.0	143.1	145.1	145.1
37.5°	97.1	100.2	106.3	107.3	107.3
40°	71.5	74.6	79.7	80.7	79.7
42.5°	54.2	56.2	60.3	60.3	58.3
45°	40.9	42.9	45.0	45.0	43.9
47.5°	30.7	32.7	35.8	34.7	32.7
50°	23.5	25.6	27.6	26.6	25.6
52.5°	18.4	19.4	22.5	20.4	19.4
55°	15.3	16.4	18.4	16.4	15.3
57.5°	12.3	13.3	15.3	14.3	13.3
60°	10.2	11.2	12.3	11.2	11.2
62.5°	9.2	9.2	10.2	10.2	9.2
65°	7.2	8.2	9.2	8.2	8.2
67.5°	7.2	7.2	8.2	7.2	7.2
70°	5.1	6.1	6.1	6.1	5.1
72.5°	4.1	5.1	5.1	4.1	4.1
75°	3.1	3.1	4.1	3.1	3.1
77.5°	1.0	2.0	2.0	2.0	2.0
80°	1.0	1.0	1.0	1.0	1.0

TEST NUMBER: P990773
CATALOG NUMBER: ML3ALSFL9FS1E-TIR4D40FL-TL3SDMW-750LM-3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
82.5°	1.0	1.0	1.0	1.0	1.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)