

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P991379

Luminaire Tested: **SMD6S07FS5-930**

Issue Date: 05/20/2025



Test Information

Test Method: LM-79-08
Report Number: P991379
Test Lab: THIRD PARTY NVLAP
Issue Date: 05/20/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: SMD6S07FS5-930
Description: HALO SURFACE MOUNT 6 inch 90 CRI COLOR SELECTABLE SQUARE FIXTURE
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 710.0 lumens
Efficiency: N/A
Efficacy: 89.9 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.25 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 7.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P991379
CATALOG NUMBER: SMD6S07FS5-930

Luminous Intensity Polar Plot





TEST NUMBER: P991379

CATALOG NUMBER: SMD6S07FS5-930

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	108	103	99	95	106	101	97	93	97	94	90		93	90	88		89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74		81	76	72		78	74	71	69
3	89	79	70	64	87	77	69	63	74	67	62		71	66	61		69	64	60	58
4	82	70	61	54	79	68	60	53	66	58	53		63	57	52		61	56	51	49
5	75	62	53	46	73	61	52	46	59	51	45		57	50	45		55	49	44	42
6	69	56	47	40	67	55	46	40	53	45	40		51	45	39		50	44	39	37
7	64	51	42	35	63	50	41	35	48	41	35		47	40	35		45	39	35	33
8	60	46	38	32	58	45	37	32	44	37	31		43	36	31		42	36	31	29
9	56	42	34	28	54	42	34	28	41	33	28		39	33	28		38	32	28	26
10	52	39	31	26	51	39	31	26	38	30	26		37	30	25		36	30	25	24

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10497	10497	10497	10497
5°	10533	10490	10481	10511
10°	10519	10475	10432	10471
15°	10488	10435	10377	10417
20°	10451	10392	10323	10346
25°	10394	10333	10247	10266
30°	10331	10261	10157	10167
35°	10249	10176	10055	10050
40°	10173	10089	9971	9937
45°	10071	9980	9858	9791
50°	9980	9867	9726	9652
55°	9841	9728	9541	9466
60°	9662	9567	9300	9257
65°	9475	9403	9067	9037
70°	9202	9202	8749	8711
75°	8933	8983	8351	8351
80°	8629	8703	7810	7810
85°	8250	8596	6768	6817



TEST NUMBER: P991379
 CATALOG NUMBER: SMD6S07FS5-930

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.1	3.3
10°-20°	66.0	9.3
20°-30°	99.9	14.1
30°-40°	120.5	17.0
40°-50°	125.5	17.7
50°-60°	114.5	16.1
60°-70°	89.3	12.6
70°-80°	54.5	7.7
80°-90°	16.8	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	189.0	26.6
0°-40°	309.5	43.6
0°-60°	549.4	77.4
0°-90°	709.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	710.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	244	244	244	244	244	
5°	244	243	242	243	244	23
15°	235	234	233	234	235	66
25°	219	218	216	216	219	101
35°	195	194	191	191	195	122
45°	165	164	162	161	165	128
55°	131	130	127	126	131	117
65°	93	92	89	89	93	92
75°	54	54	50	50	54	57
85°	17	17	14	14	17	17
90°	1	0	0	0	1	1
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	



TEST NUMBER: P991379

CATALOG NUMBER: SMD6S07F55-930

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	243.8	243.8	243.8	243.8	243.8	243.8	243.8	243.8	243.8	243.8	243.8
0.5°	243.9	243.9	244.0	243.8	243.9	243.7	243.7	243.7	243.9	243.8	243.9
1°	243.9	243.9	244.0	243.8	243.7	243.7	243.6	243.4	243.8	243.6	243.7
1.5°	243.9	243.8	244.0	243.8	243.7	243.7	243.6	243.4	243.7	243.7	243.7
2°	243.9	243.8	243.9	243.8	243.6	243.7	243.5	243.4	243.6	243.7	243.7
2.5°	243.9	243.9	243.9	243.8	243.5	243.5	243.5	243.3	243.3	243.5	243.6
3°	243.9	243.9	243.8	243.7	243.4	243.4	243.4	243.1	243.2	243.2	243.5
3.5°	244.0	243.9	243.7	243.7	243.4	243.3	243.3	243.0	242.9	243.0	243.1
4°	244.0	243.9	243.7	243.7	243.2	243.1	242.9	242.7	242.7	242.8	242.8
4.5°	243.7	243.9	243.6	243.6	242.8	243.0	242.7	242.6	242.5	242.6	242.7
5°	243.7	243.6	243.6	243.6	242.7	242.7	242.4	242.3	242.5	242.4	242.4
5.5°	243.4	243.5	243.5	243.4	242.5	242.5	242.2	242.2	242.0	242.1	242.3
6°	243.3	243.2	243.4	243.1	242.3	242.2	242.1	241.7	241.9	241.8	241.8
6.5°	242.9	242.9	243.1	242.9	242.1	242.0	241.7	241.5	241.6	241.5	241.5
7°	242.7	242.7	242.8	242.8	241.7	241.7	241.4	241.1	241.4	241.4	241.4
7.5°	242.3	242.4	242.6	242.4	241.4	241.3	241.1	240.9	240.7	240.9	241.0
8°	242.1	242.0	242.2	242.1	241.1	241.1	240.9	240.3	240.3	240.4	240.4
8.5°	241.7	241.7	241.9	241.8	240.9	240.9	240.2	240.1	239.8	240.1	240.0
9°	241.3	241.3	241.4	241.4	240.3	240.1	239.8	239.6	239.6	239.7	239.4
9.5°	240.9	240.8	241.1	240.9	239.9	239.8	239.5	239.1	239.1	239.1	239.1
10°	240.6	240.4	240.6	240.5	239.6	239.5	238.9	238.6	238.6	238.7	238.6
10.5°	240.0	240.0	240.1	240.1	239.1	239.0	238.5	238.2	238.1	238.1	238.1
11°	239.7	239.5	239.6	239.7	238.7	238.5	238.0	237.6	237.7	237.7	237.6
11.5°	239.2	239.0	239.1	239.1	238.1	237.9	237.5	237.2	237.0	237.2	237.0
12°	238.7	238.5	238.6	238.6	237.7	237.4	237.0	236.5	236.5	236.6	236.4
12.5°	238.2	237.9	238.2	238.0	237.2	236.8	236.5	236.1	236.0	236.1	235.9
13°	237.7	237.4	237.5	237.6	236.6	236.2	235.9	235.5	235.4	235.5	235.2
13.5°	237.1	236.8	237.0	237.0	236.1	235.9	235.3	234.9	234.8	234.9	234.6
14°	236.4	236.3	236.3	236.3	235.4	235.1	234.6	234.2	234.1	234.2	234.0
14.5°	235.8	235.7	235.8	235.8	234.8	234.6	234.0	233.6	233.5	233.5	233.4
15°	235.3	235.1	235.1	235.1	234.1	233.8	233.3	232.8	232.8	232.8	232.7
15.5°	234.6	234.5	234.5	234.5	233.5	233.2	232.6	232.3	232.1	232.1	232.0
16°	234.1	233.7	233.8	233.8	232.8	232.4	231.9	231.5	231.4	231.5	231.3
16.5°	233.3	233.0	233.2	233.2	232.2	231.8	231.3	230.9	230.8	230.8	230.5
17°	232.6	232.3	232.5	232.4	231.5	231.1	230.4	230.0	230.1	230.1	229.9
17.5°	231.8	231.7	231.7	231.7	230.7	230.3	229.7	229.2	229.2	229.1	228.9
18°	231.2	231.0	230.8	230.9	230.0	229.5	228.9	228.5	228.5	228.5	228.2
18.5°	230.3	230.1	230.1	230.1	229.2	228.8	228.1	227.6	227.7	227.8	227.4
19°	229.6	229.3	229.3	229.3	228.5	227.9	227.4	226.8	226.8	226.8	226.5
19.5°	228.7	228.6	228.6	228.5	227.5	227.2	226.5	226.1	226.0	226.0	225.6
20°	228.1	227.6	227.6	227.6	226.8	226.2	225.6	225.1	225.3	225.1	224.8
20.5°	227.1	226.9	226.8	226.8	226.0	225.4	224.9	224.3	224.4	224.1	223.9
21°	226.3	226.0	226.0	226.0	225.2	224.5	223.8	223.4	223.5	223.3	222.9
21.5°	225.3	225.2	225.1	225.0	224.1	223.7	223.0	222.6	222.5	222.3	222.0
22°	224.5	224.3	224.1	224.0	223.2	222.6	222.0	221.6	221.7	221.6	221.3

TEST NUMBER: P991379

CATALOG NUMBER: SMD6S07F55-930

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
22.5°	223.5	223.4	223.4	223.2	222.4	221.8	221.5	220.6	220.7	220.5	220.3
23°	222.6	222.5	222.5	222.4	221.6	220.9	220.3	219.8	219.7	219.5	219.3
23.5°	221.8	221.6	221.5	221.3	220.5	220.1	219.2	218.7	218.9	218.4	218.1
24°	220.8	220.5	220.5	220.3	219.7	218.9	218.2	217.7	217.9	217.5	217.1
24.5°	219.8	219.6	219.5	219.4	218.6	217.9	217.1	216.7	216.8	216.6	216.2
25°	218.8	218.6	218.5	218.3	217.5	216.7	216.2	215.6	215.7	215.5	215.1
25.5°	217.7	217.6	217.5	217.4	216.5	215.7	215.2	214.7	214.6	214.3	213.9
26°	216.6	216.5	216.4	216.3	215.4	214.7	214.0	213.5	213.6	213.2	212.8
26.5°	215.6	215.5	215.3	215.1	214.4	213.6	213.0	212.5	212.5	212.1	211.7
27°	214.6	214.3	214.3	214.0	213.3	212.5	211.8	211.4	211.3	211.1	210.6
27.5°	213.4	213.4	213.2	212.9	212.2	211.4	210.7	210.3	210.2	209.8	209.4
28°	212.3	212.1	212.0	211.8	211.2	210.2	209.5	209.0	209.1	208.8	208.2
28.5°	211.1	211.0	210.9	210.7	209.9	209.0	208.4	207.9	208.0	207.5	207.1
29°	210.0	209.9	209.7	209.5	208.9	207.9	207.1	206.7	206.8	206.5	205.9
29.5°	208.8	208.7	208.6	208.2	207.6	206.8	206.0	205.6	205.7	205.3	204.7
30°	207.8	207.7	207.4	207.0	206.4	205.4	204.7	204.4	204.3	204.1	203.5
30.5°	206.5	206.4	206.2	205.8	205.2	204.2	203.5	203.1	203.2	202.7	202.3
31°	205.2	205.1	205.0	204.6	204.0	203.0	202.3	201.9	202.2	201.7	200.9
31.5°	204.0	203.9	203.8	203.3	202.7	201.8	201.0	200.6	200.6	200.2	199.6
32°	202.9	202.7	202.5	202.1	201.7	200.5	199.7	199.4	199.3	199.0	198.3
32.5°	201.5	201.5	201.2	200.8	200.3	199.2	198.5	198.2	198.1	197.6	197.1
33°	200.3	200.1	200.0	199.5	198.9	197.9	197.2	196.9	196.7	196.3	195.8
33.5°	198.9	198.9	198.7	198.2	197.6	196.6	195.9	195.5	195.4	194.9	194.4
34°	197.8	197.5	197.3	196.8	196.4	195.2	194.5	194.3	194.0	193.7	193.1
34.5°	196.4	196.2	196.0	195.5	195.0	193.9	193.1	192.9	192.7	192.2	191.7
35°	195.0	194.9	194.6	194.1	193.6	192.4	191.8	191.5	191.3	190.9	190.3
35.5°	193.7	193.5	193.2	192.8	192.2	191.1	190.4	190.1	189.9	189.6	188.8
36°	192.4	192.2	191.8	191.4	190.8	189.7	189.0	188.7	188.6	188.2	187.5
36.5°	190.9	190.8	190.4	190.0	189.5	188.3	187.6	187.4	187.2	186.6	186.0
37°	189.6	189.4	189.0	188.5	188.0	186.9	186.1	185.9	185.8	185.3	184.6
37.5°	188.1	188.0	187.8	187.1	186.7	185.5	184.7	184.5	184.3	183.8	183.2
38°	186.8	186.5	186.2	185.7	185.1	184.0	183.2	183.1	182.9	182.6	181.9
38.5°	185.2	185.2	184.7	184.3	183.7	182.5	181.9	181.8	181.8	181.1	180.5
39°	183.8	183.8	183.6	183.0	182.4	181.3	180.6	180.3	180.2	179.6	178.8
39.5°	182.5	182.5	182.0	181.5	181.0	179.9	179.0	178.8	178.8	178.1	177.4
40°	181.0	181.0	180.5	180.0	179.5	178.4	177.4	177.3	177.4	176.6	175.9
40.5°	179.5	179.6	179.1	178.5	178.0	176.8	176.0	175.8	175.8	175.1	174.4
41°	178.1	178.1	177.5	176.9	176.5	175.2	174.5	174.3	174.3	173.5	172.8
41.5°	176.4	176.5	176.0	175.4	174.9	173.8	172.9	172.8	172.8	172.0	171.3
42°	174.9	174.9	174.5	173.8	173.4	172.3	171.3	171.3	171.3	170.5	169.7
42.5°	173.4	173.5	172.9	172.1	171.9	170.6	169.9	169.7	169.8	168.8	168.1
43°	171.9	171.8	171.2	170.6	170.3	169.1	168.3	168.1	168.2	167.4	166.5
43.5°	170.2	170.3	169.7	169.0	168.7	167.4	166.7	166.5	166.7	165.7	164.9
44°	168.6	168.7	168.2	167.4	167.2	165.9	165.0	164.9	165.0	164.0	163.2
44.5°	167.2	167.2	166.4	165.8	165.5	164.3	163.4	163.3	163.5	162.5	161.6

TEST NUMBER: P991379

CATALOG NUMBER: SMD6S07F55-930

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
45°	165.4	165.5	164.9	164.2	163.9	162.7	161.8	161.8	161.9	160.9	160.0
45.5°	163.8	163.9	163.3	162.5	162.4	161.0	160.3	160.1	160.3	159.2	158.4
46°	162.3	162.3	161.7	160.9	160.6	159.4	158.5	158.4	158.7	157.6	156.6
46.5°	160.7	160.6	160.0	159.2	159.0	157.7	156.9	156.9	157.1	155.8	155.0
47°	159.0	158.9	158.4	157.6	157.5	156.1	155.3	155.2	155.4	154.2	153.4
47.5°	157.4	157.4	156.7	155.9	155.7	154.3	153.5	153.5	153.8	152.6	151.7
48°	155.6	155.6	155.0	154.3	154.1	152.7	151.8	151.9	152.1	150.8	150.0
48.5°	154.1	154.0	153.3	152.5	152.4	150.9	150.1	150.2	150.3	149.1	148.2
49°	152.4	152.4	151.6	150.8	150.7	149.3	148.4	148.4	148.7	147.5	146.5
49.5°	150.6	150.6	149.9	149.0	148.9	147.6	146.7	146.8	147.0	145.7	144.8
50°	149.0	148.9	148.2	147.3	147.3	145.8	145.1	145.1	145.2	144.0	143.2
50.5°	147.2	147.2	146.5	145.5	145.5	144.0	143.3	143.4	143.5	142.4	141.5
51°	145.5	145.4	144.7	144.0	143.7	142.6	141.6	141.7	141.8	140.6	139.7
51.5°	143.9	143.9	142.9	142.2	142.1	140.6	139.9	140.1	140.0	139.0	138.0
52°	141.9	142.0	141.3	140.5	140.4	139.0	138.2	138.3	138.2	137.1	136.2
52.5°	140.2	140.2	139.5	138.7	138.7	137.1	136.4	136.5	136.4	135.3	134.4
53°	138.4	138.5	137.8	136.9	136.9	135.4	134.6	134.7	134.6	133.4	132.6
53.5°	136.7	136.6	135.9	135.0	135.0	133.6	132.9	133.0	132.6	131.7	130.8
54°	134.8	134.8	134.1	133.3	133.2	131.8	131.0	131.0	130.9	129.7	129.1
54.5°	132.9	133.0	132.3	131.5	131.5	130.0	129.2	129.2	128.9	128.0	127.3
55°	131.1	131.0	130.5	129.7	129.6	128.2	127.4	127.3	127.1	126.1	125.4
55.5°	129.2	129.3	128.7	128.0	127.8	126.4	125.6	125.5	125.2	124.3	123.6
56°	127.3	127.4	126.8	126.0	125.9	124.6	123.8	123.5	123.3	122.3	121.9
56.5°	125.5	125.5	125.0	124.3	124.2	122.7	122.0	121.6	121.3	120.5	119.9
57°	123.7	123.6	123.1	122.4	122.3	120.9	120.2	119.7	119.5	118.6	118.1
57.5°	121.7	121.7	121.2	120.5	120.4	119.1	118.3	117.8	117.6	116.6	116.2
58°	119.7	119.8	119.4	118.7	118.6	117.2	116.5	115.9	115.6	114.8	114.4
58.5°	118.0	118.0	117.4	116.8	116.7	115.3	114.7	113.9	113.8	112.9	112.5
59°	116.0	116.0	115.7	114.9	114.8	113.5	112.8	112.1	111.9	111.0	110.6
59.5°	114.1	114.2	113.9	113.0	113.0	111.6	110.9	110.1	110.0	109.0	108.7
60°	112.2	112.2	111.9	111.2	111.1	109.7	109.0	108.1	108.0	107.3	106.8
60.5°	110.3	110.2	110.0	109.3	109.1	107.7	107.1	106.2	106.1	105.2	104.9
61°	108.4	108.3	108.1	107.4	107.4	105.9	105.2	104.4	104.2	103.5	103.1
61.5°	106.4	106.4	106.2	105.5	105.4	104.0	103.5	102.6	102.5	101.6	101.2
62°	104.7	104.6	104.5	103.8	103.9	102.3	101.5	100.6	100.5	99.8	99.3
62.5°	102.8	102.6	102.4	101.9	101.9	100.4	99.6	98.8	98.6	97.7	97.3
63°	100.8	100.7	100.6	100.0	100.0	98.5	97.6	96.8	96.7	95.7	95.4
63.5°	98.9	98.9	98.7	98.1	98.0	96.6	95.7	95.0	94.8	93.8	93.5
64°	96.9	96.8	96.6	96.2	96.1	94.6	93.8	92.9	92.9	91.8	91.5
64.5°	95.0	94.9	94.9	94.3	94.2	92.8	91.7	91.0	90.8	89.9	89.5
65°	93.0	93.0	92.7	92.4	92.3	90.8	89.7	89.1	89.0	88.0	87.6
65.5°	91.0	91.0	90.8	90.4	90.4	89.0	87.9	87.2	87.0	86.0	85.5
66°	89.0	88.9	88.8	88.5	88.5	87.0	85.8	85.1	85.1	84.1	83.8
66.5°	87.0	87.0	86.9	86.5	86.5	85.0	84.0	83.2	83.0	82.1	81.7
67°	85.0	85.1	84.9	84.7	84.7	83.1	82.0	81.3	81.1	80.2	79.7



TEST NUMBER: P991379

CATALOG NUMBER: SMD6S07FS5-930

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
67.5°	82.9	83.1	82.9	82.6	82.7	81.3	80.1	79.4	79.2	78.2	77.8
68°	81.1	81.1	80.9	80.8	80.7	79.3	78.0	77.4	77.2	76.2	75.8
68.5°	79.1	79.2	79.0	78.8	78.9	77.4	76.1	75.4	75.3	74.3	73.9
69°	77.0	77.2	76.9	76.8	76.8	75.5	74.1	73.5	73.3	72.3	72.0
69.5°	75.1	75.3	75.0	74.9	74.9	73.6	72.2	71.5	71.4	70.4	70.0
70°	73.1	73.2	73.0	72.9	73.1	71.5	70.3	69.6	69.5	68.4	68.1
70.5°	71.1	71.3	71.1	70.9	71.1	69.7	68.3	67.7	67.5	66.5	66.2
71°	69.2	69.3	69.1	69.2	69.3	67.8	66.4	65.7	65.5	64.6	64.4
71.5°	67.3	67.3	67.1	67.2	67.2	65.9	64.6	63.9	63.7	62.8	62.4
72°	65.5	65.5	65.3	65.4	65.4	64.1	62.6	62.0	61.8	60.8	60.6
72.5°	63.4	63.5	63.2	63.3	63.5	62.2	60.7	60.0	59.9	58.9	58.5
73°	61.4	61.6	61.3	61.5	61.7	60.3	58.8	58.1	58.0	57.1	56.6
73.5°	59.5	59.6	59.3	59.5	59.7	58.3	56.8	56.1	56.0	55.0	54.6
74°	57.6	57.7	57.4	57.5	57.8	56.3	54.9	54.4	54.1	53.2	52.7
74.5°	55.6	55.7	55.5	55.6	55.9	54.4	53.0	52.4	52.1	51.2	50.9
75°	53.7	53.8	53.6	53.7	54.0	52.5	51.0	50.5	50.2	49.3	48.9
75.5°	51.7	51.8	51.6	51.8	52.0	50.6	49.1	48.5	48.3	47.4	46.9
76°	49.8	49.9	49.6	49.8	50.1	48.6	47.2	46.7	46.4	45.6	45.0
76.5°	47.9	48.0	47.7	47.9	48.2	46.7	45.3	44.8	44.5	43.6	43.1
77°	45.9	46.1	45.9	45.9	46.3	44.8	43.4	42.8	42.6	41.8	41.3
77.5°	44.1	44.2	43.9	44.0	44.5	42.9	41.5	40.8	40.8	39.9	39.5
78°	42.2	42.3	42.0	42.1	42.5	41.0	39.7	39.0	38.9	38.1	37.6
78.5°	40.4	40.3	40.1	40.2	40.7	39.1	37.7	37.0	37.0	36.2	35.7
79°	38.5	38.5	38.2	38.3	38.8	37.2	35.9	35.2	35.2	34.3	33.8
79.5°	36.7	36.6	36.3	36.4	36.9	35.4	34.0	33.3	33.3	32.4	31.9
80°	34.8	34.7	34.5	34.6	35.1	33.5	32.0	31.4	31.5	30.5	30.1
80.5°	32.9	32.8	32.6	32.7	33.3	31.7	30.3	29.6	29.7	28.8	28.3
81°	31.2	30.9	30.8	30.8	31.5	29.9	28.5	27.8	27.8	26.9	26.5
81.5°	29.3	29.0	28.9	29.1	29.7	28.1	26.5	25.9	26.0	25.2	24.8
82°	27.5	27.2	27.0	27.3	27.7	26.2	24.9	24.3	24.4	23.5	23.0
82.5°	25.8	25.5	25.5	25.6	26.0	24.8	23.1	22.5	22.6	21.6	21.4
83°	24.0	23.7	23.5	23.9	24.4	23.0	21.4	20.7	20.8	19.8	19.5
83.5°	22.2	21.9	21.7	22.2	22.6	21.3	19.7	18.9	19.0	18.0	17.8
84°	20.3	20.1	20.0	20.5	20.9	19.5	18.0	17.0	17.2	16.2	16.1
84.5°	18.5	18.2	18.3	18.8	19.1	17.8	16.5	15.3	15.4	14.4	14.6
85°	16.7	16.5	16.6	17.0	17.4	16.1	14.7	13.5	13.7	12.6	12.9
85.5°	14.9	14.6	15.1	15.4	15.6	14.5	13.1	11.6	11.8	10.9	11.4
86°	13.1	12.8	13.5	13.8	13.9	12.9	11.7	9.9	9.9	9.1	9.9
86.5°	11.1	11.0	11.9	12.2	12.1	11.3	10.3	8.2	7.3	7.1	8.5
87°	8.6	9.0	10.5	10.5	10.4	9.6	8.6	6.8	6.0	5.9	7.0
87.5°	7.1	7.6	9.1	8.9	8.7	8.0	7.2	5.7	4.9	5.0	5.6
88°	6.1	6.5	7.6	7.3	7.0	6.4	5.6	4.5	3.8	3.9	4.2
88.5°	4.9	5.4	6.3	5.6	5.4	4.8	4.2	3.3	2.9	2.8	2.7
89°	3.8	4.4	4.7	4.0	3.7	3.1	2.6	2.0	1.4	1.4	0.9
89.5°	2.5	3.3	3.0	2.1	2.0	1.4	0.8	0.5	0.0	0.0	0.0



TEST NUMBER: P991379

CATALOG NUMBER: SMD6S07FS5-930

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
90°	0.8	1.8	1.2	0.9	0.5	0.0	0.0	0.0	0.0	0.0	0.0
90.5°	0.1	0.4	0.3	0.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
91°	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
91.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P991379

CATALOG NUMBER: SMD6S07FS5-930

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
114°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
114.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
115.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
116°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
116.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
117°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
118°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
118.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
119°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
119.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
120.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
121°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
121.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
122°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
123°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
123.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
124°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
124.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
125.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
126°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
126.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
127°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
128°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
128.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
129°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
129.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
130.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
131°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
131.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
132°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
133°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
133.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
134°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
134.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P991379

CATALOG NUMBER: SMD6S07FS5-930

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
135°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
135.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
136°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
136.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
137°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
138°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
138.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
139°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
139.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.1	0.0	0.0
140.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.1	0.0	0.0
141°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
141.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
142°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
143°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
143.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
144°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
144.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
145.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
146°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
146.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
147°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
148°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
148.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
149°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
149.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
150.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
151°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
151.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
152°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
153°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
153.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
154°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
154.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
155.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
156°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
156.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
157°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0

TEST NUMBER: P991379

CATALOG NUMBER: SMD6S07FS5-930

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
157.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
158°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
158.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
159°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
159.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
160.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
161°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
161.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
162°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
163°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
163.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
164°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
164.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
165.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
166°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
166.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
167°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
167.5°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
168°	0.0	0.0	0.2	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
168.5°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
169°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
169.5°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
170°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
170.5°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
171°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
171.5°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
172°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
172.5°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
173°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
173.5°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
174°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.1	0.0	0.0	0.0
174.5°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.1	0.0	0.0	0.0
175°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.1	0.0	0.0	0.0
175.5°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.1	0.0	0.0	0.0
176°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.1	0.0	0.0	0.0
176.5°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.1	0.0	0.0	0.0
177°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.1	0.0	0.0	0.0
177.5°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.1	0.0	0.0	0.0
178°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.1	0.0	0.0	0.0
178.5°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.1	0.0	0.0	0.0
179°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.1	0.0	0.0	0.0
179.5°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.1	0.0	0.0	0.0



TEST NUMBER: P991379
CATALOG NUMBER: SMD6S07FS5-930

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P991379

CATALOG NUMBER: SMD6S07FS5-930

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	243.8	243.8	243.8	243.8	243.8	243.8
0.5°	243.9	243.8	243.7	243.7	243.7	243.9
1°	243.7	243.8	243.7	243.7	243.7	243.9
1.5°	243.7	243.8	243.7	243.7	243.7	243.9
2°	243.5	243.8	243.7	243.6	243.7	243.9
2.5°	243.5	243.9	243.7	243.6	243.7	243.9
3°	243.4	243.8	243.6	243.5	243.7	243.9
3.5°	243.1	243.7	243.6	243.4	243.7	244.0
4°	242.9	243.7	243.5	243.4	243.7	244.0
4.5°	242.8	243.4	243.4	243.3	243.7	243.7
5°	242.5	243.2	243.2	243.3	243.4	243.7
5.5°	242.2	242.9	243.0	243.1	243.2	243.4
6°	241.9	242.7	242.6	242.8	243.0	243.3
6.5°	241.6	242.3	242.3	242.4	242.7	242.9
7°	241.2	242.0	242.0	242.1	242.3	242.7
7.5°	241.0	241.6	241.8	241.9	242.1	242.3
8°	240.5	241.4	241.4	241.5	241.8	242.1
8.5°	240.1	240.9	240.9	241.2	241.4	241.7
9°	239.7	240.5	240.5	240.8	241.0	241.3
9.5°	239.2	240.1	240.1	240.4	240.5	240.9
10°	238.7	239.5	239.6	239.8	240.1	240.6
10.5°	238.3	239.0	239.1	239.3	239.6	240.0
11°	237.7	238.6	238.6	239.0	239.2	239.7
11.5°	237.4	238.0	238.0	238.4	238.8	239.2
12°	236.7	237.5	237.6	237.8	238.1	238.7
12.5°	236.1	237.0	237.0	237.2	237.6	238.2
13°	235.5	236.3	236.5	236.7	237.1	237.7
13.5°	234.9	235.7	235.8	236.1	236.5	237.1
14°	234.1	235.0	235.1	235.4	235.8	236.4
14.5°	233.6	234.3	234.6	234.8	235.3	235.8
15°	232.8	233.7	233.9	234.1	234.6	235.3
15.5°	232.2	232.9	233.2	233.4	234.0	234.6
16°	231.4	232.2	232.5	232.8	233.3	234.1
16.5°	230.7	231.4	231.7	232.1	232.7	233.3
17°	229.9	230.7	231.0	231.3	231.9	232.6
17.5°	229.1	229.9	230.2	230.6	231.2	231.8
18°	228.3	229.1	229.4	229.7	230.4	231.2
18.5°	227.6	228.2	228.5	228.9	229.6	230.3
19°	226.6	227.5	227.7	228.1	228.9	229.6
19.5°	225.8	226.6	227.0	227.3	228.0	228.7
20°	225.0	225.8	226.1	226.5	227.2	228.1
20.5°	224.1	224.8	225.2	225.6	226.3	227.1
21°	223.0	223.9	224.3	224.8	225.5	226.3
21.5°	222.2	222.9	223.4	223.8	224.7	225.3
22°	221.6	222.3	222.5	222.9	223.5	224.5



TEST NUMBER: P991379

CATALOG NUMBER: SMD6S07FS5-930

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
22.5°	220.4	221.2	221.5	222.3	222.8	223.5
23°	219.3	220.2	220.7	221.0	221.9	222.6
23.5°	218.4	219.2	219.5	220.1	220.9	221.8
24°	217.4	218.2	218.6	219.1	219.9	220.8
24.5°	216.3	217.1	217.5	218.1	218.9	219.8
25°	215.3	216.1	216.4	217.1	217.9	218.8
25.5°	214.2	215.0	215.3	216.0	216.9	217.7
26°	213.0	214.0	214.3	214.9	215.8	216.6
26.5°	211.9	212.8	213.1	213.8	214.8	215.6
27°	210.8	211.7	212.1	212.7	213.7	214.6
27.5°	209.6	210.5	211.0	211.5	212.5	213.4
28°	208.4	209.3	209.7	210.4	211.3	212.3
28.5°	207.2	208.1	208.5	209.2	210.3	211.1
29°	206.1	206.9	207.4	208.0	209.1	210.0
29.5°	205.0	205.8	206.2	206.8	208.0	208.8
30°	203.6	204.5	204.9	205.7	206.8	207.8
30.5°	202.4	203.2	203.6	204.3	205.6	206.5
31°	201.1	202.0	202.6	203.1	204.3	205.2
31.5°	199.9	200.6	201.1	201.8	203.1	204.0
32°	198.5	199.3	199.8	200.5	201.9	202.9
32.5°	197.2	198.0	198.6	199.3	200.6	201.5
33°	195.9	196.6	197.2	198.1	199.3	200.3
33.5°	194.6	195.3	195.9	196.7	198.0	198.9
34°	193.3	193.9	194.5	195.5	196.7	197.8
34.5°	191.9	192.7	193.2	194.0	195.3	196.4
35°	190.4	191.2	191.8	192.7	194.1	195.0
35.5°	189.1	189.8	190.4	191.3	192.6	193.7
36°	187.6	188.4	189.0	189.9	191.2	192.4
36.5°	186.3	186.8	187.6	188.4	189.7	190.9
37°	184.8	185.5	186.1	187.1	188.3	189.6
37.5°	183.4	184.0	184.6	185.7	186.9	188.1
38°	182.1	182.7	183.4	184.2	185.6	186.8
38.5°	180.7	181.2	181.8	182.9	184.1	185.2
39°	179.1	179.7	180.4	181.5	182.8	183.8
39.5°	177.7	178.3	178.9	179.9	181.4	182.5
40°	176.1	176.8	177.3	178.4	179.8	181.0
40.5°	174.6	175.1	175.9	176.9	178.4	179.5
41°	173.0	173.7	174.3	175.3	176.8	178.1
41.5°	171.5	172.1	172.8	173.8	175.3	176.4
42°	169.9	170.5	171.2	172.3	173.7	174.9
42.5°	168.4	168.9	169.6	170.7	172.1	173.4
43°	166.6	167.3	168.0	169.2	170.5	171.9
43.5°	165.1	165.7	166.4	167.5	169.0	170.2
44°	163.5	164.1	164.8	165.9	167.4	168.6
44.5°	161.9	162.4	163.1	164.3	165.8	167.2



TEST NUMBER: P991379

CATALOG NUMBER: SMD6S07FS5-930

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
45°	160.2	160.8	161.4	162.7	164.2	165.4
45.5°	158.6	159.2	159.9	161.1	162.5	163.8
46°	156.8	157.5	158.3	159.5	160.9	162.3
46.5°	155.2	155.8	156.6	157.8	159.2	160.7
47°	153.5	154.1	154.9	156.1	157.6	159.0
47.5°	151.8	152.5	153.2	154.4	156.0	157.4
48°	150.2	150.9	151.5	152.7	154.3	155.6
48.5°	148.5	149.1	149.8	151.0	152.6	154.1
49°	146.8	147.4	148.0	149.4	150.8	152.4
49.5°	145.1	145.6	146.3	147.6	149.2	150.6
50°	143.3	144.1	144.6	145.8	147.5	149.0
50.5°	141.8	142.3	142.9	144.1	145.7	147.2
51°	139.9	140.5	141.2	142.5	144.0	145.5
51.5°	138.2	138.8	139.4	140.7	142.5	143.9
52°	136.4	137.1	137.6	139.0	140.6	141.9
52.5°	134.6	135.2	135.8	137.2	138.9	140.2
53°	132.8	133.4	134.0	135.3	137.0	138.4
53.5°	130.9	131.6	132.2	133.6	135.3	136.7
54°	129.3	129.8	130.4	131.6	133.5	134.8
54.5°	127.4	127.9	128.6	129.8	131.6	132.9
55°	125.6	126.1	126.7	128.1	129.8	131.1
55.5°	123.7	124.3	124.9	126.3	128.0	129.2
56°	121.9	122.4	123.0	124.4	126.0	127.3
56.5°	120.0	120.5	121.1	122.6	124.3	125.5
57°	118.1	118.7	119.3	120.7	122.3	123.7
57.5°	116.3	116.7	117.4	118.8	120.4	121.7
58°	114.4	115.0	115.6	116.9	118.5	119.7
58.5°	112.4	113.1	113.7	115.1	116.7	118.0
59°	110.6	111.1	111.9	113.2	114.7	116.0
59.5°	108.7	109.4	110.0	111.3	112.8	114.1
60°	106.8	107.5	108.2	109.5	110.8	112.2
60.5°	104.9	105.6	106.1	107.5	108.9	110.3
61°	103.1	103.9	104.6	105.6	107.0	108.4
61.5°	101.3	102.1	102.6	103.8	105.1	106.4
62°	99.4	100.2	100.8	101.8	103.3	104.7
62.5°	97.5	98.2	98.8	100.0	101.3	102.8
63°	95.6	96.4	96.8	98.0	99.4	100.8
63.5°	93.7	94.5	95.0	96.0	97.5	98.9
64°	91.8	92.5	93.0	94.2	95.6	96.9
64.5°	89.9	90.6	91.2	92.2	93.5	95.0
65°	88.0	88.7	89.2	90.2	91.5	93.0
65.5°	86.0	86.7	87.3	88.3	89.7	91.0
66°	84.1	84.8	85.4	86.3	87.6	89.0
66.5°	82.3	82.8	83.4	84.3	85.6	87.0
67°	80.3	80.9	81.5	82.3	83.6	85.0



TEST NUMBER: P991379

CATALOG NUMBER: SMD6S07FS5-930

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
67.5°	78.5	78.9	79.6	80.3	81.5	82.9
68°	76.5	77.0	77.6	78.4	79.6	81.1
68.5°	74.6	75.0	75.8	76.4	77.6	79.1
69°	72.8	73.0	73.8	74.5	75.7	77.0
69.5°	70.8	71.1	71.7	72.4	73.7	75.1
70°	68.9	69.2	69.9	70.6	71.7	73.1
70.5°	67.0	67.2	68.0	68.6	69.8	71.1
71°	65.0	65.5	66.0	66.6	67.8	69.2
71.5°	63.2	63.5	64.2	64.8	65.9	67.3
72°	61.2	61.5	62.3	62.8	64.1	65.5
72.5°	59.4	59.6	60.4	60.8	62.0	63.4
73°	57.3	57.8	58.3	59.0	60.1	61.4
73.5°	55.5	55.8	56.5	56.9	58.1	59.5
74°	53.5	53.9	54.5	55.1	56.3	57.6
74.5°	51.5	52.0	52.6	53.0	54.4	55.6
75°	49.7	50.2	50.6	51.1	52.4	53.7
75.5°	47.7	48.2	48.6	49.2	50.5	51.7
76°	45.8	46.3	46.7	47.3	48.6	49.8
76.5°	43.8	44.5	44.7	45.5	46.7	47.9
77°	41.9	42.5	42.9	43.4	44.8	45.9
77.5°	40.1	40.8	40.9	41.5	42.9	44.1
78°	38.2	38.8	39.1	39.7	41.0	42.2
78.5°	36.3	37.0	37.2	37.7	39.1	40.4
79°	34.5	35.1	35.3	36.0	37.2	38.5
79.5°	32.6	33.3	33.4	34.1	35.3	36.7
80°	30.7	31.5	31.6	32.1	33.3	34.8
80.5°	29.0	29.8	29.9	30.2	31.5	32.9
81°	27.1	27.8	28.0	28.4	29.7	31.2
81.5°	25.5	26.3	26.4	26.6	27.9	29.3
82°	23.8	24.4	24.7	24.9	26.3	27.5
82.5°	22.1	22.7	22.9	23.1	24.4	25.8
83°	20.3	20.9	21.2	21.5	22.6	24.0
83.5°	18.6	19.0	19.5	19.7	20.7	22.2
84°	17.0	17.3	17.7	18.1	18.9	20.3
84.5°	15.4	15.6	16.1	16.4	17.1	18.5
85°	13.6	13.8	14.4	14.9	15.3	16.7
85.5°	12.1	12.0	12.7	13.2	13.4	14.9
86°	10.4	10.2	11.1	11.8	11.7	13.1
86.5°	8.7	8.5	9.4	10.3	10.1	11.1
87°	7.2	6.7	7.9	8.8	8.4	8.6
87.5°	5.6	5.1	6.3	7.3	7.2	7.1
88°	4.0	3.4	4.5	5.9	6.2	6.1
88.5°	2.3	2.1	3.1	4.3	4.9	4.9
89°	0.6	0.8	1.5	2.6	3.7	3.8
89.5°	0.0	0.2	0.5	1.1	2.3	2.5



TEST NUMBER: P991379

CATALOG NUMBER: SMD6S07FS5-930

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
90°	0.0	0.0	0.0	0.2	0.7	0.8
90.5°	0.0	0.0	0.0	0.0	0.1	0.1
91°	0.0	0.0	0.0	0.0	0.0	0.0
91.5°	0.0	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P991379

CATALOG NUMBER: SMD6S07FS5-930

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.0	0.0	0.0	0.0	0.0	0.0
113.5°	0.0	0.0	0.0	0.0	0.0	0.0
114°	0.0	0.0	0.0	0.0	0.0	0.0
114.5°	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0
115.5°	0.0	0.0	0.0	0.0	0.0	0.0
116°	0.0	0.0	0.0	0.0	0.0	0.0
116.5°	0.0	0.0	0.0	0.0	0.0	0.0
117°	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0
118°	0.0	0.0	0.0	0.0	0.0	0.0
118.5°	0.0	0.0	0.0	0.0	0.0	0.0
119°	0.0	0.0	0.0	0.0	0.0	0.0
119.5°	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0
120.5°	0.0	0.0	0.0	0.0	0.0	0.0
121°	0.0	0.0	0.0	0.0	0.0	0.0
121.5°	0.0	0.0	0.0	0.0	0.0	0.0
122°	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0
123°	0.0	0.0	0.0	0.0	0.0	0.0
123.5°	0.0	0.0	0.0	0.0	0.0	0.0
124°	0.0	0.0	0.0	0.0	0.0	0.0
124.5°	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0
125.5°	0.0	0.0	0.0	0.0	0.0	0.0
126°	0.0	0.0	0.0	0.0	0.0	0.0
126.5°	0.0	0.0	0.0	0.0	0.0	0.0
127°	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0
128°	0.0	0.0	0.0	0.0	0.0	0.0
128.5°	0.0	0.0	0.0	0.0	0.0	0.0
129°	0.0	0.0	0.0	0.0	0.0	0.0
129.5°	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0
130.5°	0.0	0.0	0.0	0.0	0.0	0.0
131°	0.0	0.0	0.0	0.0	0.0	0.0
131.5°	0.0	0.0	0.0	0.0	0.0	0.0
132°	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0
133°	0.0	0.0	0.0	0.0	0.0	0.0
133.5°	0.0	0.0	0.0	0.0	0.0	0.0
134°	0.0	0.0	0.0	0.0	0.0	0.0
134.5°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P991379

CATALOG NUMBER: SMD6S07FS5-930

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
135°	0.0	0.0	0.0	0.0	0.0	0.0
135.5°	0.0	0.0	0.0	0.0	0.0	0.0
136°	0.2	0.0	0.0	0.0	0.0	0.0
136.5°	0.2	0.0	0.0	0.0	0.0	0.0
137°	0.1	0.0	0.0	0.0	0.0	0.0
137.5°	0.1	0.0	0.0	0.0	0.0	0.0
138°	0.1	0.0	0.0	0.0	0.0	0.0
138.5°	0.1	0.0	0.0	0.0	0.0	0.0
139°	0.1	0.0	0.0	0.0	0.0	0.0
139.5°	0.1	0.0	0.0	0.0	0.0	0.0
140°	0.1	0.0	0.0	0.0	0.0	0.0
140.5°	0.1	0.0	0.0	0.0	0.0	0.0
141°	0.1	0.0	0.0	0.0	0.0	0.0
141.5°	0.1	0.0	0.0	0.0	0.0	0.0
142°	0.1	0.0	0.0	0.0	0.0	0.0
142.5°	0.1	0.0	0.0	0.0	0.0	0.0
143°	0.1	0.0	0.0	0.0	0.0	0.0
143.5°	0.1	0.0	0.0	0.0	0.0	0.0
144°	0.1	0.0	0.0	0.0	0.0	0.0
144.5°	0.1	0.0	0.0	0.0	0.0	0.0
145°	0.1	0.0	0.0	0.0	0.0	0.0
145.5°	0.1	0.0	0.0	0.0	0.0	0.0
146°	0.1	0.0	0.0	0.0	0.0	0.0
146.5°	0.1	0.0	0.0	0.0	0.0	0.0
147°	0.1	0.0	0.0	0.0	0.0	0.0
147.5°	0.1	0.0	0.0	0.0	0.0	0.0
148°	0.1	0.0	0.0	0.0	0.0	0.0
148.5°	0.1	0.0	0.0	0.0	0.0	0.0
149°	0.1	0.0	0.0	0.0	0.0	0.0
149.5°	0.1	0.0	0.0	0.0	0.0	0.0
150°	0.1	0.0	0.0	0.0	0.0	0.0
150.5°	0.1	0.0	0.0	0.0	0.0	0.0
151°	0.1	0.0	0.0	0.0	0.0	0.0
151.5°	0.1	0.0	0.0	0.0	0.0	0.0
152°	0.1	0.0	0.0	0.0	0.0	0.0
152.5°	0.1	0.0	0.0	0.0	0.0	0.0
153°	0.1	0.0	0.0	0.0	0.0	0.0
153.5°	0.1	0.0	0.0	0.0	0.0	0.0
154°	0.1	0.0	0.0	0.0	0.0	0.0
154.5°	0.1	0.0	0.0	0.0	0.0	0.0
155°	0.1	0.0	0.0	0.0	0.0	0.0
155.5°	0.1	0.0	0.0	0.0	0.0	0.0
156°	0.1	0.0	0.0	0.0	0.0	0.0
156.5°	0.1	0.0	0.0	0.0	0.0	0.0
157°	0.1	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P991379

CATALOG NUMBER: SMD6S07FS5-930

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
157.5°	0.1	0.0	0.0	0.0	0.0	0.0
158°	0.1	0.0	0.0	0.0	0.0	0.0
158.5°	0.1	0.0	0.0	0.0	0.0	0.0
159°	0.1	0.0	0.0	0.0	0.0	0.0
159.5°	0.1	0.0	0.0	0.0	0.0	0.0
160°	0.1	0.0	0.0	0.0	0.0	0.0
160.5°	0.1	0.0	0.0	0.0	0.0	0.0
161°	0.1	0.0	0.0	0.0	0.0	0.0
161.5°	0.1	0.0	0.0	0.0	0.0	0.0
162°	0.1	0.0	0.0	0.0	0.0	0.0
162.5°	0.1	0.0	0.0	0.0	0.0	0.0
163°	0.1	0.0	0.0	0.0	0.0	0.0
163.5°	0.1	0.0	0.0	0.0	0.0	0.0
164°	0.1	0.0	0.0	0.0	0.0	0.0
164.5°	0.1	0.0	0.0	0.0	0.0	0.0
165°	0.1	0.0	0.0	0.0	0.0	0.0
165.5°	0.1	0.0	0.0	0.0	0.0	0.0
166°	0.1	0.0	0.0	0.0	0.0	0.0
166.5°	0.1	0.0	0.0	0.0	0.0	0.0
167°	0.1	0.0	0.0	0.0	0.0	0.0
167.5°	0.1	0.0	0.0	0.0	0.0	0.0
168°	0.1	0.0	0.0	0.0	0.0	0.0
168.5°	0.1	0.0	0.0	0.0	0.0	0.0
169°	0.1	0.0	0.0	0.0	0.0	0.0
169.5°	0.1	0.0	0.0	0.0	0.0	0.0
170°	0.1	0.0	0.0	0.0	0.0	0.0
170.5°	0.1	0.0	0.0	0.0	0.0	0.0
171°	0.1	0.0	0.0	0.0	0.0	0.0
171.5°	0.1	0.0	0.0	0.1	0.0	0.0
172°	0.1	0.0	0.0	0.1	0.0	0.0
172.5°	0.1	0.0	0.0	0.1	0.0	0.0
173°	0.1	0.0	0.0	0.1	0.0	0.0
173.5°	0.1	0.0	0.0	0.1	0.0	0.0
174°	0.1	0.0	0.0	0.1	0.0	0.0
174.5°	0.1	0.0	0.0	0.1	0.0	0.0
175°	0.1	0.0	0.0	0.1	0.0	0.0
175.5°	0.1	0.0	0.0	0.1	0.0	0.0
176°	0.1	0.0	0.0	0.1	0.0	0.0
176.5°	0.1	0.0	0.0	0.1	0.0	0.0
177°	0.1	0.0	0.0	0.1	0.0	0.0
177.5°	0.1	0.0	0.0	0.1	0.0	0.0
178°	0.1	0.0	0.0	0.1	0.0	0.0
178.5°	0.1	0.0	0.0	0.1	0.0	0.0
179°	0.1	0.0	0.0	0.1	0.0	0.0
179.5°	0.1	0.0	0.0	0.1	0.0	0.0



TEST NUMBER: P991379
CATALOG NUMBER: SMD6S07FS5-930

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
180°	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)