

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P991381

Luminaire Tested: **SMD6S07FS5-940**

Issue Date: 05/20/2025



Test Information

Test Method: LM-79-08
Report Number: P991381
Test Lab: THIRD PARTY NVLAP
Issue Date: 05/20/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: SMD6S07FS5-940
Description: HALO SURFACE MOUNT 6 inch 90 CRI COLOR SELECTABLE SQUARE FIXTURE
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 730.0 lumens
Efficiency: N/A
Efficacy: 89.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.25 / 1.37
Luminous Opening: Rectangular (W 0.5' x L: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 8.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P991381
CATALOG NUMBER: SMD6S07FS5-940

Luminous Intensity Polar Plot



TEST NUMBER: P991381

CATALOG NUMBER: SMD6S07FS5-940

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	108	103	99	95	106	101	97	93	97	94	90		93	90	88		89
2	98	90	83	77	96	88	81	76	84	79	74		81	76	72		78
3	89	79	70	64	87	77	69	63	74	67	62		71	66	61		69
4	82	70	61	54	79	68	60	53	66	58	53		63	57	52		61
5	75	62	53	46	73	61	52	46	59	51	45		57	50	45		55
6	69	56	47	40	67	55	46	40	53	45	40		51	45	39		50
7	64	51	42	35	63	50	41	35	48	41	35		47	40	35		45
8	60	46	38	32	58	45	37	32	44	37	31		43	36	31		42
9	56	42	34	28	54	42	34	28	41	33	28		39	33	28		38
10	52	39	31	26	51	39	31	26	38	30	26		37	30	25		36

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10794	10794	10794	10794
5°	10827	10788	10775	10809
10°	10816	10768	10724	10768
15°	10783	10729	10671	10707
20°	10745	10685	10612	10639
25°	10684	10622	10537	10556
30°	10619	10555	10445	10450
35°	10539	10465	10339	10334
40°	10460	10375	10252	10218
45°	10357	10260	10132	10071
50°	10262	10141	10001	9920
55°	10119	10006	9811	9728
60°	9937	9834	9567	9515
65°	9740	9668	9322	9291
70°	9467	9454	8988	8951
75°	9183	9233	8584	8584
80°	8877	8951	8034	8009
85°	8448	8793	6966	7015



TEST NUMBER: P991381
 CATALOG NUMBER: SMD6S07FS5-940

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.7	3.3
10°-20°	67.9	9.3
20°-30°	102.7	14.1
30°-40°	123.9	17.0
40°-50°	129.0	17.7
50°-60°	117.7	16.1
60°-70°	91.8	12.6
70°-80°	56.0	7.7
80°-90°	17.2	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	194.3	26.6
0°-40°	318.2	43.6
0°-60°	564.9	77.4
0°-90°	729.9	100.0
90°-120°	0.0	0.0
90°-150°	0.1	0.0
90°-180°	0.0	0.0
0°-180°	730.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	251	251	251	251	251	
5°	250	250	249	250	250	24
15°	242	241	239	240	242	68
25°	225	224	222	222	225	104
35°	200	199	197	197	200	125
45°	170	168	166	165	170	131
55°	135	133	131	130	135	120
65°	96	95	92	91	96	94
75°	55	56	52	52	55	58
85°	17	18	14	14	17	18
90°	1	0	0	0	1	1
95°	0	0	0	0	0	0
105°	0	0	0	0	0	0
115°	0	0	0	0	0	0
125°	0	0	0	0	0	0
135°	0	0	0	0	0	0
145°	0	0	0	0	0	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	

TEST NUMBER: P991381

CATALOG NUMBER: SMD6S07F55-940

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
0°	250.7	250.7	250.7	250.7	250.7	250.7	250.7	250.7	250.7	250.7	250.7
0.5°	250.8	250.8	250.8	250.7	250.8	250.6	250.5	250.5	250.8	250.7	250.8
1°	250.8	250.8	250.8	250.7	250.6	250.6	250.5	250.3	250.7	250.5	250.6
1.5°	250.8	250.7	250.8	250.7	250.5	250.5	250.5	250.3	250.5	250.5	250.5
2°	250.8	250.7	250.8	250.7	250.5	250.5	250.4	250.3	250.5	250.5	250.5
2.5°	250.8	250.7	250.7	250.6	250.4	250.4	250.4	250.1	250.1	250.4	250.5
3°	250.8	250.7	250.7	250.6	250.3	250.2	250.2	250.0	250.1	250.1	250.4
3.5°	250.8	250.7	250.6	250.6	250.3	250.1	250.1	249.8	249.7	249.8	250.0
4°	250.8	250.8	250.6	250.5	250.0	250.0	249.8	249.6	249.6	249.7	249.7
4.5°	250.5	250.8	250.5	250.5	249.7	249.8	249.5	249.4	249.3	249.4	249.6
5°	250.5	250.5	250.4	250.5	249.6	249.5	249.3	249.1	249.3	249.3	249.3
5.5°	250.3	250.4	250.4	250.2	249.3	249.3	249.0	249.0	248.8	248.9	249.1
6°	250.1	250.1	250.2	250.0	249.1	249.0	248.9	248.5	248.7	248.6	248.6
6.5°	249.7	249.8	249.9	249.8	248.9	248.8	248.5	248.3	248.4	248.3	248.3
7°	249.5	249.5	249.6	249.6	248.5	248.5	248.2	247.9	248.2	248.2	248.2
7.5°	249.1	249.2	249.4	249.2	248.2	248.1	247.9	247.7	247.5	247.7	247.7
8°	249.0	248.8	249.0	248.9	247.8	247.8	247.7	247.1	247.1	247.2	247.1
8.5°	248.5	248.5	248.7	248.6	247.7	247.7	247.0	246.8	246.6	246.8	246.8
9°	248.1	248.1	248.2	248.2	247.1	246.9	246.6	246.3	246.3	246.4	246.2
9.5°	247.7	247.6	247.8	247.7	246.7	246.6	246.2	245.9	245.9	245.9	245.8
10°	247.4	247.1	247.4	247.2	246.3	246.2	245.7	245.3	245.3	245.4	245.3
10.5°	246.8	246.7	246.9	246.8	245.8	245.7	245.3	244.9	244.8	244.8	244.8
11°	246.4	246.2	246.3	246.4	245.4	245.2	244.7	244.3	244.4	244.4	244.3
11.5°	246.0	245.7	245.9	245.9	244.8	244.6	244.2	243.9	243.7	243.9	243.7
12°	245.5	245.2	245.4	245.4	244.4	244.1	243.7	243.2	243.2	243.3	243.0
12.5°	244.9	244.6	244.9	244.7	243.9	243.5	243.1	242.7	242.6	242.7	242.6
13°	244.4	244.1	244.2	244.3	243.3	242.9	242.6	242.1	242.0	242.2	241.8
13.5°	243.7	243.5	243.7	243.7	242.8	242.6	242.0	241.5	241.4	241.5	241.2
14°	243.1	243.0	243.0	242.9	242.0	241.8	241.2	240.8	240.7	240.8	240.6
14.5°	242.5	242.4	242.4	242.4	241.4	241.2	240.5	240.2	240.0	240.1	240.0
15°	241.9	241.7	241.7	241.7	240.7	240.4	239.9	239.4	239.4	239.4	239.2
15.5°	241.2	241.1	241.1	241.1	240.1	239.8	239.2	238.8	238.7	238.7	238.5
16°	240.7	240.3	240.4	240.4	239.4	238.9	238.5	238.0	238.0	238.0	237.8
16.5°	239.9	239.6	239.7	239.7	238.8	238.3	237.8	237.4	237.3	237.3	236.9
17°	239.2	238.9	239.0	238.9	238.0	237.6	236.9	236.5	236.6	236.5	236.4
17.5°	238.3	238.2	238.3	238.2	237.2	236.8	236.2	235.6	235.7	235.6	235.4
18°	237.7	237.5	237.3	237.4	236.5	236.0	235.3	235.0	234.9	234.9	234.6
18.5°	236.8	236.6	236.6	236.5	235.6	235.2	234.5	234.0	234.1	234.2	233.8
19°	236.1	235.8	235.8	235.7	235.0	234.3	233.8	233.2	233.2	233.2	232.9
19.5°	235.1	235.0	235.0	234.9	233.9	233.7	232.9	232.5	232.4	232.4	232.0
20°	234.5	234.1	234.1	234.0	233.2	232.6	232.0	231.5	231.6	231.5	231.2
20.5°	233.5	233.2	233.2	233.1	232.3	231.8	231.2	230.6	230.7	230.4	230.2
21°	232.7	232.4	232.3	232.3	231.5	230.8	230.1	229.7	229.8	229.5	229.2
21.5°	231.7	231.5	231.4	231.3	230.4	230.0	229.3	228.9	228.8	228.6	228.2
22°	230.8	230.6	230.4	230.4	229.5	228.9	228.2	227.9	227.9	227.9	227.6



TEST NUMBER: P991381

CATALOG NUMBER: SMD6S07F55-940

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
22.5°	229.8	229.7	229.6	229.5	228.7	228.1	227.7	226.8	227.0	226.7	226.5
23°	228.9	228.8	228.8	228.6	227.8	227.1	226.5	225.9	225.9	225.7	225.5
23.5°	228.0	227.8	227.7	227.5	226.7	226.3	225.4	224.9	225.0	224.6	224.3
24°	227.0	226.8	226.7	226.5	225.9	225.0	224.3	223.8	224.0	223.6	223.2
24.5°	226.0	225.8	225.7	225.5	224.7	224.0	223.3	222.8	222.9	222.7	222.3
25°	224.9	224.7	224.7	224.4	223.6	222.8	222.3	221.7	221.8	221.5	221.2
25.5°	223.9	223.7	223.6	223.5	222.6	221.8	221.2	220.7	220.6	220.3	219.9
26°	222.7	222.6	222.5	222.4	221.5	220.7	220.1	219.6	219.6	219.2	218.8
26.5°	221.6	221.6	221.4	221.2	220.4	219.7	219.0	218.5	218.5	218.1	217.6
27°	220.7	220.4	220.3	220.1	219.3	218.5	217.8	217.3	217.2	217.0	216.5
27.5°	219.4	219.4	219.2	218.9	218.2	217.4	216.6	216.3	216.2	215.7	215.3
28°	218.2	218.1	218.0	217.8	217.1	216.1	215.4	214.9	215.0	214.7	214.1
28.5°	217.1	217.0	216.8	216.6	215.9	214.9	214.2	213.8	213.8	213.4	212.9
29°	215.9	215.8	215.6	215.4	214.7	213.8	213.0	212.5	212.6	212.3	211.7
29.5°	214.7	214.6	214.5	214.1	213.4	212.6	211.8	211.4	211.5	211.1	210.5
30°	213.6	213.5	213.2	212.9	212.3	211.2	210.5	210.1	210.1	209.8	209.2
30.5°	212.3	212.2	212.0	211.6	211.0	210.0	209.2	208.9	208.9	208.5	208.0
31°	211.0	210.9	210.7	210.3	209.7	208.7	208.0	207.6	207.8	207.4	206.6
31.5°	209.7	209.7	209.5	209.0	208.5	207.5	206.7	206.2	206.3	205.8	205.2
32°	208.6	208.4	208.2	207.8	207.3	206.1	205.3	205.0	204.9	204.6	203.9
32.5°	207.2	207.1	206.9	206.5	205.9	204.8	204.1	203.8	203.6	203.2	202.6
33°	206.0	205.7	205.6	205.1	204.6	203.5	202.8	202.4	202.2	201.9	201.3
33.5°	204.5	204.5	204.3	203.8	203.2	202.1	201.4	201.0	200.9	200.4	199.9
34°	203.3	203.1	202.8	202.4	201.9	200.7	200.0	199.8	199.5	199.1	198.6
34.5°	201.9	201.7	201.5	201.0	200.5	199.3	198.6	198.4	198.1	197.6	197.1
35°	200.5	200.3	200.1	199.6	199.1	197.8	197.2	196.9	196.7	196.3	195.7
35.5°	199.1	199.0	198.7	198.2	197.6	196.5	195.8	195.4	195.3	194.9	194.1
36°	197.8	197.7	197.3	196.8	196.2	195.1	194.4	194.1	193.9	193.5	192.8
36.5°	196.3	196.2	195.8	195.3	194.8	193.6	192.8	192.7	192.5	191.9	191.2
37°	194.9	194.7	194.4	193.8	193.3	192.2	191.3	191.1	191.0	190.5	189.8
37.5°	193.4	193.3	193.1	192.4	192.0	190.7	189.9	189.7	189.5	188.9	188.4
38°	192.0	191.8	191.4	190.9	190.4	189.2	188.4	188.2	188.1	187.7	187.0
38.5°	190.4	190.4	189.9	189.5	188.9	187.6	187.0	186.9	186.9	186.2	185.6
39°	189.0	189.0	188.7	188.1	187.6	186.4	185.7	185.4	185.3	184.7	183.8
39.5°	187.6	187.6	187.1	186.6	186.1	185.0	184.0	183.9	183.9	183.1	182.4
40°	186.1	186.1	185.6	185.1	184.6	183.4	182.4	182.3	182.4	181.6	180.9
40.5°	184.5	184.7	184.1	183.5	183.0	181.8	180.9	180.8	180.8	180.0	179.3
41°	183.1	183.1	182.5	181.9	181.4	180.2	179.4	179.3	179.2	178.4	177.6
41.5°	181.4	181.5	180.9	180.3	179.9	178.7	177.8	177.7	177.6	176.8	176.1
42°	179.8	179.9	179.4	178.7	178.3	177.2	176.1	176.1	176.1	175.3	174.5
42.5°	178.3	178.4	177.7	177.0	176.8	175.4	174.6	174.4	174.5	173.6	172.9
43°	176.7	176.7	176.1	175.4	175.1	173.8	173.0	172.9	173.0	172.1	171.2
43.5°	175.0	175.1	174.5	173.7	173.5	172.1	171.4	171.2	171.4	170.3	169.6
44°	173.4	173.4	172.9	172.1	171.9	170.6	169.6	169.6	169.7	168.6	167.8
44.5°	171.9	171.9	171.1	170.4	170.2	168.9	168.0	167.9	168.1	167.0	166.2

TEST NUMBER: P991381

CATALOG NUMBER: SMD6S07FS5-940

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
45°	170.1	170.2	169.5	168.8	168.5	167.2	166.4	166.3	166.4	165.5	164.5
45.5°	168.4	168.5	167.9	167.1	167.0	165.5	164.8	164.6	164.8	163.6	162.8
46°	166.9	166.8	166.2	165.4	165.1	163.9	163.0	162.9	163.2	162.0	161.0
46.5°	165.2	165.2	164.6	163.7	163.5	162.2	161.3	161.3	161.5	160.2	159.4
47°	163.5	163.4	162.9	162.0	161.9	160.5	159.6	159.5	159.7	158.6	157.7
47.5°	161.8	161.8	161.1	160.3	160.1	158.7	157.8	157.8	158.1	156.9	155.9
48°	160.0	160.0	159.4	158.6	158.5	157.0	156.1	156.1	156.3	155.1	154.3
48.5°	158.4	158.3	157.6	156.8	156.7	155.2	154.3	154.4	154.6	153.3	152.4
49°	156.7	156.6	155.9	155.0	155.0	153.5	152.5	152.6	152.9	151.6	150.6
49.5°	154.9	154.8	154.1	153.2	153.1	151.7	150.8	150.9	151.2	149.8	148.9
50°	153.2	153.1	152.4	151.4	151.4	149.9	149.1	149.1	149.3	148.1	147.3
50.5°	151.3	151.3	150.6	149.6	149.6	148.1	147.3	147.5	147.6	146.4	145.5
51°	149.6	149.5	148.8	148.1	147.8	146.6	145.6	145.7	145.8	144.5	143.7
51.5°	147.9	148.0	147.0	146.2	146.1	144.6	143.8	144.0	143.9	142.9	141.8
52°	145.9	146.0	145.2	144.5	144.3	142.9	142.1	142.2	142.1	141.0	140.0
52.5°	144.1	144.2	143.5	142.6	142.6	141.0	140.2	140.3	140.2	139.1	138.2
53°	142.3	142.4	141.6	140.8	140.7	139.2	138.4	138.5	138.4	137.2	136.4
53.5°	140.5	140.5	139.7	138.8	138.8	137.4	136.7	136.7	136.3	135.4	134.4
54°	138.6	138.6	137.9	137.0	136.9	135.5	134.7	134.7	134.5	133.4	132.7
54.5°	136.7	136.7	136.1	135.2	135.2	133.7	132.8	132.8	132.6	131.7	130.9
55°	134.8	134.7	134.2	133.3	133.3	131.8	131.0	130.9	130.7	129.6	128.9
55.5°	132.8	133.0	132.3	131.6	131.4	130.0	129.2	129.0	128.7	127.8	127.0
56°	130.9	131.0	130.4	129.6	129.5	128.1	127.3	127.0	126.8	125.7	125.3
56.5°	129.0	129.1	128.5	127.8	127.7	126.2	125.4	125.0	124.7	123.9	123.3
57°	127.1	127.1	126.6	125.8	125.7	124.3	123.5	123.0	122.9	121.9	121.5
57.5°	125.1	125.2	124.6	123.9	123.8	122.5	121.7	121.1	120.9	119.9	119.5
58°	123.1	123.2	122.8	122.0	122.0	120.5	119.8	119.2	118.9	118.0	117.6
58.5°	121.3	121.4	120.7	120.1	120.0	118.6	118.0	117.2	117.0	116.1	115.7
59°	119.3	119.3	119.0	118.2	118.1	116.6	116.0	115.2	115.0	114.1	113.7
59.5°	117.3	117.4	117.1	116.2	116.1	114.7	114.0	113.2	113.1	112.1	111.8
60°	115.4	115.3	115.1	114.3	114.2	112.8	112.1	111.2	111.1	110.3	109.8
60.5°	113.4	113.3	113.1	112.4	112.2	110.8	110.1	109.2	109.1	108.2	107.9
61°	111.4	111.4	111.1	110.4	110.4	108.9	108.1	107.3	107.2	106.4	106.0
61.5°	109.4	109.4	109.2	108.4	108.4	107.0	106.4	105.5	105.4	104.5	104.0
62°	107.7	107.6	107.5	106.7	106.8	105.2	104.4	103.4	103.3	102.6	102.1
62.5°	105.7	105.5	105.3	104.8	104.7	103.2	102.4	101.6	101.4	100.5	100.0
63°	103.6	103.6	103.4	102.8	102.8	101.3	100.3	99.5	99.4	98.4	98.1
63.5°	101.7	101.6	101.4	100.8	100.8	99.3	98.3	97.6	97.5	96.4	96.1
64°	99.6	99.6	99.4	98.9	98.8	97.3	96.4	95.5	95.5	94.4	94.1
64.5°	97.7	97.6	97.5	96.9	96.8	95.4	94.3	93.6	93.4	92.4	92.0
65°	95.6	95.6	95.3	95.0	94.9	93.4	92.3	91.6	91.5	90.4	90.1
65.5°	93.5	93.6	93.4	93.0	92.9	91.5	90.4	89.6	89.4	88.4	88.0
66°	91.5	91.4	91.3	91.0	91.0	89.5	88.3	87.5	87.5	86.4	86.2
66.5°	89.5	89.5	89.3	89.0	88.9	87.4	86.3	85.6	85.4	84.4	84.0
67°	87.4	87.5	87.3	87.1	87.1	85.5	84.3	83.6	83.4	82.4	82.0

TEST NUMBER: P991381

CATALOG NUMBER: SMD6S07FS5-940

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
67.5°	85.2	85.4	85.3	84.9	85.0	83.6	82.4	81.6	81.4	80.4	80.0
68°	83.3	83.4	83.2	83.0	82.9	81.6	80.2	79.6	79.4	78.4	77.9
68.5°	81.4	81.4	81.2	81.1	81.1	79.6	78.2	77.6	77.4	76.4	76.0
69°	79.2	79.3	79.0	79.0	79.0	77.6	76.2	75.6	75.4	74.4	74.0
69.5°	77.2	77.4	77.1	77.0	77.0	75.6	74.2	73.5	73.4	72.3	72.0
70°	75.2	75.3	75.0	74.9	75.1	73.6	72.3	71.6	71.4	70.3	70.1
70.5°	73.1	73.3	73.1	72.9	73.1	71.7	70.2	69.6	69.4	68.4	68.0
71°	71.1	71.2	71.0	71.1	71.2	69.8	68.2	67.6	67.4	66.5	66.2
71.5°	69.1	69.2	68.9	69.0	69.1	67.7	66.4	65.7	65.5	64.6	64.1
72°	67.3	67.3	67.2	67.2	67.2	65.9	64.4	63.7	63.5	62.5	62.3
72.5°	65.2	65.3	65.0	65.1	65.3	64.0	62.4	61.7	61.6	60.6	60.1
73°	63.1	63.3	63.1	63.2	63.4	62.0	60.4	59.7	59.7	58.7	58.2
73.5°	61.2	61.3	61.0	61.2	61.4	60.0	58.4	57.7	57.6	56.5	56.2
74°	59.2	59.3	59.0	59.1	59.5	57.9	56.5	55.9	55.6	54.7	54.2
74.5°	57.2	57.3	57.0	57.2	57.4	56.0	54.5	53.9	53.6	52.7	52.3
75°	55.2	55.3	55.1	55.2	55.5	54.0	52.4	51.9	51.6	50.7	50.3
75.5°	53.2	53.3	53.1	53.2	53.5	52.0	50.5	49.9	49.7	48.7	48.2
76°	51.2	51.3	51.0	51.2	51.5	50.0	48.5	48.0	47.7	46.9	46.3
76.5°	49.2	49.4	49.1	49.3	49.6	48.0	46.6	46.0	45.8	44.9	44.3
77°	47.2	47.4	47.1	47.2	47.6	46.1	44.6	44.0	43.8	43.0	42.4
77.5°	45.3	45.5	45.2	45.3	45.7	44.1	42.7	42.0	42.0	41.0	40.6
78°	43.4	43.5	43.2	43.3	43.7	42.2	40.8	40.1	40.0	39.1	38.6
78.5°	41.5	41.5	41.3	41.3	41.8	40.2	38.8	38.1	38.1	37.2	36.7
79°	39.5	39.5	39.3	39.4	39.9	38.2	36.9	36.2	36.2	35.2	34.8
79.5°	37.7	37.6	37.3	37.4	38.0	36.3	35.0	34.3	34.2	33.3	32.8
80°	35.8	35.7	35.4	35.5	36.1	34.5	33.0	32.3	32.4	31.4	31.0
80.5°	33.9	33.7	33.5	33.6	34.2	32.6	31.1	30.5	30.5	29.6	29.1
81°	32.0	31.8	31.6	31.7	32.4	30.7	29.3	28.6	28.6	27.6	27.3
81.5°	30.1	29.8	29.7	29.9	30.5	28.8	27.3	26.7	26.7	25.9	25.5
82°	28.2	27.9	27.8	28.0	28.5	27.0	25.6	25.0	25.1	24.1	23.7
82.5°	26.6	26.2	26.2	26.3	26.8	25.5	23.8	23.1	23.3	22.2	22.0
83°	24.7	24.4	24.2	24.6	25.1	23.7	22.0	21.3	21.4	20.3	20.0
83.5°	22.8	22.5	22.4	22.8	23.3	21.9	20.3	19.4	19.5	18.5	18.3
84°	20.9	20.6	20.6	21.0	21.5	20.1	18.5	17.5	17.7	16.7	16.6
84.5°	19.0	18.7	18.8	19.3	19.7	18.3	16.9	15.8	15.9	14.9	15.0
85°	17.1	16.9	17.1	17.5	17.8	16.6	15.2	13.8	14.1	13.0	13.3
85.5°	15.4	15.0	15.5	15.8	16.0	14.9	13.5	11.9	12.2	11.2	11.7
86°	13.4	13.2	13.9	14.2	14.3	13.3	12.0	10.2	10.2	9.3	10.2
86.5°	11.5	11.3	12.2	12.5	12.4	11.6	10.6	8.4	7.5	7.3	8.7
87°	8.8	9.2	10.8	10.8	10.7	9.9	8.9	7.0	6.2	6.1	7.2
87.5°	7.3	7.9	9.3	9.2	8.9	8.2	7.4	5.8	5.0	5.2	5.8
88°	6.3	6.7	7.9	7.5	7.2	6.6	5.8	4.6	3.9	4.0	4.3
88.5°	5.0	5.6	6.5	5.8	5.5	4.9	4.3	3.4	3.0	2.9	2.8
89°	3.9	4.6	4.8	4.1	3.8	3.2	2.7	2.1	1.5	1.4	0.9
89.5°	2.6	3.4	3.1	2.2	2.0	1.5	0.8	0.5	0.0	0.0	0.0

TEST NUMBER: P991381

CATALOG NUMBER: SMD6S07FS5-940

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
90°	0.8	1.9	1.3	0.9	0.5	0.0	0.0	0.0	0.0	0.0	0.0
90.5°	0.1	0.4	0.3	0.2	0.0	0.0	0.0	0.0	0.0	0.0	0.0
91°	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
91.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P991381

CATALOG NUMBER: SMD6S07FS5-940

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
113.5°	0.0	0.0	0.0	0.0	0.2	0.0	0.0	0.0	0.0	0.0	0.0
114°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
114.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
115.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
116°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
116.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
117°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
118°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
118.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
119°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
119.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
120.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
121°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
121.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
122°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
123°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
123.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
124°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
124.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
125.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
126°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
126.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
127°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
128°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
128.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
129°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
129.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
130.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
131°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
131.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
132°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
133°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
133.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
134°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
134.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P991381

CATALOG NUMBER: SMD6S07FS5-940

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
135°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
135.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
136°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
136.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
137°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
138°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
138.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.0	0.0	0.0	0.0
139°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
139.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.1	0.0	0.0
140.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.1	0.0	0.0
141°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
141.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
142°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
143°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
143.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
144°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
144.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
145.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
146°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
146.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
147°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
148°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
148.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
149°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
149.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
150.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
151°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
151.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
152°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
153°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
153.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
154°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
154.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
155.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
156°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
156.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
157°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0

TEST NUMBER: P991381

CATALOG NUMBER: SMD6S07FS5-940

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
157.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
158°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
158.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
159°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
159.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
160.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
161°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
161.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
162°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
163°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
163.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
164°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
164.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
165.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
166°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
166.5°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
167°	0.0	0.0	0.0	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
167.5°	0.0	0.0	0.2	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
168°	0.0	0.0	0.2	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
168.5°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
169°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
169.5°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
170°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
170.5°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
171°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
171.5°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
172°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
172.5°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
173°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
173.5°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.2	0.0	0.0	0.0
174°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.1	0.0	0.0	0.0
174.5°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.1	0.0	0.0	0.0
175°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.1	0.0	0.0	0.0
175.5°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.1	0.0	0.0	0.0
176°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.1	0.0	0.0	0.0
176.5°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.1	0.0	0.0	0.0
177°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.1	0.0	0.0	0.0
177.5°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.1	0.0	0.0	0.0
178°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.1	0.0	0.0	0.0
178.5°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.1	0.0	0.0	0.0
179°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.1	0.0	0.0	0.0
179.5°	0.0	0.0	0.1	0.0	0.1	0.0	0.0	0.1	0.0	0.0	0.0



TEST NUMBER: P991381
CATALOG NUMBER: SMD6S07FS5-940

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°	202.5°	225°
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P991381

CATALOG NUMBER: SMD6S07FS5-940

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
0°	250.7	250.7	250.7	250.7	250.7	250.7
0.5°	250.8	250.7	250.6	250.5	250.6	250.8
1°	250.6	250.7	250.6	250.5	250.6	250.8
1.5°	250.5	250.7	250.6	250.5	250.5	250.8
2°	250.4	250.7	250.6	250.5	250.5	250.8
2.5°	250.4	250.8	250.6	250.4	250.5	250.8
3°	250.2	250.7	250.5	250.4	250.5	250.8
3.5°	249.9	250.6	250.4	250.3	250.6	250.8
4°	249.7	250.5	250.4	250.3	250.6	250.8
4.5°	249.7	250.3	250.3	250.2	250.5	250.5
5°	249.3	250.1	250.1	250.1	250.2	250.5
5.5°	249.0	249.8	249.8	249.9	250.1	250.3
6°	248.7	249.5	249.4	249.7	249.8	250.1
6.5°	248.4	249.1	249.1	249.3	249.5	249.7
7°	248.0	248.8	248.8	249.0	249.1	249.5
7.5°	247.8	248.4	248.6	248.7	248.9	249.1
8°	247.3	248.2	248.2	248.3	248.6	249.0
8.5°	246.8	247.7	247.7	248.0	248.2	248.5
9°	246.5	247.3	247.3	247.5	247.8	248.1
9.5°	246.0	246.8	246.9	247.1	247.3	247.7
10°	245.4	246.3	246.3	246.5	246.8	247.4
10.5°	245.0	245.7	245.9	246.0	246.4	246.8
11°	244.4	245.3	245.3	245.7	245.9	246.4
11.5°	244.1	244.7	244.7	245.1	245.5	246.0
12°	243.4	244.2	244.3	244.5	244.8	245.5
12.5°	242.8	243.6	243.7	243.9	244.3	244.9
13°	242.1	243.0	243.1	243.3	243.8	244.4
13.5°	241.5	242.4	242.5	242.7	243.2	243.7
14°	240.7	241.7	241.7	242.0	242.5	243.1
14.5°	240.1	240.9	241.2	241.4	241.9	242.5
15°	239.4	240.2	240.5	240.7	241.2	241.9
15.5°	238.7	239.4	239.7	240.0	240.6	241.2
16°	237.9	238.8	239.0	239.3	239.9	240.7
16.5°	237.2	238.0	238.2	238.6	239.3	239.9
17°	236.4	237.2	237.5	237.8	238.4	239.2
17.5°	235.6	236.4	236.7	237.1	237.8	238.3
18°	234.8	235.6	235.9	236.2	236.9	237.7
18.5°	234.0	234.6	234.9	235.3	236.0	236.8
19°	233.0	233.9	234.2	234.5	235.3	236.1
19.5°	232.2	233.0	233.3	233.7	234.5	235.1
20°	231.3	232.2	232.5	232.9	233.6	234.5
20.5°	230.4	231.2	231.6	231.9	232.7	233.5
21°	229.3	230.2	230.6	231.1	231.8	232.7
21.5°	228.5	229.2	229.7	230.1	231.0	231.7
22°	227.8	228.5	228.8	229.2	229.8	230.8



TEST NUMBER: P991381

CATALOG NUMBER: SMD6S07FS5-940

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
22.5°	226.6	227.5	227.8	228.6	229.1	229.8
23°	225.5	226.4	227.0	227.3	228.2	228.9
23.5°	224.5	225.4	225.7	226.3	227.1	228.0
24°	223.5	224.3	224.7	225.2	226.1	227.0
24.5°	222.4	223.3	223.6	224.3	225.1	226.0
25°	221.4	222.2	222.5	223.2	224.0	224.9
25.5°	220.2	221.1	221.4	222.1	223.0	223.9
26°	219.0	220.0	220.3	220.9	221.9	222.7
26.5°	217.9	218.8	219.1	219.8	220.8	221.6
27°	216.7	217.6	218.0	218.7	219.7	220.7
27.5°	215.5	216.4	216.9	217.5	218.5	219.4
28°	214.3	215.2	215.6	216.3	217.3	218.2
28.5°	213.1	213.9	214.4	215.1	216.2	217.1
29°	211.9	212.8	213.2	213.9	215.0	215.9
29.5°	210.7	211.6	212.0	212.6	213.9	214.7
30°	209.3	210.2	210.6	211.4	212.6	213.6
30.5°	208.1	209.0	209.4	210.1	211.3	212.3
31°	206.7	207.7	208.3	208.8	210.1	211.0
31.5°	205.5	206.2	206.8	207.5	208.8	209.7
32°	204.1	205.0	205.4	206.2	207.6	208.6
32.5°	202.7	203.5	204.2	204.9	206.2	207.2
33°	201.4	202.2	202.8	203.6	204.9	206.0
33.5°	200.1	200.8	201.4	202.3	203.6	204.5
34°	198.8	199.4	200.0	201.0	202.3	203.3
34.5°	197.3	198.1	198.7	199.5	200.8	201.9
35°	195.8	196.6	197.2	198.1	199.5	200.5
35.5°	194.4	195.1	195.8	196.7	198.0	199.1
36°	192.9	193.7	194.3	195.3	196.6	197.8
36.5°	191.5	192.1	192.9	193.8	195.1	196.3
37°	190.0	190.7	191.3	192.3	193.6	194.9
37.5°	188.6	189.2	189.8	190.9	192.2	193.4
38°	187.2	187.9	188.5	189.4	190.8	192.0
38.5°	185.8	186.3	187.0	188.0	189.3	190.4
39°	184.2	184.8	185.5	186.6	187.9	189.0
39.5°	182.7	183.3	183.9	184.9	186.5	187.6
40°	181.1	181.8	182.3	183.4	184.9	186.1
40.5°	179.5	180.1	180.8	181.9	183.4	184.5
41°	177.9	178.5	179.2	180.3	181.8	183.1
41.5°	176.3	176.9	177.6	178.7	180.3	181.4
42°	174.6	175.3	176.0	177.1	178.6	179.8
42.5°	173.1	173.7	174.4	175.5	177.0	178.3
43°	171.3	172.1	172.7	173.9	175.3	176.7
43.5°	169.8	170.4	171.1	172.2	173.8	175.0
44°	168.1	168.8	169.4	170.5	172.1	173.4
44.5°	166.4	167.0	167.7	168.9	170.5	171.9



TEST NUMBER: P991381

CATALOG NUMBER: SMD6S07FS5-940

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
45°	164.7	165.4	166.0	167.3	168.8	170.1
45.5°	163.1	163.7	164.4	165.6	167.1	168.4
46°	161.3	162.0	162.8	164.0	165.4	166.9
46.5°	159.6	160.2	161.0	162.2	163.7	165.2
47°	157.8	158.4	159.2	160.5	162.0	163.5
47.5°	156.1	156.8	157.5	158.8	160.3	161.8
48°	154.4	155.1	155.8	157.0	158.6	160.0
48.5°	152.7	153.3	154.0	155.3	156.9	158.4
49°	150.9	151.5	152.2	153.6	155.1	156.7
49.5°	149.2	149.7	150.4	151.8	153.4	154.9
50°	147.4	148.1	148.7	149.9	151.6	153.2
50.5°	145.8	146.4	147.0	148.2	149.9	151.3
51°	143.9	144.5	145.2	146.5	148.1	149.6
51.5°	142.0	142.7	143.3	144.6	146.5	147.9
52°	140.2	140.9	141.5	142.9	144.6	145.9
52.5°	138.4	139.0	139.6	141.1	142.8	144.1
53°	136.6	137.2	137.8	139.1	140.9	142.3
53.5°	134.6	135.3	135.9	137.4	139.1	140.5
54°	132.9	133.4	134.1	135.3	137.3	138.6
54.5°	131.0	131.5	132.2	133.5	135.3	136.7
55°	129.1	129.6	130.3	131.7	133.5	134.8
55.5°	127.2	127.8	128.4	129.8	131.6	132.8
56°	125.3	125.9	126.5	127.9	129.5	130.9
56.5°	123.4	123.9	124.6	126.0	127.8	129.0
57°	121.5	122.1	122.7	124.1	125.7	127.1
57.5°	119.6	120.0	120.8	122.1	123.8	125.1
58°	117.6	118.3	118.9	120.2	121.8	123.1
58.5°	115.6	116.3	116.9	118.3	120.0	121.3
59°	113.7	114.3	115.0	116.3	117.9	119.3
59.5°	111.8	112.5	113.1	114.5	116.0	117.3
60°	109.8	110.5	111.2	112.6	113.9	115.4
60.5°	107.9	108.6	109.1	110.6	111.9	113.4
61°	106.1	106.8	107.5	108.6	110.0	111.4
61.5°	104.1	104.9	105.5	106.8	108.1	109.4
62°	102.2	103.0	103.6	104.7	106.2	107.7
62.5°	100.3	101.0	101.6	102.8	104.1	105.7
63°	98.3	99.1	99.5	100.8	102.2	103.6
63.5°	96.4	97.2	97.7	98.7	100.2	101.7
64°	94.3	95.1	95.7	96.8	98.2	99.6
64.5°	92.4	93.2	93.8	94.8	96.2	97.7
65°	90.4	91.2	91.7	92.8	94.1	95.6
65.5°	88.5	89.1	89.7	90.8	92.2	93.5
66°	86.5	87.2	87.8	88.7	90.1	91.5
66.5°	84.6	85.1	85.7	86.7	88.0	89.5
67°	82.6	83.2	83.8	84.7	86.0	87.4



TEST NUMBER: P991381

CATALOG NUMBER: SMD6S07FS5-940

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
67.5°	80.7	81.1	81.8	82.6	83.8	85.2
68°	78.7	79.1	79.8	80.6	81.8	83.3
68.5°	76.7	77.1	77.9	78.6	79.8	81.4
69°	74.8	75.1	75.9	76.6	77.8	79.2
69.5°	72.8	73.2	73.7	74.4	75.7	77.2
70°	70.8	71.1	71.9	72.6	73.7	75.2
70.5°	68.9	69.1	69.9	70.5	71.8	73.1
71°	66.9	67.3	67.9	68.5	69.7	71.1
71.5°	65.0	65.3	66.0	66.6	67.8	69.1
72°	63.0	63.3	64.1	64.6	65.9	67.3
72.5°	61.0	61.2	62.1	62.5	63.8	65.2
73°	58.9	59.4	60.0	60.7	61.8	63.1
73.5°	57.1	57.3	58.1	58.5	59.8	61.2
74°	55.0	55.4	56.0	56.6	57.9	59.2
74.5°	53.0	53.4	54.1	54.5	55.9	57.2
75°	51.1	51.6	52.1	52.5	53.9	55.2
75.5°	49.1	49.6	50.0	50.6	51.9	53.2
76°	47.1	47.6	48.0	48.7	50.0	51.2
76.5°	45.0	45.7	46.0	46.7	48.1	49.2
77°	43.1	43.7	44.1	44.6	46.1	47.2
77.5°	41.2	41.9	42.1	42.7	44.1	45.3
78°	39.2	39.9	40.2	40.9	42.2	43.4
78.5°	37.3	38.1	38.3	38.8	40.2	41.5
79°	35.5	36.1	36.3	37.0	38.3	39.5
79.5°	33.5	34.3	34.4	35.1	36.3	37.7
80°	31.6	32.3	32.5	33.1	34.3	35.8
80.5°	29.8	30.6	30.7	31.1	32.4	33.9
81°	27.9	28.6	28.8	29.2	30.6	32.0
81.5°	26.2	27.1	27.2	27.4	28.7	30.1
82°	24.4	25.1	25.4	25.6	27.0	28.2
82.5°	22.7	23.3	23.6	23.8	25.1	26.6
83°	20.9	21.5	21.8	22.1	23.2	24.7
83.5°	19.1	19.6	20.0	20.3	21.3	22.8
84°	17.4	17.8	18.2	18.6	19.4	20.9
84.5°	15.8	16.0	16.6	16.9	17.6	19.0
85°	14.0	14.2	14.8	15.3	15.7	17.1
85.5°	12.4	12.3	13.1	13.6	13.8	15.4
86°	10.7	10.5	11.4	12.1	12.1	13.4
86.5°	8.9	8.8	9.7	10.6	10.4	11.5
87°	7.4	6.9	8.1	9.1	8.6	8.8
87.5°	5.7	5.3	6.5	7.5	7.4	7.3
88°	4.2	3.5	4.7	6.1	6.4	6.3
88.5°	2.4	2.2	3.1	4.4	5.0	5.0
89°	0.6	0.8	1.6	2.7	3.8	3.9
89.5°	0.0	0.2	0.5	1.1	2.4	2.6



TEST NUMBER: P991381

CATALOG NUMBER: SMD6S07FS5-940

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
90°	0.0	0.0	0.0	0.3	0.7	0.8
90.5°	0.0	0.0	0.0	0.0	0.1	0.1
91°	0.0	0.0	0.0	0.0	0.0	0.0
91.5°	0.0	0.0	0.0	0.0	0.0	0.0
92°	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.0	0.0	0.0	0.0	0.0	0.0
93°	0.0	0.0	0.0	0.0	0.0	0.0
93.5°	0.0	0.0	0.0	0.0	0.0	0.0
94°	0.0	0.0	0.0	0.0	0.0	0.0
94.5°	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.0	0.0	0.0	0.0	0.0	0.0
95.5°	0.0	0.0	0.0	0.0	0.0	0.0
96°	0.0	0.0	0.0	0.0	0.0	0.0
96.5°	0.0	0.0	0.0	0.0	0.0	0.0
97°	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.0	0.0	0.0	0.0	0.0	0.0
98°	0.0	0.0	0.0	0.0	0.0	0.0
98.5°	0.0	0.0	0.0	0.0	0.0	0.0
99°	0.0	0.0	0.0	0.0	0.0	0.0
99.5°	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.0	0.0	0.0	0.0	0.0	0.0
100.5°	0.0	0.0	0.0	0.0	0.0	0.0
101°	0.0	0.0	0.0	0.0	0.0	0.0
101.5°	0.0	0.0	0.0	0.0	0.0	0.0
102°	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.0	0.0	0.0	0.0	0.0	0.0
103°	0.0	0.0	0.0	0.0	0.0	0.0
103.5°	0.0	0.0	0.0	0.0	0.0	0.0
104°	0.0	0.0	0.0	0.0	0.0	0.0
104.5°	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.0	0.0	0.0	0.0	0.0	0.0
105.5°	0.0	0.0	0.0	0.0	0.0	0.0
106°	0.0	0.0	0.0	0.0	0.0	0.0
106.5°	0.0	0.0	0.0	0.0	0.0	0.0
107°	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.0	0.0	0.0	0.0	0.0	0.0
108°	0.0	0.0	0.0	0.0	0.0	0.0
108.5°	0.0	0.0	0.0	0.0	0.0	0.0
109°	0.0	0.0	0.0	0.0	0.0	0.0
109.5°	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.0	0.0	0.0	0.0	0.0	0.0
110.5°	0.0	0.0	0.0	0.0	0.0	0.0
111°	0.0	0.0	0.0	0.0	0.0	0.0
111.5°	0.0	0.0	0.0	0.0	0.0	0.0
112°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P991381

CATALOG NUMBER: SMD6S07FS5-940

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
112.5°	0.0	0.0	0.0	0.0	0.0	0.0
113°	0.0	0.0	0.0	0.0	0.0	0.0
113.5°	0.0	0.0	0.0	0.0	0.0	0.0
114°	0.0	0.0	0.0	0.0	0.0	0.0
114.5°	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.0	0.0	0.0	0.0	0.0	0.0
115.5°	0.0	0.0	0.0	0.0	0.0	0.0
116°	0.0	0.0	0.0	0.0	0.0	0.0
116.5°	0.0	0.0	0.0	0.0	0.0	0.0
117°	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.0	0.0	0.0	0.0	0.0	0.0
118°	0.0	0.0	0.0	0.0	0.0	0.0
118.5°	0.0	0.0	0.0	0.0	0.0	0.0
119°	0.0	0.0	0.0	0.0	0.0	0.0
119.5°	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.0	0.0	0.0	0.0	0.0	0.0
120.5°	0.0	0.0	0.0	0.0	0.0	0.0
121°	0.0	0.0	0.0	0.0	0.0	0.0
121.5°	0.0	0.0	0.0	0.0	0.0	0.0
122°	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.0	0.0	0.0	0.0	0.0	0.0
123°	0.0	0.0	0.0	0.0	0.0	0.0
123.5°	0.0	0.0	0.0	0.0	0.0	0.0
124°	0.0	0.0	0.0	0.0	0.0	0.0
124.5°	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.0	0.0	0.0	0.0	0.0	0.0
125.5°	0.0	0.0	0.0	0.0	0.0	0.0
126°	0.0	0.0	0.0	0.0	0.0	0.0
126.5°	0.0	0.0	0.0	0.0	0.0	0.0
127°	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.0	0.0	0.0	0.0	0.0	0.0
128°	0.0	0.0	0.0	0.0	0.0	0.0
128.5°	0.0	0.0	0.0	0.0	0.0	0.0
129°	0.0	0.0	0.0	0.0	0.0	0.0
129.5°	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.0	0.0	0.0	0.0	0.0	0.0
130.5°	0.0	0.0	0.0	0.0	0.0	0.0
131°	0.0	0.0	0.0	0.0	0.0	0.0
131.5°	0.0	0.0	0.0	0.0	0.0	0.0
132°	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0
133°	0.0	0.0	0.0	0.0	0.0	0.0
133.5°	0.0	0.0	0.0	0.0	0.0	0.0
134°	0.0	0.0	0.0	0.0	0.0	0.0
134.5°	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P991381

CATALOG NUMBER: SMD6S07FS5-940

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
135°	0.0	0.0	0.0	0.0	0.0	0.0
135.5°	0.0	0.0	0.0	0.0	0.0	0.0
136°	0.2	0.0	0.0	0.0	0.0	0.0
136.5°	0.2	0.0	0.0	0.0	0.0	0.0
137°	0.1	0.0	0.0	0.0	0.0	0.0
137.5°	0.1	0.0	0.0	0.0	0.0	0.0
138°	0.1	0.0	0.0	0.0	0.0	0.0
138.5°	0.1	0.0	0.0	0.0	0.0	0.0
139°	0.1	0.0	0.0	0.0	0.0	0.0
139.5°	0.1	0.0	0.0	0.0	0.0	0.0
140°	0.1	0.0	0.0	0.0	0.0	0.0
140.5°	0.1	0.0	0.0	0.0	0.0	0.0
141°	0.1	0.0	0.0	0.0	0.0	0.0
141.5°	0.1	0.0	0.0	0.0	0.0	0.0
142°	0.1	0.0	0.0	0.0	0.0	0.0
142.5°	0.1	0.0	0.0	0.0	0.0	0.0
143°	0.1	0.0	0.0	0.0	0.0	0.0
143.5°	0.1	0.0	0.0	0.0	0.0	0.0
144°	0.1	0.0	0.0	0.0	0.0	0.0
144.5°	0.1	0.0	0.0	0.0	0.0	0.0
145°	0.1	0.0	0.0	0.0	0.0	0.0
145.5°	0.1	0.0	0.0	0.0	0.0	0.0
146°	0.1	0.0	0.0	0.0	0.0	0.0
146.5°	0.1	0.0	0.0	0.0	0.0	0.0
147°	0.1	0.0	0.0	0.0	0.0	0.0
147.5°	0.1	0.0	0.0	0.0	0.0	0.0
148°	0.1	0.0	0.0	0.0	0.0	0.0
148.5°	0.1	0.0	0.0	0.0	0.0	0.0
149°	0.1	0.0	0.0	0.0	0.0	0.0
149.5°	0.1	0.0	0.0	0.0	0.0	0.0
150°	0.1	0.0	0.0	0.0	0.0	0.0
150.5°	0.1	0.0	0.0	0.0	0.0	0.0
151°	0.1	0.0	0.0	0.0	0.0	0.0
151.5°	0.1	0.0	0.0	0.0	0.0	0.0
152°	0.1	0.0	0.0	0.0	0.0	0.0
152.5°	0.1	0.0	0.0	0.0	0.0	0.0
153°	0.1	0.0	0.0	0.0	0.0	0.0
153.5°	0.1	0.0	0.0	0.0	0.0	0.0
154°	0.1	0.0	0.0	0.0	0.0	0.0
154.5°	0.1	0.0	0.0	0.0	0.0	0.0
155°	0.1	0.0	0.0	0.0	0.0	0.0
155.5°	0.1	0.0	0.0	0.0	0.0	0.0
156°	0.1	0.0	0.0	0.0	0.0	0.0
156.5°	0.1	0.0	0.0	0.0	0.0	0.0
157°	0.1	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P991381

CATALOG NUMBER: SMD6S07FS5-940

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
157.5°	0.1	0.0	0.0	0.0	0.0	0.0
158°	0.1	0.0	0.0	0.0	0.0	0.0
158.5°	0.1	0.0	0.0	0.0	0.0	0.0
159°	0.1	0.0	0.0	0.0	0.0	0.0
159.5°	0.1	0.0	0.0	0.0	0.0	0.0
160°	0.1	0.0	0.0	0.0	0.0	0.0
160.5°	0.1	0.0	0.0	0.0	0.0	0.0
161°	0.1	0.0	0.0	0.0	0.0	0.0
161.5°	0.1	0.0	0.0	0.0	0.0	0.0
162°	0.1	0.0	0.0	0.0	0.0	0.0
162.5°	0.1	0.0	0.0	0.0	0.0	0.0
163°	0.1	0.0	0.0	0.0	0.0	0.0
163.5°	0.1	0.0	0.0	0.0	0.0	0.0
164°	0.1	0.0	0.0	0.0	0.0	0.0
164.5°	0.1	0.0	0.0	0.0	0.0	0.0
165°	0.1	0.0	0.0	0.0	0.0	0.0
165.5°	0.1	0.0	0.0	0.0	0.0	0.0
166°	0.1	0.0	0.0	0.0	0.0	0.0
166.5°	0.1	0.0	0.0	0.0	0.0	0.0
167°	0.1	0.0	0.0	0.0	0.0	0.0
167.5°	0.1	0.0	0.0	0.0	0.0	0.0
168°	0.1	0.0	0.0	0.0	0.0	0.0
168.5°	0.1	0.0	0.0	0.0	0.0	0.0
169°	0.1	0.0	0.0	0.0	0.0	0.0
169.5°	0.1	0.0	0.0	0.0	0.0	0.0
170°	0.1	0.0	0.0	0.0	0.0	0.0
170.5°	0.1	0.0	0.0	0.0	0.0	0.0
171°	0.1	0.0	0.0	0.0	0.0	0.0
171.5°	0.1	0.0	0.0	0.1	0.0	0.0
172°	0.1	0.0	0.0	0.1	0.0	0.0
172.5°	0.1	0.0	0.0	0.1	0.0	0.0
173°	0.1	0.0	0.0	0.1	0.0	0.0
173.5°	0.1	0.0	0.0	0.1	0.0	0.0
174°	0.1	0.0	0.0	0.1	0.0	0.0
174.5°	0.1	0.0	0.0	0.1	0.0	0.0
175°	0.1	0.0	0.0	0.1	0.0	0.0
175.5°	0.1	0.0	0.0	0.1	0.0	0.0
176°	0.1	0.0	0.0	0.1	0.0	0.0
176.5°	0.1	0.0	0.0	0.1	0.0	0.0
177°	0.1	0.0	0.0	0.1	0.0	0.0
177.5°	0.1	0.0	0.0	0.1	0.0	0.0
178°	0.1	0.0	0.0	0.1	0.0	0.0
178.5°	0.1	0.0	0.0	0.1	0.0	0.0
179°	0.1	0.0	0.0	0.1	0.0	0.0
179.5°	0.1	0.0	0.0	0.1	0.0	0.0



TEST NUMBER: P991381
CATALOG NUMBER: SMD6S07FS5-940

CANDELA DISTRIBUTION (continued):

	247.5°	270°	292.5°	315°	337.5°	360°
180°	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)