

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P990793

Luminaire Tested: **ML3ALSFL9FS1E-TIR4D55WFL-TL3RDSL-750LM-3000K**

Issue Date: 5/13/2025

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
Report Number: P990793
Test Lab: Cooper Lighting Solutions
Issue Date: 5/13/2025
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: ML3ALSFL9FS1E-TIR4D55WFL-TL3RDSL-750LM-3000K
Description: 3IN ROUND ML FLEX ADJUSTABLE, SELECTABLE CCT, WITH 55D TIR, METALLIC SILVER TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 739.1 lumens
Efficiency: N/A
Efficacy: 76.2 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.78
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9.7
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P990793
CATALOG NUMBER: ML3ALSFL9FS1E-TIR4D55WFL-TL3RDSL-750LM-3000K

Luminous Intensity Polar Plot



TEST NUMBER: P990793
 CATALOG NUMBER: ML3ALSFL9FS1E-TIR4D55WFL-TL3RDSL-750LM-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97	96	95		94
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92	90	89		87
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88	85	83		81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77		76
5	93	85	79	75	91	84	78	74	82	77	74		80	76	73		79	75	72		71
6	88	80	74	70	87	79	73	69	77	72	69		76	72	68		75	71	68		66
7	84	75	69	65	83	74	69	65	73	68	65		72	68	64		71	67	64		63
8	80	71	65	61	79	70	65	61	69	64	61		68	64	60		67	63	60		59
9	77	67	62	58	76	67	61	58	66	61	57		65	60	57		64	60	57		56
10	73	64	58	54	72	63	58	54	63	58	54		62	57	54		61	57	54		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	216627
5°	213845
10°	204249
15°	186426
20°	160127
25°	124701
30°	84165
35°	49550
40°	27222
45°	15536
50°	9415
55°	6652
60°	4912
65°	4255
70°	3270
75°	1694
80°	0
85°	0

TEST NUMBER: P990793

CATALOG NUMBER: ML3ALSFL9FS1E-TIR4D55WFL-TL3RDSL-750LM-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.0	12.3
10°-20°	227.4	30.8
20°-30°	232.6	31.5
30°-40°	120.1	16.3
40°-50°	41.3	5.6
50°-60°	16.1	2.2
60°-70°	8.1	1.1
70°-80°	2.5	0.3
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	551.0	74.5
0°-40°	671.1	90.8
0°-60°	728.5	98.6
0°-90°	739.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	739.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	988	
5°	972	91
15°	821	227
25°	515	233
35°	185	120
45°	50	41
55°	17	16
65°	8	8
75°	2	3
85°	0	0
90°	0	

TEST NUMBER: P990793
CATALOG NUMBER: ML3ALSFL9FS1E-TIR4D55WFL-TL3RDSL-750LM-3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	987.9
2.5°	983.8
5°	971.5
7.5°	949.0
10°	917.3
12.5°	874.3
15°	821.2
17.5°	758.8
20°	686.2
22.5°	603.3
25°	515.4
27.5°	423.4
30°	332.4
32.5°	251.6
35°	185.1
37.5°	132.9
40°	95.1
42.5°	68.5
45°	50.1
47.5°	36.8
50°	27.6
52.5°	21.5
55°	17.4
57.5°	14.3
60°	11.2
62.5°	9.2
65°	8.2
67.5°	7.2
70°	5.1
72.5°	4.1
75°	2.0
77.5°	1.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)