

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P20066

Luminaire Tested: **EL405830-TL400SC**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P20066
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: EL405830-TL400SC
Description: HALO 4 INCH RECESSED LED DOWNLIGHT WITH SPECULAR REFLECTOR IN TRIM UNIT 1 LED MODULE EL405830
Light Source: (1)SURFACE MOUNT LED
14 WATTS
Ballast/Driver: 120 VOLT ELECTRONIC DRIVER

Summary


Lumens per Lamp: 651 (1 lamp)
Luminaire Lumens: 651.9 lumens
Efficiency: 100.1%
Efficacy: 44.4 lumens/watt
Spacing Criteria (0/90/45): 1.49 / 1.49 / 1.29
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 14.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P20066
CATALOG NUMBER: EL405830-TL400SC

Luminous Intensity Polar Plot





TEST NUMBER: P20066

CATALOG NUMBER: EL405830-TL400SC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		107	107	107		102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100		100	98	97		96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89		93	90	87		90	87	85	84
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83	80	78	76
4	94	85	79	74	92	84	78	73	81	76	72		79	75	71		77	74	71	69
5	88	78	71	66	86	77	71	66	75	70	66		74	69	65		72	68	64	63
6	82	72	65	60	81	71	65	60	70	64	60		68	63	59		67	62	59	57
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62	57	54	52
8	73	62	55	50	71	61	54	50	60	54	50		59	53	49		58	53	49	48
9	68	57	50	46	67	57	50	46	56	50	46		55	49	45		54	49	45	44
10	64	53	47	42	63	53	46	42	52	46	42		51	46	42		50	45	42	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	41444
5°	39374
10°	41582
15°	48397
20°	53949
25°	55936
30°	57256
35°	51799
40°	46373
45°	17618
50°	2686
55°	1290
60°	1233
65°	876
70°	721
75°	953
80°	710
85°	1415



TEST NUMBER: P20066

CATALOG NUMBER: EL405830-TL400SC

ZONAL LUMENS:

Zone	Lumens	% Fixture	% Lamp
0°-10°	30.7	4.7	4.7
10°-20°	107.8	16.5	16.6
20°-30°	189.7	29.1	29.1
30°-40°	215.2	33.0	33.1
40°-50°	96.1	14.7	14.8
50°-60°	6.1	0.9	0.9
60°-70°	3.3	0.5	0.5
70°-80°	2.0	0.3	0.3
80°-90°	1.0	0.1	0.1
90°-100°	0.0	0.0	0.0
100°-110°	0.0	0.0	0.0
110°-120°	0.0	0.0	0.0
120°-130°	0.0	0.0	0.0
130°-140°	0.0	0.0	0.0
140°-150°	0.0	0.0	0.0
150°-160°	0.0	0.0	0.0
160°-170°	0.0	0.0	0.0
170°-180°	0.0	0.0	0.0
0°-30°	328.3	50.4	50.4
0°-40°	543.5	83.4	83.5
0°-60°	645.7	99.0	99.2
0°-90°	651.9	100.0	100.1
90°-120°	0.0	0.0	0.0
90°-150°	0.0	0.0	0.0
90°-180°	0.0	0.0	0.0
0°-180°	651.9	100.0	100.1

CANDELA DISTRIBUTION:

	0°	Flux
0°	336	
5°	318	31
15°	379	108
25°	411	190
35°	344	215
45°	101	96
55°	6	6
65°	3	3
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P20066

CATALOG NUMBER: EL405830-TL400SC

CANDELA DISTRIBUTION (FULL):

	0°
0°	336
2.5°	330
5°	318
7.5°	315
10°	332
12.5°	358
15°	379
17.5°	397
20°	411
22.5°	413
25°	411
27.5°	410
30°	402
32.5°	374
35°	344
37.5°	316
40°	288
42.5°	205
45°	101
47.5°	55
50°	14
52.5°	7
55°	6
57.5°	5
60°	5
62.5°	4
65°	3
67.5°	3
70°	2
72.5°	2
75°	2
77.5°	2
80°	1
82.5°	1
85°	1
87.5°	1
90°	0

(END OF REPORT)