

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P990876

Luminaire Tested: **ML4ALSFL9FS1E-TIR4D25NFL-TL4RDSL-1000LM-5000K**

Issue Date: 5/13/2025

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P990876
 Test Lab: Cooper Lighting Solutions
 Issue Date: 5/13/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: ML4ALSFL9FS1E-TIR4D25NFL-TL4RDSL-1000LM-5000K
 Description: 4IN ROUND ML FLEX ADJUSTABLE, SELECTABLE CCT, WITH 25D TIR, METALLIC SILVER TRIM
 Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 5000K CCT
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 942.3 lumens
 Efficiency: N/A
 Efficacy: 72.5 lumens/watt
 Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.56
 Luminous Opening: Circular (Dia: 0.33' x H: 0')
 CIE Type: Direct

Input Watts (W): 13
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P990876
CATALOG NUMBER: ML4ALSFL9FS1E-TIR4D25NFL-TL4RDSL-1000LM-5000K

Luminous Intensity Polar Plot



TEST NUMBER: P990876

CATALOG NUMBER: ML4ALSFL9FS1E-TIR4D25NFL-TL4RDSL-1000LM-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	104	102		101	100	99		98
2	109	104	101	97	107	103	99	96	99	97	94		97	94	92		94
3	104	98	94	90	102	97	93	89	94	91	88		92	89	86		90
4	99	93	88	84	98	92	87	83	89	85	82		87	84	81		86
5	95	88	82	79	94	87	82	78	85	81	78		83	80	77		82
6	91	83	78	74	90	83	77	74	81	77	73		80	76	73		78
7	88	79	74	70	86	79	74	70	77	73	70		76	72	69		75
8	84	76	70	67	83	75	70	66	74	69	66		73	69	66		72
9	81	72	67	64	80	72	67	63	71	66	63		70	66	63		69
10	78	69	64	61	77	69	64	61	68	64	60		67	63	60		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	280537
5°	259693
10°	210943
15°	155203
20°	105876
25°	68429
30°	42344
35°	25673
40°	15490
45°	9524
50°	6083
55°	4236
60°	3503
65°	2860
70°	2380
75°	1573
80°	781
85°	0

TEST NUMBER: P990876
 CATALOG NUMBER: ML4ALSFL9FS1E-TIR4D25NFL-TL4RDSL-1000LM-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	186.8	19.8
10°-20°	333.7	35.4
20°-30°	234.7	24.9
30°-40°	110.8	11.8
40°-50°	44.3	4.7
50°-60°	18.7	2.0
60°-70°	9.9	1.0
70°-80°	3.3	0.4
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	755.2	80.1
0°-40°	866.0	91.9
0°-60°	929.0	98.6
0°-90°	942.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	942.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2274	
5°	2097	187
15°	1215	334
25°	503	235
35°	170	111
45°	55	44
55°	20	19
65°	10	10
75°	3	3
85°	0	0
90°	0	

TEST NUMBER: P990876
CATALOG NUMBER: ML4ALSFL9FS1E-TIR4D25NFL-TL4RDSL-1000LM-5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2274.4
1°	2264.6
2°	2241.6
3°	2204.5
4°	2156.4
5°	2097.4
6°	2027.4
7°	1953.1
8°	1868.9
9°	1778.2
10°	1684.2
11°	1590.2
12°	1494.1
13°	1399.0
14°	1305.0
15°	1215.4
16°	1123.6
17°	1036.1
18°	958.5
19°	880.9
20°	806.6
22.5°	642.7
25°	502.8
27.5°	390.2
30°	297.3
32.5°	226.2
35°	170.5
37.5°	127.9
40°	96.2
42.5°	72.1
45°	54.6
47.5°	41.5
50°	31.7
52.5°	25.1
55°	19.7
57.5°	16.4
60°	14.2
62.5°	12.0
65°	9.8
67.5°	7.7
70°	6.6
72.5°	4.4
75°	3.3
77.5°	1.1
80°	1.1

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



TEST NUMBER: P990876
CATALOG NUMBER: ML4ALSFL9FS1E-TIR4D25NFL-TL4RDSL-1000LM-5000K

CANDELA DISTRIBUTION (continued):

	0°
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)