

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P990900

Luminaire Tested: **ML4ALSFL9FS1E-TIR4D40FL-TL4RDMW-1000LM-4000K**

Issue Date: 5/13/2025

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P990900
 Test Lab: Cooper Lighting Solutions
 Issue Date: 5/13/2025
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: ML4ALSFL9FS1E-TIR4D40FL-TL4RDMW-1000LM-4000K
 Description: 4IN ROUND ML FLEX ADJUSTABLE, SELECTABLE CCT, WITH 40D TIR, MATTE WHITE TRIM
 Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 4000K CCT
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 1033.5 lumens
 Efficiency: N/A
 Efficacy: 79.5 lumens/watt
 Spacing Criteria (0/90/45): 0.64 / 0.64 / 0.64
 Luminous Opening: Circular (Dia: 0.33' x H: 0')
 CIE Type: Direct

Input Watts (W): 13
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P990900
CATALOG NUMBER: ML4ALSFL9FS1E-TIR4D40FL-TL4RDMW-1000LM-4000K

Luminous Intensity Polar Plot



TEST NUMBER: P990900

CATALOG NUMBER: ML4ALSFL9FS1E-TIR4D40FL-TL4RDMW-1000LM-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	98		98
2	108	104	100	97	106	102	98	95	99	96	93		96	93	91		93
3	103	97	92	89	101	96	91	88	93	90	87		91	88	85		89
4	99	91	86	82	97	90	85	82	88	84	81		86	83	80		84
5	94	86	81	77	93	85	80	76	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	79	75	71		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	70	67		73
8	83	74	68	64	81	73	68	64	72	67	64		71	67	64		70
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	239661
5°	230411
10°	206334
15°	169122
20°	124830
25°	82461
30°	49593
35°	28670
40°	16939
45°	10641
50°	7273
55°	5656
60°	4662
65°	4611
70°	4183
75°	3002
80°	781
85°	0

TEST NUMBER: P990900

CATALOG NUMBER: ML4ALSFL9FS1E-TIR4D40FL-TL4RDMW-1000LM-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.8	16.5
10°-20°	362.5	35.1
20°-30°	279.6	27.1
30°-40°	125.4	12.1
40°-50°	49.4	4.8
50°-60°	23.9	2.3
60°-70°	15.2	1.5
70°-80°	6.4	0.6
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	812.8	78.6
0°-40°	938.2	90.8
0°-60°	1011.5	97.9
0°-90°	1033.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1033.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1943	
5°	1861	171
15°	1324	362
25°	606	280
35°	190	125
45°	61	49
55°	26	24
65°	16	15
75°	6	6
85°	0	0
90°	0	

TEST NUMBER: P990900

CATALOG NUMBER: ML4ALSFL9FS1E-TIR4D40FL-TL4RDMW-1000LM-4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1943.0
1°	1937.7
2°	1928.2
3°	1912.4
4°	1889.3
5°	1860.9
6°	1829.3
7°	1789.4
8°	1745.2
9°	1696.8
10°	1647.4
11°	1587.4
12°	1526.4
13°	1465.4
14°	1397.0
15°	1324.4
16°	1252.9
17°	1179.2
18°	1105.6
19°	1026.7
20°	951.0
22.5°	770.0
25°	605.9
27.5°	461.8
30°	348.2
32.5°	258.8
35°	190.4
37.5°	141.0
40°	105.2
42.5°	78.9
45°	61.0
47.5°	47.3
50°	37.9
52.5°	30.5
55°	26.3
57.5°	22.1
60°	18.9
62.5°	16.8
65°	15.8
67.5°	13.7
70°	11.6
72.5°	8.4
75°	6.3
77.5°	3.2
80°	1.1

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



TEST NUMBER: P990900
CATALOG NUMBER: ML4ALSFL9FS1E-TIR4D40FL-TL4RDMW-1000LM-4000K

CANDELA DISTRIBUTION (continued):

	0°
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)